

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008038

Luminaire Tested: S122DIP-B290D530UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008038
REPORT IS A COMBINATION OF REPORTS P983961 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D530UB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3163.0 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008038

CATALOG NUMBER: S122DIP-B290D530UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008038

CATALOG NUMBER: S122DIP-B290D530UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36	36	36
1	95	90	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36	30	30	30
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	33	32	30	25	25	25
3	78	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26	21	21	21
4	72	61	54	48	65	56	49	44	45	40	36	35	32	29	26	24	22	18	18	18
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	21	19	16	16	16
6	61	49	41	35	55	44	38	33	36	31	27	29	25	22	22	19	17	14	14	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15	12	12	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	14	11	11	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10	10	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	15	13	11	9	9	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7000	7000	7000
5°	7011	6672	6625
10°	6953	6368	6242
15°	6852	6062	5838
20°	6714	5728	5457
25°	6578	5380	5075
30°	6405	5054	4676
35°	6243	4708	4283
40°	6041	4368	3911
45°	5840	4030	3548
50°	5622	3686	3170
55°	5393	3318	2812
60°	5134	2922	2440
65°	4852	2517	2049
70°	4491	2074	1654
75°	3994	1600	1279
80°	3393	1086	822
85°	2458	506	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5840 cd/sqm

TEST NUMBER: P1008038

CATALOG NUMBER: S122DIP-B290D530UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.6	1.3
10°-20°	117.1	3.7
20°-30°	172.1	5.4
30°-40°	199.9	6.3
40°-50°	199.6	6.3
50°-60°	174.1	5.5
60°-70°	128.7	4.1
70°-80°	72.8	2.3
80°-90°	20.4	0.6
90°-100°	22.9	0.7
100°-110°	85.4	2.7
110°-120°	226.5	7.2
120°-130°	375.7	11.9
130°-140°	399.0	12.6
140°-150°	370.9	11.7
150°-160°	298.2	9.4
160°-170°	192.1	6.1
170°-180°	66.1	2.1
0°-30°	330.8	10.5
0°-40°	530.7	16.8
0°-60°	904.3	28.6
0°-90°	1126.2	35.6
90°-120°	334.8	10.6
90°-150°	1480.4	46.8
90°-180°	2037.0	64.4
0°-180°	3163.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	442	442	442	442	442	
5°	442	440	436	439	438	42
15°	421	418	413	415	412	119
25°	381	378	370	371	370	175
35°	329	324	318	315	313	205
45°	267	264	258	253	252	206
55°	202	200	195	190	188	181
65°	136	134	130	126	124	135
75°	71	71	68	66	67	76
85°	17	17	17	15	15	19
90°	0	6	10	13	14	3
95°	33	16	20	22	22	39
105°	153	168	31	36	38	163
115°	289	298	310	77	41	285
125°	409	415	425	428	430	365
135°	506	514	518	523	522	391
145°	587	586	595	598	596	367
155°	646	642	648	650	646	298
165°	681	678	679	683	679	192
175°	696	693	694	697	692	66
180°	695	695	695	695	695	

TEST NUMBER: P1008038

CATALOG NUMBER: S122DIP-B290D530UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	442.2	442.2	442.2	442.2	442.2
2.5°	444.7	442.6	437.9	442.2	441.3
5°	442.2	440.5	435.8	439.2	438.4
7.5°	439.2	436.7	432.0	435.4	434.5
10°	434.5	431.6	426.5	429.9	428.6
12.5°	428.2	425.6	420.5	422.6	421.8
15°	420.9	418.4	412.9	414.6	412.4
17.5°	412.0	409.5	403.9	406.0	403.9
20°	402.2	399.7	393.7	395.0	393.3
22.5°	392.4	388.6	383.1	383.1	382.2
25°	381.0	377.6	370.3	371.2	370.3
27.5°	368.2	365.2	359.7	358.4	356.3
30°	355.5	352.1	345.7	344.4	342.7
32.5°	341.8	339.3	332.5	329.9	328.2
35°	328.7	324.4	317.6	315.1	312.9
37.5°	313.8	310.0	303.2	300.2	298.1
40°	298.5	295.1	288.3	284.4	282.7
42.5°	283.6	280.2	273.4	269.1	266.6
45°	267.4	264.5	258.1	253.4	251.7
47.5°	251.7	248.7	241.9	237.3	234.7
50°	235.1	233.0	227.0	221.1	219.0
52.5°	219.0	216.0	210.5	205.8	202.8
55°	202.4	199.8	194.7	189.6	187.5
57.5°	185.8	183.7	178.2	173.0	171.3
60°	169.2	167.5	161.6	156.9	155.6
62.5°	153.1	150.1	145.8	141.6	139.9
65°	136.5	133.9	129.7	125.9	123.7
67.5°	119.5	117.4	113.5	110.5	108.8
70°	103.7	102.0	98.2	95.2	93.5
72.5°	87.6	85.9	83.8	80.8	79.5
75°	71.4	70.6	68.5	65.9	66.8
77.5°	57.0	55.3	54.4	53.1	51.9
80°	42.5	42.1	41.2	40.0	39.1
82.5°	28.9	28.9	28.5	26.8	26.8
85°	17.4	17.0	16.6	15.3	14.9
87.5°	7.7	6.8	6.0	4.7	4.3
90°	0.5	6.0	10.1	12.6	13.6
92.5°	12.6	10.6	12.1	13.1	13.6
95°	32.7	16.1	19.6	22.1	21.6
97.5°	58.8	17.6	25.6	27.1	27.6
100°	89.0	20.1	28.7	32.7	33.7
102.5°	122.2	121.2	29.7	35.2	36.7
105°	152.8	167.9	30.7	36.2	38.2
107.5°	188.5	201.1	31.7	37.2	39.2
110°	222.7	233.3	88.0	37.7	39.7

TEST NUMBER: P1008038

CATALOG NUMBER: S122DIP-B290D530UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	254.9	263.9	255.4	38.7	40.2
115°	289.1	297.6	310.2	77.4	41.2
117.5°	318.7	328.8	337.3	265.4	133.7
120°	351.9	359.4	368.5	374.5	306.7
122.5°	380.1	388.1	398.2	401.2	401.7
125°	408.7	415.2	424.8	428.3	429.8
127.5°	434.9	441.9	449.4	454.5	455.0
130°	459.5	467.5	473.1	478.6	478.1
132.5°	484.6	491.2	496.7	501.2	500.7
135°	505.7	513.8	518.3	523.3	522.3
137.5°	527.9	533.9	538.9	543.9	542.4
140°	549.5	553.5	559.0	563.5	561.0
142.5°	567.6	571.1	577.6	581.6	579.1
145°	586.7	586.2	594.7	598.2	595.7
147.5°	603.3	601.8	610.3	612.8	610.8
150°	619.3	615.8	623.9	626.9	624.4
152.5°	632.9	628.9	636.4	639.5	635.9
155°	646.0	641.5	647.5	650.5	646.5
157.5°	656.5	652.5	657.1	660.6	656.5
160°	665.6	662.6	665.6	668.6	665.1
162.5°	673.6	670.6	673.1	676.7	672.1
165°	680.7	677.7	679.2	682.7	679.2
167.5°	686.2	683.2	684.7	688.2	683.7
170°	690.7	687.7	688.7	692.2	687.7
172.5°	693.7	690.7	691.7	695.3	690.7
175°	696.3	692.7	693.7	697.3	692.2
177.5°	697.3	693.7	694.3	697.8	693.2
180°	694.8	694.8	694.8	694.8	694.8

(END OF REPORT)