

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008045

Luminaire Tested: S122DIP-B290D725UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008045
REPORT IS A COMBINATION OF REPORTS P984013 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D725UB2750-4F0-XX-W2A-D_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3996.0 lumens
Efficiency: N/A
Efficacy: 117.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008045

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008045

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26		
1	92	87	83	79	81	78	74	71	60	58	56	44	42	41	29	28	27	20		
2	83	76	69	64	74	67	62	58	52	48	45	38	36	33	25	23	22	16		
3	76	66	59	53	67	59	53	48	46	41	38	33	30	28	22	20	19	13		
4	69	58	50	44	61	52	45	40	40	36	32	29	26	24	19	17	16	11		
5	63	52	44	38	56	46	39	34	36	31	27	26	23	20	17	15	14	10		
6	58	46	38	32	51	41	34	29	32	27	23	24	20	18	16	13	12	8		
7	53	41	34	28	47	37	30	25	29	24	20	21	18	15	14	12	10	7		
8	49	37	30	25	44	33	27	22	26	21	18	19	16	14	13	11	9	7		
9	46	34	27	22	41	30	24	20	24	19	16	18	14	12	12	10	8	6		
10	43	31	24	19	38	28	22	17	22	17	14	16	13	11	11	9	7	5		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4830	4830	4830
5°	4850	4623	4597
10°	4818	4463	4398
15°	4750	4297	4193
20°	4664	4123	4000
25°	4580	3956	3824
30°	4461	3788	3650
35°	4341	3624	3522
40°	4214	3483	3395
45°	4095	3356	3284
50°	3965	3237	3175
55°	3829	3112	3064
60°	3663	2981	2947
65°	3487	2832	2812
70°	3291	2670	2668
75°	3043	2509	2530
80°	2651	2343	2388
85°	2246	2183	2267

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4095 cd/sqm

TEST NUMBER: P1008045

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.9	0.7
10°-20°	82.9	2.1
20°-30°	125.7	3.1
30°-40°	153.0	3.8
40°-50°	164.7	4.1
50°-60°	159.9	4.0
60°-70°	139.6	3.5
70°-80°	107.5	2.7
80°-90°	73.7	1.8
90°-100°	81.5	2.0
100°-110°	154.9	3.9
110°-120°	338.7	8.5
120°-130°	535.4	13.4
130°-140°	560.1	14.0
140°-150°	516.3	12.9
150°-160°	414.3	10.4
160°-170°	267.0	6.7
170°-180°	91.9	2.3
0°-30°	237.5	5.9
0°-40°	390.6	9.8
0°-60°	715.1	17.9
0°-90°	1035.9	25.9
90°-120°	575.1	14.4
90°-150°	2186.9	54.7
90°-180°	2960.0	74.1
0°-180°	3996.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	305	305	305	305	305	
5°	306	305	302	305	304	29
15°	292	293	293	297	296	82
25°	265	268	272	278	279	122
35°	229	236	244	254	257	143
45°	188	199	215	229	233	145
55°	144	160	183	198	204	129
65°	98	120	146	164	170	98
75°	54	79	107	126	132	58
85°	16	43	72	90	96	17
90°	5	38	72	94	100	6
95°	49	47	78	98	103	56
105°	215	248	81	104	112	229
115°	404	420	458	147	102	397
125°	569	578	605	622	628	507
135°	703	714	725	741	744	543
145°	815	814	826	834	833	510
155°	898	891	900	904	898	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	965	965	965	965	965	

TEST NUMBER: P1008045

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	305.1	305.1	305.1	305.1	305.1
2.5°	307.3	305.9	302.8	305.1	304.2
5°	305.9	304.6	302.0	304.6	304.2
7.5°	303.7	302.8	300.6	303.7	303.3
10°	301.1	300.2	298.9	302.4	302.0
12.5°	296.7	297.1	296.2	299.8	299.3
15°	291.8	292.7	292.7	296.7	296.2
17.5°	285.6	287.4	288.7	292.7	292.7
20°	279.4	281.6	283.4	288.3	288.3
22.5°	272.8	275.4	278.1	283.0	283.8
25°	265.3	268.4	272.3	277.6	279.0
27.5°	256.4	261.3	265.7	272.3	273.2
30°	247.6	253.3	259.1	266.2	267.5
32.5°	237.9	244.5	251.6	260.0	262.6
35°	228.6	236.1	244.5	254.2	257.3
37.5°	218.4	226.8	237.4	248.0	251.1
40°	208.2	218.0	229.9	241.4	245.4
42.5°	198.5	208.2	222.4	235.2	239.2
45°	187.5	199.4	214.9	228.6	233.0
47.5°	176.8	189.7	207.4	221.5	226.4
50°	165.8	179.5	199.4	214.4	219.3
52.5°	155.2	169.8	191.0	206.5	211.8
55°	143.7	159.6	182.6	198.5	204.3
57.5°	132.6	150.3	173.3	190.6	196.3
60°	120.7	139.7	164.9	181.7	187.9
62.5°	110.1	130.0	155.2	173.3	179.1
65°	98.1	119.8	145.9	164.0	169.8
67.5°	87.5	110.1	136.6	154.7	160.9
70°	76.0	99.0	126.4	145.5	150.8
72.5°	65.4	89.3	117.2	135.7	142.4
75°	54.4	79.1	107.4	126.4	132.2
77.5°	43.8	69.4	98.1	117.2	123.4
80°	33.2	60.1	88.9	107.4	113.6
82.5°	24.3	50.8	80.0	98.6	104.3
85°	15.9	43.3	71.6	90.2	96.4
87.5°	9.7	36.3	64.5	82.7	88.4
90°	5.1	38.5	72.4	93.5	100.2
92.5°	21.5	42.1	71.2	89.8	95.8
95°	48.9	46.7	78.0	98.3	102.9
97.5°	84.8	46.6	83.3	101.8	107.8
100°	126.7	47.4	84.0	106.0	112.2
102.5°	172.5	185.6	82.3	105.9	112.9
105°	214.6	248.3	80.6	103.8	111.5
107.5°	264.2	292.2	78.9	101.7	109.3
110°	311.3	334.7	154.6	98.8	106.5

TEST NUMBER: P1008045

CATALOG NUMBER: S122DIP-B290D725UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	356.0	375.6	384.1	97.1	104.1
115°	403.5	420.2	457.5	147.4	102.0
117.5°	444.2	461.8	492.1	405.5	226.9
120°	490.3	502.6	532.9	553.6	464.1
122.5°	529.4	541.1	571.4	587.6	592.2
125°	568.8	577.9	605.3	622.2	628.2
127.5°	605.2	614.4	636.9	654.9	659.6
130°	639.4	650.1	667.1	685.3	688.2
132.5°	674.3	682.9	697.3	713.7	716.6
135°	703.2	714.3	725.1	741.3	743.5
137.5°	733.9	742.3	751.6	767.0	767.9
140°	763.9	769.1	777.7	791.1	790.2
142.5°	789.1	793.6	802.7	813.6	812.3
145°	815.2	814.5	826.4	834.0	832.7
147.5°	838.3	836.2	848.1	852.0	850.6
150°	860.6	855.8	866.9	871.1	867.6
152.5°	879.5	873.9	884.4	888.6	883.7
155°	897.7	891.4	899.8	904.0	898.4
157.5°	912.3	906.7	913.0	917.9	912.3
160°	924.9	920.7	924.9	929.1	924.2
162.5°	936.1	931.9	935.4	940.3	934.0
165°	945.9	941.7	943.8	948.7	943.8
167.5°	953.6	949.4	951.5	956.3	950.1
170°	959.8	955.6	957.0	961.9	955.6
172.5°	964.0	959.8	961.2	966.1	959.8
175°	967.5	962.6	964.0	968.9	961.9
177.5°	968.9	964.0	964.7	969.6	963.3
180°	965.4	965.4	965.4	965.4	965.4

(END OF REPORT)