

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008764

Luminaire Tested: S122DIP-B1005D925UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008764
REPORT IS A COMBINATION OF REPORTS P983816 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D925UB50-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7059.0 lumens
Efficiency: N/A
Efficacy: 78.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008764

CATALOG NUMBER: S122DIP-B1005D925UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1008764

CATALOG NUMBER: S122DIP-B1005D925UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	52
2	90	83	76	71	83	77	72	67	66	62	59	57	54	51	48	45	43
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	39	37
4	75	64	56	50	70	60	53	48	52	47	42	45	40	37	38	35	32
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28
6	64	52	43	37	59	48	41	36	42	36	32	36	32	28	31	27	25
7	59	47	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24315	24315	24315
5°	24355	23176	23013
10°	24156	22120	21681
15°	23803	21057	20282
20°	23324	19899	18956
25°	22848	18690	17633
30°	22249	17554	16243
35°	21683	16355	14879
40°	20984	15172	13589
45°	20289	13999	12325
50°	19533	12805	11011
55°	18732	11530	9770
60°	17837	10148	8477
65°	16854	8743	7118
70°	15608	7206	5748
75°	13879	5555	4439
80°	11792	3776	2857
85°	8560	1756	1216

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20289 cd/sqm

TEST NUMBER: P1008764

CATALOG NUMBER: S122DIP-B1005D925UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.6	2.0
10°-20°	406.8	5.8
20°-30°	597.8	8.5
30°-40°	694.3	9.8
40°-50°	693.4	9.8
50°-60°	604.6	8.6
60°-70°	446.9	6.3
70°-80°	252.9	3.6
80°-90°	69.9	1.0
90°-100°	69.6	1.0
100°-110°	221.4	3.1
110°-120°	378.9	5.4
120°-130°	498.3	7.1
130°-140°	559.3	7.9
140°-150°	548.5	7.8
150°-160°	460.1	6.5
160°-170°	305.1	4.3
170°-180°	106.6	1.5
0°-30°	1149.1	16.3
0°-40°	1843.4	26.1
0°-60°	3141.4	44.5
0°-90°	3911.2	55.4
90°-120°	669.9	9.5
90°-150°	2276.0	32.2
90°-180°	3148.0	44.6
0°-180°	7059.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1536	1536	1536	1536	1536	
5°	1536	1530	1514	1526	1523	146
15°	1462	1453	1434	1440	1433	412
25°	1323	1312	1286	1289	1286	609
35°	1142	1127	1103	1094	1087	713
45°	929	919	896	880	874	717
55°	703	694	676	659	651	629
65°	474	465	450	437	430	469
75°	248	245	238	229	232	265
85°	61	59	58	53	52	67
90°	1	12	33	31	32	7
95°	49	59	61	61	59	55
105°	204	207	209	211	211	216
115°	380	386	384	383	380	376
125°	553	562	559	556	555	494
135°	715	726	728	727	724	553
145°	868	875	881	882	878	543
155°	993	996	999	1003	1000	457
165°	1080	1079	1079	1086	1081	305
175°	1124	1121	1119	1126	1120	107
180°	1126	1126	1126	1126	1126	

TEST NUMBER: P1008764

CATALOG NUMBER: S122DIP-B1005D925UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1536.1	1536.1	1536.1	1536.1	1536.1
2.5°	1544.9	1537.5	1521.3	1536.1	1533.1
5°	1536.1	1530.2	1513.9	1525.7	1522.8
7.5°	1525.7	1516.9	1500.6	1512.4	1509.5
10°	1509.5	1499.1	1481.4	1493.2	1488.8
12.5°	1487.3	1478.5	1460.7	1468.1	1465.2
15°	1462.2	1453.4	1434.2	1440.1	1432.7
17.5°	1431.2	1422.3	1403.1	1410.5	1403.1
20°	1397.2	1388.4	1367.7	1372.1	1366.2
22.5°	1363.3	1350.0	1330.8	1330.8	1327.8
25°	1323.4	1311.6	1286.5	1289.4	1286.5
27.5°	1279.1	1268.7	1249.5	1245.1	1237.7
30°	1234.8	1222.9	1200.8	1196.4	1190.5
32.5°	1187.5	1178.6	1155.0	1146.1	1140.2
35°	1141.7	1126.9	1103.3	1094.4	1087.1
37.5°	1090.0	1076.7	1053.1	1042.8	1035.4
40°	1036.8	1025.0	1001.4	988.1	982.2
42.5°	985.2	973.3	949.7	934.9	926.1
45°	929.0	918.7	896.5	880.3	874.4
47.5°	874.4	864.0	840.4	824.2	815.3
50°	816.8	809.4	788.7	768.0	760.6
52.5°	760.6	750.3	731.1	714.9	704.5
55°	703.0	694.2	676.5	658.7	651.4
57.5°	645.4	638.1	618.9	601.1	595.2
60°	587.8	581.9	561.3	545.0	540.6
62.5°	531.7	521.4	506.6	491.8	485.9
65°	474.1	465.3	450.5	437.2	429.8
67.5°	415.0	407.6	394.4	384.0	378.1
70°	360.4	354.5	341.2	330.8	324.9
72.5°	304.3	298.4	291.0	280.6	276.2
75°	248.1	245.2	237.8	228.9	231.9
77.5°	197.9	192.0	189.1	184.6	180.2
80°	147.7	146.2	143.3	138.8	135.9
82.5°	100.4	100.4	99.0	93.1	93.1
85°	60.6	59.1	57.6	53.2	51.7
87.5°	26.6	23.6	20.7	16.2	14.8
90°	1.0	12.4	33.3	31.4	32.3
92.5°	20.9	28.5	29.5	30.4	30.4
95°	49.4	58.9	60.8	60.8	58.9
97.5°	82.7	91.2	95.0	95.0	95.0
100°	120.7	128.3	131.1	131.1	130.2
102.5°	160.6	166.3	170.1	171.0	170.1
105°	204.3	207.1	209.0	210.9	210.9
107.5°	248.0	251.8	251.8	252.7	248.0
110°	289.8	295.5	295.5	295.5	292.6



TEST NUMBER: P1008764

CATALOG NUMBER: S122DIP-B1005D925UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	335.4	341.1	340.1	337.3	335.4
115°	380.0	385.8	383.9	382.9	380.0
117.5°	424.7	432.3	427.6	424.7	421.9
120°	469.4	477.0	469.4	469.4	466.5
122.5°	510.2	519.7	515.0	512.1	510.2
125°	553.0	561.5	558.7	555.8	554.9
127.5°	594.8	605.2	601.4	597.6	594.8
130°	633.7	646.1	644.2	642.3	638.5
132.5°	677.4	686.9	687.9	683.1	680.3
135°	715.4	725.9	727.8	726.8	724.0
137.5°	757.2	765.8	767.7	766.8	762.9
140°	794.3	802.9	807.6	807.6	803.8
142.5°	832.3	840.9	843.7	844.7	840.9
145°	868.4	875.1	880.8	881.7	877.9
147.5°	900.7	909.3	913.1	915.0	911.2
150°	934.0	939.7	943.5	946.3	943.5
152.5°	963.4	969.1	973.9	977.7	973.9
155°	992.9	995.7	998.6	1003.3	1000.5
157.5°	1018.5	1020.4	1022.3	1029.0	1024.2
160°	1041.3	1043.2	1044.2	1049.9	1046.1
162.5°	1062.2	1062.2	1063.2	1069.8	1065.1
165°	1080.3	1079.3	1079.3	1086.0	1081.2
167.5°	1096.4	1093.6	1093.6	1100.2	1095.5
170°	1108.8	1105.9	1105.0	1111.6	1105.9
172.5°	1117.3	1114.5	1113.5	1120.2	1114.5
175°	1124.0	1121.1	1119.2	1125.9	1120.2
177.5°	1127.8	1124.9	1123.0	1128.7	1123.0
180°	1125.9	1125.9	1125.9	1125.9	1125.9

(END OF REPORT)