

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008060

Luminaire Tested: S122DIP-B290D925UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008060
REPORT IS A COMBINATION OF REPORTS P984073 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D925UB2750-4F0-XX-W2A-D_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4829.0 lumens
Efficiency: N/A
Efficacy: 116.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008060

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008060

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	30	30	21
1	91	86	82	79	80	76	73	70	58	56	54	41	40	38	25	25	24	24	24	17
2	82	75	69	64	73	66	61	57	50	47	44	36	33	31	22	21	20	20	20	14
3	75	66	58	53	66	58	52	47	44	40	37	31	29	26	19	18	16	16	16	11
4	68	58	50	44	60	51	45	40	39	34	31	28	25	22	17	15	14	14	14	9
5	62	51	43	37	55	45	39	34	35	30	26	25	21	19	15	13	12	12	12	8
6	57	46	38	32	50	41	34	29	31	26	23	22	19	16	14	12	10	10	10	7
7	53	41	33	28	47	36	30	25	28	23	20	20	17	14	12	11	9	9	9	6
8	49	37	29	24	43	33	26	22	25	21	17	18	15	13	11	10	8	8	8	5
9	45	34	26	21	40	30	24	19	23	18	15	17	13	11	10	9	7	7	7	5
10	42	31	24	19	37	27	21	17	21	17	14	15	12	10	10	8	7	7	7	4

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4830	4830	4830
5°	4850	4623	4597
10°	4818	4463	4398
15°	4750	4297	4193
20°	4664	4123	4000
25°	4580	3956	3824
30°	4461	3788	3650
35°	4341	3624	3522
40°	4214	3483	3395
45°	4095	3356	3284
50°	3965	3237	3175
55°	3829	3112	3064
60°	3663	2981	2947
65°	3487	2832	2812
70°	3291	2670	2668
75°	3043	2509	2530
80°	2651	2343	2388
85°	2246	2183	2267

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4095 cd/sqm

TEST NUMBER: P1008060

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.9	0.6
10°-20°	82.9	1.7
20°-30°	125.7	2.6
30°-40°	153.0	3.2
40°-50°	164.7	3.4
50°-60°	159.9	3.3
60°-70°	139.6	2.9
70°-80°	107.5	2.2
80°-90°	74.2	1.5
90°-100°	90.9	1.9
100°-110°	189.8	3.9
110°-120°	431.3	8.9
120°-130°	688.9	14.3
130°-140°	723.2	15.0
140°-150°	667.9	13.8
150°-160°	536.2	11.1
160°-170°	345.5	7.2
170°-180°	118.9	2.5
0°-30°	237.5	4.9
0°-40°	390.6	8.1
0°-60°	715.1	14.8
0°-90°	1036.4	21.5
90°-120°	711.9	14.7
90°-150°	2791.9	57.8
90°-180°	3793.0	78.5
0°-180°	4829.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	305	305	305	305	305	
5°	306	305	302	305	304	29
15°	292	293	293	297	296	82
25°	265	268	272	278	279	122
35°	229	236	244	254	257	143
45°	188	199	215	229	233	145
55°	144	160	183	198	204	129
65°	98	120	146	164	170	98
75°	54	79	107	126	132	58
85°	16	43	72	90	96	17
90°	5	41	76	99	106	6
95°	62	53	86	107	112	72
105°	277	317	93	119	127	296
115°	522	542	584	179	119	513
125°	736	748	779	797	804	656
135°	910	924	937	955	957	703
145°	1055	1054	1070	1078	1076	660
155°	1162	1154	1164	1170	1163	535
165°	1224	1219	1221	1228	1221	346
175°	1252	1246	1248	1254	1245	119
180°	1249	1249	1249	1249	1249	

TEST NUMBER: P1008060

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	305.1	305.1	305.1	305.1	305.1
2.5°	307.3	305.9	302.8	305.1	304.2
5°	305.9	304.6	302.0	304.6	304.2
7.5°	303.7	302.8	300.6	303.7	303.3
10°	301.1	300.2	298.9	302.4	302.0
12.5°	296.7	297.1	296.2	299.8	299.3
15°	291.8	292.7	292.7	296.7	296.2
17.5°	285.6	287.4	288.7	292.7	292.7
20°	279.4	281.6	283.4	288.3	288.3
22.5°	272.8	275.4	278.1	283.0	283.8
25°	265.3	268.4	272.3	277.6	279.0
27.5°	256.4	261.3	265.7	272.3	273.2
30°	247.6	253.3	259.1	266.2	267.5
32.5°	237.9	244.5	251.6	260.0	262.6
35°	228.6	236.1	244.5	254.2	257.3
37.5°	218.4	226.8	237.4	248.0	251.1
40°	208.2	218.0	229.9	241.4	245.4
42.5°	198.5	208.2	222.4	235.2	239.2
45°	187.5	199.4	214.9	228.6	233.0
47.5°	176.8	189.7	207.4	221.5	226.4
50°	165.8	179.5	199.4	214.4	219.3
52.5°	155.2	169.8	191.0	206.5	211.8
55°	143.7	159.6	182.6	198.5	204.3
57.5°	132.6	150.3	173.3	190.6	196.3
60°	120.7	139.7	164.9	181.7	187.9
62.5°	110.1	130.0	155.2	173.3	179.1
65°	98.1	119.8	145.9	164.0	169.8
67.5°	87.5	110.1	136.6	154.7	160.9
70°	76.0	99.0	126.4	145.5	150.8
72.5°	65.4	89.3	117.2	135.7	142.4
75°	54.4	79.1	107.4	126.4	132.2
77.5°	43.8	69.4	98.1	117.2	123.4
80°	33.2	60.1	88.9	107.4	113.6
82.5°	24.3	50.8	80.0	98.6	104.3
85°	15.9	43.3	71.6	90.2	96.4
87.5°	9.7	36.3	64.5	82.7	88.4
90°	5.3	40.9	76.5	98.6	105.7
92.5°	26.6	46.4	76.1	95.1	101.3
95°	62.3	53.2	86.1	107.4	111.8
97.5°	108.9	53.7	93.8	112.9	119.1
100°	163.1	55.7	95.7	119.4	126.0
102.5°	222.4	235.1	94.4	120.3	127.9
105°	277.0	317.0	93.1	118.6	127.1
107.5°	341.2	374.4	91.9	116.9	125.3
110°	402.3	430.1	190.5	114.2	122.7

TEST NUMBER: P1008060

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	460.2	483.4	488.5	112.9	120.5
115°	521.6	541.8	584.3	179.0	118.8
117.5°	574.5	596.1	630.0	514.0	281.6
120°	634.1	649.5	683.5	706.7	589.5
122.5°	684.8	699.7	734.1	751.5	756.3
125°	735.9	747.6	778.9	797.3	803.9
127.5°	782.9	795.1	820.6	840.7	845.6
130°	827.2	841.2	860.4	881.0	883.7
132.5°	872.4	883.7	900.3	918.5	921.2
135°	909.9	924.3	937.0	955.2	957.0
137.5°	949.7	960.5	971.8	989.3	989.6
140°	988.5	995.4	1006.2	1021.4	1019.5
142.5°	1021.1	1027.0	1038.8	1051.3	1049.0
145°	1055.0	1054.1	1069.5	1078.5	1076.2
147.5°	1084.9	1082.2	1097.5	1102.4	1100.2
150°	1113.8	1107.5	1121.9	1127.4	1122.8
152.5°	1138.2	1131.0	1144.5	1150.0	1143.6
155°	1161.7	1153.6	1164.4	1169.8	1162.6
157.5°	1180.7	1173.5	1181.6	1187.9	1180.7
160°	1197.0	1191.5	1197.0	1202.4	1196.1
162.5°	1211.4	1206.0	1210.5	1216.9	1208.7
165°	1224.1	1218.7	1221.4	1227.7	1221.4
167.5°	1234.0	1228.6	1231.3	1237.6	1229.5
170°	1242.2	1236.7	1238.6	1244.9	1236.7
172.5°	1247.6	1242.2	1244.0	1250.3	1242.2
175°	1252.1	1245.8	1247.6	1253.9	1244.9
177.5°	1253.9	1247.6	1248.5	1254.8	1246.7
180°	1249.4	1249.4	1249.4	1249.4	1249.4

(END OF REPORT)