

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008062

Luminaire Tested: S122DIP-B290D925UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008062
REPORT IS A COMBINATION OF REPORTS P984075 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D925UB2750-4F0-XX-W2A-D_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4803.0 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008062

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008062

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	30	30	21
1	91	86	82	79	80	76	73	70	58	56	54	41	40	38	25	25	24	24	24	17
2	82	75	69	64	73	66	61	57	50	47	44	36	33	31	22	21	20	20	20	14
3	75	66	58	53	66	58	52	47	44	40	37	31	29	26	19	18	16	16	16	11
4	68	58	50	44	60	51	45	40	39	34	31	28	25	22	17	15	14	14	14	9
5	62	51	43	37	55	45	39	34	35	30	26	25	21	19	15	13	12	12	12	8
6	57	46	38	32	50	41	34	29	31	26	23	22	19	16	14	12	10	10	10	7
7	53	41	33	28	47	36	30	25	28	23	20	20	17	14	12	11	9	9	9	6
8	49	37	29	24	43	33	26	22	25	21	17	18	15	13	11	10	8	8	8	5
9	45	34	26	21	40	30	24	19	23	18	15	17	13	11	10	9	7	7	7	5
10	42	31	24	19	37	27	21	17	21	17	14	15	12	10	10	8	7	7	7	4

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4804	4804	4804
5°	4826	4599	4573
10°	4793	4439	4375
15°	4726	4275	4172
20°	4641	4101	3979
25°	4556	3936	3803
30°	4438	3767	3631
35°	4319	3605	3504
40°	4194	3465	3377
45°	4073	3338	3267
50°	3943	3221	3159
55°	3808	3097	3048
60°	3644	2967	2931
65°	3470	2816	2797
70°	3278	2657	2654
75°	3026	2497	2517
80°	2635	2330	2376
85°	2232	2174	2255

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4073 cd/sqm

TEST NUMBER: P1008062

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.8	0.6
10°-20°	82.5	1.7
20°-30°	125.0	2.6
30°-40°	152.2	3.2
40°-50°	163.8	3.4
50°-60°	159.1	3.3
60°-70°	138.9	2.9
70°-80°	106.9	2.2
80°-90°	73.8	1.5
90°-100°	90.4	1.9
100°-110°	188.8	3.9
110°-120°	428.9	8.9
120°-130°	685.1	14.3
130°-140°	719.2	15.0
140°-150°	664.2	13.8
150°-160°	533.3	11.1
160°-170°	343.6	7.2
170°-180°	118.3	2.5
0°-30°	236.3	4.9
0°-40°	388.5	8.1
0°-60°	711.5	14.8
0°-90°	1031.1	21.5
90°-120°	708.1	14.7
90°-150°	2776.8	57.8
90°-180°	3772.0	78.5
0°-180°	4803.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	304	304	304	304	304	
5°	304	303	300	303	303	29
15°	290	291	291	295	295	82
25°	264	267	271	276	278	121
35°	227	235	243	253	256	142
45°	186	198	214	227	232	144
55°	143	159	182	198	203	128
65°	98	119	145	163	169	97
75°	54	79	107	126	132	57
85°	16	43	71	90	96	17
90°	5	41	76	98	105	6
95°	62	53	86	107	111	72
105°	276	315	93	118	126	295
115°	519	539	581	178	118	511
125°	732	744	775	793	800	653
135°	905	919	932	950	952	699
145°	1049	1048	1064	1073	1070	656
155°	1155	1147	1158	1164	1156	532
165°	1217	1212	1215	1221	1215	344
175°	1245	1239	1241	1247	1238	119
180°	1243	1243	1243	1243	1243	

TEST NUMBER: P1008062

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	303.5	303.5	303.5	303.5	303.5
2.5°	305.7	304.4	301.3	303.5	302.6
5°	304.4	303.0	300.4	303.0	302.6
7.5°	302.2	301.3	299.1	302.2	301.7
10°	299.5	298.6	297.3	300.8	300.4
12.5°	295.1	295.6	294.7	298.2	297.8
15°	290.3	291.2	291.2	295.1	294.7
17.5°	284.1	285.9	287.2	291.2	291.2
20°	278.0	280.2	281.9	286.8	286.8
22.5°	271.4	274.0	276.7	281.5	282.4
25°	263.9	267.0	270.9	276.2	277.5
27.5°	255.1	259.9	264.3	270.9	271.8
30°	246.3	252.0	257.7	264.8	266.1
32.5°	236.6	243.2	250.3	258.6	261.3
35°	227.4	234.9	243.2	252.9	256.0
37.5°	217.3	225.6	236.2	246.7	249.8
40°	207.2	216.8	228.7	240.2	244.1
42.5°	197.5	207.2	221.2	234.0	238.0
45°	186.5	198.4	213.8	227.4	231.8
47.5°	175.9	188.7	206.3	220.4	225.2
50°	164.9	178.6	198.4	213.3	218.2
52.5°	154.4	168.9	190.0	205.4	210.7
55°	142.9	158.8	181.7	197.5	203.2
57.5°	132.0	149.5	172.4	189.6	195.3
60°	120.1	139.0	164.1	180.8	186.9
62.5°	109.5	129.3	154.4	172.4	178.1
65°	97.6	119.2	145.1	163.2	168.9
67.5°	87.1	109.5	135.9	153.9	160.1
70°	75.7	98.5	125.8	144.7	150.0
72.5°	65.1	88.8	116.6	135.0	141.6
75°	54.1	78.7	106.9	125.8	131.5
77.5°	43.5	69.1	97.6	116.6	122.7
80°	33.0	59.8	88.4	106.9	113.0
82.5°	24.2	50.6	79.6	98.1	103.8
85°	15.8	43.1	71.3	89.7	95.9
87.5°	9.7	36.1	64.2	82.2	88.0
90°	5.3	40.7	76.1	98.2	105.2
92.5°	26.5	46.2	75.7	94.7	100.8
95°	61.9	53.0	85.7	106.9	111.3
97.5°	108.3	53.5	93.4	112.4	118.6
100°	162.2	55.4	95.2	118.7	125.3
102.5°	221.1	233.9	93.9	119.6	127.2
105°	275.5	315.3	92.6	117.9	126.4
107.5°	339.4	372.4	91.3	116.2	124.6
110°	400.1	427.8	189.4	113.6	122.0

TEST NUMBER: P1008062

CATALOG NUMBER: S122DIP-B290D925UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	457.7	480.8	485.8	112.3	119.8
115°	518.8	538.9	581.2	178.1	118.1
117.5°	571.3	592.8	626.6	511.2	280.1
120°	630.7	646.0	679.8	702.8	586.3
122.5°	681.0	695.9	730.1	747.4	752.3
125°	731.9	743.6	774.8	792.8	799.5
127.5°	778.6	790.7	816.1	836.1	841.0
130°	822.7	836.6	855.8	876.2	878.9
132.5°	867.7	878.8	895.3	913.6	916.2
135°	904.9	919.3	931.8	950.1	951.8
137.5°	944.5	955.3	966.5	983.8	984.2
140°	983.1	989.9	1000.7	1015.8	1014.0
142.5°	1015.5	1021.4	1033.1	1045.6	1043.3
145°	1049.3	1048.4	1063.7	1072.6	1070.3
147.5°	1078.9	1076.2	1091.5	1096.4	1094.2
150°	1107.7	1101.4	1115.8	1121.2	1116.7
152.5°	1132.0	1124.8	1138.3	1143.7	1137.4
155°	1155.4	1147.3	1158.1	1163.5	1156.3
157.5°	1174.2	1167.1	1175.1	1181.4	1174.2
160°	1190.4	1185.0	1190.4	1195.8	1189.5
162.5°	1204.8	1199.4	1203.9	1210.2	1202.1
165°	1217.4	1212.0	1214.7	1221.0	1214.7
167.5°	1227.3	1221.9	1224.6	1230.9	1222.8
170°	1235.4	1230.0	1231.8	1238.1	1230.0
172.5°	1240.8	1235.4	1237.2	1243.5	1235.4
175°	1245.3	1239.0	1240.8	1247.1	1238.1
177.5°	1247.1	1240.8	1241.7	1248.0	1239.9
180°	1242.6	1242.6	1242.6	1242.6	1242.6

(END OF REPORT)