

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008765

Luminaire Tested: S122DIP-B1005D925UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008765
REPORT IS A COMBINATION OF REPORTS P983817 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D925UB50-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7356.0 lumens
Efficiency: N/A
Efficacy: 81.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008765

CATALOG NUMBER: S122DIP-B1005D925UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1008765

CATALOG NUMBER: S122DIP-B1005D925UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	59	59	59
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	50	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	42	42	38
3	82	72	65	59	75	67	61	56	58	53	49	49	45	42	41	38	36	36	36	32
4	75	64	56	50	69	60	53	47	51	46	42	44	39	36	36	33	31	31	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	27	27	24
6	63	51	43	37	58	48	41	35	41	36	31	35	31	27	30	26	24	24	24	21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	21	21	18
8	54	42	34	29	50	39	32	27	34	29	25	29	25	22	25	21	19	19	19	17
9	51	38	31	26	47	36	29	24	31	26	22	27	23	20	23	20	17	17	17	15
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	21	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24315	24315	24315
5°	24355	23176	23013
10°	24156	22120	21681
15°	23803	21057	20282
20°	23324	19899	18956
25°	22848	18690	17633
30°	22249	17554	16243
35°	21683	16355	14879
40°	20984	15172	13589
45°	20289	13999	12325
50°	19533	12805	11011
55°	18732	11530	9770
60°	17837	10148	8477
65°	16854	8743	7118
70°	15608	7206	5748
75°	13879	5555	4439
80°	11792	3776	2857
85°	8560	1756	1216

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20289 cd/sqm

TEST NUMBER: P1008765

CATALOG NUMBER: S122DIP-B1005D925UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.6	2.0
10°-20°	406.8	5.5
20°-30°	597.8	8.1
30°-40°	694.3	9.4
40°-50°	693.4	9.4
50°-60°	604.6	8.2
60°-70°	446.9	6.1
70°-80°	252.9	3.4
80°-90°	69.9	1.0
90°-100°	200.3	2.7
100°-110°	677.1	9.2
110°-120°	711.8	9.7
120°-130°	585.3	8.0
130°-140°	470.3	6.4
140°-150°	355.3	4.8
150°-160°	249.8	3.4
160°-170°	147.1	2.0
170°-180°	47.8	0.7
0°-30°	1149.1	15.6
0°-40°	1843.4	25.1
0°-60°	3141.4	42.7
0°-90°	3911.2	53.2
90°-120°	1589.2	21.6
90°-150°	3000.1	40.8
90°-180°	3445.0	46.8
0°-180°	7356.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1536	1536	1536	1536	1536	
5°	1536	1530	1514	1526	1523	146
15°	1462	1453	1434	1440	1433	412
25°	1323	1312	1286	1289	1286	609
35°	1142	1127	1103	1094	1087	713
45°	929	919	896	880	874	717
55°	703	694	676	659	651	629
65°	474	465	450	437	430	469
75°	248	245	238	229	232	265
85°	61	59	58	53	52	67
90°	1	13	32	31	31	6
95°	33	82	372	141	108	34
105°	116	175	704	1258	1071	123
115°	204	258	589	1216	1409	203
125°	285	337	566	985	1143	253
135°	334	399	560	828	947	258
145°	382	439	557	691	756	240
155°	434	469	541	611	636	200
165°	473	487	518	549	558	133
175°	493	494	498	504	503	47
180°	494	494	494	494	494	

TEST NUMBER: P1008765

CATALOG NUMBER: S122DIP-B1005D925UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1536.1	1536.1	1536.1	1536.1	1536.1
2.5°	1544.9	1537.5	1521.3	1536.1	1533.1
5°	1536.1	1530.2	1513.9	1525.7	1522.8
7.5°	1525.7	1516.9	1500.6	1512.4	1509.5
10°	1509.5	1499.1	1481.4	1493.2	1488.8
12.5°	1487.3	1478.5	1460.7	1468.1	1465.2
15°	1462.2	1453.4	1434.2	1440.1	1432.7
17.5°	1431.2	1422.3	1403.1	1410.5	1403.1
20°	1397.2	1388.4	1367.7	1372.1	1366.2
22.5°	1363.3	1350.0	1330.8	1330.8	1327.8
25°	1323.4	1311.6	1286.5	1289.4	1286.5
27.5°	1279.1	1268.7	1249.5	1245.1	1237.7
30°	1234.8	1222.9	1200.8	1196.4	1190.5
32.5°	1187.5	1178.6	1155.0	1146.1	1140.2
35°	1141.7	1126.9	1103.3	1094.4	1087.1
37.5°	1090.0	1076.7	1053.1	1042.8	1035.4
40°	1036.8	1025.0	1001.4	988.1	982.2
42.5°	985.2	973.3	949.7	934.9	926.1
45°	929.0	918.7	896.5	880.3	874.4
47.5°	874.4	864.0	840.4	824.2	815.3
50°	816.8	809.4	788.7	768.0	760.6
52.5°	760.6	750.3	731.1	714.9	704.5
55°	703.0	694.2	676.5	658.7	651.4
57.5°	645.4	638.1	618.9	601.1	595.2
60°	587.8	581.9	561.3	545.0	540.6
62.5°	531.7	521.4	506.6	491.8	485.9
65°	474.1	465.3	450.5	437.2	429.8
67.5°	415.0	407.6	394.4	384.0	378.1
70°	360.4	354.5	341.2	330.8	324.9
72.5°	304.3	298.4	291.0	280.6	276.2
75°	248.1	245.2	237.8	228.9	231.9
77.5°	197.9	192.0	189.1	184.6	180.2
80°	147.7	146.2	143.3	138.8	135.9
82.5°	100.4	100.4	99.0	93.1	93.1
85°	60.6	59.1	57.6	53.2	51.7
87.5°	26.6	23.6	20.7	16.2	14.8
90°	1.0	12.8	32.3	30.9	31.4
92.5°	14.3	45.2	146.3	67.5	58.0
95°	33.3	81.7	372.5	140.6	108.3
97.5°	49.4	107.8	607.2	282.2	181.5
100°	73.2	132.1	750.6	562.0	340.2
102.5°	95.0	153.9	755.4	950.2	663.2
105°	115.9	174.8	704.1	1258.5	1070.8
107.5°	138.7	195.7	656.6	1370.1	1345.4
110°	161.5	217.1	624.3	1352.0	1457.6

TEST NUMBER: P1008765

CATALOG NUMBER: S122DIP-B1005D925UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	182.4	237.6	603.4	1290.8	1455.7
115°	204.3	258.0	589.1	1215.8	1409.1
117.5°	227.1	278.4	581.5	1144.0	1338.8
120°	248.0	298.4	574.8	1079.8	1271.3
122.5°	267.9	318.8	571.0	1030.0	1201.0
125°	285.0	337.3	566.3	984.8	1143.0
127.5°	299.3	354.9	563.4	946.4	1088.9
130°	311.7	370.6	561.5	907.4	1044.2
132.5°	323.1	385.8	560.6	867.0	997.7
135°	334.5	399.1	559.6	827.6	947.3
137.5°	344.9	410.4	559.6	787.6	898.9
140°	357.3	421.0	558.7	752.5	848.5
142.5°	369.6	429.5	558.7	718.8	798.1
145°	382.0	439.0	556.8	691.2	756.3
147.5°	395.3	446.6	553.9	667.0	719.3
150°	408.6	454.2	551.1	646.2	687.0
152.5°	421.9	461.8	546.3	628.6	659.4
155°	434.2	468.9	540.6	611.4	635.7
157.5°	444.7	474.6	534.9	595.3	614.8
160°	455.1	480.3	529.2	579.2	594.8
162.5°	465.6	484.6	524.5	563.9	575.8
165°	473.2	487.4	517.8	549.2	557.7
167.5°	479.8	490.3	512.1	535.9	540.6
170°	486.5	491.7	507.4	523.6	525.4
172.5°	490.3	493.2	501.7	512.6	513.1
175°	493.1	493.6	497.9	504.0	502.6
177.5°	495.0	494.1	494.1	497.9	495.0
180°	494.1	494.1	494.1	494.1	494.1

(END OF REPORT)