

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008079

Luminaire Tested: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008079
REPORT IS A COMBINATION OF REPORTS P984137 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6221.0 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008079

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1008079

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	34	34	33
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12139	12139	12139
5°	12159	11571	11488
10°	12060	11044	10825
15°	11883	10512	10125
20°	11644	9934	9464
25°	11407	9330	8802
30°	11106	8764	8109
35°	10825	8165	7428
40°	10476	7574	6783
45°	10129	6989	6152
50°	9752	6394	5497
55°	9353	5755	4877
60°	8906	5066	4232
65°	8415	4365	3554
70°	7791	3597	2869
75°	6931	2773	2216
80°	5884	1884	1425
85°	4266	878	607

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10129 cd/sqm

TEST NUMBER: P1008079

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.2	1.2
10°-20°	203.1	3.3
20°-30°	298.4	4.8
30°-40°	346.6	5.6
40°-50°	346.2	5.6
50°-60°	301.9	4.9
60°-70°	223.1	3.6
70°-80°	126.3	2.0
80°-90°	35.9	0.6
90°-100°	48.0	0.8
100°-110°	178.9	2.9
110°-120°	474.6	7.6
120°-130°	787.1	12.7
130°-140°	836.1	13.4
140°-150°	777.0	12.5
150°-160°	624.7	10.0
160°-170°	402.5	6.5
170°-180°	138.5	2.2
0°-30°	573.7	9.2
0°-40°	920.3	14.8
0°-60°	1568.3	25.2
0°-90°	1953.6	31.4
90°-120°	701.5	11.3
90°-150°	3101.6	49.9
90°-180°	4267.0	68.6
0°-180°	6221.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	767	764	756	762	760	73
15°	730	726	716	719	715	206
25°	661	655	642	644	642	304
35°	570	563	551	546	543	356
45°	464	459	448	440	436	358
55°	351	347	338	329	325	314
65°	237	232	225	218	215	234
75°	124	122	119	114	116	132
85°	30	30	29	26	26	34
90°	1	13	21	26	28	6
95°	68	34	41	46	45	81
105°	320	352	64	76	80	342
115°	606	624	650	162	86	596
125°	856	870	890	897	901	764
135°	1060	1076	1086	1096	1094	819
145°	1229	1228	1246	1253	1248	769
155°	1354	1344	1357	1363	1354	624
165°	1426	1420	1423	1430	1423	403
175°	1459	1451	1454	1461	1450	139
180°	1456	1456	1456	1456	1456	

TEST NUMBER: P1008079

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	766.9	766.9	766.9	766.9	766.9
2.5°	771.3	767.6	759.5	766.9	765.4
5°	766.9	763.9	755.8	761.7	760.2
7.5°	761.7	757.3	749.2	755.1	753.6
10°	753.6	748.4	739.6	745.5	743.3
12.5°	742.5	738.1	729.2	732.9	731.5
15°	730.0	725.6	716.0	718.9	715.2
17.5°	714.5	710.1	700.5	704.2	700.5
20°	697.5	693.1	682.8	685.0	682.1
22.5°	680.6	673.9	664.4	664.4	662.9
25°	660.7	654.8	642.2	643.7	642.2
27.5°	638.6	633.4	623.8	621.6	617.9
30°	616.4	610.5	599.5	597.3	594.3
32.5°	592.8	588.4	576.6	572.2	569.2
35°	570.0	562.6	550.8	546.4	542.7
37.5°	544.2	537.5	525.7	520.6	516.9
40°	517.6	511.7	499.9	493.3	490.3
42.5°	491.8	485.9	474.1	466.7	462.3
45°	463.8	458.6	447.6	439.5	436.5
47.5°	436.5	431.4	419.6	411.4	407.0
50°	407.8	404.1	393.8	383.4	379.7
52.5°	379.7	374.6	365.0	356.9	351.7
55°	351.0	346.6	337.7	328.9	325.2
57.5°	322.2	318.5	309.0	300.1	297.2
60°	293.5	290.5	280.2	272.1	269.9
62.5°	265.4	260.3	252.9	245.5	242.6
65°	236.7	232.3	224.9	218.3	214.6
67.5°	207.2	203.5	196.9	191.7	188.8
70°	179.9	177.0	170.3	165.2	162.2
72.5°	151.9	148.9	145.3	140.1	137.9
75°	123.9	122.4	118.7	114.3	115.8
77.5°	98.8	95.9	94.4	92.2	90.0
80°	73.7	73.0	71.5	69.3	67.8
82.5°	50.1	50.1	49.4	46.5	46.5
85°	30.2	29.5	28.8	26.5	25.8
87.5°	13.3	11.8	10.3	8.1	7.4
90°	1.1	12.6	21.1	26.3	28.4
92.5°	26.3	22.1	25.3	27.4	28.4
95°	68.5	33.7	41.1	46.3	45.3
97.5°	123.2	36.9	53.7	56.9	57.9
100°	186.4	42.1	60.0	68.5	70.6
102.5°	255.9	253.8	62.1	73.7	76.9
105°	320.2	351.8	64.3	75.8	80.0
107.5°	395.0	421.3	66.4	77.9	82.2
110°	466.6	488.7	184.3	79.0	83.2

TEST NUMBER: P1008079

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	534.0	553.0	535.1	81.1	84.3
115°	605.6	623.5	649.9	162.2	86.4
117.5°	667.8	688.9	706.8	556.1	280.2
120°	737.3	753.1	772.1	784.7	642.5
122.5°	796.3	813.1	834.2	840.5	841.6
125°	856.3	870.0	890.0	897.4	900.6
127.5°	911.1	925.8	941.6	952.2	953.2
130°	962.7	979.6	991.1	1002.7	1001.7
132.5°	1015.4	1029.1	1040.6	1050.1	1049.1
135°	1059.6	1076.5	1085.9	1096.5	1094.4
137.5°	1106.0	1118.6	1129.1	1139.7	1136.5
140°	1151.2	1159.7	1171.3	1180.7	1175.5
142.5°	1189.2	1196.5	1210.2	1218.7	1213.4
145°	1229.2	1228.1	1246.0	1253.4	1248.1
147.5°	1263.9	1260.8	1278.7	1284.0	1279.7
150°	1297.7	1290.3	1307.1	1313.5	1308.2
152.5°	1326.1	1317.7	1333.5	1339.8	1332.4
155°	1353.5	1344.0	1356.6	1363.0	1354.5
157.5°	1375.6	1367.2	1376.6	1384.0	1375.6
160°	1394.6	1388.2	1394.6	1400.9	1393.5
162.5°	1411.4	1405.1	1410.4	1417.7	1408.2
165°	1426.2	1419.8	1423.0	1430.4	1423.0
167.5°	1437.7	1431.4	1434.6	1442.0	1432.5
170°	1447.2	1440.9	1443.0	1450.4	1440.9
172.5°	1453.5	1447.2	1449.3	1456.7	1447.2
175°	1458.8	1451.4	1453.5	1460.9	1450.4
177.5°	1460.9	1453.5	1454.6	1462.0	1452.5
180°	1455.6	1455.6	1455.6	1455.6	1455.6

(END OF REPORT)