

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008080

Luminaire Tested: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008080
REPORT IS A COMBINATION OF REPORTS P984138 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6275.0 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008080

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008080

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	39	39	39
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	34	34	33	33	33	33
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28	28	28	28
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	24	24	24
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	20	20	20
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	18	18	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	16	16	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	14	14	14
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	12	12	12
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11	11	11	11
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10	10	10	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12244	12244	12244
5°	12264	11672	11588
10°	12164	11139	10918
15°	11986	10603	10214
20°	11745	10020	9546
25°	11505	9411	8879
30°	11204	8840	8180
35°	10918	8236	7492
40°	10567	7641	6843
45°	10217	7050	6206
50°	9836	6449	5545
55°	9433	5807	4919
60°	8982	5109	4268
65°	8489	4404	3584
70°	7860	3628	2894
75°	6993	2796	2236
80°	5940	1900	1438
85°	4308	884	611

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10217 cd/sqm

TEST NUMBER: P1008080

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.8	1.2
10°-20°	204.8	3.3
20°-30°	301.0	4.8
30°-40°	349.6	5.6
40°-50°	349.2	5.6
50°-60°	304.5	4.9
60°-70°	225.1	3.6
70°-80°	127.3	2.0
80°-90°	36.2	0.6
90°-100°	48.4	0.8
100°-110°	180.5	2.9
110°-120°	478.7	7.6
120°-130°	793.9	12.7
130°-140°	843.3	13.4
140°-150°	783.8	12.5
150°-160°	630.1	10.0
160°-170°	406.0	6.5
170°-180°	139.7	2.2
0°-30°	578.7	9.2
0°-40°	928.3	14.8
0°-60°	1582.0	25.2
0°-90°	1970.6	31.4
90°-120°	707.6	11.3
90°-150°	3128.5	49.9
90°-180°	4304.0	68.6
0°-180°	6275.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	774	774	774	774	774	
5°	774	771	762	768	767	73
15°	736	732	722	725	722	207
25°	666	660	648	649	648	307
35°	575	568	556	551	547	359
45°	468	463	452	443	440	361
55°	354	350	341	332	328	317
65°	239	234	227	220	216	236
75°	125	124	120	115	117	133
85°	30	30	29	27	26	34
90°	1	13	21	27	29	6
95°	69	34	41	47	46	82
105°	323	355	65	76	81	345
115°	611	629	656	164	87	601
125°	864	878	898	905	908	770
135°	1069	1086	1095	1106	1104	826
145°	1240	1239	1257	1264	1259	775
155°	1365	1356	1368	1375	1366	629
165°	1438	1432	1435	1443	1435	406
175°	1471	1464	1466	1474	1463	140
180°	1468	1468	1468	1468	1468	

TEST NUMBER: P1008080

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	773.5	773.5	773.5	773.5	773.5
2.5°	778.0	774.3	766.1	773.5	772.0
5°	773.5	770.6	762.4	768.3	766.8
7.5°	768.3	763.9	755.7	761.6	760.1
10°	760.1	754.9	746.0	752.0	749.7
12.5°	749.0	744.5	735.6	739.3	737.8
15°	736.3	731.9	722.2	725.2	721.5
17.5°	720.7	716.3	706.6	710.3	706.6
20°	703.6	699.2	688.7	691.0	688.0
22.5°	686.5	679.8	670.2	670.2	668.7
25°	666.4	660.5	647.8	649.3	647.8
27.5°	644.1	638.9	629.2	627.0	623.3
30°	621.8	615.9	604.7	602.5	599.5
32.5°	598.0	593.5	581.6	577.2	574.2
35°	574.9	567.5	555.6	551.1	547.4
37.5°	548.9	542.2	530.3	525.1	521.4
40°	522.1	516.2	504.3	497.6	494.6
42.5°	496.1	490.2	478.3	470.8	466.4
45°	467.8	462.6	451.5	443.3	440.3
47.5°	440.3	435.1	423.2	415.0	410.6
50°	411.3	407.6	397.2	386.8	383.0
52.5°	383.0	377.8	368.2	360.0	354.8
55°	354.0	349.6	340.7	331.7	328.0
57.5°	325.0	321.3	311.6	302.7	299.7
60°	296.0	293.1	282.6	274.5	272.2
62.5°	267.8	262.6	255.1	247.7	244.7
65°	238.8	234.3	226.9	220.2	216.4
67.5°	209.0	205.3	198.6	193.4	190.4
70°	181.5	178.5	171.8	166.6	163.6
72.5°	153.2	150.2	146.5	141.3	139.1
75°	125.0	123.5	119.7	115.3	116.8
77.5°	99.7	96.7	95.2	93.0	90.7
80°	74.4	73.6	72.1	69.9	68.4
82.5°	50.6	50.6	49.8	46.9	46.9
85°	30.5	29.8	29.0	26.8	26.0
87.5°	13.4	11.9	10.4	8.2	7.4
90°	1.1	12.7	21.2	26.6	28.7
92.5°	26.6	22.3	25.5	27.6	28.7
95°	69.1	34.0	41.4	46.7	45.7
97.5°	124.3	37.2	54.2	57.4	58.4
100°	188.0	42.5	60.6	69.1	71.2
102.5°	258.2	256.0	62.7	74.4	77.6
105°	323.0	354.8	64.8	76.5	80.7
107.5°	398.4	425.0	66.9	78.6	82.9
110°	470.6	493.0	185.9	79.7	83.9

TEST NUMBER: P1008080

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	538.6	557.8	539.7	81.8	85.0
115°	610.9	628.9	655.5	163.6	87.1
117.5°	673.6	694.8	712.9	561.0	282.6
120°	743.7	759.6	778.8	791.5	648.1
122.5°	803.2	820.2	841.4	847.8	848.9
125°	863.7	877.6	897.7	905.2	908.4
127.5°	919.0	933.9	949.8	960.4	961.5
130°	971.0	988.0	999.7	1011.4	1010.4
132.5°	1024.2	1038.0	1049.7	1059.2	1058.2
135°	1068.8	1085.8	1095.3	1106.0	1103.8
137.5°	1115.5	1128.3	1138.9	1149.5	1146.3
140°	1161.2	1169.7	1181.4	1191.0	1185.7
142.5°	1199.5	1206.9	1220.7	1229.2	1223.9
145°	1239.8	1238.8	1256.8	1264.3	1259.0
147.5°	1274.9	1271.7	1289.8	1295.1	1290.8
150°	1308.9	1301.5	1318.5	1324.8	1319.5
152.5°	1337.6	1329.1	1345.0	1351.4	1344.0
155°	1365.2	1355.6	1368.4	1374.8	1366.3
157.5°	1387.5	1379.0	1388.6	1396.0	1387.5
160°	1406.6	1400.3	1406.6	1413.0	1405.6
162.5°	1423.6	1417.3	1422.6	1430.0	1420.4
165°	1438.5	1432.1	1435.3	1442.8	1435.3
167.5°	1450.2	1443.8	1447.0	1454.4	1444.9
170°	1459.8	1453.4	1455.5	1462.9	1453.4
172.5°	1466.1	1459.8	1461.9	1469.3	1459.8
175°	1471.4	1464.0	1466.1	1473.6	1462.9
177.5°	1473.6	1466.1	1467.2	1474.6	1465.1
180°	1468.3	1468.3	1468.3	1468.3	1468.3

(END OF REPORT)