

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008082

Luminaire Tested: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008082
REPORT IS A COMBINATION OF REPORTS P984140 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6239.0 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008082

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008082

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	34	34	33
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12176	12176	12176
5°	12196	11606	11524
10°	12097	11076	10857
15°	11919	10544	10156
20°	11680	9965	9493
25°	11441	9359	8829
30°	11141	8790	8133
35°	10857	8190	7451
40°	10508	7598	6805
45°	10160	7011	6172
50°	9781	6413	5514
55°	9382	5772	4892
60°	8933	5082	4245
65°	8439	4378	3564
70°	7817	3609	2878
75°	6953	2782	2222
80°	5908	1889	1430
85°	4280	878	609

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10160 cd/sqm

TEST NUMBER: P1008082

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.4	1.2
10°-20°	203.7	3.3
20°-30°	299.3	4.8
30°-40°	347.7	5.6
40°-50°	347.2	5.6
50°-60°	302.8	4.9
60°-70°	223.8	3.6
70°-80°	126.6	2.0
80°-90°	36.0	0.6
90°-100°	48.1	0.8
100°-110°	179.4	2.9
110°-120°	475.9	7.6
120°-130°	789.3	12.7
130°-140°	838.4	13.4
140°-150°	779.2	12.5
150°-160°	626.5	10.0
160°-170°	403.7	6.5
170°-180°	138.9	2.2
0°-30°	575.4	9.2
0°-40°	923.1	14.8
0°-60°	1573.1	25.2
0°-90°	1959.6	31.4
90°-120°	703.5	11.3
90°-150°	3110.3	49.9
90°-180°	4279.0	68.6
0°-180°	6239.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	769	769	769	769	769	
5°	769	766	758	764	763	73
15°	732	728	718	721	717	206
25°	663	657	644	646	644	305
35°	572	564	552	548	544	357
45°	465	460	449	441	438	359
55°	352	348	339	330	326	315
65°	237	233	226	219	215	235
75°	124	123	119	115	116	133
85°	30	30	29	27	26	34
90°	1	13	21	26	28	6
95°	69	34	41	46	45	81
105°	321	353	64	76	80	343
115°	607	625	652	163	87	598
125°	859	872	892	900	903	766
135°	1063	1080	1089	1100	1097	821
145°	1233	1232	1250	1257	1252	771
155°	1357	1348	1360	1367	1358	625
165°	1430	1424	1427	1434	1427	404
175°	1463	1456	1458	1465	1454	139
180°	1460	1460	1460	1460	1460	

TEST NUMBER: P1008082

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	769.2	769.2	769.2	769.2	769.2
2.5°	773.7	770.0	761.8	769.2	767.7
5°	769.2	766.3	758.1	764.0	762.6
7.5°	764.0	759.6	751.5	757.4	755.9
10°	755.9	750.7	741.8	747.8	745.5
12.5°	744.8	740.4	731.5	735.2	733.7
15°	732.2	727.8	718.2	721.1	717.4
17.5°	716.7	712.3	702.6	706.3	702.6
20°	699.7	695.2	684.9	687.1	684.2
22.5°	682.7	676.0	666.4	666.4	664.9
25°	662.7	656.8	644.2	645.7	644.2
27.5°	640.5	635.3	625.7	623.5	619.8
30°	618.3	612.4	601.3	599.1	596.1
32.5°	594.7	590.2	578.4	574.0	571.0
35°	571.7	564.3	552.5	548.1	544.4
37.5°	545.8	539.2	527.4	522.2	518.5
40°	519.2	513.3	501.5	494.8	491.9
42.5°	493.3	487.4	475.6	468.2	463.7
45°	465.2	460.0	449.0	440.8	437.9
47.5°	437.9	432.7	420.8	412.7	408.3
50°	409.0	405.3	395.0	384.6	380.9
52.5°	380.9	375.7	366.1	358.0	352.8
55°	352.1	347.6	338.7	329.9	326.2
57.5°	323.2	319.5	309.9	301.0	298.1
60°	294.4	291.4	281.1	272.9	270.7
62.5°	266.3	261.1	253.7	246.3	243.3
65°	237.4	233.0	225.6	218.9	215.2
67.5°	207.8	204.1	197.5	192.3	189.3
70°	180.5	177.5	170.9	165.7	162.7
72.5°	152.4	149.4	145.7	140.5	138.3
75°	124.3	122.8	119.1	114.6	116.1
77.5°	99.1	96.2	94.7	92.5	90.2
80°	74.0	73.2	71.7	69.5	68.0
82.5°	50.3	50.3	49.6	46.6	46.6
85°	30.3	29.6	28.8	26.6	25.9
87.5°	13.3	11.8	10.4	8.1	7.4
90°	1.1	12.7	21.1	26.4	28.5
92.5°	26.4	22.2	25.3	27.5	28.5
95°	68.7	33.8	41.2	46.5	45.4
97.5°	123.6	37.0	53.9	57.0	58.1
100°	187.0	42.2	60.2	68.7	70.8
102.5°	256.7	254.6	62.3	73.9	77.1
105°	321.1	352.8	64.4	76.0	80.3
107.5°	396.1	422.5	66.5	78.2	82.4
110°	467.9	490.1	184.8	79.2	83.4

TEST NUMBER: P1008082

CATALOG NUMBER: S122DIP-B485D1080UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	535.5	554.5	536.6	81.3	84.5
115°	607.3	625.3	651.7	162.7	86.6
117.5°	669.7	690.8	708.7	557.7	281.0
120°	739.4	755.2	774.2	786.9	644.3
122.5°	798.5	815.4	836.5	842.9	843.9
125°	858.7	872.5	892.5	899.9	903.1
127.5°	913.7	928.4	944.3	954.8	955.9
130°	965.4	982.3	993.9	1005.5	1004.5
132.5°	1018.2	1032.0	1043.6	1053.1	1052.0
135°	1062.6	1079.5	1089.0	1099.6	1097.4
137.5°	1109.1	1121.7	1132.3	1142.9	1139.7
140°	1154.5	1162.9	1174.5	1184.1	1178.8
142.5°	1192.5	1199.9	1213.6	1222.1	1216.8
145°	1232.6	1231.6	1249.5	1256.9	1251.7
147.5°	1267.5	1264.3	1282.3	1287.6	1283.3
150°	1301.3	1293.9	1310.8	1317.1	1311.9
152.5°	1329.8	1321.4	1337.2	1343.5	1336.2
155°	1357.3	1347.8	1360.4	1366.8	1358.3
157.5°	1379.5	1371.0	1380.5	1387.9	1379.5
160°	1398.5	1392.1	1398.5	1404.8	1397.4
162.5°	1415.4	1409.0	1414.3	1421.7	1412.2
165°	1430.2	1423.8	1427.0	1434.4	1427.0
167.5°	1441.8	1435.4	1438.6	1446.0	1436.5
170°	1451.3	1444.9	1447.1	1454.5	1444.9
172.5°	1457.6	1451.3	1453.4	1460.8	1451.3
175°	1462.9	1455.5	1457.6	1465.0	1454.5
177.5°	1465.0	1457.6	1458.7	1466.1	1456.6
180°	1459.7	1459.7	1459.7	1459.7	1459.7

(END OF REPORT)