

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008095

Luminaire Tested: S122DIP-B485D330UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008095
REPORT IS A COMBINATION OF REPORTS P984198 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D330UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3287.0 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008095

CATALOG NUMBER: S122DIP-B485D330UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008095

CATALOG NUMBER: S122DIP-B485D330UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	89	89	89	77	77	77	65	65	65
1	100	96	92	88	93	89	86	83	78	75	73	67	66	64	58	56	55
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12244	12244	12244
5°	12264	11672	11588
10°	12164	11139	10918
15°	11986	10603	10214
20°	11745	10020	9546
25°	11505	9411	8879
30°	11204	8840	8180
35°	10918	8236	7492
40°	10567	7641	6843
45°	10217	7050	6206
50°	9836	6449	5545
55°	9433	5807	4919
60°	8982	5109	4268
65°	8489	4404	3584
70°	7860	3628	2894
75°	6993	2796	2236
80°	5940	1900	1438
85°	4308	884	611

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10217 cd/sqm

TEST NUMBER: P1008095

CATALOG NUMBER: S122DIP-B485D330UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.8	2.2
10°-20°	204.8	6.2
20°-30°	301.0	9.2
30°-40°	349.6	10.6
40°-50°	349.2	10.6
50°-60°	304.5	9.3
60°-70°	225.1	6.8
70°-80°	127.3	3.9
80°-90°	34.4	1.0
90°-100°	14.8	0.5
100°-110°	55.3	1.7
110°-120°	146.6	4.5
120°-130°	243.1	7.4
130°-140°	258.3	7.9
140°-150°	240.0	7.3
150°-160°	193.0	5.9
160°-170°	124.3	3.8
170°-180°	42.8	1.3
0°-30°	578.7	17.6
0°-40°	928.3	28.2
0°-60°	1582.0	48.1
0°-90°	1968.8	59.9
90°-120°	216.7	6.6
90°-150°	958.1	29.1
90°-180°	1318.0	40.1
0°-180°	3287.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	774	774	774	774	774	
5°	774	771	762	768	767	73
15°	736	732	722	725	722	207
25°	666	660	648	649	648	307
35°	575	568	556	551	547	359
45°	468	463	452	443	440	361
55°	354	350	341	332	328	317
65°	239	234	227	220	216	236
75°	125	124	120	115	117	133
85°	30	30	29	27	26	34
90°	0	4	6	8	9	3
95°	21	10	13	14	14	25
105°	99	109	20	23	25	106
115°	187	193	201	50	27	184
125°	264	269	275	277	278	236
135°	327	332	335	339	338	253
145°	380	379	385	387	386	237
155°	418	415	419	421	418	193
165°	440	439	440	442	440	124
175°	451	448	449	451	448	43
180°	450	450	450	450	450	

TEST NUMBER: P1008095

CATALOG NUMBER: S122DIP-B485D330UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	773.5	773.5	773.5	773.5	773.5
2.5°	778.0	774.3	766.1	773.5	772.0
5°	773.5	770.6	762.4	768.3	766.8
7.5°	768.3	763.9	755.7	761.6	760.1
10°	760.1	754.9	746.0	752.0	749.7
12.5°	749.0	744.5	735.6	739.3	737.8
15°	736.3	731.9	722.2	725.2	721.5
17.5°	720.7	716.3	706.6	710.3	706.6
20°	703.6	699.2	688.7	691.0	688.0
22.5°	686.5	679.8	670.2	670.2	668.7
25°	666.4	660.5	647.8	649.3	647.8
27.5°	644.1	638.9	629.2	627.0	623.3
30°	621.8	615.9	604.7	602.5	599.5
32.5°	598.0	593.5	581.6	577.2	574.2
35°	574.9	567.5	555.6	551.1	547.4
37.5°	548.9	542.2	530.3	525.1	521.4
40°	522.1	516.2	504.3	497.6	494.6
42.5°	496.1	490.2	478.3	470.8	466.4
45°	467.8	462.6	451.5	443.3	440.3
47.5°	440.3	435.1	423.2	415.0	410.6
50°	411.3	407.6	397.2	386.8	383.0
52.5°	383.0	377.8	368.2	360.0	354.8
55°	354.0	349.6	340.7	331.7	328.0
57.5°	325.0	321.3	311.6	302.7	299.7
60°	296.0	293.1	282.6	274.5	272.2
62.5°	267.8	262.6	255.1	247.7	244.7
65°	238.8	234.3	226.9	220.2	216.4
67.5°	209.0	205.3	198.6	193.4	190.4
70°	181.5	178.5	171.8	166.6	163.6
72.5°	153.2	150.2	146.5	141.3	139.1
75°	125.0	123.5	119.7	115.3	116.8
77.5°	99.7	96.7	95.2	93.0	90.7
80°	74.4	73.6	72.1	69.9	68.4
82.5°	50.6	50.6	49.8	46.9	46.9
85°	30.5	29.8	29.0	26.8	26.0
87.5°	13.4	11.9	10.4	8.2	7.4
90°	0.3	3.9	6.5	8.1	8.8
92.5°	8.1	6.8	7.8	8.5	8.8
95°	21.1	10.4	12.7	14.3	14.0
97.5°	38.1	11.4	16.6	17.6	17.9
100°	57.6	13.0	18.5	21.1	21.8
102.5°	79.1	78.4	19.2	22.8	23.8
105°	98.9	108.7	19.8	23.4	24.7
107.5°	122.0	130.1	20.5	24.1	25.4
110°	144.1	151.0	56.9	24.4	25.7

TEST NUMBER: P1008095

CATALOG NUMBER: S122DIP-B485D330UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	165.0	170.8	165.3	25.1	26.0
115°	187.1	192.6	200.7	50.1	26.7
117.5°	206.3	212.8	218.3	171.8	86.5
120°	227.8	232.6	238.5	242.4	198.5
122.5°	246.0	251.2	257.7	259.6	260.0
125°	264.5	268.7	274.9	277.2	278.2
127.5°	281.4	286.0	290.9	294.1	294.5
130°	297.4	302.6	306.2	309.7	309.4
132.5°	313.6	317.9	321.5	324.4	324.1
135°	327.3	332.5	335.4	338.7	338.0
137.5°	341.6	345.5	348.8	352.0	351.1
140°	355.6	358.2	361.8	364.7	363.1
142.5°	367.3	369.6	373.8	376.4	374.8
145°	379.7	379.4	384.9	387.2	385.6
147.5°	390.4	389.5	395.0	396.6	395.3
150°	400.8	398.6	403.8	405.7	404.1
152.5°	409.6	407.0	411.9	413.9	411.6
155°	418.1	415.2	419.1	421.0	418.4
157.5°	424.9	422.3	425.2	427.5	424.9
160°	430.8	428.8	430.8	432.7	430.5
162.5°	436.0	434.0	435.7	437.9	435.0
165°	440.5	438.6	439.6	441.8	439.6
167.5°	444.1	442.2	443.1	445.4	442.5
170°	447.0	445.1	445.7	448.0	445.1
172.5°	449.0	447.0	447.7	450.0	447.0
175°	450.6	448.3	449.0	451.3	448.0
177.5°	451.3	449.0	449.3	451.6	448.7
180°	449.6	449.6	449.6	449.6	449.6

(END OF REPORT)