

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008112

Luminaire Tested: S122DIP-B485D530UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008112
REPORT IS A COMBINATION OF REPORTS P984260 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D530UB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4065.0 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008112

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008112

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46	41	41	41
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39	34	34	34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29	29	29
4	74	63	55	49	68	58	52	46	50	44	40	41	37	34	34	31	28	25	25	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	21	21	21
6	63	51	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19	19	19
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19	17	17	17
8	54	41	34	28	49	38	32	27	33	28	24	28	24	20	23	20	17	15	15	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14	14	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12176	12176	12176
5°	12196	11606	11524
10°	12097	11076	10857
15°	11919	10544	10156
20°	11680	9965	9493
25°	11441	9359	8829
30°	11141	8790	8133
35°	10857	8190	7451
40°	10508	7598	6805
45°	10160	7011	6172
50°	9781	6413	5514
55°	9382	5772	4892
60°	8933	5082	4245
65°	8439	4378	3564
70°	7817	3609	2878
75°	6953	2782	2222
80°	5908	1889	1430
85°	4280	878	609

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10160 cd/sqm

TEST NUMBER: P1008112

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.4	1.8
10°-20°	203.7	5.0
20°-30°	299.3	7.4
30°-40°	347.7	8.6
40°-50°	347.2	8.5
50°-60°	302.8	7.4
60°-70°	223.8	5.5
70°-80°	126.6	3.1
80°-90°	34.7	0.9
90°-100°	23.7	0.6
100°-110°	88.3	2.2
110°-120°	234.3	5.8
120°-130°	388.6	9.6
130°-140°	412.7	10.2
140°-150°	383.6	9.4
150°-160°	308.4	7.6
160°-170°	198.7	4.9
170°-180°	68.4	1.7
0°-30°	575.4	14.2
0°-40°	923.1	22.7
0°-60°	1573.1	38.7
0°-90°	1958.3	48.2
90°-120°	346.3	8.5
90°-150°	1531.2	37.7
90°-180°	2107.0	51.8
0°-180°	4065.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	769	769	769	769	769	
5°	769	766	758	764	763	73
15°	732	728	718	721	717	206
25°	663	657	644	646	644	305
35°	572	564	552	548	544	357
45°	465	460	449	441	438	359
55°	352	348	339	330	326	315
65°	237	233	226	219	215	235
75°	124	123	119	115	116	133
85°	30	30	29	27	26	34
90°	0	6	10	13	14	4
95°	34	17	20	23	22	40
105°	158	174	32	37	40	169
115°	299	308	321	80	43	294
125°	423	430	439	443	445	377
135°	523	531	536	541	540	404
145°	607	606	615	619	616	380
155°	668	664	670	673	669	308
165°	704	701	702	706	702	199
175°	720	716	718	721	716	69
180°	719	719	719	719	719	

TEST NUMBER: P1008112

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	769.2	769.2	769.2	769.2	769.2
2.5°	773.7	770.0	761.8	769.2	767.7
5°	769.2	766.3	758.1	764.0	762.6
7.5°	764.0	759.6	751.5	757.4	755.9
10°	755.9	750.7	741.8	747.8	745.5
12.5°	744.8	740.4	731.5	735.2	733.7
15°	732.2	727.8	718.2	721.1	717.4
17.5°	716.7	712.3	702.6	706.3	702.6
20°	699.7	695.2	684.9	687.1	684.2
22.5°	682.7	676.0	666.4	666.4	664.9
25°	662.7	656.8	644.2	645.7	644.2
27.5°	640.5	635.3	625.7	623.5	619.8
30°	618.3	612.4	601.3	599.1	596.1
32.5°	594.7	590.2	578.4	574.0	571.0
35°	571.7	564.3	552.5	548.1	544.4
37.5°	545.8	539.2	527.4	522.2	518.5
40°	519.2	513.3	501.5	494.8	491.9
42.5°	493.3	487.4	475.6	468.2	463.7
45°	465.2	460.0	449.0	440.8	437.9
47.5°	437.9	432.7	420.8	412.7	408.3
50°	409.0	405.3	395.0	384.6	380.9
52.5°	380.9	375.7	366.1	358.0	352.8
55°	352.1	347.6	338.7	329.9	326.2
57.5°	323.2	319.5	309.9	301.0	298.1
60°	294.4	291.4	281.1	272.9	270.7
62.5°	266.3	261.1	253.7	246.3	243.3
65°	237.4	233.0	225.6	218.9	215.2
67.5°	207.8	204.1	197.5	192.3	189.3
70°	180.5	177.5	170.9	165.7	162.7
72.5°	152.4	149.4	145.7	140.5	138.3
75°	124.3	122.8	119.1	114.6	116.1
77.5°	99.1	96.2	94.7	92.5	90.2
80°	74.0	73.2	71.7	69.5	68.0
82.5°	50.3	50.3	49.6	46.6	46.6
85°	30.3	29.6	28.8	26.6	25.9
87.5°	13.3	11.8	10.4	8.1	7.4
90°	0.5	6.2	10.4	13.0	14.0
92.5°	13.0	10.9	12.5	13.5	14.0
95°	33.8	16.6	20.3	22.9	22.4
97.5°	60.8	18.2	26.5	28.1	28.6
100°	92.0	20.8	29.6	33.8	34.8
102.5°	126.4	125.3	30.7	36.4	38.0
105°	158.1	173.7	31.7	37.4	39.5
107.5°	195.0	208.0	32.8	38.5	40.6
110°	230.4	241.3	91.0	39.0	41.1

TEST NUMBER: P1008112

CATALOG NUMBER: S122DIP-B485D530UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	263.6	273.0	264.2	40.0	41.6
115°	299.0	307.8	320.8	80.1	42.6
117.5°	329.7	340.1	348.9	274.6	138.3
120°	364.0	371.8	381.1	387.4	317.2
122.5°	393.1	401.4	411.8	414.9	415.5
125°	422.7	429.5	439.4	443.0	444.6
127.5°	449.8	457.1	464.9	470.1	470.6
130°	475.3	483.6	489.3	495.0	494.5
132.5°	501.3	508.0	513.7	518.4	517.9
135°	523.1	531.4	536.1	541.3	540.3
137.5°	546.0	552.2	557.4	562.6	561.1
140°	568.3	572.5	578.2	582.9	580.3
142.5°	587.1	590.7	597.5	601.6	599.0
145°	606.8	606.3	615.1	618.8	616.2
147.5°	624.0	622.4	631.3	633.9	631.8
150°	640.6	637.0	645.3	648.4	645.8
152.5°	654.7	650.5	658.3	661.4	657.8
155°	668.2	663.5	669.7	672.9	668.7
157.5°	679.1	674.9	679.6	683.3	679.1
160°	688.5	685.3	688.5	691.6	687.9
162.5°	696.8	693.7	696.3	699.9	695.2
165°	704.1	700.9	702.5	706.1	702.5
167.5°	709.8	706.7	708.2	711.9	707.2
170°	714.5	711.3	712.4	716.0	711.3
172.5°	717.6	714.5	715.5	719.1	714.5
175°	720.2	716.5	717.6	721.2	716.0
177.5°	721.2	717.6	718.1	721.7	717.1
180°	718.6	718.6	718.6	718.6	718.6

(END OF REPORT)