

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008120

Luminaire Tested: S122DIP-B485D725UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008120
REPORT IS A COMBINATION OF REPORTS P984313 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D725UB2750-4F0-XX-W2A-D_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4790.0 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008120

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008120

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	44	44	36
1	94	89	85	81	84	80	77	74	65	62	60	50	48	47	37	36	35	35	35	28
2	85	77	71	65	76	70	64	59	56	52	49	43	41	38	32	30	28	28	28	23
3	77	67	60	54	69	61	54	49	49	44	40	38	35	32	28	25	24	24	24	19
4	70	59	51	45	63	54	47	41	43	38	34	34	30	27	25	22	20	20	20	16
5	64	53	44	38	58	48	40	35	39	33	29	30	26	23	22	19	17	17	17	14
6	59	47	39	33	53	43	35	30	35	29	25	27	23	20	20	17	15	15	15	12
7	55	42	34	29	49	38	31	26	31	26	22	24	20	18	18	15	13	13	13	10
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	17	14	12	12	12	9
9	47	35	27	22	42	32	25	20	26	21	17	20	17	14	15	13	11	11	11	8
10	44	32	24	20	39	29	23	18	24	19	15	19	15	12	14	11	10	10	10	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8122	8122	8122
5°	8159	7775	7733
10°	8105	7506	7397
15°	7990	7228	7054
20°	7846	6935	6728
25°	7703	6655	6432
30°	7505	6371	6139
35°	7302	6097	5924
40°	7090	5859	5711
45°	6886	5643	5524
50°	6669	5445	5341
55°	6440	5234	5153
60°	6160	5015	4957
65°	5869	4763	4730
70°	5539	4492	4486
75°	5119	4221	4257
80°	4455	3940	4018
85°	3786	3674	3812

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6886 cd/sqm

TEST NUMBER: P1008120

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.6	1.0
10°-20°	139.5	2.9
20°-30°	211.4	4.4
30°-40°	257.4	5.4
40°-50°	277.0	5.8
50°-60°	269.0	5.6
60°-70°	234.9	4.9
70°-80°	180.8	3.8
80°-90°	122.8	2.6
90°-100°	115.4	2.4
100°-110°	179.7	3.8
110°-120°	355.0	7.4
120°-130°	544.5	11.4
130°-140°	563.9	11.8
140°-150°	516.9	10.8
150°-160°	414.3	8.6
160°-170°	267.0	5.6
170°-180°	91.9	1.9
0°-30°	399.6	8.3
0°-40°	657.0	13.7
0°-60°	1202.9	25.1
0°-90°	1741.4	36.4
90°-120°	650.1	13.6
90°-150°	2275.4	47.5
90°-180°	3049.0	63.7
0°-180°	4790.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	513	513	513	513	513	
5°	515	512	508	512	512	49
15°	491	492	492	499	498	138
25°	446	451	458	467	469	205
35°	384	397	411	428	433	240
45°	315	335	361	384	392	243
55°	242	268	307	334	344	216
65°	165	202	245	276	286	164
75°	92	133	181	213	222	97
85°	27	73	120	152	162	28
90°	8	59	112	145	156	8
95°	51	63	113	144	153	58
105°	216	259	107	140	151	231
115°	405	425	476	174	132	398
125°	569	578	616	641	649	508
135°	704	715	728	751	756	544
145°	815	814	826	836	836	510
155°	898	891	900	904	898	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	965	965	965	965	965	

TEST NUMBER: P1008120

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	513.1	513.1	513.1	513.1	513.1
2.5°	516.9	514.6	509.4	513.1	511.7
5°	514.6	512.4	507.9	512.4	511.7
7.5°	510.9	509.4	505.7	510.9	510.2
10°	506.5	505.0	502.7	508.7	507.9
12.5°	499.0	499.8	498.3	504.2	503.5
15°	490.8	492.3	492.3	499.0	498.3
17.5°	480.4	483.4	485.6	492.3	492.3
20°	470.0	473.7	476.7	484.9	484.9
22.5°	458.9	463.3	467.8	476.0	477.5
25°	446.2	451.4	458.1	467.0	469.3
27.5°	431.3	439.5	447.0	458.1	459.6
30°	416.5	426.1	435.8	447.7	449.9
32.5°	400.1	411.3	423.2	437.3	441.8
35°	384.5	397.1	411.3	427.6	432.8
37.5°	367.4	381.5	399.4	417.2	422.4
40°	350.3	366.6	386.7	406.1	412.8
42.5°	333.9	350.3	374.1	395.6	402.3
45°	315.3	335.4	361.4	384.5	391.9
47.5°	297.5	319.0	348.8	372.6	380.8
50°	278.9	301.9	335.4	360.7	368.9
52.5°	261.0	285.6	321.3	347.3	356.2
55°	241.7	268.5	307.1	333.9	343.6
57.5°	223.1	252.9	291.5	320.5	330.2
60°	203.0	235.0	277.4	305.7	316.1
62.5°	185.2	218.6	261.0	291.5	301.2
65°	165.1	201.5	245.4	275.9	285.6
67.5°	147.3	185.2	229.8	260.3	270.7
70°	127.9	166.6	212.7	244.7	253.6
72.5°	110.1	150.2	197.1	228.3	239.5
75°	91.5	133.1	180.7	212.7	222.4
77.5°	73.6	116.8	165.1	197.1	207.5
80°	55.8	101.1	149.5	180.7	191.1
82.5°	40.9	85.5	134.6	165.8	175.5
85°	26.8	72.9	120.5	151.7	162.1
87.5°	16.4	61.0	108.6	139.1	148.7
90°	8.1	59.0	112.2	145.4	155.7
92.5°	24.2	60.8	108.3	138.7	148.3
95°	51.3	63.3	112.7	144.5	152.7
97.5°	86.9	61.7	115.9	145.5	155.2
100°	128.8	60.6	114.2	147.3	156.9
102.5°	174.3	197.4	110.4	144.8	155.1
105°	216.1	258.6	106.6	140.3	151.3
107.5°	265.7	301.0	102.8	135.7	146.7
110°	312.5	341.9	176.6	130.5	141.5

TEST NUMBER: P1008120

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	357.2	381.7	404.0	126.7	137.0
115°	404.7	424.8	475.6	174.5	132.4
117.5°	445.1	465.1	508.1	430.5	255.0
120°	491.2	504.7	547.1	576.2	490.1
122.5°	530.3	542.3	583.8	608.1	615.5
125°	569.4	578.5	615.6	640.6	649.4
127.5°	605.8	614.7	645.3	670.9	678.3
130°	640.0	650.4	673.8	699.2	704.5
132.5°	674.9	683.2	702.1	725.5	730.8
135°	703.5	714.6	728.4	751.0	755.5
137.5°	734.2	742.6	753.4	774.5	777.6
140°	764.2	769.1	778.3	796.5	797.4
142.5°	789.4	793.6	802.7	817.2	817.4
145°	815.2	814.5	826.4	835.8	836.0
147.5°	838.3	836.2	848.1	852.3	851.8
150°	860.6	855.8	866.9	871.1	867.6
152.5°	879.5	873.9	884.4	888.6	883.7
155°	897.7	891.4	899.8	904.0	898.4
157.5°	912.3	906.7	913.0	917.9	912.3
160°	924.9	920.7	924.9	929.1	924.2
162.5°	936.1	931.9	935.4	940.3	934.0
165°	945.9	941.7	943.8	948.7	943.8
167.5°	953.6	949.4	951.5	956.3	950.1
170°	959.8	955.6	957.0	961.9	955.6
172.5°	964.0	959.8	961.2	966.1	959.8
175°	967.5	962.6	964.0	968.9	961.9
177.5°	968.9	964.0	964.7	969.6	963.3
180°	965.4	965.4	965.4	965.4	965.4

(END OF REPORT)