

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008125

Luminaire Tested: S122DIP-B485D725UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008125
REPORT IS A COMBINATION OF REPORTS P984318 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D725UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4800.0 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008125

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008125

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41		
1	96	92	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35		
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29		
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	25		
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21		
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18		
6	61	50	42	36	56	45	38	33	38	33	29	31	27	24	24	21	19	16		
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14		
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13		
9	49	37	30	25	45	34	27	23	29	23	20	23	20	17	19	16	14	12		
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12244	12244	12244
5°	12264	11672	11588
10°	12164	11139	10918
15°	11986	10603	10214
20°	11745	10020	9546
25°	11505	9411	8879
30°	11204	8840	8180
35°	10918	8236	7492
40°	10567	7641	6843
45°	10217	7050	6206
50°	9836	6449	5545
55°	9433	5807	4919
60°	8982	5109	4268
65°	8489	4404	3584
70°	7860	3628	2894
75°	6993	2796	2236
80°	5940	1900	1438
85°	4308	884	611

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10217 cd/sqm

TEST NUMBER: P1008125

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.8	1.5
10°-20°	204.8	4.3
20°-30°	301.0	6.3
30°-40°	349.6	7.3
40°-50°	349.2	7.3
50°-60°	304.5	6.3
60°-70°	225.1	4.7
70°-80°	127.3	2.7
80°-90°	35.3	0.7
90°-100°	31.8	0.7
100°-110°	118.7	2.5
110°-120°	314.7	6.6
120°-130°	522.0	10.9
130°-140°	554.5	11.6
140°-150°	515.4	10.7
150°-160°	414.3	8.6
160°-170°	267.0	5.6
170°-180°	91.9	1.9
0°-30°	578.7	12.1
0°-40°	928.3	19.3
0°-60°	1582.0	33.0
0°-90°	1969.7	41.0
90°-120°	465.3	9.7
90°-150°	2057.1	42.9
90°-180°	2830.0	59.0
0°-180°	4800.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	774	774	774	774	774	
5°	774	771	762	768	767	73
15°	736	732	722	725	722	207
25°	666	660	648	649	648	307
35°	575	568	556	551	547	359
45°	468	463	452	443	440	361
55°	354	350	341	332	328	317
65°	239	234	227	220	216	236
75°	125	124	120	115	117	133
85°	30	30	29	27	26	34
90°	1	8	14	18	19	4
95°	45	22	27	31	30	54
105°	212	233	43	50	53	227
115°	402	414	431	108	57	395
125°	568	577	590	595	597	507
135°	703	714	720	727	726	543
145°	815	814	826	831	828	510
155°	898	891	900	904	898	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	965	965	965	965	965	

TEST NUMBER: P1008125

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	773.5	773.5	773.5	773.5	773.5
2.5°	778.0	774.3	766.1	773.5	772.0
5°	773.5	770.6	762.4	768.3	766.8
7.5°	768.3	763.9	755.7	761.6	760.1
10°	760.1	754.9	746.0	752.0	749.7
12.5°	749.0	744.5	735.6	739.3	737.8
15°	736.3	731.9	722.2	725.2	721.5
17.5°	720.7	716.3	706.6	710.3	706.6
20°	703.6	699.2	688.7	691.0	688.0
22.5°	686.5	679.8	670.2	670.2	668.7
25°	666.4	660.5	647.8	649.3	647.8
27.5°	644.1	638.9	629.2	627.0	623.3
30°	621.8	615.9	604.7	602.5	599.5
32.5°	598.0	593.5	581.6	577.2	574.2
35°	574.9	567.5	555.6	551.1	547.4
37.5°	548.9	542.2	530.3	525.1	521.4
40°	522.1	516.2	504.3	497.6	494.6
42.5°	496.1	490.2	478.3	470.8	466.4
45°	467.8	462.6	451.5	443.3	440.3
47.5°	440.3	435.1	423.2	415.0	410.6
50°	411.3	407.6	397.2	386.8	383.0
52.5°	383.0	377.8	368.2	360.0	354.8
55°	354.0	349.6	340.7	331.7	328.0
57.5°	325.0	321.3	311.6	302.7	299.7
60°	296.0	293.1	282.6	274.5	272.2
62.5°	267.8	262.6	255.1	247.7	244.7
65°	238.8	234.3	226.9	220.2	216.4
67.5°	209.0	205.3	198.6	193.4	190.4
70°	181.5	178.5	171.8	166.6	163.6
72.5°	153.2	150.2	146.5	141.3	139.1
75°	125.0	123.5	119.7	115.3	116.8
77.5°	99.7	96.7	95.2	93.0	90.7
80°	74.4	73.6	72.1	69.9	68.4
82.5°	50.6	50.6	49.8	46.9	46.9
85°	30.5	29.8	29.0	26.8	26.0
87.5°	13.4	11.9	10.4	8.2	7.4
90°	0.7	8.4	14.0	17.5	18.9
92.5°	17.5	14.7	16.8	18.2	18.9
95°	45.4	22.4	27.2	30.7	30.0
97.5°	81.7	24.5	35.6	37.7	38.4
100°	123.6	27.9	39.8	45.4	46.8
102.5°	169.8	168.4	41.2	48.9	51.0
105°	212.4	233.3	42.6	50.3	53.1
107.5°	262.0	279.4	44.0	51.7	54.5
110°	309.5	324.1	122.3	52.4	55.2

TEST NUMBER: P1008125

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	354.2	366.8	354.9	53.8	55.9
115°	401.7	413.6	431.0	107.6	57.3
117.5°	442.9	456.9	468.7	368.8	185.8
120°	489.0	499.5	512.1	520.4	426.1
122.5°	528.1	539.3	553.3	557.5	558.2
125°	567.9	577.0	590.3	595.2	597.3
127.5°	604.3	614.0	624.5	631.5	632.2
130°	638.5	649.7	657.4	665.0	664.3
132.5°	673.4	682.5	690.2	696.5	695.8
135°	702.8	713.9	720.2	727.2	725.8
137.5°	733.5	741.9	748.9	755.9	753.8
140°	763.5	769.1	776.8	783.1	779.6
142.5°	788.7	793.6	802.7	808.3	804.8
145°	815.2	814.5	826.4	831.3	827.8
147.5°	838.3	836.2	848.1	851.6	848.8
150°	860.6	855.8	866.9	871.1	867.6
152.5°	879.5	873.9	884.4	888.6	883.7
155°	897.7	891.4	899.8	904.0	898.4
157.5°	912.3	906.7	913.0	917.9	912.3
160°	924.9	920.7	924.9	929.1	924.2
162.5°	936.1	931.9	935.4	940.3	934.0
165°	945.9	941.7	943.8	948.7	943.8
167.5°	953.6	949.4	951.5	956.3	950.1
170°	959.8	955.6	957.0	961.9	955.6
172.5°	964.0	959.8	961.2	966.1	959.8
175°	967.5	962.6	964.0	968.9	961.9
177.5°	968.9	964.0	964.7	969.6	963.3
180°	965.4	965.4	965.4	965.4	965.4

(END OF REPORT)