

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008126

Luminaire Tested: S122DIP-B485D725UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008126
REPORT IS A COMBINATION OF REPORTS P984319 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D725UB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4820.0 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008126

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008126

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41		
1	96	92	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35		
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29		
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	25		
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21		
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18		
6	61	50	42	36	56	45	38	33	38	33	29	31	27	24	24	21	19	16		
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14		
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13		
9	49	37	30	25	45	34	27	23	29	23	20	23	20	17	19	16	14	12		
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12295	12295	12295
5°	12315	11719	11636
10°	12213	11184	10963
15°	12035	10647	10255
20°	11794	10061	9585
25°	11552	9451	8916
30°	11249	8876	8212
35°	10964	8270	7524
40°	10611	7671	6870
45°	10258	7078	6231
50°	9876	6475	5568
55°	9473	5829	4939
60°	9018	5131	4286
65°	8521	4421	3599
70°	7891	3643	2907
75°	7021	2808	2243
80°	5964	1908	1444
85°	4322	887	614

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10258 cd/sqm

TEST NUMBER: P1008126

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.1	1.5
10°-20°	205.7	4.3
20°-30°	302.3	6.3
30°-40°	351.0	7.3
40°-50°	350.6	7.3
50°-60°	305.7	6.3
60°-70°	226.0	4.7
70°-80°	127.9	2.7
80°-90°	35.4	0.7
90°-100°	32.0	0.7
100°-110°	119.2	2.5
110°-120°	316.1	6.6
120°-130°	524.2	10.9
130°-140°	556.8	11.6
140°-150°	517.5	10.7
150°-160°	416.1	8.6
160°-170°	268.1	5.6
170°-180°	92.3	1.9
0°-30°	581.0	12.1
0°-40°	932.1	19.3
0°-60°	1588.4	33.0
0°-90°	1977.7	41.0
90°-120°	467.2	9.7
90°-150°	2065.8	42.9
90°-180°	2842.0	59.0
0°-180°	4820.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	777	777	777	777	777	
5°	777	774	766	772	770	74
15°	739	735	725	728	724	208
25°	669	663	650	652	650	308
35°	577	570	558	553	550	360
45°	470	464	453	445	442	363
55°	356	351	342	333	329	318
65°	240	235	228	221	217	237
75°	126	124	120	116	117	134
85°	31	30	29	27	26	34
90°	1	8	14	18	19	4
95°	46	22	27	31	30	54
105°	213	234	43	50	53	228
115°	403	415	433	108	58	397
125°	570	580	593	598	600	509
135°	706	717	723	730	729	545
145°	819	818	830	835	831	512
155°	902	895	904	908	902	415
165°	950	946	948	953	948	268
175°	972	967	968	973	966	92
180°	970	970	970	970	970	

TEST NUMBER: P1008126

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	776.7	776.7	776.7	776.7	776.7
2.5°	781.2	777.4	769.2	776.7	775.2
5°	776.7	773.7	765.5	771.5	770.0
7.5°	771.5	767.0	758.8	764.7	763.2
10°	763.2	758.0	749.0	755.0	752.8
12.5°	752.0	747.6	738.6	742.3	740.8
15°	739.3	734.9	725.2	728.1	724.4
17.5°	723.7	719.2	709.5	713.2	709.5
20°	706.5	702.0	691.5	693.8	690.8
22.5°	689.3	682.6	672.9	672.9	671.4
25°	669.1	663.2	650.5	652.0	650.5
27.5°	646.7	641.5	631.8	629.6	625.8
30°	624.3	618.4	607.2	604.9	601.9
32.5°	600.4	596.0	584.0	579.5	576.5
35°	577.3	569.8	557.9	553.4	549.7
37.5°	551.1	544.4	532.5	527.2	523.5
40°	524.3	518.3	506.3	499.6	496.6
42.5°	498.1	492.1	480.2	472.7	468.2
45°	469.7	464.5	453.3	445.1	442.1
47.5°	442.1	436.9	424.9	416.7	412.2
50°	413.0	409.3	398.8	388.3	384.6
52.5°	384.6	379.4	369.7	361.5	356.2
55°	355.5	351.0	342.0	333.1	329.3
57.5°	326.4	322.6	312.9	304.0	301.0
60°	297.2	294.2	283.8	275.6	273.3
62.5°	268.9	263.6	256.2	248.7	245.7
65°	239.7	235.2	227.8	221.1	217.3
67.5°	209.9	206.1	199.4	194.2	191.2
70°	182.2	179.2	172.5	167.3	164.3
72.5°	153.8	150.9	147.1	141.9	139.7
75°	125.5	124.0	120.2	115.8	117.2
77.5°	100.1	97.1	95.6	93.4	91.1
80°	74.7	73.9	72.4	70.2	68.7
82.5°	50.8	50.8	50.0	47.0	47.0
85°	30.6	29.9	29.1	26.9	26.1
87.5°	13.4	11.9	10.5	8.2	7.5
90°	0.7	8.4	14.0	17.5	18.9
92.5°	17.5	14.7	16.8	18.2	18.9
95°	45.6	22.4	27.4	30.9	30.2
97.5°	82.1	24.6	35.8	37.9	38.6
100°	124.2	28.1	40.0	45.6	47.0
102.5°	170.5	169.1	41.4	49.1	51.2
105°	213.3	234.3	42.8	50.5	53.3
107.5°	263.1	280.6	44.2	51.9	54.7
110°	310.8	325.5	122.8	52.6	55.4

TEST NUMBER: P1008126

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	355.7	368.3	356.4	54.0	56.1
115°	403.4	415.3	432.8	108.0	57.5
117.5°	444.8	458.8	470.7	370.4	186.6
120°	491.1	501.6	514.2	522.6	427.9
122.5°	530.4	541.6	555.6	559.8	560.5
125°	570.3	579.5	592.8	597.7	599.8
127.5°	606.8	616.6	627.2	634.2	634.9
130°	641.2	652.4	660.1	667.9	667.2
132.5°	676.3	685.4	693.1	699.4	698.7
135°	705.7	717.0	723.3	730.3	728.9
137.5°	736.6	745.0	752.0	759.1	757.0
140°	766.8	772.4	780.1	786.4	782.9
142.5°	792.0	796.9	806.1	811.7	808.2
145°	818.7	818.0	829.9	834.8	831.3
147.5°	841.8	839.7	851.7	855.2	852.4
150°	864.3	859.4	870.6	874.8	871.3
152.5°	883.2	877.6	888.1	892.4	887.4
155°	901.5	895.2	903.6	907.8	902.2
157.5°	916.2	910.6	916.9	921.8	916.2
160°	928.8	924.6	928.8	933.0	928.1
162.5°	940.1	935.8	939.4	944.3	938.0
165°	949.9	945.7	947.8	952.7	947.8
167.5°	957.6	953.4	955.5	960.4	954.1
170°	963.9	959.7	961.1	966.0	959.7
172.5°	968.1	963.9	965.3	970.2	963.9
175°	971.6	966.7	968.1	973.0	966.0
177.5°	973.0	968.1	968.8	973.7	967.4
180°	969.5	969.5	969.5	969.5	969.5

(END OF REPORT)