

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008128

Luminaire Tested: S122DIP-B485D725UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008128
REPORT IS A COMBINATION OF REPORTS P984321 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D725UB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4615.0 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008128

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008128

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41		
1	96	92	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35		
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29		
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	25		
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21		
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18		
6	61	50	42	36	56	45	38	33	38	33	29	31	27	24	24	21	19	16		
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14		
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13		
9	49	37	30	25	45	34	27	23	29	23	20	23	20	17	19	16	14	12		
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11772	11772	11772
5°	11791	11220	11141
10°	11695	10709	10497
15°	11524	10194	9819
20°	11291	9633	9177
25°	11061	9048	8536
30°	10771	8498	7863
35°	10497	7919	7203
40°	10160	7345	6579
45°	9824	6777	5966
50°	9455	6199	5332
55°	9070	5582	4729
60°	8636	4912	4104
65°	8159	4233	3447
70°	7557	3489	2783
75°	6718	2689	2149
80°	5708	1829	1383
85°	4139	851	588

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9824 cd/sqm

TEST NUMBER: P1008128

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.0	1.5
10°-20°	196.9	4.3
20°-30°	289.4	6.3
30°-40°	336.1	7.3
40°-50°	335.7	7.3
50°-60°	292.7	6.3
60°-70°	216.4	4.7
70°-80°	122.4	2.7
80°-90°	33.9	0.7
90°-100°	30.6	0.7
100°-110°	114.1	2.5
110°-120°	302.6	6.6
120°-130°	501.9	10.9
130°-140°	533.2	11.6
140°-150°	495.5	10.7
150°-160°	398.4	8.6
160°-170°	256.7	5.6
170°-180°	88.4	1.9
0°-30°	556.3	12.1
0°-40°	892.4	19.3
0°-60°	1520.9	33.0
0°-90°	1893.6	41.0
90°-120°	447.3	9.7
90°-150°	1977.9	42.9
90°-180°	2721.0	59.0
0°-180°	4615.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	744	744	744	744	744	
5°	744	741	733	739	737	71
15°	708	704	694	697	694	199
25°	641	635	623	624	623	295
35°	553	546	534	530	526	345
45°	450	445	434	426	423	347
55°	340	336	328	319	315	304
65°	230	225	218	212	208	227
75°	120	119	115	111	112	128
85°	29	29	28	26	25	33
90°	1	8	13	17	18	4
95°	44	22	26	30	29	52
105°	204	224	41	48	51	218
115°	386	398	414	103	55	380
125°	546	555	568	572	574	487
135°	676	686	692	699	698	522
145°	784	783	795	799	796	490
155°	863	857	865	869	864	398
165°	910	905	907	912	907	257
175°	930	926	927	932	925	89
180°	928	928	928	928	928	

TEST NUMBER: P1008128

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	743.7	743.7	743.7	743.7	743.7
2.5°	748.0	744.4	736.5	743.7	742.2
5°	743.7	740.8	732.9	738.7	737.2
7.5°	738.7	734.4	726.5	732.2	730.8
10°	730.8	725.8	717.2	722.9	720.8
12.5°	720.1	715.8	707.2	710.8	709.3
15°	707.9	703.6	694.3	697.2	693.6
17.5°	692.9	688.6	679.3	682.9	679.3
20°	676.4	672.2	662.1	664.3	661.4
22.5°	660.0	653.6	644.3	644.3	642.8
25°	640.7	635.0	622.8	624.2	622.8
27.5°	619.2	614.2	604.9	602.8	599.2
30°	597.8	592.1	581.3	579.2	576.3
32.5°	574.9	570.6	559.2	554.9	552.0
35°	552.7	545.6	534.2	529.9	526.3
37.5°	527.7	521.3	509.8	504.8	501.3
40°	502.0	496.3	484.8	478.4	475.5
42.5°	476.9	471.2	459.8	452.6	448.3
45°	449.8	444.8	434.0	426.2	423.3
47.5°	423.3	418.3	406.9	399.0	394.7
50°	395.4	391.9	381.8	371.8	368.3
52.5°	368.3	363.3	354.0	346.1	341.1
55°	340.4	336.1	327.5	318.9	315.3
57.5°	312.5	308.9	299.6	291.0	288.2
60°	284.6	281.7	271.7	263.9	261.7
62.5°	257.4	252.4	245.3	238.1	235.3
65°	229.5	225.2	218.1	211.7	208.1
67.5°	200.9	197.4	190.9	185.9	183.1
70°	174.5	171.6	165.2	160.2	157.3
72.5°	147.3	144.4	140.9	135.9	133.7
75°	120.1	118.7	115.1	110.8	112.3
77.5°	95.8	93.0	91.5	89.4	87.2
80°	71.5	70.8	69.4	67.2	65.8
82.5°	48.6	48.6	47.9	45.0	45.0
85°	29.3	28.6	27.9	25.7	25.0
87.5°	12.9	11.4	10.0	7.9	7.2
90°	0.7	8.1	13.4	16.8	18.1
92.5°	16.8	14.1	16.1	17.5	18.1
95°	43.7	21.5	26.2	29.6	28.9
97.5°	78.6	23.5	34.3	36.3	36.9
100°	118.9	26.9	38.3	43.7	45.0
102.5°	163.2	161.9	39.6	47.0	49.0
105°	204.2	224.3	41.0	48.4	51.0
107.5°	251.9	268.7	42.3	49.7	52.4
110°	297.6	311.7	117.5	50.4	53.1

TEST NUMBER: P1008128

CATALOG NUMBER: S122DIP-B485D725UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	340.5	352.6	341.2	51.7	53.7
115°	386.2	397.6	414.4	103.4	55.1
117.5°	425.8	439.3	450.7	354.7	178.7
120°	470.2	480.3	492.3	500.4	409.7
122.5°	507.8	518.5	532.0	536.0	536.7
125°	546.1	554.8	567.6	572.3	574.3
127.5°	581.0	590.4	600.5	607.2	607.9
130°	613.9	624.7	632.1	639.4	638.8
132.5°	647.5	656.2	663.6	669.7	669.0
135°	675.7	686.5	692.5	699.2	697.9
137.5°	705.3	713.3	720.0	726.8	724.8
140°	734.2	739.5	746.9	753.0	749.6
142.5°	758.3	763.0	771.8	777.1	773.8
145°	783.9	783.2	794.6	799.3	795.9
147.5°	806.0	804.0	815.4	818.8	816.1
150°	827.5	822.8	833.6	837.6	834.2
152.5°	845.7	840.3	850.4	854.4	849.7
155°	863.1	857.1	865.1	869.2	863.8
157.5°	877.2	871.8	877.9	882.6	877.2
160°	889.3	885.3	889.3	893.3	888.6
162.5°	900.1	896.0	899.4	904.1	898.0
165°	909.5	905.4	907.4	912.2	907.4
167.5°	916.9	912.8	914.8	919.5	913.5
170°	922.9	918.9	920.2	924.9	918.9
172.5°	926.9	922.9	924.2	928.9	922.9
175°	930.3	925.6	926.9	931.6	924.9
177.5°	931.6	926.9	927.6	932.3	926.3
180°	928.3	928.3	928.3	928.3	928.3

(END OF REPORT)