

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008135

Luminaire Tested: S122DIP-B485D925UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008135
REPORT IS A COMBINATION OF REPORTS P984373 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D925UB2750-4F0-XX-W2A-D_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5623.0 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008135

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008135

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	93	88	84	80	83	79	76	72	62	60	58	47	45	44	33	32	31
2	84	76	70	65	75	69	63	59	54	50	47	41	38	36	28	27	25
3	76	67	59	53	68	60	54	48	47	43	39	36	32	30	25	23	21
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	22	20	18
5	64	52	44	38	57	47	40	35	37	32	28	28	24	22	20	17	15
6	58	46	38	33	52	42	35	30	33	28	24	25	22	19	18	15	13
7	54	42	34	28	48	38	31	26	30	25	21	23	19	16	16	14	12
8	50	38	30	25	45	34	27	23	27	22	19	21	17	14	15	12	10
9	46	34	27	22	41	31	25	20	25	20	16	19	15	13	14	11	9
10	43	31	24	19	39	28	22	18	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8122	8122	8122
5°	8159	7775	7733
10°	8105	7506	7397
15°	7990	7228	7054
20°	7846	6935	6728
25°	7703	6655	6432
30°	7505	6371	6139
35°	7302	6097	5924
40°	7090	5859	5711
45°	6886	5643	5524
50°	6669	5445	5341
55°	6440	5234	5153
60°	6160	5015	4957
65°	5869	4763	4730
70°	5539	4492	4486
75°	5119	4221	4257
80°	4455	3940	4018
85°	3786	3674	3812

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6886 cd/sqm

TEST NUMBER: P1008135

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.6	0.9
10°-20°	139.5	2.5
20°-30°	211.4	3.8
30°-40°	257.4	4.6
40°-50°	277.0	4.9
50°-60°	269.0	4.8
60°-70°	234.9	4.2
70°-80°	180.8	3.2
80°-90°	123.3	2.2
90°-100°	124.7	2.2
100°-110°	214.6	3.8
110°-120°	447.6	8.0
120°-130°	698.0	12.4
130°-140°	727.0	12.9
140°-150°	668.5	11.9
150°-160°	536.2	9.5
160°-170°	345.5	6.1
170°-180°	118.9	2.1
0°-30°	399.6	7.1
0°-40°	657.0	11.7
0°-60°	1202.9	21.4
0°-90°	1741.9	31.0
90°-120°	786.9	14.0
90°-150°	2880.5	51.2
90°-180°	3881.0	69.0
0°-180°	5623.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	513	513	513	513	513	
5°	515	512	508	512	512	49
15°	491	492	492	499	498	138
25°	446	451	458	467	469	205
35°	384	397	411	428	433	240
45°	315	335	361	384	392	243
55°	242	268	307	334	344	216
65°	165	202	245	276	286	164
75°	92	133	181	213	222	97
85°	27	73	120	152	162	28
90°	8	61	116	150	161	9
95°	65	70	121	154	162	74
105°	278	327	119	155	167	298
115°	523	546	602	206	149	514
125°	736	748	789	816	825	657
135°	910	925	940	965	969	703
145°	1055	1054	1070	1080	1080	660
155°	1162	1154	1164	1170	1163	535
165°	1224	1219	1221	1228	1221	346
175°	1252	1246	1248	1254	1245	119
180°	1249	1249	1249	1249	1249	

TEST NUMBER: P1008135

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	513.1	513.1	513.1	513.1	513.1
2.5°	516.9	514.6	509.4	513.1	511.7
5°	514.6	512.4	507.9	512.4	511.7
7.5°	510.9	509.4	505.7	510.9	510.2
10°	506.5	505.0	502.7	508.7	507.9
12.5°	499.0	499.8	498.3	504.2	503.5
15°	490.8	492.3	492.3	499.0	498.3
17.5°	480.4	483.4	485.6	492.3	492.3
20°	470.0	473.7	476.7	484.9	484.9
22.5°	458.9	463.3	467.8	476.0	477.5
25°	446.2	451.4	458.1	467.0	469.3
27.5°	431.3	439.5	447.0	458.1	459.6
30°	416.5	426.1	435.8	447.7	449.9
32.5°	400.1	411.3	423.2	437.3	441.8
35°	384.5	397.1	411.3	427.6	432.8
37.5°	367.4	381.5	399.4	417.2	422.4
40°	350.3	366.6	386.7	406.1	412.8
42.5°	333.9	350.3	374.1	395.6	402.3
45°	315.3	335.4	361.4	384.5	391.9
47.5°	297.5	319.0	348.8	372.6	380.8
50°	278.9	301.9	335.4	360.7	368.9
52.5°	261.0	285.6	321.3	347.3	356.2
55°	241.7	268.5	307.1	333.9	343.6
57.5°	223.1	252.9	291.5	320.5	330.2
60°	203.0	235.0	277.4	305.7	316.1
62.5°	185.2	218.6	261.0	291.5	301.2
65°	165.1	201.5	245.4	275.9	285.6
67.5°	147.3	185.2	229.8	260.3	270.7
70°	127.9	166.6	212.7	244.7	253.6
72.5°	110.1	150.2	197.1	228.3	239.5
75°	91.5	133.1	180.7	212.7	222.4
77.5°	73.6	116.8	165.1	197.1	207.5
80°	55.8	101.1	149.5	180.7	191.1
82.5°	40.9	85.5	134.6	165.8	175.5
85°	26.8	72.9	120.5	151.7	162.1
87.5°	16.4	61.0	108.6	139.1	148.7
90°	8.3	61.4	116.3	150.5	161.2
92.5°	29.3	65.1	113.2	144.0	153.8
95°	64.7	69.8	120.8	153.6	161.6
97.5°	111.0	68.8	126.4	156.6	166.5
100°	165.2	68.9	125.9	160.7	170.7
102.5°	224.2	246.9	122.5	159.2	170.1
105°	278.5	327.3	119.1	155.1	166.9
107.5°	342.7	383.2	115.8	150.9	162.7
110°	403.5	437.3	212.5	145.9	157.7

TEST NUMBER: P1008135

CATALOG NUMBER: S122DIP-B485D925UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	461.4	489.5	508.4	142.5	153.4
115°	522.8	546.4	602.4	206.1	149.2
117.5°	575.4	599.4	646.0	539.0	309.7
120°	635.0	651.6	697.7	729.3	615.5
122.5°	685.7	700.9	746.5	772.0	779.6
125°	736.5	748.2	789.2	815.7	825.1
127.5°	783.5	795.4	829.0	856.7	864.3
130°	827.8	841.5	867.1	894.9	900.0
132.5°	873.0	884.0	905.1	930.3	935.4
135°	910.2	924.6	940.3	964.9	969.0
137.5°	950.0	960.8	973.6	996.8	999.3
140°	988.8	995.4	1006.8	1026.8	1026.7
142.5°	1021.4	1027.0	1038.8	1054.9	1054.1
145°	1055.0	1054.1	1069.5	1080.3	1079.5
147.5°	1084.9	1082.2	1097.5	1102.7	1101.4
150°	1113.8	1107.5	1121.9	1127.4	1122.8
152.5°	1138.2	1131.0	1144.5	1150.0	1143.6
155°	1161.7	1153.6	1164.4	1169.8	1162.6
157.5°	1180.7	1173.5	1181.6	1187.9	1180.7
160°	1197.0	1191.5	1197.0	1202.4	1196.1
162.5°	1211.4	1206.0	1210.5	1216.9	1208.7
165°	1224.1	1218.7	1221.4	1227.7	1221.4
167.5°	1234.0	1228.6	1231.3	1237.6	1229.5
170°	1242.2	1236.7	1238.6	1244.9	1236.7
172.5°	1247.6	1242.2	1244.0	1250.3	1242.2
175°	1252.1	1245.8	1247.6	1253.9	1244.9
177.5°	1253.9	1247.6	1248.5	1254.8	1246.7
180°	1249.4	1249.4	1249.4	1249.4	1249.4

(END OF REPORT)