

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008172

Luminaire Tested: S122DIP-B675D330UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008172
REPORT IS A COMBINATION OF REPORTS P984500 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D330UB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4011.0 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008172

CATALOG NUMBER: S122DIP-B675D330UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008172

CATALOG NUMBER: S122DIP-B675D330UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	102	97	93	90	96	92	88	85	82	79	77	72	70	68	64	62	61
2	93	85	79	73	87	80	75	70	72	67	63	64	60	57	56	54	51
3	85	75	67	61	79	71	64	59	63	58	53	56	52	48	50	46	44
4	77	66	58	52	73	63	55	50	56	50	46	50	45	42	44	41	38
5	71	59	51	45	67	56	49	43	50	44	39	45	40	36	40	36	33
6	66	53	45	39	62	51	43	37	45	39	35	41	36	32	36	32	29
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	33	29	26
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	31	26	23
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21
10	49	37	29	25	47	35	28	24	32	26	22	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16800	16800	16800
5°	16827	16012	15899
10°	16689	15283	14979
15°	16445	14547	14012
20°	16114	13747	13096
25°	15785	12913	12182
30°	15371	12127	11222
35°	14981	11300	10279
40°	14497	10483	9388
45°	14019	9672	8515
50°	13494	8847	7608
55°	12942	7966	6749
60°	12323	7011	5857
65°	11646	6040	4917
70°	10783	4978	3972
75°	9588	3838	3066
80°	8143	2609	1974
85°	5905	1214	839

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14019 cd/sqm

TEST NUMBER: P1008172

CATALOG NUMBER: S122DIP-B675D330UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	2.5
10°-20°	281.0	7.0
20°-30°	413.0	10.3
30°-40°	479.7	12.0
40°-50°	479.1	11.9
50°-60°	417.7	10.4
60°-70°	308.8	7.7
70°-80°	174.7	4.4
80°-90°	46.9	1.2
90°-100°	14.7	0.4
100°-110°	54.9	1.4
110°-120°	145.7	3.6
120°-130°	241.7	6.0
130°-140°	256.7	6.4
140°-150°	238.6	5.9
150°-160°	191.8	4.8
160°-170°	123.6	3.1
170°-180°	42.5	1.1
0°-30°	793.9	19.8
0°-40°	1273.6	31.8
0°-60°	2170.4	54.1
0°-90°	2700.8	67.3
90°-120°	215.4	5.4
90°-150°	952.3	23.7
90°-180°	1310.0	32.7
0°-180°	4011.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1061	1061	1061	1061	1061	
5°	1061	1057	1046	1054	1052	101
15°	1010	1004	991	995	990	285
25°	914	906	889	891	889	421
35°	789	779	762	756	751	493
45°	642	635	619	608	604	495
55°	486	480	467	455	450	434
65°	328	321	311	302	297	324
75°	171	169	164	158	160	183
85°	42	41	40	37	36	47
90°	0	4	6	8	9	4
95°	21	10	13	14	14	25
105°	98	108	20	23	25	105
115°	186	191	200	50	26	183
125°	263	267	273	276	276	234
135°	325	330	333	337	336	251
145°	377	377	383	385	383	236
155°	416	413	416	418	416	191
165°	438	436	437	439	437	124
175°	448	446	446	448	445	43
180°	447	447	447	447	447	

TEST NUMBER: P1008172

CATALOG NUMBER: S122DIP-B675D330UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1067.4	1062.3	1051.0	1061.3	1059.2
5°	1061.3	1057.2	1045.9	1054.1	1052.1
7.5°	1054.1	1048.0	1036.8	1044.9	1042.9
10°	1042.9	1035.7	1023.5	1031.7	1028.6
12.5°	1027.6	1021.5	1009.2	1014.3	1012.3
15°	1010.2	1004.1	990.8	994.9	989.8
17.5°	988.8	982.7	969.4	974.5	969.4
20°	965.3	959.2	944.9	948.0	943.9
22.5°	941.9	932.7	919.4	919.4	917.4
25°	914.3	906.1	888.8	890.8	888.8
27.5°	883.7	876.6	863.3	860.2	855.1
30°	853.1	844.9	829.6	826.6	822.5
32.5°	820.4	814.3	798.0	791.9	787.8
35°	788.8	778.6	762.3	756.1	751.0
37.5°	753.1	743.9	727.6	720.4	715.3
40°	716.3	708.2	691.9	682.7	678.6
42.5°	680.6	672.5	656.1	645.9	639.8
45°	641.9	634.7	619.4	608.2	604.1
47.5°	604.1	597.0	580.6	569.4	563.3
50°	564.3	559.2	544.9	530.6	525.5
52.5°	525.5	518.4	505.1	493.9	486.7
55°	485.7	479.6	467.4	455.1	450.0
57.5°	445.9	440.8	427.6	415.3	411.2
60°	406.1	402.1	387.8	376.5	373.5
62.5°	367.4	360.2	350.0	339.8	335.7
65°	327.6	321.4	311.2	302.0	296.9
67.5°	286.7	281.6	272.5	265.3	261.2
70°	249.0	244.9	235.7	228.6	224.5
72.5°	210.2	206.1	201.0	193.9	190.8
75°	171.4	169.4	164.3	158.2	160.2
77.5°	136.7	132.7	130.6	127.6	124.5
80°	102.0	101.0	99.0	95.9	93.9
82.5°	69.4	69.4	68.4	64.3	64.3
85°	41.8	40.8	39.8	36.7	35.7
87.5°	18.4	16.3	14.3	11.2	10.2
90°	0.3	3.9	6.5	8.1	8.7
92.5°	8.1	6.8	7.8	8.4	8.7
95°	21.0	10.3	12.6	14.2	13.9
97.5°	37.8	11.3	16.5	17.5	17.8
100°	57.2	12.9	18.4	21.0	21.7
102.5°	78.6	77.9	19.1	22.6	23.6
105°	98.3	108.0	19.7	23.3	24.6
107.5°	121.3	129.4	20.4	23.9	25.2
110°	143.3	150.1	56.6	24.3	25.5

TEST NUMBER: P1008172

CATALOG NUMBER: S122DIP-B675D330UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	164.0	169.8	164.3	24.9	25.9
115°	185.9	191.4	199.5	49.8	26.5
117.5°	205.0	211.5	217.0	170.7	86.0
120°	226.4	231.2	237.0	240.9	197.3
122.5°	244.5	249.7	256.1	258.1	258.4
125°	262.9	267.1	273.3	275.5	276.5
127.5°	279.7	284.3	289.1	292.3	292.7
130°	295.6	300.7	304.3	307.9	307.5
132.5°	311.7	315.9	319.5	322.4	322.1
135°	325.3	330.5	333.4	336.6	336.0
137.5°	339.6	343.4	346.7	349.9	348.9
140°	353.5	356.0	359.6	362.5	360.9
142.5°	365.1	367.4	371.6	374.2	372.5
145°	377.4	377.1	382.6	384.8	383.2
147.5°	388.1	387.1	392.6	394.2	392.9
150°	398.4	396.1	401.3	403.3	401.6
152.5°	407.1	404.6	409.4	411.3	409.1
155°	415.6	412.6	416.5	418.5	415.9
157.5°	422.3	419.8	422.7	424.9	422.3
160°	428.2	426.2	428.2	430.1	427.8
162.5°	433.3	431.4	433.0	435.3	432.4
165°	437.9	435.9	436.9	439.2	436.9
167.5°	441.4	439.5	440.5	442.7	439.8
170°	444.3	442.4	443.0	445.3	442.4
172.5°	446.3	444.3	445.0	447.2	444.3
175°	447.9	445.6	446.3	448.5	445.3
177.5°	448.5	446.3	446.6	448.9	446.0
180°	446.9	446.9	446.9	446.9	446.9

(END OF REPORT)