

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008888

Luminaire Tested: S122DIP-B290D530UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008888
REPORT IS A COMBINATION OF REPORTS P983988 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D530UB40-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3225.3 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008888

CATALOG NUMBER: S122DIP-B290D530UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1008888

CATALOG NUMBER: S122DIP-B290D530UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36		
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37	30		
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	34	32	31	25		
3	79	69	62	57	71	63	57	52	51	47	43	40	37	34	30	28	26	22		
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	23	19		
5	66	55	47	41	59	50	43	38	41	35	31	32	28	26	24	22	20	16		
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17	14		
7	56	44	36	31	51	40	33	29	33	28	24	26	22	20	20	17	15	13		
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14	11		
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10		
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	9		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7236	7236	7236
5°	7247	6897	6849
10°	7189	6583	6453
15°	7083	6266	6036
20°	6941	5921	5641
25°	6799	5561	5247
30°	6622	5223	4834
35°	6453	4866	4428
40°	6246	4515	4044
45°	6039	4166	3667
50°	5813	3811	3278
55°	5574	3431	2907
60°	5307	3019	2523
65°	5016	2603	2118
70°	4643	2144	1711
75°	4128	1654	1321
80°	3513	1123	849
85°	2543	521	362

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6039 cd/sqm

TEST NUMBER: P1008888

CATALOG NUMBER: S122DIP-B290D530UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.0	1.3
10°-20°	121.1	3.8
20°-30°	177.9	5.5
30°-40°	206.6	6.4
40°-50°	206.4	6.4
50°-60°	179.9	5.6
60°-70°	133.0	4.1
70°-80°	75.3	2.3
80°-90°	21.7	0.7
90°-100°	119.8	3.7
100°-110°	405.0	12.6
110°-120°	425.7	13.2
120°-130°	350.1	10.9
130°-140°	281.3	8.7
140°-150°	212.5	6.6
150°-160°	149.4	4.6
160°-170°	88.0	2.7
170°-180°	28.6	0.9
0°-30°	342.0	10.6
0°-40°	548.6	17.0
0°-60°	934.9	29.0
0°-90°	1164.9	36.1
90°-120°	950.6	29.5
90°-150°	1794.5	55.6
90°-180°	2060.0	63.9
0°-180°	3225.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	457	457	457	457	457	
5°	457	455	450	454	453	43
15°	435	432	427	429	426	123
25°	394	390	383	384	383	181
35°	340	335	328	326	324	212
45°	276	273	267	262	260	213
55°	209	207	201	196	194	187
65°	141	138	134	130	128	139
75°	74	73	71	68	69	79
85°	18	18	17	16	15	20
90°	1	8	19	18	19	2
95°	20	49	223	84	65	21
105°	69	105	421	753	640	74
115°	122	154	352	727	843	121
125°	170	202	339	589	684	152
135°	200	239	335	495	567	155
145°	228	263	333	413	452	143
155°	260	280	323	366	380	120
165°	283	292	310	328	334	80
175°	295	295	298	302	301	28
180°	296	296	296	296	296	

TEST NUMBER: P1008888

CATALOG NUMBER: S122DIP-B290D530UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	457.1	457.1	457.1	457.1	457.1
2.5°	459.8	457.6	452.7	457.1	456.2
5°	457.1	455.4	450.5	454.0	453.2
7.5°	454.0	451.4	446.6	450.1	449.2
10°	449.2	446.1	440.9	444.4	443.1
12.5°	442.6	440.0	434.7	436.9	436.0
15°	435.1	432.5	426.8	428.6	426.4
17.5°	425.9	423.3	417.6	419.8	417.6
20°	415.8	413.2	407.0	408.3	406.6
22.5°	405.7	401.7	396.0	396.0	395.1
25°	393.8	390.3	382.8	383.7	382.8
27.5°	380.6	377.6	371.9	370.5	368.3
30°	367.5	363.9	357.3	356.0	354.3
32.5°	353.4	350.8	343.7	341.1	339.3
35°	339.8	335.4	328.3	325.7	323.5
37.5°	324.4	320.4	313.4	310.3	308.1
40°	308.6	305.0	298.0	294.1	292.3
42.5°	293.2	289.7	282.6	278.2	275.6
45°	276.5	273.4	266.8	262.0	260.2
47.5°	260.2	257.1	250.1	245.3	242.6
50°	243.1	240.9	234.7	228.6	226.4
52.5°	226.4	223.3	217.6	212.7	209.7
55°	209.2	206.6	201.3	196.0	193.8
57.5°	192.1	189.9	184.2	178.9	177.1
60°	174.9	173.2	167.0	162.2	160.9
62.5°	158.2	155.2	150.8	146.4	144.6
65°	141.1	138.5	134.1	130.1	127.9
67.5°	123.5	121.3	117.4	114.3	112.5
70°	107.2	105.5	101.5	98.5	96.7
72.5°	90.5	88.8	86.6	83.5	82.2
75°	73.8	73.0	70.8	68.1	69.0
77.5°	58.9	57.1	56.3	54.9	53.6
80°	44.0	43.5	42.6	41.3	40.4
82.5°	29.9	29.9	29.4	27.7	27.7
85°	18.0	17.6	17.1	15.8	15.4
87.5°	7.9	7.0	6.2	4.8	4.4
90°	0.6	7.6	19.3	18.5	18.8
92.5°	8.5	27.0	87.5	40.4	34.7
95°	19.9	48.9	222.8	84.2	64.8
97.5°	29.6	64.5	363.2	168.8	108.6
100°	43.8	79.0	449.0	336.2	203.5
102.5°	56.8	92.0	451.8	568.3	396.7
105°	69.3	104.6	421.1	752.8	640.5
107.5°	83.0	117.0	392.7	819.6	804.8
110°	96.6	129.8	373.4	808.7	871.8

TEST NUMBER: P1008888

CATALOG NUMBER: S122DIP-B290D530UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	109.1	142.1	360.9	772.0	870.7
115°	122.2	154.3	352.4	727.2	842.8
117.5°	135.8	166.6	347.8	684.2	800.8
120°	148.3	178.4	343.8	646.0	760.4
122.5°	160.3	190.6	341.6	616.0	718.4
125°	170.5	201.8	338.7	589.1	683.7
127.5°	179.0	212.2	337.0	566.1	651.3
130°	186.4	221.6	335.9	542.8	624.6
132.5°	193.2	230.8	335.3	518.6	596.7
135°	200.1	238.7	334.7	495.0	566.6
137.5°	206.3	245.5	334.7	471.2	537.6
140°	213.7	251.8	334.2	450.1	507.5
142.5°	221.1	256.9	334.2	430.0	477.4
145°	228.5	262.6	333.0	413.4	452.4
147.5°	236.4	267.1	331.3	399.0	430.2
150°	244.4	271.6	329.6	386.5	410.9
152.5°	252.3	276.2	326.8	376.0	394.4
155°	259.7	280.4	323.4	365.7	380.2
157.5°	266.0	283.9	320.0	356.0	367.7
160°	272.2	287.3	316.6	346.4	355.8
162.5°	278.5	289.8	313.7	337.3	344.4
165°	283.0	291.6	309.7	328.5	333.6
167.5°	287.0	293.2	306.3	320.5	323.4
170°	291.0	294.2	303.5	313.2	314.3
172.5°	293.3	295.0	300.1	306.6	306.9
175°	295.0	295.2	297.8	301.5	300.6
177.5°	296.1	295.5	295.5	297.8	296.1
180°	295.5	295.5	295.5	295.5	295.5

(END OF REPORT)