

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008195

Luminaire Tested: S122DIP-B675D725UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008195
REPORT IS A COMBINATION OF REPORTS P984613 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D725UB2750-4F0-XX-W2A-D_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5534.0 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008195

CATALOG NUMBER: S122DIP-B675D725UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008195

CATALOG NUMBER: S122DIP-B675D725UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	106	106	106	106	97	97	97	97		80	80	80		64	64	64		50	50	50
1	95	90	86	82	87	82	79	75		68	65	63		54	53	51		42	41	40
2	86	78	71	66	78	71	66	61		59	54	51		47	44	41		36	34	32
3	78	68	60	54	71	62	56	50		51	46	42		41	38	34		32	29	27
4	71	60	52	45	65	55	48	42		45	40	35		36	32	29		28	25	23
5	65	53	45	39	59	49	41	36		40	35	30		33	28	25		25	22	20
6	60	48	39	33	54	44	36	31		36	30	26		29	25	22		23	20	17
7	55	43	35	29	50	39	32	27		33	27	23		27	22	19		21	18	15
8	51	39	31	25	47	36	29	24		30	24	20		24	20	17		19	16	13
9	48	35	28	22	43	32	26	21		27	22	18		22	18	15		17	14	12
10	44	32	25	20	41	30	23	19		25	20	16		20	16	14		16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11209	11209	11209
5°	11260	10732	10671
10°	11184	10360	10209
15°	11026	9975	9734
20°	10827	9570	9284
25°	10631	9185	8876
30°	10355	8791	8472
35°	10077	8412	8175
40°	9784	8086	7880
45°	9503	7789	7624
50°	9204	7516	7369
55°	8886	7225	7111
60°	8503	6921	6840
65°	8098	6573	6527
70°	7644	6199	6192
75°	7060	5826	5874
80°	6148	5436	5546
85°	5212	5071	5260

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9503 cd/sqm

TEST NUMBER: P1008195

CATALOG NUMBER: S122DIP-B675D725UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.1	1.2
10°-20°	192.5	3.5
20°-30°	291.7	5.3
30°-40°	355.2	6.4
40°-50°	382.2	6.9
50°-60°	371.2	6.7
60°-70°	324.2	5.9
70°-80°	249.5	4.5
80°-90°	168.8	3.1
90°-100°	147.1	2.7
100°-110°	202.9	3.7
110°-120°	370.3	6.7
120°-130°	553.0	10.0
130°-140°	567.5	10.3
140°-150°	517.5	9.4
150°-160°	414.3	7.5
160°-170°	267.0	4.8
170°-180°	91.9	1.7
0°-30°	551.4	10.0
0°-40°	906.6	16.4
0°-60°	1660.0	30.0
0°-90°	2402.5	43.4
90°-120°	720.3	13.0
90°-150°	2358.3	42.6
90°-180°	3132.0	56.6
0°-180°	5534.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	708	708	708	708	708	
5°	710	707	701	707	706	67
15°	677	679	679	689	688	191
25°	616	623	632	644	648	283
35°	531	548	568	590	597	332
45°	435	463	499	531	541	336
55°	334	370	424	461	474	298
65°	228	278	339	381	394	226
75°	126	184	249	294	307	134
85°	37	101	166	209	224	39
90°	11	78	150	194	208	10
95°	54	79	145	188	199	60
105°	218	268	131	174	189	233
115°	406	429	493	200	161	399
125°	570	579	625	658	669	509
135°	704	715	732	760	767	544
145°	815	814	826	838	839	510
155°	898	891	900	904	898	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	965	965	965	965	965	

TEST NUMBER: P1008195

CATALOG NUMBER: S122DIP-B675D725UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	708.1	708.1	708.1	708.1	708.1
2.5°	713.3	710.2	703.0	708.1	706.1
5°	710.2	707.1	701.0	707.1	706.1
7.5°	705.1	703.0	697.9	705.1	704.0
10°	698.9	696.8	693.8	702.0	701.0
12.5°	688.6	689.7	687.6	695.8	694.8
15°	677.3	679.4	679.4	688.6	687.6
17.5°	663.0	667.1	670.2	679.4	679.4
20°	648.6	653.7	657.8	669.1	669.1
22.5°	633.2	639.4	645.5	656.8	658.9
25°	615.8	623.0	632.2	644.5	647.6
27.5°	595.2	606.5	616.8	632.2	634.2
30°	574.7	588.1	601.4	617.8	620.9
32.5°	552.1	567.5	584.0	603.5	609.6
35°	530.6	548.0	567.5	590.1	597.3
37.5°	507.0	526.5	551.1	575.7	582.9
40°	483.4	506.0	533.7	560.4	569.6
42.5°	460.8	483.4	516.2	546.0	555.2
45°	435.1	462.9	498.8	530.6	540.9
47.5°	410.5	440.3	481.3	514.2	525.5
50°	384.9	416.7	462.9	497.7	509.0
52.5°	360.2	394.1	443.4	479.3	491.6
55°	333.5	370.5	423.9	460.8	474.1
57.5°	307.9	348.9	402.3	442.3	455.7
60°	280.2	324.3	382.8	421.8	436.2
62.5°	255.5	301.7	360.2	402.3	415.6
65°	227.8	278.1	338.7	380.8	394.1
67.5°	203.2	255.5	317.1	359.2	373.6
70°	176.5	229.9	293.5	337.6	350.0
72.5°	151.9	207.3	272.0	315.1	330.5
75°	126.2	183.7	249.4	293.5	306.9
77.5°	101.6	161.1	227.8	272.0	286.3
80°	77.0	139.6	206.3	249.4	263.8
82.5°	56.4	118.0	185.8	228.9	242.2
85°	36.9	100.6	166.3	209.4	223.7
87.5°	22.6	84.2	149.8	191.9	205.3
90°	11.0	78.2	149.5	194.0	207.7
92.5°	26.7	78.3	143.0	184.5	197.5
95°	53.6	78.8	145.2	187.7	199.3
97.5°	88.9	75.8	146.4	186.5	199.5
100°	130.8	73.1	142.4	186.0	198.7
102.5°	176.0	208.4	136.6	181.3	194.7
105°	217.5	268.2	130.9	174.5	188.6
107.5°	267.1	309.2	125.1	167.7	181.8
110°	313.6	348.7	197.2	160.2	174.2

TEST NUMBER: P1008195

CATALOG NUMBER: S122DIP-B675D725UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	358.3	387.3	422.6	154.4	167.8
115°	405.8	429.0	492.6	200.0	161.0
117.5°	446.0	468.2	523.1	454.0	281.2
120°	492.1	506.7	560.3	597.4	514.4
122.5°	531.2	543.4	595.4	627.3	637.2
125°	570.0	579.1	625.2	657.8	669.1
127.5°	606.4	615.0	653.2	685.9	695.8
130°	640.6	650.7	680.0	712.2	719.7
132.5°	675.5	683.5	706.6	736.5	744.0
135°	703.8	714.9	731.5	760.0	766.9
137.5°	734.5	742.9	755.1	781.6	786.6
140°	764.5	769.1	778.9	801.6	804.2
142.5°	789.7	793.6	802.7	820.6	822.2
145°	815.2	814.5	826.4	837.5	839.1
147.5°	838.3	836.2	848.1	852.6	852.9
150°	860.6	855.8	866.9	871.1	867.6
152.5°	879.5	873.9	884.4	888.6	883.7
155°	897.7	891.4	899.8	904.0	898.4
157.5°	912.3	906.7	913.0	917.9	912.3
160°	924.9	920.7	924.9	929.1	924.2
162.5°	936.1	931.9	935.4	940.3	934.0
165°	945.9	941.7	943.8	948.7	943.8
167.5°	953.6	949.4	951.5	956.3	950.1
170°	959.8	955.6	957.0	961.9	955.6
172.5°	964.0	959.8	961.2	966.1	959.8
175°	967.5	962.6	964.0	968.9	961.9
177.5°	968.9	964.0	964.7	969.6	963.3
180°	965.4	965.4	965.4	965.4	965.4

(END OF REPORT)