

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008211

Luminaire Tested: S122DIP-B675D925UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008211
REPORT IS A COMBINATION OF REPORTS P984674 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D925UB2750-4F0-XX-W2A-D_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6395.0 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008211

CATALOG NUMBER: S122DIP-B675D925UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008211

CATALOG NUMBER: S122DIP-B675D925UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	94	89	85	81	85	81	77	74	65	63	60	51	49	48	38	37	36
2	85	77	71	65	77	70	64	60	57	53	49	44	41	39	33	31	29
3	77	67	60	54	70	61	55	49	49	45	41	39	35	32	29	26	24
4	70	59	51	45	63	54	47	41	44	38	34	34	30	27	25	23	21
5	64	53	44	38	58	48	41	35	39	33	29	30	27	23	23	20	18
6	59	47	39	33	53	43	36	30	35	29	25	27	23	20	20	18	15
7	55	42	34	29	49	39	31	26	31	26	22	25	21	18	19	16	14
8	51	38	30	25	46	35	28	23	29	23	19	23	19	16	17	14	12
9	47	35	27	22	42	32	25	21	26	21	17	21	17	14	16	13	11
10	44	32	25	20	40	29	23	18	24	19	15	19	15	13	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11259	11259	11259
5°	11309	10779	10717
10°	11234	10404	10254
15°	11076	10019	9778
20°	10876	9614	9325
25°	10678	9225	8916
30°	10402	8831	8510
35°	10121	8451	8212
40°	9826	8121	7915
45°	9546	7823	7658
50°	9245	7548	7402
55°	8926	7255	7142
60°	8539	6952	6870
65°	8134	6603	6555
70°	7678	6226	6218
75°	7093	5851	5899
80°	6171	5460	5569
85°	5241	5092	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9546 cd/sqm

TEST NUMBER: P1008211

CATALOG NUMBER: S122DIP-B675D925UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.4	1.1
10°-20°	193.4	3.0
20°-30°	293.0	4.6
30°-40°	356.8	5.6
40°-50°	383.9	6.0
50°-60°	372.8	5.8
60°-70°	325.6	5.1
70°-80°	250.6	3.9
80°-90°	170.1	2.7
90°-100°	157.2	2.5
100°-110°	238.8	3.7
110°-120°	464.9	7.3
120°-130°	709.6	11.1
130°-140°	733.8	11.5
140°-150°	672.1	10.5
150°-160°	538.5	8.4
160°-170°	347.0	5.4
170°-180°	119.4	1.9
0°-30°	553.8	8.7
0°-40°	910.7	14.2
0°-60°	1667.4	26.1
0°-90°	2413.6	37.7
90°-120°	860.9	13.5
90°-150°	2976.4	46.5
90°-180°	3981.0	62.3
0°-180°	6395.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	711	711	711	711	711	
5°	713	710	704	710	709	68
15°	680	682	682	692	691	192
25°	618	626	635	647	650	284
35°	533	550	570	593	600	333
45°	437	465	501	533	543	337
55°	335	372	426	463	476	300
65°	229	279	340	382	396	227
75°	127	184	250	295	308	134
85°	37	101	167	210	225	39
90°	11	81	154	200	214	11
95°	67	86	154	198	209	76
105°	281	338	144	190	205	301
115°	526	553	622	233	179	518
125°	740	752	802	836	848	661
135°	914	929	947	978	985	707
145°	1060	1059	1074	1087	1087	663
155°	1167	1159	1170	1175	1168	538
165°	1229	1224	1227	1233	1227	347
175°	1258	1251	1253	1259	1250	120
180°	1255	1255	1255	1255	1255	

TEST NUMBER: P1008211

CATALOG NUMBER: S122DIP-B675D925UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	711.3	711.3	711.3	711.3	711.3
2.5°	716.4	713.3	706.1	711.3	709.2
5°	713.3	710.3	704.1	710.3	709.2
7.5°	708.2	706.1	701.0	708.2	707.2
10°	702.0	699.9	696.8	705.1	704.1
12.5°	691.7	692.7	690.7	698.9	697.9
15°	680.4	682.4	682.4	691.7	690.7
17.5°	665.9	670.0	673.1	682.4	682.4
20°	651.5	656.6	660.8	672.1	672.1
22.5°	636.0	642.2	648.4	659.7	661.8
25°	618.5	625.7	635.0	647.4	650.5
27.5°	597.9	609.2	619.5	635.0	637.1
30°	577.3	590.7	604.1	620.6	623.7
32.5°	554.6	570.1	586.5	606.1	612.3
35°	532.9	550.5	570.1	592.7	600.0
37.5°	509.2	528.8	553.6	578.3	585.5
40°	485.5	508.2	536.0	562.8	572.1
42.5°	462.8	485.5	518.5	548.4	557.7
45°	437.1	464.9	501.0	532.9	543.3
47.5°	412.3	442.2	483.5	516.5	527.8
50°	386.6	418.5	464.9	500.0	511.3
52.5°	361.8	395.8	445.3	481.4	493.8
55°	335.0	372.1	425.7	462.8	476.2
57.5°	309.3	350.5	404.1	444.3	457.7
60°	281.4	325.7	384.5	423.7	438.1
62.5°	256.7	303.1	361.8	404.1	417.5
65°	228.8	279.4	340.2	382.4	395.8
67.5°	204.1	256.7	318.5	360.8	375.2
70°	177.3	230.9	294.8	339.1	351.5
72.5°	152.6	208.2	273.2	316.5	331.9
75°	126.8	184.5	250.5	294.8	308.2
77.5°	102.1	161.8	228.8	273.2	287.6
80°	77.3	140.2	207.2	250.5	264.9
82.5°	56.7	118.5	186.6	229.9	243.3
85°	37.1	101.0	167.0	210.3	224.7
87.5°	22.7	84.5	150.5	192.8	206.2
90°	11.2	81.0	154.3	200.0	214.2
92.5°	32.0	83.0	148.6	190.6	203.9
95°	67.2	85.8	153.9	197.7	209.1
97.5°	113.4	83.3	157.6	198.5	211.7
100°	167.9	81.7	154.9	200.2	213.4
102.5°	226.8	259.0	149.5	196.6	210.6
105°	281.2	338.3	144.1	190.1	205.1
107.5°	345.7	393.1	138.6	183.7	198.6
110°	406.3	446.0	234.2	176.3	191.3

TEST NUMBER: P1008211

CATALOG NUMBER: S122DIP-B675D925UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	464.5	497.3	529.3	170.9	185.0
115°	526.2	553.0	622.1	232.6	178.6
117.5°	578.8	605.1	663.9	565.0	337.4
120°	638.7	656.4	714.0	753.8	642.6
122.5°	689.5	705.1	761.4	794.7	804.9
125°	740.3	752.1	802.3	836.5	848.5
127.5°	787.5	799.1	840.7	875.4	885.6
130°	832.0	845.4	877.1	911.8	919.2
132.5°	877.4	888.1	913.6	945.5	952.8
135°	914.4	929.0	947.4	978.2	984.6
137.5°	954.4	965.3	979.6	1008.3	1012.7
140°	993.4	999.7	1011.8	1036.5	1038.0
142.5°	1026.1	1031.5	1043.3	1063.0	1063.5
145°	1059.6	1058.7	1074.2	1086.7	1087.3
147.5°	1089.6	1086.9	1102.3	1107.9	1107.3
150°	1118.7	1112.3	1126.8	1132.3	1127.7
152.5°	1143.2	1135.9	1149.5	1155.0	1148.6
155°	1166.8	1158.6	1169.5	1175.0	1167.7
157.5°	1185.8	1178.6	1186.8	1193.1	1185.8
160°	1202.2	1196.7	1202.2	1207.6	1201.3
162.5°	1216.7	1211.3	1215.8	1222.2	1214.0
165°	1229.4	1224.0	1226.7	1233.1	1226.7
167.5°	1239.4	1234.0	1236.7	1243.1	1234.9
170°	1247.6	1242.1	1244.0	1250.3	1242.1
172.5°	1253.0	1247.6	1249.4	1255.8	1247.6
175°	1257.6	1251.2	1253.0	1259.4	1250.3
177.5°	1259.4	1253.0	1253.9	1260.3	1252.1
180°	1254.9	1254.9	1254.9	1254.9	1254.9

(END OF REPORT)