

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008224

Luminaire Tested: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008224
REPORT IS A COMBINATION OF REPORTS P984732 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7713.0 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 81.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008224

CATALOG NUMBER: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1008224

CATALOG NUMBER: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47			40
1	94	90	85	81	85	81	78	74	66	64	61	52	50	49	39	38	37			31
2	85	77	71	65	77	70	65	60	57	53	50	45	42	40	34	32	30			25
3	78	68	60	54	70	62	55	50	50	45	41	39	36	33	30	27	25			21
4	71	60	51	45	64	54	47	42	44	39	35	35	31	28	26	24	21			17
5	65	53	45	38	58	48	41	35	39	34	30	31	27	24	24	21	18			15
6	59	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16			13
7	55	42	34	29	50	39	32	27	32	26	22	25	21	18	19	16	14			11
8	51	38	31	25	46	35	28	23	29	24	20	23	19	16	18	15	13			10
9	47	35	27	22	43	32	25	21	26	21	18	21	17	14	16	13	11			9
10	44	32	25	20	40	29	23	18	24	19	16	20	16	13	15	12	10			8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14283	14283	14283
5°	14349	13674	13596
10°	14252	13200	13008
15°	14050	12710	12404
20°	13797	12196	11829
25°	13546	11704	11310
30°	13195	11202	10795
35°	12840	10720	10417
40°	12465	10303	10041
45°	12110	9925	9714
50°	11727	9576	9390
55°	11325	9205	9062
60°	10833	8819	8716
65°	10320	8376	8318
70°	9740	7899	7888
75°	9001	7423	7484
80°	7832	6928	7066
85°	6653	6461	6704

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12110 cd/sqm

TEST NUMBER: P1008224

CATALOG NUMBER: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.5	1.1
10°-20°	245.3	3.2
20°-30°	371.7	4.8
30°-40°	452.7	5.9
40°-50°	487.0	6.3
50°-60°	473.0	6.1
60°-70°	413.1	5.4
70°-80°	317.9	4.1
80°-90°	215.5	2.8
90°-100°	194.9	2.5
100°-110°	286.2	3.7
110°-120°	545.4	7.1
120°-130°	826.5	10.7
130°-140°	852.6	11.1
140°-150°	779.8	10.1
150°-160°	624.7	8.1
160°-170°	402.5	5.2
170°-180°	138.5	1.8
0°-30°	702.6	9.1
0°-40°	1155.3	15.0
0°-60°	2115.3	27.4
0°-90°	3061.7	39.7
90°-120°	1026.5	13.3
90°-150°	3485.5	45.2
90°-180°	4651.0	60.3
0°-180°	7713.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	902	902	902	902	902	
5°	905	901	893	901	900	86
15°	863	866	866	878	876	243
25°	785	794	806	821	825	361
35°	676	698	723	752	761	423
45°	554	590	636	676	689	428
55°	425	472	540	587	604	380
65°	290	354	432	485	502	288
75°	161	234	318	374	391	170
85°	47	128	212	267	285	50
90°	14	102	194	251	269	13
95°	79	106	192	246	261	89
105°	327	396	177	234	253	350
115°	611	643	728	280	218	601
125°	859	873	934	977	992	767
135°	1061	1078	1100	1138	1147	820
145°	1229	1228	1246	1261	1262	769
155°	1354	1344	1357	1363	1354	624
165°	1426	1420	1423	1430	1423	403
175°	1459	1451	1454	1461	1450	139
180°	1456	1456	1456	1456	1456	

TEST NUMBER: P1008224

CATALOG NUMBER: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	902.3	902.3	902.3	902.3	902.3
2.5°	908.9	905.0	895.8	902.3	899.7
5°	905.0	901.0	893.2	901.0	899.7
7.5°	898.4	895.8	889.3	898.4	897.1
10°	890.6	888.0	884.0	894.5	893.2
12.5°	877.5	878.8	876.2	886.6	885.3
15°	863.1	865.7	865.7	877.5	876.2
17.5°	844.8	850.0	854.0	865.7	865.7
20°	826.5	833.0	838.3	852.6	852.6
22.5°	806.9	814.7	822.6	836.9	839.6
25°	784.6	793.8	805.6	821.3	825.2
27.5°	758.5	772.9	785.9	805.6	808.2
30°	732.3	749.3	766.3	787.3	791.2
32.5°	703.6	723.2	744.1	768.9	776.8
35°	676.1	698.3	723.2	751.9	761.1
37.5°	646.0	670.9	702.3	733.6	742.8
40°	615.9	644.7	680.0	714.0	725.8
42.5°	587.2	615.9	657.8	695.7	707.5
45°	554.5	589.8	635.6	676.1	689.2
47.5°	523.1	561.0	613.3	655.2	669.6
50°	490.4	530.9	589.8	634.3	648.6
52.5°	459.0	502.2	564.9	610.7	626.4
55°	425.0	472.1	540.1	587.2	604.2
57.5°	392.3	444.6	512.6	563.6	580.6
60°	357.0	413.2	487.8	537.5	555.8
62.5°	325.6	384.5	459.0	512.6	529.6
65°	290.3	354.4	431.6	485.2	502.2
67.5°	258.9	325.6	404.1	457.7	476.0
70°	224.9	292.9	374.0	430.2	445.9
72.5°	193.5	264.2	346.5	401.5	421.1
75°	160.9	234.1	317.8	374.0	391.0
77.5°	129.5	205.3	290.3	346.5	364.9
80°	98.1	177.9	262.9	317.8	336.1
82.5°	71.9	150.4	236.7	291.6	308.6
85°	47.1	128.2	211.9	266.8	285.1
87.5°	28.8	107.2	190.9	244.5	261.5
90°	14.2	101.5	193.7	251.2	269.0
92.5°	38.1	103.2	186.2	239.3	255.9
95°	79.0	105.6	191.5	246.4	261.1
97.5°	132.4	102.3	194.9	246.5	263.2
100°	195.6	99.6	190.8	247.7	264.1
102.5°	263.7	304.8	183.7	242.4	260.0
105°	326.7	396.3	176.8	234.0	252.6
107.5°	401.5	459.2	169.7	225.7	244.4
110°	471.8	520.1	279.8	216.3	234.9

TEST NUMBER: P1008224

CATALOG NUMBER: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	539.2	579.2	621.4	209.3	226.8
115°	610.8	643.1	728.4	279.9	218.5
117.5°	671.7	703.3	776.1	664.6	401.8
120°	741.2	762.3	833.6	882.8	755.0
122.5°	800.2	818.3	887.8	929.4	942.3
125°	858.9	872.6	934.5	977.2	992.1
127.5°	913.7	927.1	978.2	1021.5	1034.3
130°	965.3	980.9	1019.9	1062.9	1072.3
132.5°	1018.0	1030.4	1061.5	1101.1	1110.6
135°	1060.9	1077.8	1100.3	1138.3	1146.7
137.5°	1107.3	1119.9	1136.9	1172.4	1178.3
140°	1152.5	1159.7	1173.9	1204.2	1206.9
142.5°	1190.5	1196.5	1210.2	1234.4	1235.6
145°	1229.2	1228.1	1246.0	1261.2	1262.5
147.5°	1263.9	1260.8	1278.7	1285.3	1284.9
150°	1297.7	1290.3	1307.1	1313.5	1308.2
152.5°	1326.1	1317.7	1333.5	1339.8	1332.4
155°	1353.5	1344.0	1356.6	1363.0	1354.5
157.5°	1375.6	1367.2	1376.6	1384.0	1375.6
160°	1394.6	1388.2	1394.6	1400.9	1393.5
162.5°	1411.4	1405.1	1410.4	1417.7	1408.2
165°	1426.2	1419.8	1423.0	1430.4	1423.0
167.5°	1437.7	1431.4	1434.6	1442.0	1432.5
170°	1447.2	1440.9	1443.0	1450.4	1440.9
172.5°	1453.5	1447.2	1449.3	1456.7	1447.2
175°	1458.8	1451.4	1453.5	1460.9	1450.4
177.5°	1460.9	1453.5	1454.6	1462.0	1452.5
180°	1455.6	1455.6	1455.6	1455.6	1455.6

(END OF REPORT)