

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008228

Luminaire Tested: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008228
REPORT IS A COMBINATION OF REPORTS P984736 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7480.0 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008228

CATALOG NUMBER: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008228

CATALOG NUMBER: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47			40
1	94	90	85	81	85	81	78	74	66	64	61	52	50	49	39	38	37			31
2	85	77	71	65	77	70	65	60	57	53	50	45	42	40	34	32	30			25
3	78	68	60	54	70	62	55	50	50	45	41	39	36	33	30	27	25			21
4	71	60	51	45	64	54	47	42	44	39	35	35	31	28	26	24	21			17
5	65	53	45	38	58	48	41	35	39	34	30	31	27	24	24	21	18			15
6	59	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16			13
7	55	42	34	29	50	39	32	27	32	26	22	25	21	18	19	16	14			11
8	51	38	31	25	46	35	28	23	29	24	20	23	19	16	18	15	13			10
9	47	35	27	22	43	32	25	21	26	21	18	21	17	14	16	13	11			9
10	44	32	25	20	40	29	23	18	24	19	16	20	16	13	15	12	10			8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13852	13852	13852
5°	13914	13261	13185
10°	13822	12801	12614
15°	13625	12327	12029
20°	13380	11827	11473
25°	13136	11349	10969
30°	12796	10864	10469
35°	12453	10396	10102
40°	12089	9992	9738
45°	11743	9625	9421
50°	11373	9287	9106
55°	10984	8927	8787
60°	10505	8554	8452
65°	10007	8122	8066
70°	9445	7660	7651
75°	8727	7199	7258
80°	7593	6717	6851
85°	6455	6266	6502

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11743 cd/sqm

TEST NUMBER: P1008228

CATALOG NUMBER: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.0	1.1
10°-20°	237.9	3.2
20°-30°	360.5	4.8
30°-40°	439.0	5.9
40°-50°	472.3	6.3
50°-60°	458.7	6.1
60°-70°	400.6	5.4
70°-80°	308.3	4.1
80°-90°	209.0	2.8
90°-100°	189.0	2.5
100°-110°	277.6	3.7
110°-120°	528.9	7.1
120°-130°	801.6	10.7
130°-140°	826.9	11.1
140°-150°	756.3	10.1
150°-160°	605.8	8.1
160°-170°	390.4	5.2
170°-180°	134.4	1.8
0°-30°	681.4	9.1
0°-40°	1120.4	15.0
0°-60°	2051.4	27.4
0°-90°	2969.2	39.7
90°-120°	995.5	13.3
90°-150°	3380.2	45.2
90°-180°	4511.0	60.3
0°-180°	7480.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	875	875	875	875	875	
5°	878	874	866	874	872	83
15°	837	840	840	851	850	236
25°	761	770	781	796	800	350
35°	656	677	701	729	738	410
45°	538	572	616	656	668	415
55°	412	458	524	569	586	369
65°	282	344	418	470	487	280
75°	156	227	308	363	379	165
85°	46	124	206	259	276	48
90°	14	98	188	244	261	13
95°	76	102	186	239	253	87
105°	317	384	171	227	245	339
115°	592	624	706	271	212	583
125°	833	846	906	948	962	743
135°	1029	1045	1067	1104	1112	795
145°	1192	1191	1208	1223	1224	746
155°	1313	1303	1316	1322	1314	605
165°	1383	1377	1380	1387	1380	391
175°	1415	1408	1410	1417	1407	135
180°	1412	1412	1412	1412	1412	

TEST NUMBER: P1008228

CATALOG NUMBER: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	875.1	875.1	875.1	875.1	875.1
2.5°	881.4	877.6	868.7	875.1	872.5
5°	877.6	873.8	866.2	873.8	872.5
7.5°	871.3	868.7	862.4	871.3	870.0
10°	863.7	861.1	857.3	867.5	866.2
12.5°	851.0	852.3	849.7	859.9	858.6
15°	837.0	839.6	839.6	851.0	849.7
17.5°	819.3	824.4	828.2	839.6	839.6
20°	801.5	807.9	812.9	826.9	826.9
22.5°	782.5	790.1	797.7	811.7	814.2
25°	760.9	769.8	781.2	796.5	800.3
27.5°	735.6	749.5	762.2	781.2	783.8
30°	710.2	726.7	743.2	763.5	767.3
32.5°	682.3	701.3	721.6	745.7	753.3
35°	655.7	677.2	701.3	729.2	738.1
37.5°	626.5	650.6	681.0	711.5	720.4
40°	597.3	625.2	659.5	692.5	703.9
42.5°	569.4	597.3	637.9	674.7	686.1
45°	537.7	572.0	616.4	655.7	668.4
47.5°	507.3	544.1	594.8	635.4	649.3
50°	475.6	514.9	572.0	615.1	629.0
52.5°	445.1	487.0	547.9	592.3	607.5
55°	412.2	457.8	523.8	569.4	585.9
57.5°	380.5	431.2	497.1	546.6	563.1
60°	346.2	400.8	473.1	521.2	539.0
62.5°	315.8	372.9	445.1	497.1	513.6
65°	281.5	343.7	418.5	470.5	487.0
67.5°	251.1	315.8	391.9	443.9	461.6
70°	218.1	284.1	362.7	417.2	432.5
72.5°	187.7	256.2	336.1	389.3	408.4
75°	156.0	227.0	308.2	362.7	379.2
77.5°	125.6	199.1	281.5	336.1	353.8
80°	95.1	172.5	254.9	308.2	325.9
82.5°	69.8	145.8	229.6	282.8	299.3
85°	45.7	124.3	205.5	258.7	276.5
87.5°	27.9	104.0	185.2	237.2	253.6
90°	13.7	98.5	187.8	243.6	261.0
92.5°	36.9	100.1	180.5	232.1	248.3
95°	76.5	102.5	185.6	238.9	253.2
97.5°	128.4	99.2	189.1	239.1	255.3
100°	189.7	96.7	185.0	240.1	256.1
102.5°	255.8	295.7	178.2	235.1	252.2
105°	316.8	384.3	171.4	227.0	245.0
107.5°	389.4	445.4	164.6	218.9	237.0
110°	457.6	504.4	271.4	209.8	227.8

TEST NUMBER: P1008228

CATALOG NUMBER: S122DIP-B865D1080UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	523.0	561.7	602.6	203.0	219.9
115°	592.4	623.7	706.3	271.4	211.9
117.5°	651.4	682.0	752.6	644.6	389.6
120°	718.8	739.2	808.3	856.1	732.2
122.5°	776.0	793.7	861.0	901.3	913.9
125°	833.0	846.2	906.2	947.7	962.2
127.5°	886.1	899.2	948.7	990.6	1003.0
130°	936.1	951.3	989.1	1030.7	1039.9
132.5°	987.2	999.3	1029.5	1067.9	1077.0
135°	1028.9	1045.2	1067.1	1103.9	1112.0
137.5°	1073.8	1086.1	1102.6	1136.9	1142.8
140°	1117.8	1124.6	1138.4	1167.9	1170.4
142.5°	1154.5	1160.4	1173.7	1197.0	1198.3
145°	1192.1	1191.0	1208.4	1223.1	1224.4
147.5°	1225.8	1222.7	1240.1	1246.5	1246.2
150°	1258.4	1251.3	1267.6	1273.8	1268.7
152.5°	1286.0	1277.9	1293.2	1299.3	1292.2
155°	1312.6	1303.4	1315.7	1321.8	1313.6
157.5°	1334.0	1325.9	1335.1	1342.2	1334.0
160°	1352.4	1346.3	1352.4	1358.6	1351.4
162.5°	1368.8	1362.6	1367.7	1374.9	1365.7
165°	1383.1	1376.9	1380.0	1387.2	1380.0
167.5°	1394.3	1388.2	1391.2	1398.4	1389.2
170°	1403.5	1397.4	1399.4	1406.6	1397.4
172.5°	1409.6	1403.5	1405.5	1412.7	1403.5
175°	1414.7	1407.6	1409.6	1416.8	1406.6
177.5°	1416.8	1409.6	1410.6	1417.8	1408.6
180°	1411.7	1411.7	1411.7	1411.7	1411.7

(END OF REPORT)