

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008246

Luminaire Tested: S122DIP-B865D330UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008246
REPORT IS A COMBINATION OF REPORTS P984799 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D330UB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4829.0 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008246

CATALOG NUMBER: S122DIP-B865D330UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008246

CATALOG NUMBER: S122DIP-B865D330UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	73
1	103	98	94	91	97	93	90	87	84	82	79	76	74	72	68	66	65	65	65	61
2	94	86	80	74	89	82	76	71	74	69	65	67	63	60	60	57	55	55	55	51
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	47	47	43
4	78	67	59	53	74	64	56	51	58	52	47	53	48	44	47	44	40	40	40	37
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35	35	35	32
6	66	54	45	39	63	52	44	38	47	41	36	43	37	33	39	34	31	31	31	28
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	28	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25	25	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	22	22	20
10	50	38	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20	20	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21808	21808	21808
5°	21844	20787	20638
10°	21665	19840	19446
15°	21348	18885	18190
20°	20918	17847	17001
25°	20491	16763	15814
30°	19953	15744	14568
35°	19447	14668	13344
40°	18820	13607	12187
45°	18197	12556	11053
50°	17517	11485	9876
55°	16800	10340	8762
60°	15998	9101	7602
65°	15116	7841	6385
70°	13997	6463	5155
75°	12447	4982	3981
80°	10578	3386	2563
85°	7670	1576	1091

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18197 cd/sqm

TEST NUMBER: P1008246

CATALOG NUMBER: S122DIP-B865D330UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.7	2.7
10°-20°	364.8	7.6
20°-30°	536.1	11.1
30°-40°	622.7	12.9
40°-50°	621.9	12.9
50°-60°	542.3	11.2
60°-70°	400.8	8.3
70°-80°	226.8	4.7
80°-90°	60.7	1.3
90°-100°	14.9	0.3
100°-110°	55.5	1.1
110°-120°	147.1	3.0
120°-130°	244.0	5.1
130°-140°	259.2	5.4
140°-150°	240.9	5.0
150°-160°	193.7	4.0
160°-170°	124.8	2.6
170°-180°	43.0	0.9
0°-30°	1030.6	21.3
0°-40°	1653.3	34.2
0°-60°	2817.5	58.3
0°-90°	3505.8	72.6
90°-120°	217.5	4.5
90°-150°	961.7	19.9
90°-180°	1323.0	27.4
0°-180°	4829.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1378	1378	1378	1378	1378	
5°	1378	1372	1358	1368	1366	131
15°	1311	1304	1286	1292	1285	369
25°	1187	1176	1154	1156	1154	546
35°	1024	1011	990	982	975	639
45°	833	824	804	790	784	643
55°	630	623	607	591	584	564
65°	425	417	404	392	386	420
75°	222	220	213	205	208	237
85°	54	53	52	48	46	61
90°	0	4	6	8	9	4
95°	21	10	13	14	14	25
105°	99	109	20	24	25	106
115°	188	193	202	50	27	185
125°	266	270	276	278	279	237
135°	329	334	337	340	339	254
145°	381	381	386	389	387	238
155°	420	417	421	423	420	193
165°	442	440	441	444	441	125
175°	452	450	451	453	450	43
180°	451	451	451	451	451	

TEST NUMBER: P1008246

CATALOG NUMBER: S122DIP-B865D330UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1377.7	1377.7	1377.7	1377.7	1377.7
2.5°	1385.6	1379.0	1364.4	1377.7	1375.0
5°	1377.7	1372.4	1357.8	1368.4	1365.7
7.5°	1368.4	1360.4	1345.9	1356.5	1353.8
10°	1353.8	1344.5	1328.7	1339.2	1335.3
12.5°	1334.0	1326.0	1310.1	1316.7	1314.1
15°	1311.4	1303.5	1286.3	1291.6	1284.9
17.5°	1283.6	1275.7	1258.4	1265.1	1258.4
20°	1253.1	1245.2	1226.7	1230.6	1225.3
22.5°	1222.7	1210.8	1193.5	1193.5	1190.9
25°	1186.9	1176.3	1153.8	1156.4	1153.8
27.5°	1147.2	1137.9	1120.7	1116.7	1110.1
30°	1107.4	1096.8	1077.0	1073.0	1067.7
32.5°	1065.0	1057.1	1035.9	1028.0	1022.7
35°	1024.0	1010.7	989.5	981.6	975.0
37.5°	977.6	965.7	944.5	935.2	928.6
40°	929.9	919.3	898.1	886.2	880.9
42.5°	883.6	873.0	851.8	838.5	830.6
45°	833.2	823.9	804.1	789.5	784.2
47.5°	784.2	774.9	753.7	739.2	731.2
50°	732.5	725.9	707.4	688.8	682.2
52.5°	682.2	672.9	655.7	641.1	631.9
55°	630.5	622.6	606.7	590.8	584.2
57.5°	578.9	572.3	555.0	539.1	533.8
60°	527.2	521.9	503.4	488.8	484.8
62.5°	476.9	467.6	454.4	441.1	435.8
65°	425.2	417.3	404.0	392.1	385.5
67.5°	372.2	365.6	353.7	344.4	339.1
70°	323.2	317.9	306.0	296.7	291.4
72.5°	272.9	267.6	261.0	251.7	247.7
75°	222.5	219.9	213.3	205.3	208.0
77.5°	177.5	172.2	169.6	165.6	161.6
80°	132.5	131.1	128.5	124.5	121.9
82.5°	90.1	90.1	88.8	83.5	83.5
85°	54.3	53.0	51.7	47.7	46.4
87.5°	23.8	21.2	18.5	14.6	13.2
90°	0.3	3.9	6.5	8.2	8.8
92.5°	8.2	6.9	7.8	8.5	8.8
95°	21.2	10.5	12.7	14.4	14.0
97.5°	38.2	11.4	16.7	17.6	18.0
100°	57.8	13.1	18.6	21.2	21.9
102.5°	79.4	78.7	19.3	22.9	23.8
105°	99.3	109.1	19.9	23.5	24.8
107.5°	122.5	130.6	20.6	24.2	25.5
110°	144.7	151.5	57.2	24.5	25.8

TEST NUMBER: P1008246

CATALOG NUMBER: S122DIP-B865D330UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	165.6	171.5	165.9	25.1	26.1
115°	187.8	193.3	201.5	50.3	26.8
117.5°	207.1	213.6	219.1	172.4	86.9
120°	228.6	233.5	239.4	243.3	199.2
122.5°	246.9	252.1	258.7	260.6	260.9
125°	265.5	269.8	276.0	278.3	279.2
127.5°	282.5	287.1	292.0	295.2	295.6
130°	298.5	303.7	307.3	310.9	310.6
132.5°	314.8	319.1	322.7	325.6	325.3
135°	328.6	333.8	336.7	340.0	339.3
137.5°	342.9	346.8	350.1	353.4	352.4
140°	357.0	359.6	363.2	366.1	364.5
142.5°	368.7	371.0	375.3	377.9	376.2
145°	381.1	380.8	386.4	388.6	387.0
147.5°	391.9	390.9	396.5	398.1	396.8
150°	402.4	400.1	405.3	407.3	405.6
152.5°	411.2	408.6	413.5	415.4	413.1
155°	419.7	416.7	420.7	422.6	420.0
157.5°	426.5	423.9	426.9	429.1	426.5
160°	432.4	430.5	432.4	434.4	432.1
162.5°	437.6	435.7	437.3	439.6	436.7
165°	442.2	440.2	441.2	443.5	441.2
167.5°	445.8	443.8	444.8	447.1	444.2
170°	448.7	446.8	447.4	449.7	446.8
172.5°	450.7	448.7	449.4	451.7	448.7
175°	452.3	450.0	450.7	453.0	449.7
177.5°	453.0	450.7	451.0	453.3	450.4
180°	451.4	451.4	451.4	451.4	451.4

(END OF REPORT)