

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008959

Luminaire Tested: S122DIP-B290D925UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008959
REPORT IS A COMBINATION OF REPORTS P984089 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D925UB30-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4447.0 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008959

CATALOG NUMBER: S122DIP-B290D925UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1008959

CATALOG NUMBER: S122DIP-B290D925UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	34	34	34
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	30	29
2	84	77	71	66	75	69	64	60	54	50	47	40	38	36	27	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18
5	64	53	45	40	57	48	41	36	37	33	29	28	25	22	19	17	16
6	59	47	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14
7	54	43	35	30	48	38	32	27	30	26	22	23	19	17	16	14	12
8	50	39	31	26	45	35	28	24	28	23	19	21	17	15	14	12	11
9	47	35	28	23	42	32	25	21	25	21	17	19	16	13	13	11	10
10	44	32	25	21	39	29	23	19	23	19	15	18	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7280	7280	7280
5°	7292	6938	6890
10°	7232	6622	6491
15°	7127	6304	6072
20°	6983	5958	5675
25°	6840	5595	5278
30°	6661	5255	4863
35°	6491	4896	4455
40°	6282	4542	4069
45°	6074	4191	3690
50°	5847	3833	3296
55°	5609	3451	2925
60°	5341	3037	2537
65°	5044	2618	2132
70°	4673	2156	1721
75°	4156	1663	1328
80°	3529	1131	856
85°	2557	524	364

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6074 cd/sqm

TEST NUMBER: P1008959

CATALOG NUMBER: S122DIP-B290D925UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.3	1.0
10°-20°	121.8	2.7
20°-30°	179.0	4.0
30°-40°	207.9	4.7
40°-50°	207.6	4.7
50°-60°	181.0	4.1
60°-70°	133.8	3.0
70°-80°	75.7	1.7
80°-90°	23.3	0.5
90°-100°	72.4	1.6
100°-110°	230.3	5.2
110°-120°	394.0	8.9
120°-130°	518.2	11.7
130°-140°	581.7	13.1
140°-150°	570.4	12.8
150°-160°	478.5	10.8
160°-170°	317.3	7.1
170°-180°	110.9	2.5
0°-30°	344.0	7.7
0°-40°	551.9	12.4
0°-60°	940.5	21.1
0°-90°	1173.3	26.4
90°-120°	696.7	15.7
90°-150°	2367.0	53.2
90°-180°	3274.0	73.6
0°-180°	4447.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	460	460	460	460	460	
5°	460	458	453	457	456	44
15°	438	435	429	431	429	123
25°	396	393	385	386	385	182
35°	342	337	330	328	326	213
45°	278	275	268	264	262	215
55°	210	208	202	197	195	188
65°	142	139	135	131	129	140
75°	74	73	71	68	69	79
85°	18	18	17	16	16	20
90°	1	13	35	33	34	4
95°	51	61	63	63	61	57
105°	212	215	217	219	219	224
115°	395	401	399	398	395	391
125°	575	584	581	578	577	514
135°	744	755	757	756	753	575
145°	903	910	916	917	913	564
155°	1033	1036	1038	1044	1040	475
165°	1124	1122	1122	1129	1124	317
175°	1169	1166	1164	1171	1165	111
180°	1171	1171	1171	1171	1171	

TEST NUMBER: P1008959

CATALOG NUMBER: S122DIP-B290D925UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	459.9	459.9	459.9	459.9	459.9
2.5°	462.5	460.3	455.5	459.9	459.0
5°	459.9	458.1	453.2	456.8	455.9
7.5°	456.8	454.1	449.3	452.8	451.9
10°	451.9	448.8	443.5	447.1	445.7
12.5°	445.3	442.6	437.3	439.5	438.7
15°	437.8	435.1	429.4	431.1	428.9
17.5°	428.5	425.8	420.1	422.3	420.1
20°	418.3	415.7	409.5	410.8	409.0
22.5°	408.1	404.2	398.4	398.4	397.5
25°	396.2	392.7	385.1	386.0	385.1
27.5°	382.9	379.8	374.1	372.8	370.6
30°	369.7	366.1	359.5	358.2	356.4
32.5°	355.5	352.9	345.8	343.1	341.4
35°	341.8	337.4	330.3	327.7	325.5
37.5°	326.3	322.4	315.3	312.2	310.0
40°	310.4	306.9	299.8	295.8	294.1
42.5°	294.9	291.4	284.3	279.9	277.3
45°	278.1	275.0	268.4	263.5	261.8
47.5°	261.8	258.7	251.6	246.7	244.1
50°	244.5	242.3	236.1	229.9	227.7
52.5°	227.7	224.6	218.9	214.0	210.9
55°	210.5	207.8	202.5	197.2	195.0
57.5°	193.2	191.0	185.3	180.0	178.2
60°	176.0	174.2	168.0	163.2	161.8
62.5°	159.2	156.1	151.7	147.2	145.5
65°	141.9	139.3	134.9	130.9	128.7
67.5°	124.3	122.0	118.1	115.0	113.2
70°	107.9	106.1	102.1	99.1	97.3
72.5°	91.1	89.3	87.1	84.0	82.7
75°	74.3	73.4	71.2	68.5	69.4
77.5°	59.3	57.5	56.6	55.3	53.9
80°	44.2	43.8	42.9	41.6	40.7
82.5°	30.1	30.1	29.6	27.9	27.9
85°	18.1	17.7	17.2	15.9	15.5
87.5°	8.0	7.1	6.2	4.9	4.4
90°	1.0	12.8	34.6	32.6	33.6
92.5°	21.7	29.6	30.6	31.6	31.6
95°	51.4	61.3	63.2	63.2	61.3
97.5°	86.0	94.9	98.8	98.8	98.8
100°	125.5	133.4	136.4	136.4	135.4
102.5°	167.0	172.9	176.9	177.9	176.9
105°	212.4	215.4	217.4	219.4	219.4
107.5°	257.9	261.9	261.9	262.8	257.9
110°	301.4	307.3	307.3	307.3	304.3

TEST NUMBER: P1008959

CATALOG NUMBER: S122DIP-B290D925UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	348.8	354.7	353.7	350.8	348.8
115°	395.2	401.2	399.2	398.2	395.2
117.5°	441.7	449.6	444.7	441.7	438.7
120°	488.1	496.0	488.1	488.1	485.2
122.5°	530.6	540.5	535.6	532.6	530.6
125°	575.1	584.0	581.0	578.0	577.1
127.5°	618.6	629.4	625.5	621.5	618.6
130°	659.1	671.9	669.9	668.0	664.0
132.5°	704.5	714.4	715.4	710.5	707.5
135°	744.1	754.9	756.9	755.9	752.9
137.5°	787.5	796.4	798.4	797.4	793.5
140°	826.1	835.0	839.9	839.9	835.9
142.5°	865.6	874.5	877.4	878.4	874.5
145°	903.1	910.1	916.0	917.0	913.0
147.5°	936.7	945.6	949.6	951.6	947.6
150°	971.3	977.2	981.2	984.2	981.2
152.5°	1002.0	1007.9	1012.8	1016.8	1012.8
155°	1032.6	1035.5	1038.5	1043.5	1040.5
157.5°	1059.3	1061.2	1063.2	1070.1	1065.2
160°	1083.0	1085.0	1085.9	1091.9	1087.9
162.5°	1104.7	1104.7	1105.7	1112.6	1107.7
165°	1123.5	1122.5	1122.5	1129.4	1124.5
167.5°	1140.3	1137.3	1137.3	1144.2	1139.3
170°	1153.1	1150.2	1149.2	1156.1	1150.2
172.5°	1162.0	1159.1	1158.1	1165.0	1159.1
175°	1168.9	1166.0	1164.0	1170.9	1165.0
177.5°	1172.9	1169.9	1168.0	1173.9	1168.0
180°	1170.9	1170.9	1170.9	1170.9	1170.9

(END OF REPORT)