

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008255

Luminaire Tested: S122DIP-B865D530UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008255
REPORT IS A COMBINATION OF REPORTS P984853 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D530UB2750-4F0-XX-W2A-D_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5593.0 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008255

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008255

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	97	92	88	84	90	86	82	78	73	70	67	62	60	57	51	50	48
2	88	80	73	67	81	74	68	63	63	59	55	53	50	47	44	42	39
3	80	69	61	55	74	64	57	52	55	50	45	47	42	39	39	35	33
4	73	61	53	46	67	57	49	43	49	43	38	41	37	33	34	31	28
5	67	54	46	39	61	50	43	37	43	37	32	37	32	28	31	27	24
6	61	49	40	34	57	45	37	32	39	33	28	33	28	24	28	24	21
7	57	44	35	29	52	41	33	28	35	29	25	30	25	21	25	21	18
8	53	40	32	26	49	37	30	25	32	26	22	27	23	19	23	19	16
9	49	36	28	23	45	34	27	22	29	24	19	25	20	17	21	17	15
10	46	33	26	21	42	31	24	20	27	21	17	23	19	15	20	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14408	14408	14408
5°	14473	13793	13716
10°	14375	13315	13121
15°	14172	12822	12511
20°	13917	12303	11934
25°	13665	11806	11409
30°	13310	11300	10889
35°	12952	10814	10507
40°	12575	10392	10129
45°	12215	10011	9799
50°	11830	9659	9472
55°	11423	9285	9140
60°	10927	8895	8791
65°	10409	8448	8389
70°	9826	7969	7957
75°	9079	7486	7549
80°	7896	6986	7127
85°	6710	6516	6763

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12215 cd/sqm

TEST NUMBER: P1008255

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.3	1.5
10°-20°	247.5	4.4
20°-30°	375.0	6.7
30°-40°	456.6	8.2
40°-50°	491.3	8.8
50°-60°	477.1	8.5
60°-70°	416.7	7.4
70°-80°	320.7	5.7
80°-90°	216.1	3.9
90°-100°	172.0	3.1
100°-110°	197.1	3.5
110°-120°	307.1	5.5
120°-130°	430.6	7.7
130°-140°	431.8	7.7
140°-150°	388.6	6.9
150°-160°	310.2	5.5
160°-170°	199.9	3.6
170°-180°	68.8	1.2
0°-30°	708.7	12.7
0°-40°	1165.3	20.8
0°-60°	2133.7	38.1
0°-90°	3087.1	55.2
90°-120°	676.1	12.1
90°-150°	1927.1	34.5
90°-180°	2506.0	44.8
0°-180°	5593.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	910	910	910	910	910	
5°	913	909	901	909	908	87
15°	871	873	873	885	884	245
25°	792	801	813	828	832	364
35°	682	704	730	758	768	426
45°	559	595	641	682	695	432
55°	429	476	545	592	609	383
65°	293	358	435	489	506	291
75°	162	236	320	377	394	172
85°	48	129	214	269	288	50
90°	14	96	185	240	257	11
95°	45	89	172	225	240	49
105°	166	220	145	197	214	177
115°	306	329	402	199	176	301
125°	428	435	487	526	539	382
135°	527	536	554	587	596	408
145°	610	610	619	630	634	382
155°	672	667	674	677	672	310
165°	708	705	706	710	706	200
175°	724	721	722	725	720	69
180°	723	723	723	723	723	

TEST NUMBER: P1008255

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	910.2	910.2	910.2	910.2	910.2
2.5°	916.8	912.8	903.6	910.2	907.6
5°	912.8	908.9	901.0	908.9	907.6
7.5°	906.2	903.6	897.0	906.2	904.9
10°	898.3	895.7	891.7	902.3	901.0
12.5°	885.1	886.5	883.8	894.4	893.1
15°	870.6	873.3	873.3	885.1	883.8
17.5°	852.2	857.4	861.4	873.3	873.3
20°	833.7	840.3	845.6	860.1	860.1
22.5°	813.9	821.8	829.7	844.2	846.9
25°	791.5	800.7	812.6	828.4	832.4
27.5°	765.1	779.6	792.8	812.6	815.2
30°	738.7	755.9	773.0	794.1	798.1
32.5°	709.7	729.5	750.6	775.6	783.6
35°	682.0	704.4	729.5	758.5	767.7
37.5°	651.6	676.7	708.4	740.0	749.3
40°	621.3	650.3	685.9	720.2	732.1
42.5°	592.3	621.3	663.5	701.8	713.6
45°	559.3	594.9	641.1	682.0	695.2
47.5°	527.7	565.9	618.7	660.9	675.4
50°	494.7	535.6	594.9	639.8	654.3
52.5°	463.0	506.5	569.9	616.0	631.9
55°	428.7	476.2	544.8	592.3	609.4
57.5°	395.7	448.5	517.1	568.5	585.7
60°	360.1	416.8	492.0	542.2	560.6
62.5°	328.5	387.8	463.0	517.1	534.2
65°	292.8	357.5	435.3	489.4	506.5
67.5°	261.2	328.5	407.6	461.7	480.2
70°	226.9	295.5	377.3	434.0	449.8
72.5°	195.2	266.5	349.6	405.0	424.8
75°	162.3	236.1	320.5	377.3	394.4
77.5°	130.6	207.1	292.8	349.6	368.0
80°	98.9	179.4	265.1	320.5	339.0
82.5°	72.6	151.7	238.8	294.2	311.3
85°	47.5	129.3	213.7	269.1	287.6
87.5°	29.0	108.2	192.6	246.7	263.8
90°	13.7	96.0	184.6	240.0	256.8
92.5°	25.0	92.8	174.9	227.3	243.6
95°	44.6	89.3	172.1	224.8	240.2
97.5°	70.4	84.3	169.2	219.5	235.9
100°	101.8	78.9	161.7	214.7	230.2
102.5°	135.0	177.4	153.6	206.8	222.9
105°	165.6	219.6	145.3	197.3	213.8
107.5°	202.7	247.5	137.1	187.8	204.4
110°	237.0	274.3	187.8	177.7	194.3



TEST NUMBER: P1008255

CATALOG NUMBER: S122DIP-B865D530UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	270.4	300.9	352.8	169.6	185.6
115°	306.0	329.4	401.8	199.2	176.1
117.5°	335.5	356.5	420.8	385.6	261.8
120°	370.1	383.1	445.3	488.5	432.4
122.5°	399.3	409.0	468.3	507.0	519.4
125°	427.8	434.6	486.8	526.0	539.4
127.5°	454.9	461.0	504.4	542.6	555.1
130°	480.6	487.6	521.1	558.5	568.5
132.5°	506.7	512.2	537.8	572.8	582.9
135°	527.4	535.7	553.7	586.6	596.1
137.5°	550.4	556.7	568.5	598.8	606.5
140°	572.9	575.8	584.1	609.9	615.3
142.5°	591.7	594.1	600.9	620.8	624.8
145°	610.3	609.8	618.6	630.2	634.2
147.5°	627.5	626.0	634.9	638.8	640.7
150°	644.3	640.6	649.0	652.1	649.5
152.5°	658.4	654.2	662.0	665.2	661.5
155°	672.0	667.3	673.6	676.7	672.5
157.5°	683.0	678.8	683.5	687.1	683.0
160°	692.4	689.2	692.4	695.5	691.9
162.5°	700.7	697.6	700.2	703.9	699.2
165°	708.1	704.9	706.5	710.2	706.5
167.5°	713.8	710.7	712.2	715.9	711.2
170°	718.5	715.4	716.4	720.1	715.4
172.5°	721.7	718.5	719.6	723.2	718.5
175°	724.3	720.6	721.7	725.3	720.1
177.5°	725.3	721.7	722.2	725.8	721.1
180°	722.7	722.7	722.7	722.7	722.7

(END OF REPORT)