

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008274

Luminaire Tested: S122DIP-B865D725UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008274
REPORT IS A COMBINATION OF REPORTS P984917 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D725UB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6268.0 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008274

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1008274

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	51
2	90	83	76	71	83	77	72	67	66	62	59	56	53	51	47	45	43
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	39	37
4	75	64	56	50	70	60	53	47	52	46	42	45	40	37	38	34	32
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	30	28
6	64	51	43	37	59	48	41	36	42	36	32	36	32	28	31	27	24
7	59	47	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21528	21528	21528
5°	21563	20520	20374
10°	21386	19585	19195
15°	21074	18642	17956
20°	20651	17617	16783
25°	20229	16547	15611
30°	19697	15541	14381
35°	19197	14479	13172
40°	18579	13433	12031
45°	17963	12395	10911
50°	17292	11337	9750
55°	16587	10207	8649
60°	15794	8984	7505
65°	14924	7740	6302
70°	13819	6380	5090
75°	12290	4917	3930
80°	10443	3341	2529
85°	7571	1555	1077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17963 cd/sqm

TEST NUMBER: P1008274

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.0	2.0
10°-20°	360.1	5.7
20°-30°	529.2	8.4
30°-40°	614.7	9.8
40°-50°	613.9	9.8
50°-60°	535.3	8.5
60°-70°	395.7	6.3
70°-80°	223.9	3.6
80°-90°	60.8	1.0
90°-100°	31.6	0.5
100°-110°	117.7	1.9
110°-120°	312.1	5.0
120°-130°	517.6	8.3
130°-140°	549.8	8.8
140°-150°	511.0	8.2
150°-160°	410.8	6.6
160°-170°	264.7	4.2
170°-180°	91.1	1.5
0°-30°	1017.4	16.2
0°-40°	1632.1	26.0
0°-60°	2781.3	44.4
0°-90°	3461.7	55.2
90°-120°	461.3	7.4
90°-150°	2039.7	32.5
90°-180°	2806.0	44.8
0°-180°	6268.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1360	1360	1360	1360	1360	
5°	1360	1355	1340	1351	1348	129
15°	1295	1287	1270	1275	1268	365
25°	1172	1161	1139	1142	1139	539
35°	1011	998	977	969	962	631
45°	822	813	794	779	774	635
55°	622	615	599	583	577	557
65°	420	412	399	387	380	415
75°	220	217	210	203	205	234
85°	54	52	51	47	46	60
90°	1	8	14	17	19	6
95°	45	22	27	30	30	53
105°	211	231	42	50	53	225
115°	398	410	427	107	57	392
125°	563	572	585	590	592	502
135°	697	708	714	721	720	538
145°	808	808	819	824	821	506
155°	890	884	892	896	891	410
165°	938	934	936	941	936	265
175°	959	954	956	961	954	91
180°	957	957	957	957	957	

TEST NUMBER: P1008274

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1360.0	1360.0	1360.0	1360.0	1360.0
2.5°	1367.8	1361.3	1346.9	1360.0	1357.4
5°	1360.0	1354.7	1340.4	1350.8	1348.2
7.5°	1350.8	1343.0	1328.6	1339.1	1336.4
10°	1336.4	1327.3	1311.6	1322.1	1318.1
12.5°	1316.8	1309.0	1293.3	1299.8	1297.2
15°	1294.6	1286.7	1269.7	1275.0	1268.4
17.5°	1267.1	1259.3	1242.3	1248.8	1242.3
20°	1237.1	1229.2	1210.9	1214.8	1209.6
22.5°	1207.0	1195.2	1178.2	1178.2	1175.6
25°	1171.7	1161.2	1139.0	1141.6	1139.0
27.5°	1132.4	1123.3	1106.3	1102.4	1095.8
30°	1093.2	1082.8	1063.1	1059.2	1054.0
32.5°	1051.4	1043.5	1022.6	1014.8	1009.5
35°	1010.8	997.8	976.8	969.0	962.4
37.5°	965.1	953.3	932.4	923.2	916.7
40°	918.0	907.5	886.6	874.8	869.6
42.5°	872.2	861.8	840.8	827.8	819.9
45°	822.5	813.4	793.8	779.4	774.1
47.5°	774.1	765.0	744.1	729.7	721.8
50°	723.1	716.6	698.3	680.0	673.5
52.5°	673.5	664.3	647.3	632.9	623.8
55°	622.5	614.6	598.9	583.2	576.7
57.5°	571.5	564.9	547.9	532.2	527.0
60°	520.5	515.2	496.9	482.5	478.6
62.5°	470.8	461.6	448.5	435.5	430.2
65°	419.8	411.9	398.8	387.1	380.5
67.5°	367.5	360.9	349.1	340.0	334.8
70°	319.1	313.8	302.1	292.9	287.7
72.5°	269.4	264.1	257.6	248.5	244.5
75°	219.7	217.1	210.5	202.7	205.3
77.5°	175.2	170.0	167.4	163.5	159.5
80°	130.8	129.5	126.8	122.9	120.3
82.5°	88.9	88.9	87.6	82.4	82.4
85°	53.6	52.3	51.0	47.1	45.8
87.5°	23.5	20.9	18.3	14.4	13.1
90°	0.7	8.3	13.9	17.3	18.7
92.5°	17.3	14.5	16.6	18.0	18.7
95°	45.0	22.2	27.0	30.5	29.8
97.5°	81.0	24.2	35.3	37.4	38.1
100°	122.6	27.7	39.5	45.0	46.4
102.5°	168.3	166.9	40.9	48.5	50.6
105°	210.6	231.3	42.3	49.9	52.6
107.5°	259.7	277.1	43.6	51.3	54.0
110°	306.8	321.4	121.2	51.9	54.7

TEST NUMBER: P1008274

CATALOG NUMBER: S122DIP-B865D725UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	351.2	363.6	351.9	53.3	55.4
115°	398.3	410.1	427.4	106.7	56.8
117.5°	439.1	453.0	464.8	365.7	184.2
120°	484.9	495.2	507.7	516.0	422.5
122.5°	523.6	534.7	548.6	552.7	553.4
125°	563.1	572.1	585.3	590.1	592.2
127.5°	599.1	608.8	619.2	626.2	626.9
130°	633.1	644.2	651.8	659.4	658.7
132.5°	667.7	676.7	684.3	690.6	689.9
135°	696.8	707.9	714.1	721.1	719.7
137.5°	727.3	735.6	742.5	749.5	747.4
140°	757.1	762.6	770.2	776.5	773.0
142.5°	782.0	786.9	795.9	801.4	797.9
145°	808.3	807.6	819.4	824.3	820.8
147.5°	831.2	829.1	840.9	844.3	841.6
150°	853.3	848.5	859.6	863.7	860.3
152.5°	872.1	866.5	876.9	881.1	876.2
155°	890.1	883.8	892.1	896.3	890.8
157.5°	904.6	899.1	905.3	910.1	904.6
160°	917.1	912.9	917.1	921.2	916.4
162.5°	928.2	924.0	927.5	932.3	926.1
165°	937.9	933.7	935.8	940.6	935.8
167.5°	945.5	941.3	943.4	948.2	942.0
170°	951.7	947.6	948.9	953.8	947.6
172.5°	955.9	951.7	953.1	957.9	951.7
175°	959.3	954.5	955.9	960.7	953.8
177.5°	960.7	955.9	956.6	961.4	955.2
180°	957.2	957.2	957.2	957.2	957.2

(END OF REPORT)