

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008290

Luminaire Tested: S122DIP-B865D925UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008290
REPORT IS A COMBINATION OF REPORTS P984978 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D925UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7155.0 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008290

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008290

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49		
1	98	93	89	86	90	86	83	80	72	70	68	60	58	57	49	48	46	41		
2	89	81	75	70	82	75	70	65	64	60	56	53	50	47	43	41	39	34		
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33	29		
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29	25		
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	27	25	22		
6	63	51	42	37	58	47	40	35	40	34	30	34	29	26	28	25	22	19		
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17		
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15		
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	21	18	16	14		
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21715	21715	21715
5°	21750	20698	20551
10°	21572	19755	19363
15°	21257	18804	18112
20°	20830	17770	16928
25°	20403	16691	15747
30°	19868	15677	14505
35°	19364	14605	13287
40°	18739	13549	12135
45°	18121	12501	11007
50°	17443	11436	9834
55°	16728	10296	8724
60°	15931	9062	7571
65°	15052	7808	6357
70°	13936	6435	5134
75°	12396	4961	3964
80°	10531	3370	2550
85°	7642	1567	1086

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18121 cd/sqm

TEST NUMBER: P1008290

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.1	1.8
10°-20°	363.3	5.1
20°-30°	533.8	7.5
30°-40°	620.0	8.7
40°-50°	619.2	8.7
50°-60°	540.0	7.5
60°-70°	399.1	5.6
70°-80°	225.8	3.2
80°-90°	61.8	0.9
90°-100°	41.2	0.6
100°-110°	153.6	2.1
110°-120°	407.3	5.7
120°-130°	675.6	9.4
130°-140°	717.6	10.0
140°-150°	666.9	9.3
150°-160°	536.2	7.5
160°-170°	345.5	4.8
170°-180°	118.9	1.7
0°-30°	1026.2	14.3
0°-40°	1646.2	23.0
0°-60°	2805.4	39.2
0°-90°	3492.2	48.8
90°-120°	602.1	8.4
90°-150°	2662.2	37.2
90°-180°	3663.0	51.2
0°-180°	7155.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1279	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	985	977	971	637
45°	830	820	801	786	781	640
55°	628	620	604	588	582	561
65°	423	416	402	390	384	419
75°	222	219	212	204	207	236
85°	54	53	51	48	46	60
90°	1	11	18	23	24	7
95°	59	29	35	40	39	70
105°	275	302	55	65	69	294
115°	520	535	558	139	74	512
125°	735	747	764	770	773	656
135°	910	924	932	941	939	703
145°	1055	1054	1070	1076	1071	660
155°	1162	1154	1164	1170	1163	535
165°	1224	1219	1221	1228	1221	346
175°	1252	1246	1248	1254	1245	119
180°	1249	1249	1249	1249	1249	

TEST NUMBER: P1008290

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1371.8	1371.8	1371.8	1371.8	1371.8
2.5°	1379.7	1373.1	1358.6	1371.8	1369.1
5°	1371.8	1366.5	1352.0	1362.5	1359.9
7.5°	1362.5	1354.6	1340.1	1350.7	1348.0
10°	1348.0	1338.8	1323.0	1333.5	1329.6
12.5°	1328.2	1320.3	1304.5	1311.1	1308.5
15°	1305.8	1297.9	1280.8	1286.0	1279.4
17.5°	1278.1	1270.2	1253.1	1259.7	1253.1
20°	1247.8	1239.9	1221.4	1225.4	1220.1
22.5°	1217.4	1205.6	1188.4	1188.4	1185.8
25°	1181.8	1171.3	1148.9	1151.5	1148.9
27.5°	1142.3	1133.0	1115.9	1111.9	1105.3
30°	1102.7	1092.1	1072.4	1068.4	1063.1
32.5°	1060.5	1052.6	1031.5	1023.6	1018.3
35°	1019.6	1006.4	985.3	977.4	970.8
37.5°	973.4	961.6	940.5	931.2	924.6
40°	925.9	915.4	894.3	882.4	877.1
42.5°	879.8	869.2	848.1	834.9	827.0
45°	829.7	820.4	800.6	786.1	780.9
47.5°	780.9	771.6	750.5	736.0	728.1
50°	729.4	722.8	704.4	685.9	679.3
52.5°	679.3	670.1	652.9	638.4	629.2
55°	627.8	619.9	604.1	588.3	581.7
57.5°	576.4	569.8	552.7	536.8	531.6
60°	525.0	519.7	501.2	486.7	482.8
62.5°	474.8	465.6	452.4	439.2	434.0
65°	423.4	415.5	402.3	390.4	383.8
67.5°	370.6	364.0	352.2	342.9	337.7
70°	321.8	316.6	304.7	295.5	290.2
72.5°	271.7	266.4	259.8	250.6	246.7
75°	221.6	219.0	212.4	204.4	207.1
77.5°	176.7	171.5	168.8	164.9	160.9
80°	131.9	130.6	127.9	124.0	121.3
82.5°	89.7	89.7	88.4	83.1	83.1
85°	54.1	52.8	51.4	47.5	46.2
87.5°	23.7	21.1	18.5	14.5	13.2
90°	0.9	10.8	18.1	22.6	24.4
92.5°	22.6	19.0	21.7	23.5	24.4
95°	58.8	28.9	35.3	39.8	38.9
97.5°	105.8	31.6	46.1	48.8	49.7
100°	160.0	36.2	51.5	58.8	60.6
102.5°	219.7	217.9	53.3	63.3	66.0
105°	274.8	302.0	55.1	65.1	68.7
107.5°	339.0	361.6	57.0	66.9	70.5
110°	400.5	419.5	158.2	67.8	71.4

TEST NUMBER: P1008290

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	458.4	474.6	459.3	69.6	72.3
115°	519.8	535.2	557.8	139.2	74.1
117.5°	573.2	591.2	606.6	477.3	240.5
120°	632.8	646.4	662.7	673.5	551.5
122.5°	683.5	697.9	716.0	721.4	722.3
125°	735.0	746.7	763.9	770.3	773.0
127.5°	782.0	794.7	808.2	817.3	818.2
130°	826.3	840.8	850.7	860.7	859.8
132.5°	871.5	883.3	893.2	901.3	900.4
135°	909.5	923.9	932.1	941.1	939.3
137.5°	949.3	960.1	969.1	978.2	975.5
140°	988.1	995.4	1005.3	1013.4	1008.9
142.5°	1020.7	1027.0	1038.8	1046.0	1041.5
145°	1055.0	1054.1	1069.5	1075.8	1071.3
147.5°	1084.9	1082.2	1097.5	1102.0	1098.4
150°	1113.8	1107.5	1121.9	1127.4	1122.8
152.5°	1138.2	1131.0	1144.5	1150.0	1143.6
155°	1161.7	1153.6	1164.4	1169.8	1162.6
157.5°	1180.7	1173.5	1181.6	1187.9	1180.7
160°	1197.0	1191.5	1197.0	1202.4	1196.1
162.5°	1211.4	1206.0	1210.5	1216.9	1208.7
165°	1224.1	1218.7	1221.4	1227.7	1221.4
167.5°	1234.0	1228.6	1231.3	1237.6	1229.5
170°	1242.2	1236.7	1238.6	1244.9	1236.7
172.5°	1247.6	1242.2	1244.0	1250.3	1242.2
175°	1252.1	1245.8	1247.6	1253.9	1244.9
177.5°	1253.9	1247.6	1248.5	1254.8	1246.7
180°	1249.4	1249.4	1249.4	1249.4	1249.4

(END OF REPORT)