

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008292

Luminaire Tested: S122DIP-B865D925UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008292
REPORT IS A COMBINATION OF REPORTS P984980 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D925UB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7115.0 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008292

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008292

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55			49
1	98	93	89	86	90	86	83	80	72	70	68	60	58	57	49	48	46			41
2	89	81	75	70	82	75	70	65	64	60	56	53	50	47	43	41	39			34
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33			29
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29			25
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	27	25			22
6	63	51	42	37	58	47	40	35	40	34	30	34	29	26	28	25	22			19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20			17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18			15
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	21	18	16			14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21590	21590	21590
5°	21625	20578	20433
10°	21449	19641	19251
15°	21135	18696	18008
20°	20710	17668	16831
25°	20287	16595	15656
30°	19755	15586	14422
35°	19254	14522	13210
40°	18632	13472	12065
45°	18016	12431	10943
50°	17342	11370	9778
55°	16635	10236	8673
60°	15840	9011	7527
65°	14966	7763	6320
70°	13858	6397	5104
75°	12324	4931	3941
80°	10467	3352	2537
85°	7600	1558	1079

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18016 cd/sqm

TEST NUMBER: P1008292

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	1.8
10°-20°	361.2	5.1
20°-30°	530.8	7.5
30°-40°	616.5	8.7
40°-50°	615.7	8.7
50°-60°	536.9	7.5
60°-70°	396.9	5.6
70°-80°	224.5	3.2
80°-90°	61.4	0.9
90°-100°	41.0	0.6
100°-110°	152.7	2.1
110°-120°	405.1	5.7
120°-130°	671.9	9.4
130°-140°	713.7	10.0
140°-150°	663.3	9.3
150°-160°	533.3	7.5
160°-170°	343.6	4.8
170°-180°	118.3	1.7
0°-30°	1020.3	14.3
0°-40°	1636.8	23.0
0°-60°	2789.4	39.2
0°-90°	3472.2	48.8
90°-120°	598.8	8.4
90°-150°	2647.7	37.2
90°-180°	3643.0	51.2
0°-180°	7115.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1364	1364	1364	1364	1364	
5°	1364	1359	1344	1355	1352	129
15°	1298	1290	1273	1279	1272	366
25°	1175	1165	1142	1145	1142	541
35°	1014	1001	980	972	965	633
45°	825	816	796	782	776	637
55°	624	616	601	585	578	558
65°	421	413	400	388	382	416
75°	220	218	211	203	206	235
85°	54	52	51	47	46	60
90°	1	11	18	22	24	7
95°	58	29	35	40	39	69
105°	273	300	55	65	68	292
115°	517	532	555	138	74	509
125°	731	743	760	766	769	652
135°	904	919	927	936	934	699
145°	1049	1048	1064	1070	1066	656
155°	1155	1147	1158	1164	1156	532
165°	1217	1212	1215	1221	1215	344
175°	1245	1239	1241	1247	1238	119
180°	1243	1243	1243	1243	1243	

TEST NUMBER: P1008292

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1363.9	1363.9	1363.9	1363.9	1363.9
2.5°	1371.8	1365.2	1350.8	1363.9	1361.3
5°	1363.9	1358.7	1344.2	1354.7	1352.1
7.5°	1354.7	1346.9	1332.4	1342.9	1340.3
10°	1340.3	1331.1	1315.4	1325.9	1321.9
12.5°	1320.6	1312.8	1297.0	1303.6	1301.0
15°	1298.3	1290.5	1273.4	1278.7	1272.1
17.5°	1270.8	1262.9	1245.9	1252.4	1245.9
20°	1240.6	1232.8	1214.4	1218.3	1213.1
22.5°	1210.5	1198.7	1181.6	1181.6	1179.0
25°	1175.1	1164.6	1142.3	1144.9	1142.3
27.5°	1135.7	1126.5	1109.5	1105.6	1099.0
30°	1096.4	1085.9	1066.2	1062.3	1057.0
32.5°	1054.4	1046.5	1025.6	1017.7	1012.4
35°	1013.8	1000.6	979.7	971.8	965.2
37.5°	967.9	956.0	935.1	925.9	919.3
40°	920.6	910.1	889.2	877.4	872.1
42.5°	874.7	864.2	843.3	830.1	822.3
45°	824.9	815.7	796.1	781.6	776.4
47.5°	776.4	767.2	746.2	731.8	723.9
50°	725.2	718.7	700.3	682.0	675.4
52.5°	675.4	666.2	649.2	634.7	625.6
55°	624.3	616.4	600.6	584.9	578.3
57.5°	573.1	566.5	549.5	533.8	528.5
60°	522.0	516.7	498.4	483.9	480.0
62.5°	472.1	462.9	449.8	436.7	431.5
65°	421.0	413.1	400.0	388.2	381.6
67.5°	368.5	362.0	350.2	341.0	335.7
70°	320.0	314.7	302.9	293.8	288.5
72.5°	270.2	264.9	258.4	249.2	245.2
75°	220.3	217.7	211.1	203.3	205.9
77.5°	175.7	170.5	167.9	163.9	160.0
80°	131.1	129.8	127.2	123.3	120.7
82.5°	89.2	89.2	87.9	82.6	82.6
85°	53.8	52.5	51.1	47.2	45.9
87.5°	23.6	21.0	18.4	14.4	13.1
90°	0.9	10.8	18.0	22.5	24.3
92.5°	22.5	18.9	21.6	23.4	24.3
95°	58.4	28.8	35.1	39.6	38.7
97.5°	105.2	31.5	45.9	48.6	49.5
100°	159.1	36.0	51.2	58.4	60.2
102.5°	218.5	216.7	53.0	62.9	65.6
105°	273.3	300.3	54.8	64.7	68.3
107.5°	337.2	359.6	56.6	66.5	70.1
110°	398.3	417.2	157.3	67.4	71.0

TEST NUMBER: P1008292

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	455.9	472.0	456.8	69.2	71.9
115°	517.0	532.3	554.8	138.5	73.7
117.5°	570.0	588.0	603.3	474.7	239.2
120°	629.4	642.9	659.1	669.8	548.5
122.5°	679.7	694.1	712.1	717.5	718.4
125°	731.0	742.7	759.8	766.0	768.7
127.5°	777.7	790.3	803.8	812.8	813.7
130°	821.8	836.2	846.1	856.0	855.1
132.5°	866.8	878.4	888.3	896.4	895.5
135°	904.5	918.9	927.0	936.0	934.2
137.5°	944.1	954.9	963.9	972.8	970.1
140°	982.7	989.9	999.8	1007.9	1003.4
142.5°	1015.1	1021.4	1033.1	1040.3	1035.8
145°	1049.3	1048.4	1063.7	1070.0	1065.5
147.5°	1078.9	1076.2	1091.5	1096.0	1092.4
150°	1107.7	1101.4	1115.8	1121.2	1116.7
152.5°	1132.0	1124.8	1138.3	1143.7	1137.4
155°	1155.4	1147.3	1158.1	1163.5	1156.3
157.5°	1174.2	1167.1	1175.1	1181.4	1174.2
160°	1190.4	1185.0	1190.4	1195.8	1189.5
162.5°	1204.8	1199.4	1203.9	1210.2	1202.1
165°	1217.4	1212.0	1214.7	1221.0	1214.7
167.5°	1227.3	1221.9	1224.6	1230.9	1222.8
170°	1235.4	1230.0	1231.8	1238.1	1230.0
172.5°	1240.8	1235.4	1237.2	1243.5	1235.4
175°	1245.3	1239.0	1240.8	1247.1	1238.1
177.5°	1247.1	1240.8	1241.7	1248.0	1239.9
180°	1242.6	1242.6	1242.6	1242.6	1242.6

(END OF REPORT)