

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008318

Luminaire Tested: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008318
REPORT IS A COMBINATION OF REPORTS P987908 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5711.0 lumens
Efficiency: N/A
Efficacy: 74.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64		
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	60	56		
2	94	87	81	76	88	82	77	73	73	69	66	64	61	59	57	54	53	49		
3	86	77	70	65	81	73	67	62	65	60	57	58	54	51	51	48	46	43		
4	80	69	62	56	75	66	59	54	59	53	49	52	48	45	47	43	41	38		
5	74	62	55	49	69	59	52	47	53	48	43	48	43	40	43	39	36	34		
6	68	57	49	43	64	54	47	42	49	43	39	44	39	36	39	35	33	30		
7	64	52	44	39	60	49	42	37	45	39	35	40	36	32	36	32	30	27		
8	59	47	40	35	56	45	38	34	41	35	31	37	33	29	33	30	27	25		
9	56	44	36	31	52	42	35	30	38	32	29	34	30	27	31	27	25	23		
10	52	40	33	29	49	39	32	28	35	30	26	32	28	24	29	25	23	21		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	33644	33644	33644	33644
5°	33722	35735	33839	28548
10°	33352	37771	33587	23575
15°	32627	37783	33181	17710
20°	31757	31232	32448	14611
25°	30701	19515	31364	12430
30°	29353	12494	30153	10701
35°	27714	9603	28613	9158
40°	25888	8071	26993	8010
45°	23934	6870	24935	6725
50°	21933	5837	22959	5815
55°	19718	5072	20781	5006
60°	17749	3869	18689	3822
65°	15908	2912	16854	3303
70°	13880	2326	14967	2691
75°	11731	1782	12805	2035
80°	9317	1211	10020	1335
85°	6470	626	7091	661

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 30776 cd/sqm

TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.6	3.5
10°-20°	562.7	9.9
20°-30°	724.2	12.7
30°-40°	687.1	12.0
40°-50°	588.8	10.3
50°-60°	448.4	7.9
60°-70°	282.8	5.0
70°-80°	141.1	2.5
80°-90°	37.5	0.7
90°-100°	22.9	0.4
100°-110°	85.4	1.5
110°-120°	226.5	4.0
120°-130°	375.7	6.6
130°-140°	399.0	7.0
140°-150°	370.9	6.5
150°-160°	298.2	5.2
160°-170°	192.1	3.4
170°-180°	66.1	1.2
0°-30°	1488.5	26.1
0°-40°	2175.6	38.1
0°-60°	3212.9	56.3
0°-90°	3674.2	64.3
90°-120°	334.8	5.9
90°-150°	1480.4	25.9
90°-180°	2037.0	35.7
0°-180°	5711.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2125	2125	2125	2125	2125	
5°	2127	2365	2134	1889	2127	202
15°	2004	2669	2038	1251	2004	564
25°	1778	1424	1817	907	1778	817
35°	1459	702	1507	669	1459	913
45°	1096	487	1142	477	1096	846
55°	740	338	780	334	740	667
65°	448	176	474	199	448	444
75°	210	93	229	106	210	227
85°	46	27	50	28	46	52
90°	0	14	0	14	0	5
95°	33	22	33	22	33	39
105°	153	38	153	38	153	163
115°	289	41	289	41	289	285
125°	409	430	409	430	409	365
135°	506	522	506	522	506	391
145°	587	596	587	596	587	367
155°	646	646	646	646	646	298
165°	681	679	681	679	681	192
175°	696	692	696	692	696	66
180°	695	695	695	695	695	

TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2138.7	2147.6	2152.0	2157.9	2171.2	2180.1	2193.4	2196.3	2194.8	2200.8	2184.5
5°	2126.9	2146.1	2163.8	2178.6	2202.2	2217.0	2233.2	2252.4	2256.9	2279.0	2265.7
7.5°	2110.7	2138.7	2163.8	2193.4	2228.8	2248.0	2273.1	2302.7	2316.0	2342.5	2349.9
10°	2084.1	2123.9	2166.8	2197.8	2246.5	2280.5	2304.1	2351.4	2382.4	2422.3	2416.4
12.5°	2041.2	2092.9	2150.5	2202.2	2265.7	2287.9	2332.2	2380.9	2420.8	2457.8	2490.2
15°	2004.3	2063.4	2126.9	2190.4	2262.8	2304.1	2348.5	2412.0	2454.8	2519.8	2547.9
17.5°	1954.1	2029.4	2104.7	2175.6	2261.3	2308.6	2363.2	2425.3	2488.8	2550.8	2573.0
20°	1902.4	1983.6	2064.9	2160.9	2258.4	2304.1	2360.3	2437.1	2499.1	2547.9	2547.9
22.5°	1840.4	1939.3	2032.4	2123.9	2230.3	2296.8	2354.4	2444.5	2488.8	2499.1	2459.2
25°	1778.3	1877.3	1979.2	2092.9	2214.0	2273.1	2338.1	2422.3	2437.1	2395.7	2292.3
27.5°	1704.5	1815.3	1930.5	2053.1	2180.1	2253.9	2313.0	2369.1	2341.1	2230.3	2069.3
30°	1629.1	1748.8	1878.8	1995.4	2149.1	2217.0	2267.2	2283.5	2194.8	2014.6	1806.4
32.5°	1550.9	1667.6	1804.9	1945.2	2100.3	2165.3	2197.8	2155.0	1992.5	1765.0	1511.0
35°	1459.3	1590.7	1734.0	1880.2	2033.9	2082.6	2101.8	1996.9	1788.7	1494.7	1242.2
37.5°	1376.6	1508.0	1661.6	1810.8	1960.0	1986.6	1967.4	1803.4	1539.1	1248.1	1001.4
40°	1279.1	1419.4	1570.1	1737.0	1859.6	1866.9	1819.7	1607.0	1279.1	1005.8	853.7
42.5°	1189.0	1330.8	1481.4	1651.3	1744.4	1719.2	1655.7	1376.6	1067.9	867.0	744.4
45°	1095.9	1230.4	1392.8	1543.5	1609.9	1550.9	1454.9	1158.0	896.5	745.9	651.4
47.5°	1005.8	1131.4	1292.4	1437.1	1449.0	1382.5	1268.8	970.4	776.9	655.8	579.0
50°	917.2	1042.8	1193.4	1313.1	1301.3	1209.7	1081.2	843.4	675.0	579.0	515.5
52.5°	828.6	942.3	1088.6	1183.1	1132.9	1044.3	917.2	714.9	589.3	505.1	456.4
55°	740.0	846.3	971.9	1050.2	970.4	868.5	778.4	613.0	511.0	443.1	406.2
57.5°	666.1	750.3	865.5	912.8	816.8	737.0	658.7	527.3	443.1	394.4	351.5
60°	584.9	661.7	756.2	784.3	685.3	620.3	553.9	446.1	379.6	336.8	308.7
62.5°	515.5	579.0	651.4	651.4	564.2	515.5	465.3	373.7	319.0	285.1	271.8
65°	447.5	493.3	545.0	539.1	465.3	422.4	382.5	308.7	267.3	243.7	230.4
67.5°	381.1	416.5	450.5	429.8	376.6	339.7	302.8	249.6	221.6	205.3	187.6
70°	320.5	348.6	366.3	347.1	293.9	262.9	236.3	200.9	178.7	158.0	147.7
72.5°	268.8	280.6	286.5	262.9	218.6	200.9	181.7	156.6	137.4	127.0	124.1
75°	209.7	220.1	215.6	197.9	161.0	147.7	132.9	115.2	110.8	104.9	101.9
77.5°	163.9	163.9	156.6	140.3	115.2	104.9	99.0	90.1	85.7	84.2	81.2
80°	116.7	115.2	110.8	93.1	78.3	72.4	72.4	66.5	65.0	62.0	62.0
82.5°	76.8	76.8	70.9	56.1	51.7	50.2	48.7	45.8	45.8	44.3	44.3
85°	45.8	42.8	35.4	31.0	29.5	29.5	28.1	26.6	28.1	26.6	26.6
87.5°	20.7	16.2	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8
90°	0.5	1.7	2.9	4.2	5.4	6.0	6.5	7.4	8.3	9.2	10.1
92.5°	12.6	12.2	11.7	11.3	10.8	10.6	10.8	11.1	11.4	11.8	12.1
95°	32.7	29.0	25.3	21.6	17.9	16.1	16.5	17.3	18.0	18.8	19.6
97.5°	58.8	49.6	40.5	31.3	22.2	17.6	18.5	20.3	22.0	23.8	25.6
100°	89.0	73.7	58.4	43.1	27.8	20.1	21.1	23.0	24.9	26.8	28.7
102.5°	122.2	122.0	121.8	121.5	121.3	121.2	111.0	90.7	70.4	50.0	29.7
105°	152.8	156.2	159.5	162.9	166.2	167.9	152.7	122.2	91.7	61.2	30.7
107.5°	188.5	191.3	194.1	196.9	199.7	201.1	182.3	144.6	107.0	69.3	31.7
110°	222.7	225.1	227.4	229.8	232.1	233.3	217.2	184.9	152.6	120.3	88.0

TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	254.9	256.9	258.9	260.9	262.9	263.9	263.0	261.1	259.2	257.3	255.4
115°	289.1	291.0	292.9	294.8	296.7	297.6	299.0	301.8	304.6	307.4	310.2
117.5°	318.7	320.9	323.2	325.4	327.7	328.8	329.7	331.6	333.5	335.4	337.3
120°	351.9	353.6	355.2	356.9	358.6	359.4	360.4	362.4	364.5	366.5	368.5
122.5°	380.1	381.9	383.7	385.4	387.2	388.1	389.2	391.5	393.7	396.0	398.2
125°	408.7	410.1	411.6	413.0	414.5	415.2	416.3	418.4	420.5	422.7	424.8
127.5°	434.9	436.5	438.0	439.6	441.1	441.9	442.7	444.4	446.1	447.7	449.4
130°	459.5	461.3	463.1	464.8	466.6	467.5	468.1	469.4	470.6	471.9	473.1
132.5°	484.6	486.1	487.5	489.0	490.5	491.2	491.8	493.0	494.3	495.5	496.7
135°	505.7	507.5	509.3	511.1	512.9	513.8	514.3	515.3	516.3	517.3	518.3
137.5°	527.9	529.2	530.6	531.9	533.2	533.9	534.5	535.6	536.7	537.8	538.9
140°	549.5	550.4	551.3	552.2	553.1	553.5	554.1	555.3	556.6	557.8	559.0
142.5°	567.6	568.4	569.2	569.9	570.7	571.1	571.8	573.3	574.7	576.2	577.6
145°	586.7	586.6	586.5	586.4	586.3	586.2	587.1	589.0	590.9	592.8	594.7
147.5°	603.3	603.0	602.6	602.3	602.0	601.8	602.7	604.6	606.5	608.4	610.3
150°	619.3	618.5	617.7	617.0	616.2	615.8	616.7	618.5	620.3	622.1	623.9
152.5°	632.9	632.0	631.1	630.2	629.3	628.9	629.7	631.4	633.1	634.7	636.4
155°	646.0	645.0	644.0	643.0	642.0	641.5	642.2	643.5	644.8	646.2	647.5
157.5°	656.5	655.6	654.7	653.8	652.9	652.5	653.0	654.0	655.1	656.1	657.1
160°	665.6	664.9	664.3	663.6	662.9	662.6	662.9	663.6	664.3	664.9	665.6
162.5°	673.6	672.9	672.3	671.6	670.9	670.6	670.9	671.4	672.0	672.5	673.1
165°	680.7	680.0	679.4	678.7	678.0	677.7	677.9	678.2	678.5	678.9	679.2
167.5°	686.2	685.5	684.9	684.2	683.5	683.2	683.4	683.7	684.0	684.4	684.7
170°	690.7	690.0	689.4	688.7	688.0	687.7	687.8	688.0	688.3	688.5	688.7
172.5°	693.7	693.0	692.4	691.7	691.0	690.7	690.8	691.0	691.3	691.5	691.7
175°	696.3	695.5	694.7	693.9	693.1	692.7	692.8	693.0	693.3	693.5	693.7
177.5°	697.3	696.5	695.7	694.9	694.1	693.7	693.8	693.9	694.0	694.2	694.3
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2200.8	2203.7	2208.1	2228.8	2231.8	2237.7	2234.7	2234.7	2236.2	2233.2	2234.7
5°	2295.3	2299.7	2321.9	2347.0	2352.9	2347.0	2354.4	2364.7	2364.7	2364.7	2361.7
7.5°	2383.9	2400.2	2425.3	2462.2	2469.6	2477.0	2490.2	2481.4	2484.3	2497.6	2493.2
10°	2469.6	2493.2	2521.3	2552.3	2568.5	2578.9	2584.8	2598.1	2629.1	2593.6	2606.9
12.5°	2550.8	2584.8	2614.3	2648.3	2660.1	2673.4	2677.8	2689.6	2689.6	2688.2	2698.5
15°	2604.0	2635.0	2661.6	2683.7	2686.7	2683.7	2680.8	2682.3	2686.7	2669.0	2679.3
17.5°	2615.8	2618.7	2627.6	2618.7	2620.2	2589.2	2571.5	2567.1	2525.7	2527.2	2561.1
20°	2558.2	2508.0	2494.7	2445.9	2416.4	2336.6	2333.7	2311.5	2224.4	2251.0	2245.1
22.5°	2400.2	2314.5	2200.8	2144.6	2116.6	2032.4	1967.4	1921.6	1890.6	1859.6	1846.3
25°	2191.9	2053.1	1892.1	1781.3	1765.0	1686.8	1567.1	1511.0	1444.5	1423.8	1459.3
27.5°	1923.1	1742.9	1561.2	1391.3	1360.3	1289.4	1228.9	1189.0	1112.2	1107.8	1110.7
30°	1558.3	1376.6	1224.4	1113.7	1036.9	1004.4	964.5	935.0	903.9	915.7	918.7
32.5°	1280.6	1107.8	966.0	906.9	871.4	850.8	816.8	797.6	784.3	779.9	778.4
35°	1017.7	902.5	838.9	781.3	760.7	745.9	720.8	711.9	700.1	701.6	701.6
37.5°	871.4	775.4	728.2	698.6	679.4	672.0	655.8	646.9	639.5	636.6	641.0
40°	751.8	685.3	655.8	629.2	613.0	610.0	601.1	590.8	581.9	583.4	587.9
42.5°	664.7	626.3	590.8	570.1	558.3	553.9	546.5	539.1	539.1	534.7	533.2
45°	595.2	564.2	534.7	515.5	508.1	502.2	493.3	491.8	485.9	487.4	488.9
47.5°	533.2	508.1	485.9	466.7	459.4	457.9	449.0	443.1	443.1	441.6	440.2
50°	477.1	452.0	432.8	422.4	412.1	409.1	407.7	406.2	403.2	403.2	404.7
52.5°	431.3	406.2	391.4	382.5	376.6	373.7	373.7	372.2	372.2	372.2	370.7
55°	381.1	360.4	348.6	345.6	342.7	341.2	339.7	336.8	335.3	338.2	335.3
57.5°	333.8	326.4	316.1	313.1	305.7	305.7	301.3	298.4	295.4	298.4	298.4
60°	296.9	286.5	280.6	271.8	265.9	260.0	252.6	251.1	248.1	246.7	245.2
62.5°	258.5	249.6	234.8	221.6	212.7	206.8	203.8	202.4	202.4	200.9	200.9
65°	215.6	195.0	187.6	183.1	181.7	180.2	177.2	175.8	177.2	175.8	177.2
67.5°	168.4	165.4	161.0	158.0	156.6	155.1	155.1	153.6	153.6	153.6	153.6
70°	146.2	138.8	137.4	134.4	134.4	132.9	132.9	132.9	132.9	131.5	134.4
72.5°	121.1	116.7	115.2	113.7	113.7	113.7	112.3	112.3	112.3	110.8	112.3
75°	99.0	97.5	94.5	94.5	93.1	94.5	93.1	93.1	91.6	93.1	93.1
77.5°	79.8	78.3	76.8	76.8	75.3	75.3	75.3	75.3	75.3	75.3	76.8
80°	60.6	59.1	57.6	59.1	57.6	59.1	57.6	57.6	59.1	57.6	57.6
82.5°	44.3	42.8	42.8	41.4	41.4	41.4	41.4	41.4	41.4	41.4	41.4
85°	26.6	25.1	25.1	26.6	25.1	26.6	25.1	25.1	25.1	26.6	26.6
87.5°	11.8	13.3	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	13.3
90°	10.7	11.2	11.8	12.3	12.6	12.7	12.9	13.2	13.4	13.6	13.4
92.5°	12.3	12.5	12.8	13.0	13.1	13.2	13.3	13.4	13.5	13.6	13.5
95°	20.2	20.7	21.3	21.8	22.1	22.0	21.9	21.8	21.7	21.6	21.7
97.5°	25.9	26.3	26.6	26.9	27.1	27.2	27.3	27.4	27.5	27.6	27.5
100°	29.6	30.5	31.4	32.3	32.7	32.8	33.0	33.3	33.5	33.7	33.5
102.5°	30.9	32.1	33.4	34.6	35.2	35.4	35.7	36.0	36.4	36.7	36.4
105°	31.9	33.1	34.4	35.6	36.2	36.4	36.9	37.3	37.8	38.2	37.8
107.5°	32.9	34.1	35.4	36.6	37.2	37.4	37.9	38.3	38.8	39.2	38.8
110°	76.8	65.6	54.5	43.3	37.7	37.9	38.4	38.8	39.3	39.7	39.3

TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	207.2	159.1	110.9	62.8	38.7	38.9	39.2	39.5	39.9	40.2	39.9
115°	258.5	206.7	155.0	103.3	77.4	73.4	65.3	57.3	49.2	41.2	49.2
117.5°	321.3	305.3	289.4	273.4	265.4	250.8	221.5	192.2	163.0	133.7	163.0
120°	369.8	371.2	372.5	373.8	374.5	367.0	351.9	336.8	321.8	306.7	321.8
122.5°	398.9	399.5	400.2	400.9	401.2	401.3	401.4	401.5	401.6	401.7	401.6
125°	425.6	426.4	427.1	427.9	428.3	428.5	428.8	429.1	429.5	429.8	429.5
127.5°	450.5	451.7	452.8	453.9	454.5	454.6	454.7	454.8	454.9	455.0	454.9
130°	474.3	475.5	476.8	478.0	478.6	478.5	478.4	478.3	478.2	478.1	478.2
132.5°	497.7	498.7	499.7	500.7	501.2	501.1	501.0	500.9	500.8	500.7	500.8
135°	519.4	520.5	521.6	522.7	523.3	523.2	523.0	522.7	522.5	522.3	522.5
137.5°	540.0	541.1	542.2	543.3	543.9	543.7	543.4	543.1	542.7	542.4	542.7
140°	560.0	561.0	562.0	563.0	563.5	563.2	562.7	562.1	561.6	561.0	561.6
142.5°	578.5	579.4	580.3	581.2	581.6	581.3	580.8	580.2	579.7	579.1	579.7
145°	595.5	596.3	597.0	597.8	598.2	597.9	597.4	596.8	596.3	595.7	596.3
147.5°	610.9	611.4	612.0	612.5	612.8	612.6	612.1	611.7	611.2	610.8	611.2
150°	624.6	625.2	625.9	626.6	626.9	626.6	626.1	625.5	625.0	624.4	625.0
152.5°	637.1	637.8	638.5	639.2	639.5	639.1	638.3	637.5	636.7	635.9	636.7
155°	648.2	648.8	649.5	650.2	650.5	650.1	649.2	648.3	647.4	646.5	647.4
157.5°	657.9	658.7	659.4	660.2	660.6	660.1	659.2	658.3	657.4	656.5	657.4
160°	666.3	666.9	667.6	668.3	668.6	668.2	667.4	666.7	665.9	665.1	665.9
162.5°	673.9	674.7	675.5	676.3	676.7	676.2	675.2	674.1	673.1	672.1	673.1
165°	680.0	680.8	681.5	682.3	682.7	682.3	681.5	680.8	680.0	679.2	680.0
167.5°	685.5	686.3	687.0	687.8	688.2	687.7	686.7	685.7	684.7	683.7	684.7
170°	689.5	690.3	691.0	691.8	692.2	691.7	690.7	689.7	688.7	687.7	688.7
172.5°	692.5	693.3	694.1	694.9	695.3	694.8	693.8	692.7	691.7	690.7	691.7
175°	694.5	695.3	696.1	696.9	697.3	696.7	695.6	694.5	693.3	692.2	693.3
177.5°	695.1	695.9	696.6	697.4	697.8	697.3	696.3	695.2	694.2	693.2	694.2
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2240.6	2230.3	2227.3	2230.3	2227.3	2228.8	2218.5	2180.1	2190.4	2174.2	2183.0
5°	2367.7	2358.8	2339.6	2336.6	2333.7	2330.7	2316.0	2282.0	2268.7	2246.5	2245.1
7.5°	2488.8	2488.8	2474.0	2463.7	2450.4	2440.0	2420.8	2370.6	2349.9	2323.3	2308.6
10°	2608.4	2570.0	2586.3	2575.9	2543.4	2537.5	2502.1	2472.5	2432.6	2406.1	2382.4
12.5°	2694.1	2682.3	2667.5	2658.6	2649.8	2630.6	2606.9	2531.6	2510.9	2457.8	2431.2
15°	2691.1	2683.7	2688.2	2688.2	2685.2	2680.8	2661.6	2606.9	2571.5	2519.8	2474.0
17.5°	2546.4	2565.6	2584.8	2598.1	2627.6	2640.9	2658.6	2626.1	2604.0	2559.7	2510.9
20°	2293.8	2341.1	2397.2	2409.0	2435.6	2513.9	2549.3	2577.4	2586.3	2571.5	2531.6
22.5°	1942.3	1982.2	2118.0	2115.1	2153.5	2246.5	2349.9	2434.1	2500.6	2537.5	2522.7
25°	1521.3	1577.5	1649.8	1704.5	1830.0	1968.9	2097.4	2231.8	2347.0	2448.9	2474.0
27.5°	1150.6	1224.4	1282.0	1354.4	1417.9	1581.9	1747.3	1957.0	2091.5	2284.9	2385.4
30°	930.5	964.5	1022.1	1056.1	1087.1	1212.6	1400.2	1607.0	1843.3	2066.3	2239.2
32.5°	794.6	818.3	861.1	875.9	908.4	992.6	1110.7	1299.8	1543.5	1813.8	2041.2
35°	713.4	738.5	747.4	760.7	787.2	840.4	921.7	1059.0	1279.1	1543.5	1815.3
37.5°	644.0	657.3	682.4	691.2	700.1	740.0	794.6	890.6	1036.9	1254.0	1555.3
40°	595.2	602.6	615.9	623.3	629.2	657.3	706.0	771.0	878.8	1044.3	1321.9
42.5°	543.5	552.4	561.3	570.1	577.5	599.7	629.2	691.2	763.6	889.2	1090.0
45°	493.3	499.2	509.6	515.5	525.8	543.5	570.1	613.0	678.0	757.7	920.2
47.5°	447.5	454.9	459.4	466.7	474.1	493.3	518.4	546.5	599.7	678.0	796.1
50°	406.2	415.0	420.9	422.4	428.3	446.1	466.7	497.8	531.7	592.3	695.7
52.5°	376.6	378.1	382.5	388.5	387.0	397.3	416.5	440.2	475.6	524.3	599.7
55°	342.7	347.1	350.1	351.5	351.5	360.4	370.7	392.9	420.9	460.8	524.3
57.5°	299.8	304.3	313.1	316.1	320.5	324.9	329.4	344.1	367.8	406.2	457.9
60°	255.5	258.5	267.3	273.2	276.2	288.0	293.9	305.7	319.0	347.1	395.8
62.5°	205.3	208.3	212.7	218.6	224.5	242.2	257.0	268.8	279.2	298.4	338.2
65°	178.7	180.2	183.1	184.6	186.1	193.5	206.8	223.0	242.2	257.0	280.6
67.5°	155.1	156.6	158.0	161.0	162.5	163.9	169.9	174.3	193.5	214.2	231.9
70°	132.9	135.9	137.4	137.4	138.8	141.8	144.7	150.7	156.6	166.9	189.1
72.5°	112.3	113.7	116.7	116.7	116.7	119.6	122.6	125.5	128.5	134.4	143.3
75°	93.1	96.0	96.0	96.0	97.5	97.5	100.4	103.4	106.3	110.8	113.7
77.5°	76.8	76.8	76.8	76.8	78.3	78.3	79.8	82.7	84.2	85.7	88.6
80°	57.6	59.1	59.1	59.1	60.6	60.6	60.6	63.5	65.0	65.0	67.9
82.5°	42.8	42.8	42.8	44.3	42.8	44.3	44.3	45.8	44.3	45.8	47.3
85°	26.6	26.6	26.6	28.1	28.1	28.1	28.1	28.1	28.1	28.1	29.5
87.5°	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	14.8	13.3	13.3
90°	13.2	12.9	12.7	12.6	12.3	11.8	11.2	10.7	10.1	9.2	8.3
92.5°	13.4	13.3	13.2	13.1	13.0	12.8	12.5	12.3	12.1	11.8	11.4
95°	21.8	21.9	22.0	22.1	21.8	21.3	20.7	20.2	19.6	18.8	18.0
97.5°	27.4	27.3	27.2	27.1	26.9	26.6	26.3	25.9	25.6	23.8	22.0
100°	33.3	33.0	32.8	32.7	32.3	31.4	30.5	29.6	28.7	26.8	24.9
102.5°	36.0	35.7	35.4	35.2	34.6	33.4	32.1	30.9	29.7	50.0	70.4
105°	37.3	36.9	36.4	36.2	35.6	34.4	33.1	31.9	30.7	61.2	91.7
107.5°	38.3	37.9	37.4	37.2	36.6	35.4	34.1	32.9	31.7	69.3	107.0
110°	38.8	38.4	37.9	37.7	43.3	54.5	65.6	76.8	88.0	120.3	152.6

TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	39.5	39.2	38.9	38.7	62.8	110.9	159.1	207.2	255.4	257.3	259.2
115°	57.3	65.3	73.4	77.4	103.3	155.0	206.7	258.5	310.2	307.4	304.6
117.5°	192.2	221.5	250.8	265.4	273.4	289.4	305.3	321.3	337.3	335.4	333.5
120°	336.8	351.9	367.0	374.5	373.8	372.5	371.2	369.8	368.5	366.5	364.5
122.5°	401.5	401.4	401.3	401.2	400.9	400.2	399.5	398.9	398.2	396.0	393.7
125°	429.1	428.8	428.5	428.3	427.9	427.1	426.4	425.6	424.8	422.7	420.5
127.5°	454.8	454.7	454.6	454.5	453.9	452.8	451.7	450.5	449.4	447.7	446.1
130°	478.3	478.4	478.5	478.6	478.0	476.8	475.5	474.3	473.1	471.9	470.6
132.5°	500.9	501.0	501.1	501.2	500.7	499.7	498.7	497.7	496.7	495.5	494.3
135°	522.7	523.0	523.2	523.3	522.7	521.6	520.5	519.4	518.3	517.3	516.3
137.5°	543.1	543.4	543.7	543.9	543.3	542.2	541.1	540.0	538.9	537.8	536.7
140°	562.1	562.7	563.2	563.5	563.0	562.0	561.0	560.0	559.0	557.8	556.6
142.5°	580.2	580.8	581.3	581.6	581.2	580.3	579.4	578.5	577.6	576.2	574.7
145°	596.8	597.4	597.9	598.2	597.8	597.0	596.3	595.5	594.7	592.8	590.9
147.5°	611.7	612.1	612.6	612.8	612.5	612.0	611.4	610.9	610.3	608.4	606.5
150°	625.5	626.1	626.6	626.9	626.6	625.9	625.2	624.6	623.9	622.1	620.3
152.5°	637.5	638.3	639.1	639.5	639.2	638.5	637.8	637.1	636.4	634.7	633.1
155°	648.3	649.2	650.1	650.5	650.2	649.5	648.8	648.2	647.5	646.2	644.8
157.5°	658.3	659.2	660.1	660.6	660.2	659.4	658.7	657.9	657.1	656.1	655.1
160°	666.7	667.4	668.2	668.6	668.3	667.6	666.9	666.3	665.6	664.9	664.3
162.5°	674.1	675.2	676.2	676.7	676.3	675.5	674.7	673.9	673.1	672.5	672.0
165°	680.8	681.5	682.3	682.7	682.3	681.5	680.8	680.0	679.2	678.9	678.5
167.5°	685.7	686.7	687.7	688.2	687.8	687.0	686.3	685.5	684.7	684.4	684.0
170°	689.7	690.7	691.7	692.2	691.8	691.0	690.3	689.5	688.7	688.5	688.3
172.5°	692.7	693.8	694.8	695.3	694.9	694.1	693.3	692.5	691.7	691.5	691.3
175°	694.5	695.6	696.7	697.3	696.9	696.1	695.3	694.5	693.7	693.5	693.3
177.5°	695.2	696.3	697.3	697.8	697.4	696.6	695.9	695.1	694.3	694.2	694.0
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2169.7	2162.4	2162.4	2157.9	2157.9	2134.3	2134.3	2141.7	2132.8	2122.5	2107.7
5°	2225.9	2209.6	2205.2	2199.3	2180.1	2150.5	2138.7	2134.3	2116.6	2094.4	2069.3
7.5°	2279.0	2252.4	2239.2	2225.9	2200.8	2159.4	2135.8	2119.5	2092.9	2059.0	2026.5
10°	2330.7	2296.8	2262.8	2246.5	2211.1	2159.4	2125.4	2098.8	2060.4	2014.6	1968.9
12.5°	2378.0	2307.1	2301.2	2268.7	2217.0	2157.9	2106.2	2067.8	2019.1	1965.9	1912.7
15°	2419.4	2347.0	2311.5	2282.0	2214.0	2140.2	2085.5	2038.3	1973.3	1912.7	1847.7
17.5°	2440.0	2361.7	2338.1	2289.4	2220.0	2123.9	2050.1	1992.5	1921.6	1849.2	1775.4
20°	2460.7	2369.1	2330.7	2296.8	2202.2	2092.9	2010.2	1943.8	1865.5	1779.8	1698.6
22.5°	2471.0	2369.1	2323.3	2276.1	2184.5	2059.0	1961.5	1883.2	1791.6	1704.5	1607.0
25°	2453.3	2360.3	2305.6	2256.9	2153.5	2017.6	1905.4	1816.7	1719.2	1620.3	1521.3
27.5°	2409.0	2339.6	2276.1	2225.9	2110.7	1964.4	1846.3	1745.8	1645.4	1534.6	1434.2
30°	2326.3	2295.3	2245.1	2188.9	2063.4	1917.2	1776.9	1673.5	1562.7	1451.9	1347.0
32.5°	2197.8	2224.4	2191.9	2143.2	2007.3	1852.2	1703.0	1598.1	1477.0	1357.4	1261.4
35°	2041.2	2135.8	2118.0	2084.1	1948.2	1782.8	1633.6	1506.6	1385.4	1264.3	1168.3
37.5°	1869.9	2013.2	2027.9	2007.3	1880.2	1711.9	1547.9	1423.8	1299.8	1177.2	1079.7
40°	1635.1	1855.1	1902.4	1911.3	1809.3	1626.2	1454.9	1333.7	1211.2	1091.5	973.4
42.5°	1419.4	1697.1	1756.2	1793.1	1719.2	1542.0	1369.2	1234.8	1113.7	1005.8	887.7
45°	1217.1	1506.6	1602.6	1649.8	1617.3	1446.0	1267.3	1141.7	1031.0	932.0	818.3
47.5°	1008.8	1299.8	1434.2	1509.5	1509.5	1348.5	1169.8	1045.7	939.4	855.2	754.8
50°	870.0	1112.2	1251.0	1350.0	1376.6	1249.6	1081.2	960.1	859.6	768.0	691.2
52.5°	741.5	958.6	1073.8	1177.2	1254.0	1143.2	982.2	872.9	774.0	688.3	627.7
55°	641.0	803.5	908.4	1022.1	1107.8	1035.4	886.2	779.9	694.2	623.3	571.6
57.5°	545.0	686.8	772.5	872.9	964.5	909.8	790.2	698.6	623.3	561.3	515.5
60°	463.8	579.0	645.5	723.7	837.5	799.1	700.1	615.9	555.4	499.2	460.8
62.5°	394.4	485.9	542.1	598.2	701.6	683.9	607.1	542.1	490.4	443.1	410.6
65°	323.5	398.8	443.1	491.8	574.6	581.9	519.9	474.1	426.9	385.5	356.0
67.5°	261.4	320.5	360.4	401.7	468.2	488.9	446.1	407.7	367.8	333.8	307.2
70°	211.2	252.6	282.1	314.6	369.3	394.4	372.2	345.6	313.1	285.1	261.4
72.5°	166.9	193.5	211.2	236.3	280.6	305.7	304.3	280.6	257.0	237.8	218.6
75°	122.6	143.3	158.0	174.3	209.7	233.4	239.3	228.9	205.3	190.5	175.8
77.5°	93.1	104.9	112.3	124.1	149.2	169.9	178.7	175.8	159.5	147.7	137.4
80°	70.9	73.9	76.8	81.2	101.9	121.1	127.0	125.5	116.7	112.3	100.4
82.5°	50.2	51.7	53.2	54.6	62.0	78.3	84.2	87.1	79.8	75.3	65.0
85°	29.5	31.0	31.0	34.0	35.4	39.9	50.2	50.2	48.7	42.8	41.4
87.5°	14.8	14.8	13.3	13.3	14.8	16.2	19.2	22.2	19.2	17.7	16.2
90°	7.4	6.5	6.0	5.4	4.2	2.9	1.7	0.5	1.7	2.9	4.2
92.5°	11.1	10.8	10.6	10.8	11.3	11.7	12.2	12.6	12.2	11.7	11.3
95°	17.3	16.5	16.1	17.9	21.6	25.3	29.0	32.7	29.0	25.3	21.6
97.5°	20.3	18.5	17.6	22.2	31.3	40.5	49.6	58.8	49.6	40.5	31.3
100°	23.0	21.1	20.1	27.8	43.1	58.4	73.7	89.0	73.7	58.4	43.1
102.5°	90.7	111.0	121.2	121.3	121.5	121.8	122.0	122.2	122.0	121.8	121.5
105°	122.2	152.7	167.9	166.2	162.9	159.5	156.2	152.8	156.2	159.5	162.9
107.5°	144.6	182.3	201.1	199.7	196.9	194.1	191.3	188.5	191.3	194.1	196.9
110°	184.9	217.2	233.3	232.1	229.8	227.4	225.1	222.7	225.1	227.4	229.8

TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	261.1	263.0	263.9	262.9	260.9	258.9	256.9	254.9	256.9	258.9	260.9
115°	301.8	299.0	297.6	296.7	294.8	292.9	291.0	289.1	291.0	292.9	294.8
117.5°	331.6	329.7	328.8	327.7	325.4	323.2	320.9	318.7	320.9	323.2	325.4
120°	362.4	360.4	359.4	358.6	356.9	355.2	353.6	351.9	353.6	355.2	356.9
122.5°	391.5	389.2	388.1	387.2	385.4	383.7	381.9	380.1	381.9	383.7	385.4
125°	418.4	416.3	415.2	414.5	413.0	411.6	410.1	408.7	410.1	411.6	413.0
127.5°	444.4	442.7	441.9	441.1	439.6	438.0	436.5	434.9	436.5	438.0	439.6
130°	469.4	468.1	467.5	466.6	464.8	463.1	461.3	459.5	461.3	463.1	464.8
132.5°	493.0	491.8	491.2	490.5	489.0	487.5	486.1	484.6	486.1	487.5	489.0
135°	515.3	514.3	513.8	512.9	511.1	509.3	507.5	505.7	507.5	509.3	511.1
137.5°	535.6	534.5	533.9	533.2	531.9	530.6	529.2	527.9	529.2	530.6	531.9
140°	555.3	554.1	553.5	553.1	552.2	551.3	550.4	549.5	550.4	551.3	552.2
142.5°	573.3	571.8	571.1	570.7	569.9	569.2	568.4	567.6	568.4	569.2	569.9
145°	589.0	587.1	586.2	586.3	586.4	586.5	586.6	586.7	586.6	586.5	586.4
147.5°	604.6	602.7	601.8	602.0	602.3	602.6	603.0	603.3	603.0	602.6	602.3
150°	618.5	616.7	615.8	616.2	617.0	617.7	618.5	619.3	618.5	617.7	617.0
152.5°	631.4	629.7	628.9	629.3	630.2	631.1	632.0	632.9	632.0	631.1	630.2
155°	643.5	642.2	641.5	642.0	643.0	644.0	645.0	646.0	645.0	644.0	643.0
157.5°	654.0	653.0	652.5	652.9	653.8	654.7	655.6	656.5	655.6	654.7	653.8
160°	663.6	662.9	662.6	662.9	663.6	664.3	664.9	665.6	664.9	664.3	663.6
162.5°	671.4	670.9	670.6	670.9	671.6	672.3	672.9	673.6	672.9	672.3	671.6
165°	678.2	677.9	677.7	678.0	678.7	679.4	680.0	680.7	680.0	679.4	678.7
167.5°	683.7	683.4	683.2	683.5	684.2	684.9	685.5	686.2	685.5	684.9	684.2
170°	688.0	687.8	687.7	688.0	688.7	689.4	690.0	690.7	690.0	689.4	688.7
172.5°	691.0	690.8	690.7	691.0	691.7	692.4	693.0	693.7	693.0	692.4	691.7
175°	693.0	692.8	692.7	693.1	693.9	694.7	695.5	696.3	695.5	694.7	693.9
177.5°	693.9	693.8	693.7	694.1	694.9	695.7	696.5	697.3	696.5	695.7	694.9
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2101.8	2103.3	2107.7	2094.4	2073.7	2064.9	2038.3	2033.9	2029.4	2029.4	2033.9
5°	2054.5	2048.6	2050.1	2025.0	1995.4	1977.7	1940.8	1946.7	1927.5	1915.7	1918.6
7.5°	2002.8	1986.6	1985.1	1952.6	1915.7	1883.2	1844.8	1835.9	1818.2	1797.5	1788.7
10°	1937.8	1926.0	1903.9	1866.9	1819.7	1793.1	1741.4	1710.4	1706.0	1674.9	1663.1
12.5°	1871.4	1850.7	1828.5	1776.9	1723.7	1680.8	1642.4	1608.5	1584.8	1558.3	1540.5
15°	1794.6	1769.5	1744.4	1689.7	1627.7	1584.8	1527.2	1477.0	1407.6	1352.9	1321.9
17.5°	1710.4	1682.3	1648.3	1587.8	1527.2	1468.2	1361.8	1302.7	1254.0	1221.5	1202.3
20°	1623.2	1592.2	1558.3	1497.7	1392.8	1289.4	1230.4	1184.6	1155.0	1122.5	1098.9
22.5°	1531.7	1499.2	1462.2	1367.7	1256.9	1184.6	1138.8	1095.9	1053.1	1035.4	1023.6
25°	1446.0	1416.5	1369.2	1240.7	1153.5	1087.1	1035.4	1007.3	985.2	961.5	939.4
27.5°	1357.4	1302.7	1236.3	1128.4	1073.8	1005.8	968.9	948.2	909.8	893.6	883.3
30°	1251.0	1190.5	1127.0	1050.2	986.6	939.4	905.4	871.4	849.3	833.0	815.3
32.5°	1143.2	1085.6	1045.7	966.0	918.7	870.0	837.5	816.8	784.3	774.0	766.6
35°	1050.2	1001.4	966.0	901.0	856.7	812.4	788.7	757.7	737.0	717.8	706.0
37.5°	958.6	932.0	895.1	840.4	793.2	757.7	725.2	714.9	686.8	676.5	664.7
40°	895.1	855.2	824.2	776.9	737.0	698.6	678.0	654.3	635.1	618.9	614.4
42.5°	818.3	788.7	771.0	719.3	678.0	655.8	630.7	604.1	589.3	576.0	559.8
45°	760.7	734.1	709.0	667.6	630.7	602.6	580.5	562.7	537.6	531.7	506.6
47.5°	700.1	673.5	654.3	613.0	579.0	552.4	536.2	512.5	491.8	478.6	466.7
50°	639.5	617.4	599.7	564.2	534.7	506.6	484.5	460.8	452.0	429.8	422.4
52.5°	581.9	567.2	548.0	514.0	484.5	460.8	437.2	418.0	404.7	392.9	384.0
55°	533.2	509.6	500.7	463.8	438.7	413.6	392.9	381.1	364.8	357.4	350.1
57.5°	478.6	465.3	450.5	422.4	394.4	370.7	356.0	338.2	329.4	320.5	314.6
60°	431.3	412.1	400.3	376.6	351.5	329.4	316.1	302.8	291.0	283.6	271.8
62.5°	376.6	361.9	354.5	329.4	308.7	288.0	276.2	262.9	254.0	240.8	226.0
65°	329.4	317.6	308.7	288.0	268.8	249.6	237.8	221.6	209.7	202.4	200.9
67.5°	288.0	279.2	265.9	246.7	227.5	212.7	199.4	186.1	184.6	181.7	181.7
70°	242.2	233.4	226.0	205.3	189.1	172.8	169.9	165.4	161.0	159.5	156.6
72.5°	202.4	195.0	186.1	168.4	152.1	147.7	144.7	141.8	137.4	135.9	134.4
75°	163.9	153.6	147.7	131.5	127.0	124.1	121.1	116.7	113.7	112.3	109.3
77.5°	125.5	115.2	115.2	106.3	103.4	99.0	96.0	93.1	91.6	88.6	88.6
80°	88.6	88.6	85.7	81.2	76.8	75.3	70.9	69.4	67.9	69.4	66.5
82.5°	65.0	59.1	59.1	56.1	53.2	51.7	48.7	48.7	47.3	47.3	47.3
85°	36.9	36.9	35.4	32.5	31.0	31.0	29.5	29.5	28.1	28.1	26.6
87.5°	14.8	13.3	14.8	13.3	13.3	11.8	11.8	11.8	10.3	11.8	10.3
90°	5.4	6.0	6.5	7.4	8.3	9.2	10.1	10.7	11.2	11.8	12.3
92.5°	10.8	10.6	10.8	11.1	11.4	11.8	12.1	12.3	12.5	12.8	13.0
95°	17.9	16.1	16.5	17.3	18.0	18.8	19.6	20.2	20.7	21.3	21.8
97.5°	22.2	17.6	18.5	20.3	22.0	23.8	25.6	25.9	26.3	26.6	26.9
100°	27.8	20.1	21.1	23.0	24.9	26.8	28.7	29.6	30.5	31.4	32.3
102.5°	121.3	121.2	111.0	90.7	70.4	50.0	29.7	30.9	32.1	33.4	34.6
105°	166.2	167.9	152.7	122.2	91.7	61.2	30.7	31.9	33.1	34.4	35.6
107.5°	199.7	201.1	182.3	144.6	107.0	69.3	31.7	32.9	34.1	35.4	36.6
110°	232.1	233.3	217.2	184.9	152.6	120.3	88.0	76.8	65.6	54.5	43.3

TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	262.9	263.9	263.0	261.1	259.2	257.3	255.4	207.2	159.1	110.9	62.8
115°	296.7	297.6	299.0	301.8	304.6	307.4	310.2	258.5	206.7	155.0	103.3
117.5°	327.7	328.8	329.7	331.6	333.5	335.4	337.3	321.3	305.3	289.4	273.4
120°	358.6	359.4	360.4	362.4	364.5	366.5	368.5	369.8	371.2	372.5	373.8
122.5°	387.2	388.1	389.2	391.5	393.7	396.0	398.2	398.9	399.5	400.2	400.9
125°	414.5	415.2	416.3	418.4	420.5	422.7	424.8	425.6	426.4	427.1	427.9
127.5°	441.1	441.9	442.7	444.4	446.1	447.7	449.4	450.5	451.7	452.8	453.9
130°	466.6	467.5	468.1	469.4	470.6	471.9	473.1	474.3	475.5	476.8	478.0
132.5°	490.5	491.2	491.8	493.0	494.3	495.5	496.7	497.7	498.7	499.7	500.7
135°	512.9	513.8	514.3	515.3	516.3	517.3	518.3	519.4	520.5	521.6	522.7
137.5°	533.2	533.9	534.5	535.6	536.7	537.8	538.9	540.0	541.1	542.2	543.3
140°	553.1	553.5	554.1	555.3	556.6	557.8	559.0	560.0	561.0	562.0	563.0
142.5°	570.7	571.1	571.8	573.3	574.7	576.2	577.6	578.5	579.4	580.3	581.2
145°	586.3	586.2	587.1	589.0	590.9	592.8	594.7	595.5	596.3	597.0	597.8
147.5°	602.0	601.8	602.7	604.6	606.5	608.4	610.3	610.9	611.4	612.0	612.5
150°	616.2	615.8	616.7	618.5	620.3	622.1	623.9	624.6	625.2	625.9	626.6
152.5°	629.3	628.9	629.7	631.4	633.1	634.7	636.4	637.1	637.8	638.5	639.2
155°	642.0	641.5	642.2	643.5	644.8	646.2	647.5	648.2	648.8	649.5	650.2
157.5°	652.9	652.5	653.0	654.0	655.1	656.1	657.1	657.9	658.7	659.4	660.2
160°	662.9	662.6	662.9	663.6	664.3	664.9	665.6	666.3	666.9	667.6	668.3
162.5°	670.9	670.6	670.9	671.4	672.0	672.5	673.1	673.9	674.7	675.5	676.3
165°	678.0	677.7	677.9	678.2	678.5	678.9	679.2	680.0	680.8	681.5	682.3
167.5°	683.5	683.2	683.4	683.7	684.0	684.4	684.7	685.5	686.3	687.0	687.8
170°	688.0	687.7	687.8	688.0	688.3	688.5	688.7	689.5	690.3	691.0	691.8
172.5°	691.0	690.7	690.8	691.0	691.3	691.5	691.7	692.5	693.3	694.1	694.9
175°	693.1	692.7	692.8	693.0	693.3	693.5	693.7	694.5	695.3	696.1	696.9
177.5°	694.1	693.7	693.8	693.9	694.0	694.2	694.3	695.1	695.9	696.6	697.4
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2033.9	2030.9	2022.0	2025.0	2020.6	2020.6	2017.6	2017.6	2017.6	2025.0	2020.6
5°	1923.1	1912.7	1902.4	1898.0	1893.5	1889.1	1889.1	1887.6	1900.9	1898.0	1909.8
7.5°	1785.7	1782.8	1762.1	1762.1	1754.7	1751.7	1759.1	1760.6	1762.1	1765.0	1772.4
10°	1663.1	1655.7	1626.2	1629.1	1624.7	1618.8	1623.2	1620.3	1630.6	1633.6	1630.6
12.5°	1518.4	1505.1	1472.6	1456.3	1438.6	1425.3	1441.6	1429.8	1471.1	1482.9	1515.4
15°	1326.4	1301.3	1279.1	1279.1	1262.8	1251.0	1258.4	1271.7	1280.6	1293.9	1299.8
17.5°	1197.9	1187.5	1169.8	1159.5	1155.0	1150.6	1150.6	1156.5	1175.7	1174.2	1186.0
20°	1088.6	1082.7	1073.8	1060.5	1056.1	1053.1	1053.1	1053.1	1066.4	1078.2	1085.6
22.5°	1013.2	1008.8	1002.9	985.2	976.3	973.4	980.7	985.2	995.5	1004.4	1011.8
25°	937.9	927.6	917.2	911.3	906.9	906.9	909.8	911.3	915.7	920.2	929.0
27.5°	875.9	868.5	853.7	837.5	837.5	833.0	836.0	838.9	849.3	864.1	871.4
30°	806.5	805.0	799.1	793.2	787.2	784.3	790.2	794.6	796.1	803.5	803.5
32.5°	756.2	745.9	735.6	729.6	726.7	725.2	726.7	732.6	732.6	741.5	751.8
35°	706.0	700.1	689.8	679.4	676.5	669.1	675.0	680.9	691.2	695.7	700.1
37.5°	651.4	644.0	639.5	636.6	630.7	632.2	627.7	636.6	645.5	644.0	646.9
40°	610.0	596.7	583.4	581.9	580.5	579.0	579.0	580.5	586.4	592.3	601.1
42.5°	556.8	552.4	540.6	528.8	525.8	522.9	519.9	525.8	537.6	548.0	552.4
45°	502.2	496.3	493.3	484.5	478.6	477.1	474.1	481.5	491.8	496.3	499.2
47.5°	452.0	450.5	441.6	443.1	438.7	440.2	438.7	443.1	443.1	447.5	450.5
50°	418.0	413.6	409.1	406.2	401.7	401.7	400.3	401.7	407.7	413.6	412.1
52.5°	384.0	376.6	375.2	373.7	370.7	373.7	369.3	370.7	376.6	379.6	378.1
55°	344.1	342.7	339.7	336.8	335.3	333.8	333.8	333.8	339.7	344.1	345.6
57.5°	313.1	305.7	299.8	299.8	293.9	292.4	295.4	296.9	301.3	304.3	307.2
60°	270.3	267.3	258.5	254.0	245.2	243.7	243.7	249.6	257.0	267.3	270.3
62.5°	224.5	220.1	218.6	218.6	218.6	218.6	218.6	218.6	218.6	220.1	220.1
65°	199.4	200.9	199.4	197.9	199.4	199.4	197.9	197.9	197.9	199.4	200.9
67.5°	178.7	177.2	178.7	177.2	175.8	175.8	174.3	175.8	177.2	178.7	178.7
70°	155.1	155.1	153.6	155.1	153.6	152.1	150.7	150.7	153.6	155.1	155.1
72.5°	132.9	132.9	131.5	131.5	128.5	128.5	130.0	128.5	128.5	132.9	132.9
75°	110.8	109.3	107.8	107.8	106.3	106.3	106.3	104.9	107.8	107.8	109.3
77.5°	87.1	87.1	87.1	85.7	85.7	84.2	84.2	85.7	85.7	85.7	87.1
80°	66.5	66.5	66.5	65.0	63.5	63.5	63.5	63.5	63.5	65.0	63.5
82.5°	45.8	45.8	45.8	45.8	45.8	44.3	44.3	44.3	45.8	45.8	44.3
85°	28.1	26.6	28.1	28.1	26.6	28.1	26.6	26.6	25.1	25.1	26.6
87.5°	11.8	10.3	8.9	8.9	10.3	8.9	8.9	8.9	10.3	8.9	8.9
90°	12.6	12.7	12.9	13.2	13.4	13.6	13.4	13.2	12.9	12.7	12.6
92.5°	13.1	13.2	13.3	13.4	13.5	13.6	13.5	13.4	13.3	13.2	13.1
95°	22.1	22.0	21.9	21.8	21.7	21.6	21.7	21.8	21.9	22.0	22.1
97.5°	27.1	27.2	27.3	27.4	27.5	27.6	27.5	27.4	27.3	27.2	27.1
100°	32.7	32.8	33.0	33.3	33.5	33.7	33.5	33.3	33.0	32.8	32.7
102.5°	35.2	35.4	35.7	36.0	36.4	36.7	36.4	36.0	35.7	35.4	35.2
105°	36.2	36.4	36.9	37.3	37.8	38.2	37.8	37.3	36.9	36.4	36.2
107.5°	37.2	37.4	37.9	38.3	38.8	39.2	38.8	38.3	37.9	37.4	37.2
110°	37.7	37.9	38.4	38.8	39.3	39.7	39.3	38.8	38.4	37.9	37.7

TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	38.7	38.9	39.2	39.5	39.9	40.2	39.9	39.5	39.2	38.9	38.7
115°	77.4	73.4	65.3	57.3	49.2	41.2	49.2	57.3	65.3	73.4	77.4
117.5°	265.4	250.8	221.5	192.2	163.0	133.7	163.0	192.2	221.5	250.8	265.4
120°	374.5	367.0	351.9	336.8	321.8	306.7	321.8	336.8	351.9	367.0	374.5
122.5°	401.2	401.3	401.4	401.5	401.6	401.7	401.6	401.5	401.4	401.3	401.2
125°	428.3	428.5	428.8	429.1	429.5	429.8	429.5	429.1	428.8	428.5	428.3
127.5°	454.5	454.6	454.7	454.8	454.9	455.0	454.9	454.8	454.7	454.6	454.5
130°	478.6	478.5	478.4	478.3	478.2	478.1	478.2	478.3	478.4	478.5	478.6
132.5°	501.2	501.1	501.0	500.9	500.8	500.7	500.8	500.9	501.0	501.1	501.2
135°	523.3	523.2	523.0	522.7	522.5	522.3	522.5	522.7	523.0	523.2	523.3
137.5°	543.9	543.7	543.4	543.1	542.7	542.4	542.7	543.1	543.4	543.7	543.9
140°	563.5	563.2	562.7	562.1	561.6	561.0	561.6	562.1	562.7	563.2	563.5
142.5°	581.6	581.3	580.8	580.2	579.7	579.1	579.7	580.2	580.8	581.3	581.6
145°	598.2	597.9	597.4	596.8	596.3	595.7	596.3	596.8	597.4	597.9	598.2
147.5°	612.8	612.6	612.1	611.7	611.2	610.8	611.2	611.7	612.1	612.6	612.8
150°	626.9	626.6	626.1	625.5	625.0	624.4	625.0	625.5	626.1	626.6	626.9
152.5°	639.5	639.1	638.3	637.5	636.7	635.9	636.7	637.5	638.3	639.1	639.5
155°	650.5	650.1	649.2	648.3	647.4	646.5	647.4	648.3	649.2	650.1	650.5
157.5°	660.6	660.1	659.2	658.3	657.4	656.5	657.4	658.3	659.2	660.1	660.6
160°	668.6	668.2	667.4	666.7	665.9	665.1	665.9	666.7	667.4	668.2	668.6
162.5°	676.7	676.2	675.2	674.1	673.1	672.1	673.1	674.1	675.2	676.2	676.7
165°	682.7	682.3	681.5	680.8	680.0	679.2	680.0	680.8	681.5	682.3	682.7
167.5°	688.2	687.7	686.7	685.7	684.7	683.7	684.7	685.7	686.7	687.7	688.2
170°	692.2	691.7	690.7	689.7	688.7	687.7	688.7	689.7	690.7	691.7	692.2
172.5°	695.3	694.8	693.8	692.7	691.7	690.7	691.7	692.7	693.8	694.8	695.3
175°	697.3	696.7	695.6	694.5	693.3	692.2	693.3	694.5	695.6	696.7	697.3
177.5°	697.8	697.3	696.3	695.2	694.2	693.2	694.2	695.2	696.3	697.3	697.8
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2025.0	2032.4	2029.4	2013.2	2029.4	2033.9	2042.7	2051.6	2057.5	2066.3	2073.7
5°	1898.0	1912.7	1921.6	1912.7	1942.3	1946.7	1967.4	1979.2	1996.9	2011.7	2023.5
7.5°	1778.3	1790.1	1807.9	1810.8	1828.5	1849.2	1878.8	1908.3	1936.4	1951.1	1964.4
10°	1649.8	1670.5	1697.1	1691.2	1717.8	1750.3	1781.3	1828.5	1852.2	1878.8	1902.4
12.5°	1521.3	1534.6	1570.1	1581.9	1620.3	1645.4	1688.2	1717.8	1776.9	1807.9	1828.5
15°	1296.8	1351.5	1395.8	1449.0	1499.2	1546.4	1584.8	1638.0	1689.7	1713.3	1747.3
17.5°	1194.9	1220.0	1246.6	1273.2	1338.2	1422.4	1490.3	1547.9	1592.2	1623.2	1663.1
20°	1088.6	1113.7	1143.2	1168.3	1208.2	1268.8	1352.9	1451.9	1505.1	1537.6	1576.0
22.5°	1013.2	1036.9	1056.1	1078.2	1109.2	1153.5	1217.1	1339.7	1410.6	1450.4	1484.4
25°	932.0	961.5	982.2	998.5	1023.6	1072.3	1124.0	1193.4	1320.5	1351.5	1398.7
27.5°	875.9	884.7	908.4	933.5	958.6	985.2	1038.3	1097.4	1183.1	1251.0	1308.6
30°	809.4	831.6	853.7	864.1	886.2	924.6	957.1	1020.6	1087.1	1140.3	1209.7
32.5°	759.2	772.5	787.2	812.4	833.0	859.6	892.1	945.3	1001.4	1035.4	1088.6
35°	703.1	711.9	742.9	753.3	774.0	800.5	833.0	874.4	935.0	961.5	999.9
37.5°	649.9	670.6	679.4	703.1	722.3	748.8	772.5	819.7	859.6	890.6	926.1
40°	608.5	617.4	633.6	654.3	670.6	691.2	720.8	754.8	797.6	822.7	853.7
42.5°	558.3	565.7	586.4	598.2	624.8	644.0	661.7	703.1	741.5	760.7	791.7
45°	503.7	521.4	534.7	558.3	573.1	596.7	618.9	648.4	683.9	706.0	723.7
47.5°	456.4	474.1	487.4	509.6	533.2	543.5	567.2	598.2	630.7	648.4	673.5
50°	418.0	423.9	449.0	459.4	484.5	505.1	521.4	548.0	583.4	593.8	614.4
52.5°	381.1	385.5	401.7	415.0	437.2	454.9	475.6	500.7	530.2	546.5	562.7
55°	348.6	351.5	358.9	373.7	388.5	410.6	429.8	453.4	478.6	496.3	511.0
57.5°	311.7	317.6	323.5	332.3	347.1	367.8	388.5	410.6	431.3	443.1	462.3
60°	268.8	277.7	288.0	298.4	308.7	323.5	347.1	367.8	387.0	397.3	412.1
62.5°	223.0	240.8	249.6	261.4	270.3	283.6	301.3	324.9	338.2	351.5	363.3
65°	200.9	202.4	203.8	215.6	231.9	245.2	261.4	279.2	299.8	308.7	317.6
67.5°	178.7	180.2	183.1	184.6	190.5	205.3	223.0	242.2	258.5	264.4	273.2
70°	156.6	156.6	162.5	163.9	165.4	166.9	181.7	200.9	215.6	223.0	233.4
72.5°	132.9	134.4	137.4	138.8	141.8	144.7	149.2	159.5	177.2	184.6	196.4
75°	109.3	110.8	112.3	113.7	118.2	119.6	124.1	130.0	137.4	146.2	153.6
77.5°	87.1	87.1	88.6	91.6	94.5	96.0	100.4	103.4	106.3	110.8	116.7
80°	65.0	66.5	66.5	69.4	69.4	70.9	72.4	76.8	79.8	82.7	85.7
82.5°	44.3	47.3	47.3	47.3	48.7	50.2	51.7	51.7	54.6	56.1	60.6
85°	26.6	28.1	28.1	28.1	26.6	29.5	29.5	31.0	31.0	31.0	32.5
87.5°	10.3	8.9	10.3	10.3	10.3	11.8	10.3	10.3	11.8	13.3	13.3
90°	12.3	11.8	11.2	10.7	10.1	9.2	8.3	7.4	6.5	6.0	5.4
92.5°	13.0	12.8	12.5	12.3	12.1	11.8	11.4	11.1	10.8	10.6	10.8
95°	21.8	21.3	20.7	20.2	19.6	18.8	18.0	17.3	16.5	16.1	17.9
97.5°	26.9	26.6	26.3	25.9	25.6	23.8	22.0	20.3	18.5	17.6	22.2
100°	32.3	31.4	30.5	29.6	28.7	26.8	24.9	23.0	21.1	20.1	27.8
102.5°	34.6	33.4	32.1	30.9	29.7	50.0	70.4	90.7	111.0	121.2	121.3
105°	35.6	34.4	33.1	31.9	30.7	61.2	91.7	122.2	152.7	167.9	166.2
107.5°	36.6	35.4	34.1	32.9	31.7	69.3	107.0	144.6	182.3	201.1	199.7
110°	43.3	54.5	65.6	76.8	88.0	120.3	152.6	184.9	217.2	233.3	232.1

TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	62.8	110.9	159.1	207.2	255.4	257.3	259.2	261.1	263.0	263.9	262.9
115°	103.3	155.0	206.7	258.5	310.2	307.4	304.6	301.8	299.0	297.6	296.7
117.5°	273.4	289.4	305.3	321.3	337.3	335.4	333.5	331.6	329.7	328.8	327.7
120°	373.8	372.5	371.2	369.8	368.5	366.5	364.5	362.4	360.4	359.4	358.6
122.5°	400.9	400.2	399.5	398.9	398.2	396.0	393.7	391.5	389.2	388.1	387.2
125°	427.9	427.1	426.4	425.6	424.8	422.7	420.5	418.4	416.3	415.2	414.5
127.5°	453.9	452.8	451.7	450.5	449.4	447.7	446.1	444.4	442.7	441.9	441.1
130°	478.0	476.8	475.5	474.3	473.1	471.9	470.6	469.4	468.1	467.5	466.6
132.5°	500.7	499.7	498.7	497.7	496.7	495.5	494.3	493.0	491.8	491.2	490.5
135°	522.7	521.6	520.5	519.4	518.3	517.3	516.3	515.3	514.3	513.8	512.9
137.5°	543.3	542.2	541.1	540.0	538.9	537.8	536.7	535.6	534.5	533.9	533.2
140°	563.0	562.0	561.0	560.0	559.0	557.8	556.6	555.3	554.1	553.5	553.1
142.5°	581.2	580.3	579.4	578.5	577.6	576.2	574.7	573.3	571.8	571.1	570.7
145°	597.8	597.0	596.3	595.5	594.7	592.8	590.9	589.0	587.1	586.2	586.3
147.5°	612.5	612.0	611.4	610.9	610.3	608.4	606.5	604.6	602.7	601.8	602.0
150°	626.6	625.9	625.2	624.6	623.9	622.1	620.3	618.5	616.7	615.8	616.2
152.5°	639.2	638.5	637.8	637.1	636.4	634.7	633.1	631.4	629.7	628.9	629.3
155°	650.2	649.5	648.8	648.2	647.5	646.2	644.8	643.5	642.2	641.5	642.0
157.5°	660.2	659.4	658.7	657.9	657.1	656.1	655.1	654.0	653.0	652.5	652.9
160°	668.3	667.6	666.9	666.3	665.6	664.9	664.3	663.6	662.9	662.6	662.9
162.5°	676.3	675.5	674.7	673.9	673.1	672.5	672.0	671.4	670.9	670.6	670.9
165°	682.3	681.5	680.8	680.0	679.2	678.9	678.5	678.2	677.9	677.7	678.0
167.5°	687.8	687.0	686.3	685.5	684.7	684.4	684.0	683.7	683.4	683.2	683.5
170°	691.8	691.0	690.3	689.5	688.7	688.5	688.3	688.0	687.8	687.7	688.0
172.5°	694.9	694.1	693.3	692.5	691.7	691.5	691.3	691.0	690.8	690.7	691.0
175°	696.9	696.1	695.3	694.5	693.7	693.5	693.3	693.0	692.8	692.7	693.1
177.5°	697.4	696.6	695.9	695.1	694.3	694.2	694.0	693.9	693.8	693.7	694.1
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2125.4	2125.4	2125.4	2125.4
2.5°	2087.0	2082.6	2109.2	2138.7
5°	2044.2	2051.6	2085.5	2126.9
7.5°	1999.9	2016.1	2056.0	2110.7
10°	1937.8	1967.4	2027.9	2084.1
12.5°	1877.3	1917.2	1974.8	2041.2
15°	1809.3	1853.7	1924.6	2004.3
17.5°	1734.0	1784.2	1866.9	1954.1
20°	1654.3	1720.7	1807.9	1902.4
22.5°	1565.6	1645.4	1735.5	1840.4
25°	1480.0	1567.1	1657.2	1778.3
27.5°	1395.8	1481.4	1581.9	1704.5
30°	1311.6	1389.9	1497.7	1629.1
32.5°	1221.5	1302.7	1416.5	1550.9
35°	1138.8	1220.0	1326.4	1459.3
37.5°	1050.2	1137.3	1239.2	1376.6
40°	946.8	1048.7	1147.6	1279.1
42.5°	861.1	968.9	1064.9	1189.0
45°	793.2	895.1	974.8	1095.9
47.5°	729.6	812.4	893.6	1005.8
50°	669.1	732.6	816.8	917.2
52.5°	607.1	661.7	734.1	828.6
55°	550.9	602.6	667.6	740.0
57.5°	499.2	536.2	601.1	666.1
60°	441.6	480.0	530.2	584.9
62.5°	392.9	422.4	469.7	515.5
65°	341.2	369.3	404.7	447.5
67.5°	293.9	319.0	347.1	381.1
70°	251.1	270.3	291.0	320.5
72.5°	205.3	226.0	245.2	268.8
75°	168.4	177.2	193.5	209.7
77.5°	130.0	141.8	150.7	163.9
80°	93.1	103.4	106.3	116.7
82.5°	62.0	67.9	73.9	76.8
85°	35.4	38.4	44.3	45.8
87.5°	13.3	14.8	17.7	20.7
90°	4.2	2.9	1.7	0.5
92.5°	11.3	11.7	12.2	12.6
95°	21.6	25.3	29.0	32.7
97.5°	31.3	40.5	49.6	58.8
100°	43.1	58.4	73.7	89.0
102.5°	121.5	121.8	122.0	122.2
105°	162.9	159.5	156.2	152.8
107.5°	196.9	194.1	191.3	188.5
110°	229.8	227.4	225.1	222.7



TEST NUMBER: P1008318

CATALOG NUMBER: S122RDIP-B1005D530UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	260.9	258.9	256.9	254.9
115°	294.8	292.9	291.0	289.1
117.5°	325.4	323.2	320.9	318.7
120°	356.9	355.2	353.6	351.9
122.5°	385.4	383.7	381.9	380.1
125°	413.0	411.6	410.1	408.7
127.5°	439.6	438.0	436.5	434.9
130°	464.8	463.1	461.3	459.5
132.5°	489.0	487.5	486.1	484.6
135°	511.1	509.3	507.5	505.7
137.5°	531.9	530.6	529.2	527.9
140°	552.2	551.3	550.4	549.5
142.5°	569.9	569.2	568.4	567.6
145°	586.4	586.5	586.6	586.7
147.5°	602.3	602.6	603.0	603.3
150°	617.0	617.7	618.5	619.3
152.5°	630.2	631.1	632.0	632.9
155°	643.0	644.0	645.0	646.0
157.5°	653.8	654.7	655.6	656.5
160°	663.6	664.3	664.9	665.6
162.5°	671.6	672.3	672.9	673.6
165°	678.7	679.4	680.0	680.7
167.5°	684.2	684.9	685.5	686.2
170°	688.7	689.4	690.0	690.7
172.5°	691.7	692.4	693.0	693.7
175°	693.9	694.7	695.5	696.3
177.5°	694.9	695.7	696.5	697.3
180°	694.8	694.8	694.8	694.8

(END OF REPORT)