

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008327

Luminaire Tested: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008327
REPORT IS A COMBINATION OF REPORTS P987947 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6614.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57	57	57
1	100	96	93	89	93	90	87	84	78	76	74	67	66	64	57	56	55	50	50	50
2	92	85	79	75	86	80	75	71	70	66	63	60	57	55	51	49	48	44	44	44
3	85	76	69	63	79	71	65	60	62	58	54	54	51	48	46	44	42	38	38	38
4	78	68	60	55	73	64	57	52	56	51	47	49	45	42	42	39	37	34	34	34
5	72	61	53	48	67	57	51	45	51	45	41	44	40	37	39	35	33	30	30	30
6	67	55	48	42	62	52	45	40	46	41	37	41	36	33	35	32	30	27	27	27
7	62	50	43	37	58	48	41	36	42	37	33	37	33	30	33	29	27	24	24	24
8	58	46	39	34	54	44	37	32	39	33	30	34	30	27	30	27	24	22	22	22
9	54	42	35	30	51	40	34	29	36	31	27	32	28	25	28	25	22	20	20	20
10	51	39	32	28	48	37	31	26	33	28	24	30	26	23	26	23	21	19	19	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	34790	34790	34790	34790
5°	34870	36952	34991	29520
10°	34486	39056	34731	24377
15°	33737	39069	34309	18313
20°	32837	32295	33552	15109
25°	31746	20180	32433	12854
30°	30353	12920	31178	11065
35°	28658	9930	29585	9470
40°	26768	8347	27912	8283
45°	24749	7104	25784	6953
50°	22680	6036	23739	6014
55°	20390	5245	21487	5177
60°	18352	4000	19326	3952
65°	16452	3009	17430	3415
70°	14352	2404	15478	2783
75°	12133	1841	13241	2105
80°	9636	1253	10363	1381
85°	6681	647	7331	682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 31825 cd/sqm

TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.5	3.2
10°-20°	581.9	8.8
20°-30°	748.9	11.3
30°-40°	710.4	10.7
40°-50°	608.9	9.2
50°-60°	463.7	7.0
60°-70°	292.4	4.4
70°-80°	145.9	2.2
80°-90°	39.2	0.6
90°-100°	31.7	0.5
100°-110°	118.0	1.8
110°-120°	313.0	4.7
120°-130°	519.1	7.8
130°-140°	551.4	8.3
140°-150°	512.4	7.7
150°-160°	412.0	6.2
160°-170°	265.5	4.0
170°-180°	91.4	1.4
0°-30°	1539.2	23.3
0°-40°	2249.6	34.0
0°-60°	3322.2	50.2
0°-90°	3799.7	57.4
90°-120°	462.7	7.0
90°-150°	2045.5	30.9
90°-180°	2814.0	42.5
0°-180°	6614.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2198	2198	2198	2198	2198	
5°	2199	2445	2207	1953	2199	209
15°	2072	2760	2108	1294	2072	583
25°	1839	1472	1879	938	1839	844
35°	1509	726	1558	692	1509	944
45°	1133	504	1181	493	1133	875
55°	765	350	806	345	765	690
65°	463	182	490	206	463	459
75°	217	96	237	110	217	235
85°	47	28	52	29	47	54
90°	1	19	1	19	1	6
95°	45	30	45	30	45	53
105°	211	53	211	53	211	226
115°	399	57	399	57	399	393
125°	565	594	565	594	565	504
135°	699	722	699	722	699	540
145°	811	823	811	823	811	507
155°	893	893	893	893	893	411
165°	940	938	940	938	940	266
175°	962	956	962	956	962	92
180°	960	960	960	960	960	

TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2211.5	2220.7	2225.2	2231.4	2245.1	2254.3	2268.0	2271.1	2269.5	2275.7	2258.9
5°	2199.3	2219.1	2237.5	2252.7	2277.2	2292.5	2309.3	2329.1	2333.7	2356.6	2342.9
7.5°	2182.5	2211.5	2237.5	2268.0	2304.7	2324.5	2350.5	2381.0	2394.8	2422.3	2429.9
10°	2155.0	2196.2	2240.5	2272.6	2323.0	2358.1	2382.6	2431.4	2463.5	2504.7	2498.6
12.5°	2110.7	2164.2	2223.7	2277.2	2342.9	2365.8	2411.6	2462.0	2503.2	2541.4	2575.0
15°	2072.5	2133.6	2199.3	2265.0	2339.8	2382.6	2428.4	2494.1	2538.3	2605.5	2634.6
17.5°	2020.6	2098.5	2176.4	2249.7	2338.3	2387.1	2443.7	2507.8	2573.5	2637.6	2660.5
20°	1967.1	2051.1	2135.1	2234.4	2335.2	2382.6	2440.6	2520.0	2584.2	2634.6	2634.6
22.5°	1903.0	2005.3	2101.5	2196.2	2306.2	2374.9	2434.5	2527.7	2573.5	2584.2	2542.9
25°	1838.8	1941.2	2046.6	2164.2	2289.4	2350.5	2417.7	2504.7	2520.0	2477.3	2370.3
27.5°	1762.5	1877.0	1996.2	2122.9	2254.3	2330.6	2391.7	2449.8	2420.7	2306.2	2139.7
30°	1684.6	1808.3	1942.7	2063.4	2222.2	2292.5	2344.4	2361.2	2269.5	2083.2	1867.9
32.5°	1603.6	1724.3	1866.3	2011.4	2171.8	2239.0	2272.6	2228.3	2060.3	1825.1	1562.4
35°	1509.0	1644.9	1793.0	1944.2	2103.1	2153.5	2173.3	2064.9	1849.5	1545.6	1284.4
37.5°	1423.4	1559.4	1718.2	1872.4	2026.7	2054.2	2034.3	1864.8	1591.4	1290.6	1035.5
40°	1322.6	1467.7	1623.5	1796.1	1922.8	1930.5	1881.6	1661.7	1322.6	1040.1	882.8
42.5°	1229.5	1376.1	1531.9	1707.5	1803.7	1777.8	1712.1	1423.4	1104.2	896.5	769.8
45°	1133.2	1272.2	1440.2	1596.0	1664.7	1603.6	1504.4	1197.4	927.1	771.3	673.5
47.5°	1040.1	1169.9	1336.4	1486.0	1498.3	1429.5	1311.9	1003.4	803.4	678.1	598.7
50°	948.4	1078.3	1234.0	1357.8	1345.5	1250.8	1118.0	872.1	698.0	598.7	533.0
52.5°	856.8	974.4	1125.6	1223.4	1171.4	1079.8	948.4	739.2	609.4	522.3	471.9
55°	765.2	875.1	1005.0	1085.9	1003.4	898.0	804.9	633.8	528.4	458.2	420.0
57.5°	688.8	775.9	895.0	943.9	844.6	762.1	681.2	545.2	458.2	407.8	363.5
60°	604.8	684.2	782.0	811.0	708.7	641.5	572.7	461.2	392.5	348.2	319.2
62.5°	533.0	598.7	673.5	673.5	583.4	533.0	481.1	386.4	329.9	294.8	281.0
65°	462.8	510.1	563.6	557.5	481.1	436.8	395.6	319.2	276.4	252.0	238.3
67.5°	394.0	430.7	465.8	444.4	389.5	351.3	313.1	258.1	229.1	212.3	194.0
70°	331.4	360.4	378.8	358.9	303.9	271.9	244.4	207.7	184.8	163.4	152.7
72.5°	278.0	290.2	296.3	271.9	226.0	207.7	187.9	161.9	142.0	131.3	128.3
75°	216.9	227.6	223.0	204.7	166.5	152.7	137.5	119.1	114.5	108.4	105.4
77.5°	169.5	169.5	161.9	145.1	119.1	108.4	102.3	93.2	88.6	87.1	84.0
80°	120.7	119.1	114.5	96.2	80.9	74.8	74.8	68.7	67.2	64.1	64.1
82.5°	79.4	79.4	73.3	58.0	53.5	51.9	50.4	47.3	47.3	45.8	45.8
85°	47.3	44.3	36.7	32.1	30.5	30.5	29.0	27.5	29.0	27.5	27.5
87.5°	21.4	16.8	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2
90°	0.7	2.4	4.1	5.8	7.5	8.3	8.9	10.2	11.4	12.7	13.9
92.5°	17.4	16.8	16.2	15.5	14.9	14.6	14.8	15.3	15.8	16.2	16.7
95°	45.2	40.1	35.0	29.9	24.8	22.2	22.7	23.8	24.9	26.0	27.1
97.5°	81.3	68.6	56.0	43.3	30.6	24.3	25.5	28.0	30.5	32.9	35.4
100°	122.9	101.8	80.6	59.5	38.4	27.8	29.1	31.7	34.4	37.0	39.6
102.5°	168.8	168.5	168.2	167.9	167.6	167.4	153.4	125.3	97.2	69.1	41.0
105°	211.2	215.8	220.4	225.1	229.7	232.0	210.9	168.8	126.7	84.5	42.4
107.5°	260.5	264.4	268.2	272.1	276.0	277.9	251.9	199.9	147.8	95.8	43.8
110°	307.7	310.9	314.2	317.4	320.7	322.3	300.0	255.4	210.8	166.2	121.6

TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	352.2	355.0	357.8	360.5	363.3	364.7	363.4	360.8	358.1	355.5	352.9
115°	399.4	402.0	404.6	407.3	409.9	411.2	413.1	417.0	420.9	424.7	428.6
117.5°	440.4	443.5	446.6	449.7	452.8	454.3	455.6	458.2	460.9	463.5	466.1
120°	486.2	488.5	490.9	493.2	495.5	496.7	498.1	500.9	503.6	506.4	509.2
122.5°	525.1	527.6	530.1	532.6	535.1	536.3	537.8	540.9	544.0	547.0	550.1
125°	564.7	566.7	568.7	570.8	572.8	573.8	575.3	578.2	581.1	584.1	587.0
127.5°	600.9	603.1	605.2	607.4	609.5	610.6	611.8	614.1	616.4	618.7	621.0
130°	634.9	637.4	639.8	642.3	644.8	646.0	646.8	648.5	650.2	651.9	653.6
132.5°	669.6	671.6	673.6	675.7	677.7	678.7	679.5	681.2	682.9	684.6	686.3
135°	698.8	701.3	703.7	706.2	708.7	709.9	710.6	712.0	713.4	714.8	716.2
137.5°	729.4	731.2	733.1	734.9	736.8	737.7	738.5	740.0	741.5	743.1	744.6
140°	759.2	760.4	761.7	762.9	764.2	764.8	765.6	767.3	769.0	770.7	772.4
142.5°	784.2	785.3	786.4	787.5	788.6	789.1	790.1	792.1	794.1	796.1	798.1
145°	810.6	810.4	810.3	810.1	810.0	809.9	811.2	813.8	816.5	819.1	821.7
147.5°	833.6	833.1	832.7	832.2	831.7	831.5	832.8	835.4	838.1	840.7	843.3
150°	855.8	854.7	853.6	852.5	851.4	850.9	852.1	854.6	857.1	859.5	862.0
152.5°	874.5	873.3	872.1	870.8	869.6	869.0	870.2	872.5	874.8	877.1	879.4
155°	892.6	891.2	889.8	888.4	887.0	886.3	887.2	889.1	891.0	892.8	894.7
157.5°	907.2	906.0	904.7	903.5	902.2	901.6	902.3	903.7	905.1	906.5	907.9
160°	919.7	918.8	917.8	916.9	916.0	915.5	916.0	916.9	917.8	918.8	919.7
162.5°	930.8	929.9	928.9	928.0	927.1	926.6	927.0	927.8	928.5	929.3	930.1
165°	940.5	939.6	938.7	937.8	936.9	936.4	936.6	937.1	937.5	938.0	938.4
167.5°	948.2	947.3	946.3	945.4	944.5	944.0	944.2	944.7	945.2	945.6	946.1
170°	954.4	953.5	952.6	951.7	950.8	950.3	950.4	950.7	951.0	951.3	951.6
172.5°	958.6	957.7	956.7	955.8	954.9	954.4	954.6	954.9	955.2	955.5	955.8
175°	962.1	961.0	959.9	958.8	957.7	957.2	957.4	957.7	958.0	958.3	958.6
177.5°	963.4	962.3	961.3	960.2	959.1	958.6	958.7	958.8	959.0	959.1	959.3
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2275.7	2278.7	2283.3	2304.7	2307.7	2313.8	2310.8	2310.8	2312.3	2309.3	2310.8
5°	2373.4	2378.0	2400.9	2426.9	2433.0	2426.9	2434.5	2445.2	2445.2	2445.2	2442.1
7.5°	2465.0	2481.8	2507.8	2546.0	2553.6	2561.3	2575.0	2565.8	2568.9	2582.6	2578.1
10°	2553.6	2578.1	2607.1	2639.1	2655.9	2666.6	2672.7	2686.5	2718.6	2681.9	2695.7
12.5°	2637.6	2672.7	2703.3	2738.4	2750.6	2764.4	2769.0	2781.2	2781.2	2779.7	2790.3
15°	2692.6	2724.7	2752.2	2775.1	2778.1	2775.1	2772.0	2773.5	2778.1	2759.8	2770.5
17.5°	2704.8	2707.9	2717.0	2707.9	2709.4	2677.3	2659.0	2654.4	2611.7	2613.2	2648.3
20°	2645.3	2593.3	2579.6	2529.2	2498.6	2416.2	2413.1	2390.2	2300.1	2327.6	2321.5
22.5°	2481.8	2393.3	2275.7	2217.6	2188.6	2101.5	2034.3	1987.0	1954.9	1922.8	1909.1
25°	2266.5	2122.9	1956.4	1841.9	1825.1	1744.2	1620.4	1562.4	1493.7	1472.3	1509.0
27.5°	1988.5	1802.2	1614.3	1438.7	1406.6	1333.3	1270.7	1229.5	1150.0	1145.5	1148.5
30°	1611.3	1423.4	1266.1	1151.6	1072.2	1038.6	997.3	966.8	934.7	946.9	950.0
32.5°	1324.2	1145.5	998.8	937.8	901.1	879.7	844.6	824.7	811.0	806.4	804.9
35°	1052.3	933.2	867.5	807.9	786.6	771.3	745.3	736.1	723.9	725.5	725.5
37.5°	901.1	801.8	753.0	722.4	702.5	694.9	678.1	668.9	661.3	658.3	662.8
40°	777.4	708.7	678.1	650.6	633.8	630.8	621.6	610.9	601.7	603.3	607.9
42.5°	687.3	647.6	610.9	589.5	577.3	572.7	565.1	557.5	557.5	552.9	551.3
45°	615.5	583.4	552.9	533.0	525.4	519.3	510.1	508.6	502.5	504.0	505.5
47.5°	551.3	525.4	502.5	482.6	475.0	473.5	464.3	458.2	458.2	456.7	455.1
50°	493.3	467.3	447.5	436.8	426.1	423.1	421.5	420.0	416.9	416.9	418.5
52.5°	446.0	420.0	404.7	395.6	389.5	386.4	386.4	384.9	384.9	384.9	383.3
55°	394.0	372.7	360.4	357.4	354.3	352.8	351.3	348.2	346.7	349.7	346.7
57.5°	345.2	337.5	326.8	323.8	316.1	316.1	311.6	308.5	305.5	308.5	308.5
60°	307.0	296.3	290.2	281.0	274.9	268.8	261.2	259.6	256.6	255.1	253.5
62.5°	267.3	258.1	242.8	229.1	219.9	213.8	210.8	209.2	209.2	207.7	207.7
65°	223.0	201.6	194.0	189.4	187.9	186.3	183.3	181.7	183.3	181.7	183.3
67.5°	174.1	171.1	166.5	163.4	161.9	160.4	160.4	158.8	158.8	158.8	158.8
70°	151.2	143.6	142.0	139.0	139.0	137.5	137.5	137.5	137.5	135.9	139.0
72.5°	125.2	120.7	119.1	117.6	117.6	117.6	116.1	116.1	116.1	114.5	116.1
75°	102.3	100.8	97.7	97.7	96.2	97.7	96.2	96.2	94.7	96.2	96.2
77.5°	82.5	80.9	79.4	79.4	77.9	77.9	77.9	77.9	77.9	77.9	79.4
80°	62.6	61.1	59.6	61.1	59.6	61.1	59.6	59.6	61.1	59.6	59.6
82.5°	45.8	44.3	44.3	42.8	42.8	42.8	42.8	42.8	42.8	42.8	42.8
85°	27.5	26.0	26.0	27.5	26.0	27.5	26.0	26.0	26.0	27.5	27.5
87.5°	12.2	13.7	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	13.7
90°	14.7	15.5	16.2	17.0	17.4	17.6	17.9	18.2	18.5	18.8	18.5
92.5°	17.0	17.3	17.6	17.9	18.1	18.2	18.3	18.5	18.6	18.8	18.6
95°	27.9	28.7	29.4	30.2	30.6	30.5	30.4	30.2	30.1	29.9	30.1
97.5°	35.9	36.3	36.8	37.3	37.5	37.6	37.7	37.9	38.0	38.2	38.0
100°	40.8	42.1	43.3	44.6	45.2	45.3	45.6	45.9	46.2	46.5	46.2
102.5°	42.7	44.4	46.1	47.8	48.6	48.8	49.3	49.8	50.2	50.7	50.2
105°	44.1	45.8	47.5	49.2	50.0	50.3	50.9	51.6	52.2	52.8	52.2
107.5°	45.5	47.2	48.9	50.6	51.4	51.7	52.3	53.0	53.6	54.2	53.6
110°	106.2	90.7	75.3	59.8	52.1	52.4	53.0	53.7	54.3	54.9	54.3

TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	286.4	219.8	153.3	86.8	53.5	53.7	54.2	54.7	55.1	55.6	55.1
115°	357.1	285.7	214.2	142.7	107.0	101.4	90.3	79.2	68.1	57.0	68.1
117.5°	444.0	422.0	399.9	377.8	366.8	346.6	306.1	265.7	225.2	184.8	225.2
120°	511.0	512.9	514.7	516.6	517.5	507.1	486.2	465.4	444.5	423.7	444.5
122.5°	551.0	552.0	552.9	553.8	554.3	554.4	554.5	554.7	554.8	555.0	554.8
125°	588.1	589.1	590.2	591.3	591.8	592.0	592.5	593.0	593.4	593.9	593.4
127.5°	622.5	624.1	625.6	627.1	627.9	628.0	628.1	628.3	628.4	628.6	628.4
130°	655.3	657.0	658.7	660.4	661.3	661.2	661.1	660.9	660.8	660.6	660.8
132.5°	687.7	689.1	690.4	691.8	692.5	692.4	692.3	692.1	692.0	691.8	692.0
135°	717.7	719.3	720.8	722.3	723.1	722.9	722.6	722.3	722.0	721.7	722.0
137.5°	746.2	747.7	749.3	750.8	751.6	751.4	750.9	750.4	750.0	749.5	750.0
140°	773.8	775.2	776.6	778.0	778.7	778.3	777.5	776.8	776.0	775.2	776.0
142.5°	799.3	800.6	801.8	803.1	803.7	803.3	802.5	801.8	801.0	800.2	801.0
145°	822.8	823.9	825.0	826.1	826.6	826.2	825.4	824.7	823.9	823.1	823.9
147.5°	844.1	844.9	845.6	846.4	846.8	846.5	845.9	845.2	844.6	844.0	844.6
150°	862.9	863.9	864.8	865.7	866.2	865.8	865.0	864.3	863.5	862.7	863.5
152.5°	880.3	881.3	882.2	883.1	883.6	883.1	882.0	880.9	879.8	878.7	879.8
155°	895.6	896.5	897.4	898.3	898.8	898.2	897.0	895.7	894.5	893.3	894.5
157.5°	909.0	910.0	911.1	912.2	912.7	912.1	910.9	909.6	908.4	907.2	908.4
160°	920.6	921.6	922.5	923.4	923.9	923.4	922.3	921.2	920.1	919.0	920.1
162.5°	931.2	932.3	933.4	934.5	935.0	934.3	932.9	931.5	930.1	928.7	930.1
165°	939.5	940.6	941.7	942.8	943.3	942.8	941.7	940.6	939.5	938.4	939.5
167.5°	947.2	948.2	949.3	950.4	950.9	950.2	948.8	947.5	946.1	944.7	946.1
170°	952.7	953.8	954.9	956.0	956.5	955.8	954.4	953.1	951.7	950.3	951.7
172.5°	956.9	958.0	959.1	960.2	960.7	960.0	958.6	957.2	955.8	954.4	955.8
175°	959.7	960.7	961.8	962.9	963.4	962.6	961.1	959.6	958.0	956.5	958.0
177.5°	960.4	961.4	962.5	963.6	964.1	963.4	962.0	960.7	959.3	957.9	959.3
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2316.9	2306.2	2303.1	2306.2	2303.1	2304.7	2294.0	2254.3	2265.0	2248.2	2257.3
5°	2448.2	2439.1	2419.2	2416.2	2413.1	2410.1	2394.8	2359.7	2345.9	2323.0	2321.5
7.5°	2573.5	2573.5	2558.2	2547.5	2533.8	2523.1	2503.2	2451.3	2429.9	2402.4	2387.1
10°	2697.2	2657.5	2674.3	2663.6	2630.0	2623.9	2587.2	2556.7	2515.4	2487.9	2463.5
12.5°	2785.8	2773.5	2758.3	2749.1	2739.9	2720.1	2695.7	2617.8	2596.4	2541.4	2513.9
15°	2782.7	2775.1	2779.7	2779.7	2776.6	2772.0	2752.2	2695.7	2659.0	2605.5	2558.2
17.5°	2633.0	2652.9	2672.7	2686.5	2717.0	2730.8	2749.1	2715.5	2692.6	2646.8	2596.4
20°	2371.9	2420.7	2478.8	2491.0	2518.5	2599.4	2636.1	2665.1	2674.3	2659.0	2617.8
22.5°	2008.4	2049.6	2190.1	2187.1	2226.8	2323.0	2429.9	2517.0	2585.7	2623.9	2608.6
25°	1573.1	1631.1	1706.0	1762.5	1892.3	2035.9	2168.7	2307.7	2426.9	2532.2	2558.2
27.5°	1189.8	1266.1	1325.7	1400.5	1466.2	1635.7	1806.8	2023.6	2162.6	2362.7	2466.6
30°	962.2	997.3	1056.9	1092.0	1124.1	1253.9	1447.9	1661.7	1906.0	2136.7	2315.4
32.5°	821.7	846.1	890.4	905.7	939.3	1026.3	1148.5	1344.0	1596.0	1875.5	2110.7
35°	737.7	763.6	772.8	786.6	814.0	869.0	953.0	1095.1	1322.6	1596.0	1877.0
37.5°	665.9	679.6	705.6	714.8	723.9	765.2	821.7	921.0	1072.2	1296.7	1608.2
40°	615.5	623.1	636.9	644.5	650.6	679.6	730.0	797.2	908.7	1079.8	1366.9
42.5°	562.0	571.2	580.4	589.5	597.2	620.1	650.6	714.8	789.6	919.4	1127.1
45°	510.1	516.2	526.9	533.0	543.7	562.0	589.5	633.8	701.0	783.5	951.5
47.5°	462.8	470.4	475.0	482.6	490.3	510.1	536.1	565.1	620.1	701.0	823.2
50°	420.0	429.2	435.3	436.8	442.9	461.2	482.6	514.7	549.8	612.4	719.3
52.5°	389.5	391.0	395.6	401.7	400.1	410.8	430.7	455.1	491.8	542.2	620.1
55°	354.3	358.9	362.0	363.5	363.5	372.7	383.3	406.3	435.3	476.5	542.2
57.5°	310.0	314.6	323.8	326.8	331.4	336.0	340.6	355.9	380.3	420.0	473.5
60°	264.2	267.3	276.4	282.5	285.6	297.8	303.9	316.1	329.9	358.9	409.3
62.5°	212.3	215.3	219.9	226.0	232.1	250.5	265.7	278.0	288.7	308.5	349.7
65°	184.8	186.3	189.4	190.9	192.4	200.1	213.8	230.6	250.5	265.7	290.2
67.5°	160.4	161.9	163.4	166.5	168.0	169.5	175.6	180.2	200.1	221.5	239.8
70°	137.5	140.5	142.0	142.0	143.6	146.6	149.7	155.8	161.9	172.6	195.5
72.5°	116.1	117.6	120.7	120.7	120.7	123.7	126.8	129.8	132.9	139.0	148.1
75°	96.2	99.3	99.3	99.3	100.8	100.8	103.9	106.9	110.0	114.5	117.6
77.5°	79.4	79.4	79.4	79.4	80.9	80.9	82.5	85.5	87.1	88.6	91.6
80°	59.6	61.1	61.1	61.1	62.6	62.6	62.6	65.7	67.2	67.2	70.3
82.5°	44.3	44.3	44.3	45.8	44.3	45.8	45.8	47.3	45.8	47.3	48.9
85°	27.5	27.5	27.5	29.0	29.0	29.0	29.0	29.0	29.0	29.0	30.5
87.5°	13.7	13.7	13.7	13.7	13.7	13.7	13.7	13.7	15.3	13.7	13.7
90°	18.2	17.9	17.6	17.4	17.0	16.2	15.5	14.7	13.9	12.7	11.4
92.5°	18.5	18.3	18.2	18.1	17.9	17.6	17.3	17.0	16.7	16.2	15.8
95°	30.2	30.4	30.5	30.6	30.2	29.4	28.7	27.9	27.1	26.0	24.9
97.5°	37.9	37.7	37.6	37.5	37.3	36.8	36.3	35.9	35.4	32.9	30.5
100°	45.9	45.6	45.3	45.2	44.6	43.3	42.1	40.8	39.6	37.0	34.4
102.5°	49.8	49.3	48.8	48.6	47.8	46.1	44.4	42.7	41.0	39.1	37.2
105°	51.6	50.9	50.3	50.0	49.2	47.5	45.8	44.1	42.4	40.5	38.6
107.5°	53.0	52.3	51.7	51.4	50.6	48.9	47.2	45.5	43.8	42.0	40.2
110°	53.7	53.0	52.4	52.1	51.8	51.3	50.7	50.2	49.6	49.0	48.4

TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	54.7	54.2	53.7	53.5	86.8	153.3	219.8	286.4	352.9	355.5	358.1
115°	79.2	90.3	101.4	107.0	142.7	214.2	285.7	357.1	428.6	424.7	420.9
117.5°	265.7	306.1	346.6	366.8	377.8	399.9	422.0	444.0	466.1	463.5	460.9
120°	465.4	486.2	507.1	517.5	516.6	514.7	512.9	511.0	509.2	506.4	503.6
122.5°	554.7	554.5	554.4	554.3	553.8	552.9	552.0	551.0	550.1	547.0	544.0
125°	593.0	592.5	592.0	591.8	591.3	590.2	589.1	588.1	587.0	584.1	581.1
127.5°	628.3	628.1	628.0	627.9	627.1	625.6	624.1	622.5	621.0	618.7	616.4
130°	660.9	661.1	661.2	661.3	660.4	658.7	657.0	655.3	653.6	651.9	650.2
132.5°	692.1	692.3	692.4	692.5	691.8	690.4	689.1	687.7	686.3	684.6	682.9
135°	722.3	722.6	722.9	723.1	722.3	720.8	719.3	717.7	716.2	714.8	713.4
137.5°	750.4	750.9	751.4	751.6	750.8	749.3	747.7	746.2	744.6	743.1	741.5
140°	776.8	777.5	778.3	778.7	778.0	776.6	775.2	773.8	772.4	770.7	769.0
142.5°	801.8	802.5	803.3	803.7	803.1	801.8	800.6	799.3	798.1	796.1	794.1
145°	824.7	825.4	826.2	826.6	826.1	825.0	823.9	822.8	821.7	819.1	816.5
147.5°	845.2	845.9	846.5	846.8	846.4	845.6	844.9	844.1	843.3	840.7	838.1
150°	864.3	865.0	865.8	866.2	865.7	864.8	863.9	862.9	862.0	859.5	857.1
152.5°	880.9	882.0	883.1	883.6	883.1	882.2	881.3	880.3	879.4	877.1	874.8
155°	895.7	897.0	898.2	898.8	898.3	897.4	896.5	895.6	894.7	892.8	891.0
157.5°	909.6	910.9	912.1	912.7	912.2	911.1	910.0	909.0	907.9	906.5	905.1
160°	921.2	922.3	923.4	923.9	923.4	922.5	921.6	920.6	919.7	918.8	917.8
162.5°	931.5	932.9	934.3	935.0	934.5	933.4	932.3	931.2	930.1	929.3	928.5
165°	940.6	941.7	942.8	943.3	942.8	941.7	940.6	939.5	938.4	938.0	937.5
167.5°	947.5	948.8	950.2	950.9	950.4	949.3	948.2	947.2	946.1	945.6	945.2
170°	953.1	954.4	955.8	956.5	956.0	954.9	953.8	952.7	951.6	951.3	951.0
172.5°	957.2	958.6	960.0	960.7	960.2	959.1	958.0	956.9	955.8	955.5	955.2
175°	959.6	961.1	962.6	963.4	962.9	961.8	960.7	959.7	958.6	958.3	958.0
177.5°	960.7	962.0	963.4	964.1	963.6	962.5	961.4	960.4	959.3	959.1	959.0
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2243.6	2235.9	2235.9	2231.4	2231.4	2206.9	2206.9	2214.6	2205.4	2194.7	2179.4
5°	2301.6	2284.8	2280.2	2274.1	2254.3	2223.7	2211.5	2206.9	2188.6	2165.7	2139.7
7.5°	2356.6	2329.1	2315.4	2301.6	2275.7	2232.9	2208.4	2191.6	2164.2	2129.0	2095.4
10°	2410.1	2374.9	2339.8	2323.0	2286.3	2232.9	2197.8	2170.3	2130.6	2083.2	2035.9
12.5°	2458.9	2385.6	2379.5	2345.9	2292.5	2231.4	2177.9	2138.2	2087.8	2032.8	1977.8
15°	2501.7	2426.9	2390.2	2359.7	2289.4	2213.0	2156.5	2107.6	2040.4	1977.8	1910.6
17.5°	2523.1	2442.1	2417.7	2367.3	2295.5	2196.2	2119.9	2060.3	1987.0	1912.2	1835.8
20°	2544.5	2449.8	2410.1	2374.9	2277.2	2164.2	2078.6	2009.9	1929.0	1840.4	1756.4
22.5°	2555.1	2449.8	2402.4	2353.5	2258.9	2129.0	2028.2	1947.3	1852.6	1762.5	1661.7
25°	2536.8	2440.6	2384.1	2333.7	2226.8	2086.3	1970.2	1878.6	1777.8	1675.4	1573.1
27.5°	2491.0	2419.2	2353.5	2301.6	2182.5	2031.3	1909.1	1805.2	1701.4	1586.8	1483.0
30°	2405.5	2373.4	2321.5	2263.4	2133.6	1982.4	1837.3	1730.4	1615.9	1501.3	1392.9
32.5°	2272.6	2300.1	2266.5	2216.1	2075.6	1915.2	1761.0	1652.5	1527.3	1403.6	1304.3
35°	2110.7	2208.4	2190.1	2155.0	2014.5	1843.4	1689.2	1557.8	1432.6	1307.4	1208.1
37.5°	1933.5	2081.7	2097.0	2075.6	1944.2	1770.1	1600.6	1472.3	1344.0	1217.2	1116.4
40°	1690.7	1918.3	1967.1	1976.3	1870.9	1681.5	1504.4	1379.1	1252.4	1128.7	1006.5
42.5°	1467.7	1754.8	1815.9	1854.1	1777.8	1594.5	1415.8	1276.8	1151.6	1040.1	917.9
45°	1258.5	1557.8	1657.1	1706.0	1672.4	1495.2	1310.4	1180.6	1066.0	963.7	846.1
47.5°	1043.1	1344.0	1483.0	1560.9	1560.9	1394.4	1209.6	1081.3	971.4	884.3	780.4
50°	899.6	1150.0	1293.6	1395.9	1423.4	1292.1	1118.0	992.7	888.9	794.2	714.8
52.5°	766.7	991.2	1110.3	1217.2	1296.7	1182.1	1015.6	902.6	800.3	711.7	649.1
55°	662.8	830.8	939.3	1056.9	1145.5	1070.6	916.4	806.4	717.8	644.5	591.1
57.5°	563.6	710.2	798.8	902.6	997.3	940.8	817.1	722.4	644.5	580.4	533.0
60°	479.6	598.7	667.4	748.4	866.0	826.3	723.9	636.9	574.3	516.2	476.5
62.5°	407.8	502.5	560.5	618.5	725.5	707.1	627.7	560.5	507.1	458.2	424.6
65°	334.5	412.4	458.2	508.6	594.1	601.7	537.6	490.3	441.4	398.6	368.1
67.5°	270.3	331.4	372.7	415.4	484.1	505.5	461.2	421.5	380.3	345.2	317.7
70°	218.4	261.2	291.7	325.3	381.8	407.8	384.9	357.4	323.8	294.8	270.3
72.5°	172.6	200.1	218.4	244.4	290.2	316.1	314.6	290.2	265.7	245.9	226.0
75°	126.8	148.1	163.4	180.2	216.9	241.3	247.4	236.7	212.3	197.0	181.7
77.5°	96.2	108.4	116.1	128.3	154.3	175.6	184.8	181.7	164.9	152.7	142.0
80°	73.3	76.4	79.4	84.0	105.4	125.2	131.3	129.8	120.7	116.1	103.9
82.5°	51.9	53.5	55.0	56.5	64.1	80.9	87.1	90.1	82.5	77.9	67.2
85°	30.5	32.1	32.1	35.1	36.7	41.2	51.9	51.9	50.4	44.3	42.8
87.5°	15.3	15.3	13.7	13.7	15.3	16.8	19.9	22.9	19.9	18.3	16.8
90°	10.2	8.9	8.3	7.5	5.8	4.1	2.4	0.7	2.4	4.1	5.8
92.5°	15.3	14.8	14.6	14.9	15.5	16.2	16.8	17.4	16.8	16.2	15.5
95°	23.8	22.7	22.2	24.8	29.9	35.0	40.1	45.2	40.1	35.0	29.9
97.5°	28.0	25.5	24.3	30.6	43.3	56.0	68.6	81.3	68.6	56.0	43.3
100°	31.7	29.1	27.8	38.4	59.5	80.6	101.8	122.9	101.8	80.6	59.5
102.5°	125.3	153.4	167.4	167.6	167.9	168.2	168.5	168.8	168.5	168.2	167.9
105°	168.8	210.9	232.0	229.7	225.1	220.4	215.8	211.2	215.8	220.4	225.1
107.5°	199.9	251.9	277.9	276.0	272.1	268.2	264.4	260.5	264.4	268.2	272.1
110°	255.4	300.0	322.3	320.7	317.4	314.2	310.9	307.7	310.9	314.2	317.4

TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	360.8	363.4	364.7	363.3	360.5	357.8	355.0	352.2	355.0	357.8	360.5
115°	417.0	413.1	411.2	409.9	407.3	404.6	402.0	399.4	402.0	404.6	407.3
117.5°	458.2	455.6	454.3	452.8	449.7	446.6	443.5	440.4	443.5	446.6	449.7
120°	500.9	498.1	496.7	495.5	493.2	490.9	488.5	486.2	488.5	490.9	493.2
122.5°	540.9	537.8	536.3	535.1	532.6	530.1	527.6	525.1	527.6	530.1	532.6
125°	578.2	575.3	573.8	572.8	570.8	568.7	566.7	564.7	566.7	568.7	570.8
127.5°	614.1	611.8	610.6	609.5	607.4	605.2	603.1	600.9	603.1	605.2	607.4
130°	648.5	646.8	646.0	644.8	642.3	639.8	637.4	634.9	637.4	639.8	642.3
132.5°	681.2	679.5	678.7	677.7	675.7	673.6	671.6	669.6	671.6	673.6	675.7
135°	712.0	710.6	709.9	708.7	706.2	703.7	701.3	698.8	701.3	703.7	706.2
137.5°	740.0	738.5	737.7	736.8	734.9	733.1	731.2	729.4	731.2	733.1	734.9
140°	767.3	765.6	764.8	764.2	762.9	761.7	760.4	759.2	760.4	761.7	762.9
142.5°	792.1	790.1	789.1	788.6	787.5	786.4	785.3	784.2	785.3	786.4	787.5
145°	813.8	811.2	809.9	810.0	810.1	810.3	810.4	810.6	810.4	810.3	810.1
147.5°	835.4	832.8	831.5	831.7	832.2	832.7	833.1	833.6	833.1	832.7	832.2
150°	854.6	852.1	850.9	851.4	852.5	853.6	854.7	855.8	854.7	853.6	852.5
152.5°	872.5	870.2	869.0	869.6	870.8	872.1	873.3	874.5	873.3	872.1	870.8
155°	889.1	887.2	886.3	887.0	888.4	889.8	891.2	892.6	891.2	889.8	888.4
157.5°	903.7	902.3	901.6	902.2	903.5	904.7	906.0	907.2	906.0	904.7	903.5
160°	916.9	916.0	915.5	916.0	916.9	917.8	918.8	919.7	918.8	917.8	916.9
162.5°	927.8	927.0	926.6	927.1	928.0	928.9	929.9	930.8	929.9	928.9	928.0
165°	937.1	936.6	936.4	936.9	937.8	938.7	939.6	940.5	939.6	938.7	937.8
167.5°	944.7	944.2	944.0	944.5	945.4	946.3	947.3	948.2	947.3	946.3	945.4
170°	950.7	950.4	950.3	950.8	951.7	952.6	953.5	954.4	953.5	952.6	951.7
172.5°	954.9	954.6	954.4	954.9	955.8	956.7	957.7	958.6	957.7	956.7	955.8
175°	957.7	957.4	957.2	957.7	958.8	959.9	961.0	962.1	961.0	959.9	958.8
177.5°	958.8	958.7	958.6	959.1	960.2	961.3	962.3	963.4	962.3	961.3	960.2
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2173.3	2174.8	2179.4	2165.7	2144.3	2135.1	2107.6	2103.1	2098.5	2098.5	2103.1
5°	2124.4	2118.3	2119.9	2093.9	2063.4	2045.0	2006.8	2013.0	1993.1	1980.9	1983.9
7.5°	2071.0	2054.2	2052.7	2019.1	1980.9	1947.3	1907.6	1898.4	1880.1	1858.7	1849.5
10°	2003.8	1991.6	1968.7	1930.5	1881.6	1854.1	1800.7	1768.6	1764.0	1731.9	1719.7
12.5°	1935.1	1913.7	1890.8	1837.3	1782.3	1738.0	1698.3	1663.2	1638.8	1611.3	1593.0
15°	1855.6	1829.7	1803.7	1747.2	1683.1	1638.8	1579.2	1527.3	1455.5	1399.0	1366.9
17.5°	1768.6	1739.6	1704.4	1641.8	1579.2	1518.1	1408.2	1347.1	1296.7	1263.1	1243.2
20°	1678.5	1646.4	1611.3	1548.7	1440.2	1333.3	1272.2	1224.9	1194.3	1160.7	1136.3
22.5°	1583.8	1550.2	1512.0	1414.3	1299.7	1224.9	1177.5	1133.2	1089.0	1070.6	1058.4
25°	1495.2	1464.7	1415.8	1282.9	1192.8	1124.1	1070.6	1041.6	1018.7	994.3	971.4
27.5°	1403.6	1347.1	1278.3	1166.8	1110.3	1040.1	1001.9	980.5	940.8	924.0	913.3
30°	1293.6	1231.0	1165.3	1085.9	1020.2	971.4	936.2	901.1	878.2	861.4	843.1
32.5°	1182.1	1122.6	1081.3	998.8	950.0	899.6	866.0	844.6	811.0	800.3	792.7
35°	1085.9	1035.5	998.8	931.6	885.8	840.0	815.6	783.5	762.1	742.3	730.0
37.5°	991.2	963.7	925.5	869.0	820.2	783.5	749.9	739.2	710.2	699.5	687.3
40°	925.5	884.3	852.2	803.4	762.1	722.4	701.0	676.6	656.7	639.9	635.3
42.5°	846.1	815.6	797.2	743.8	701.0	678.1	652.1	624.7	609.4	595.6	578.8
45°	786.6	759.1	733.1	690.3	652.1	623.1	600.2	581.9	555.9	549.8	523.9
47.5°	723.9	696.4	676.6	633.8	598.7	571.2	554.4	530.0	508.6	494.8	482.6
50°	661.3	638.4	620.1	583.4	552.9	523.9	500.9	476.5	467.3	444.4	436.8
52.5°	601.7	586.5	566.6	531.5	500.9	476.5	452.1	432.2	418.5	406.3	397.1
55°	551.3	526.9	517.7	479.6	453.6	427.6	406.3	394.0	377.2	369.6	362.0
57.5°	494.8	481.1	465.8	436.8	407.8	383.3	368.1	349.7	340.6	331.4	325.3
60°	446.0	426.1	413.9	389.5	363.5	340.6	326.8	313.1	300.9	293.2	281.0
62.5°	389.5	374.2	366.5	340.6	319.2	297.8	285.6	271.9	262.7	248.9	233.7
65°	340.6	328.4	319.2	297.8	278.0	258.1	245.9	229.1	216.9	209.2	207.7
67.5°	297.8	288.7	274.9	255.1	235.2	219.9	206.2	192.4	190.9	187.9	187.9
70°	250.5	241.3	233.7	212.3	195.5	178.7	175.6	171.1	166.5	164.9	161.9
72.5°	209.2	201.6	192.4	174.1	157.3	152.7	149.7	146.6	142.0	140.5	139.0
75°	169.5	158.8	152.7	135.9	131.3	128.3	125.2	120.7	117.6	116.1	113.0
77.5°	129.8	119.1	119.1	110.0	106.9	102.3	99.3	96.2	94.7	91.6	91.6
80°	91.6	91.6	88.6	84.0	79.4	77.9	73.3	71.8	70.3	71.8	68.7
82.5°	67.2	61.1	61.1	58.0	55.0	53.5	50.4	50.4	48.9	48.9	48.9
85°	38.2	38.2	36.7	33.6	32.1	32.1	30.5	30.5	29.0	29.0	27.5
87.5°	15.3	13.7	15.3	13.7	13.7	12.2	12.2	12.2	10.7	12.2	10.7
90°	7.5	8.3	8.9	10.2	11.4	12.7	13.9	14.7	15.5	16.2	17.0
92.5°	14.9	14.6	14.8	15.3	15.8	16.2	16.7	17.0	17.3	17.6	17.9
95°	24.8	22.2	22.7	23.8	24.9	26.0	27.1	27.9	28.7	29.4	30.2
97.5°	30.6	24.3	25.5	28.0	30.5	32.9	35.4	35.9	36.3	36.8	37.3
100°	38.4	27.8	29.1	31.7	34.4	37.0	39.6	40.8	42.1	43.3	44.6
102.5°	167.6	167.4	153.4	125.3	97.2	69.1	41.0	42.7	44.4	46.1	47.8
105°	229.7	232.0	210.9	168.8	126.7	84.5	42.4	44.1	45.8	47.5	49.2
107.5°	276.0	277.9	251.9	199.9	147.8	95.8	43.8	45.5	47.2	48.9	50.6
110°	320.7	322.3	300.0	255.4	210.8	166.2	121.6	106.2	90.7	75.3	59.8

TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	363.3	364.7	363.4	360.8	358.1	355.5	352.9	286.4	219.8	153.3	86.8
115°	409.9	411.2	413.1	417.0	420.9	424.7	428.6	357.1	285.7	214.2	142.7
117.5°	452.8	454.3	455.6	458.2	460.9	463.5	466.1	444.0	422.0	399.9	377.8
120°	495.5	496.7	498.1	500.9	503.6	506.4	509.2	511.0	512.9	514.7	516.6
122.5°	535.1	536.3	537.8	540.9	544.0	547.0	550.1	551.0	552.0	552.9	553.8
125°	572.8	573.8	575.3	578.2	581.1	584.1	587.0	588.1	589.1	590.2	591.3
127.5°	609.5	610.6	611.8	614.1	616.4	618.7	621.0	622.5	624.1	625.6	627.1
130°	644.8	646.0	646.8	648.5	650.2	651.9	653.6	655.3	657.0	658.7	660.4
132.5°	677.7	678.7	679.5	681.2	682.9	684.6	686.3	687.7	689.1	690.4	691.8
135°	708.7	709.9	710.6	712.0	713.4	714.8	716.2	717.7	719.3	720.8	722.3
137.5°	736.8	737.7	738.5	740.0	741.5	743.1	744.6	746.2	747.7	749.3	750.8
140°	764.2	764.8	765.6	767.3	769.0	770.7	772.4	773.8	775.2	776.6	778.0
142.5°	788.6	789.1	790.1	792.1	794.1	796.1	798.1	799.3	800.6	801.8	803.1
145°	810.0	809.9	811.2	813.8	816.5	819.1	821.7	822.8	823.9	825.0	826.1
147.5°	831.7	831.5	832.8	835.4	838.1	840.7	843.3	844.1	844.9	845.6	846.4
150°	851.4	850.9	852.1	854.6	857.1	859.5	862.0	862.9	863.9	864.8	865.7
152.5°	869.6	869.0	870.2	872.5	874.8	877.1	879.4	880.3	881.3	882.2	883.1
155°	887.0	886.3	887.2	889.1	891.0	892.8	894.7	895.6	896.5	897.4	898.3
157.5°	902.2	901.6	902.3	903.7	905.1	906.5	907.9	909.0	910.0	911.1	912.2
160°	916.0	915.5	916.0	916.9	917.8	918.8	919.7	920.6	921.6	922.5	923.4
162.5°	927.1	926.6	927.0	927.8	928.5	929.3	930.1	931.2	932.3	933.4	934.5
165°	936.9	936.4	936.6	937.1	937.5	938.0	938.4	939.5	940.6	941.7	942.8
167.5°	944.5	944.0	944.2	944.7	945.2	945.6	946.1	947.2	948.2	949.3	950.4
170°	950.8	950.3	950.4	950.7	951.0	951.3	951.6	952.7	953.8	954.9	956.0
172.5°	954.9	954.4	954.6	954.9	955.2	955.5	955.8	956.9	958.0	959.1	960.2
175°	957.7	957.2	957.4	957.7	958.0	958.3	958.6	959.7	960.7	961.8	962.9
177.5°	959.1	958.6	958.7	958.8	959.0	959.1	959.3	960.4	961.4	962.5	963.6
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2103.1	2100.0	2090.8	2093.9	2089.3	2089.3	2086.3	2086.3	2086.3	2093.9	2089.3
5°	1988.5	1977.8	1967.1	1962.6	1958.0	1953.4	1953.4	1951.9	1965.6	1962.6	1974.8
7.5°	1846.5	1843.4	1822.0	1822.0	1814.4	1811.4	1819.0	1820.5	1822.0	1825.1	1832.7
10°	1719.7	1712.1	1681.5	1684.6	1680.0	1673.9	1678.5	1675.4	1686.1	1689.2	1686.1
12.5°	1570.0	1556.3	1522.7	1505.9	1487.6	1473.8	1490.6	1478.4	1521.2	1533.4	1567.0
15°	1371.5	1345.5	1322.6	1322.6	1305.8	1293.6	1301.2	1315.0	1324.2	1337.9	1344.0
17.5°	1238.6	1227.9	1209.6	1198.9	1194.3	1189.8	1189.8	1195.9	1215.7	1214.2	1226.4
20°	1125.6	1119.5	1110.3	1096.6	1092.0	1089.0	1089.0	1089.0	1102.7	1114.9	1122.6
22.5°	1047.7	1043.1	1037.0	1018.7	1009.5	1006.5	1014.1	1018.7	1029.4	1038.6	1046.2
25°	969.8	959.1	948.4	942.3	937.8	937.8	940.8	942.3	946.9	951.5	960.7
27.5°	905.7	898.0	882.8	866.0	866.0	861.4	864.4	867.5	878.2	893.5	901.1
30°	833.9	832.4	826.3	820.2	814.0	811.0	817.1	821.7	823.2	830.8	830.8
32.5°	782.0	771.3	760.6	754.5	751.4	749.9	751.4	757.5	757.5	766.7	777.4
35°	730.0	723.9	713.2	702.5	699.5	691.9	698.0	704.1	714.8	719.3	723.9
37.5°	673.5	665.9	661.3	658.3	652.1	653.7	649.1	658.3	667.4	665.9	668.9
40°	630.8	617.0	603.3	601.7	600.2	598.7	598.7	600.2	606.3	612.4	621.6
42.5°	575.8	571.2	559.0	546.8	543.7	540.7	537.6	543.7	555.9	566.6	571.2
45°	519.3	513.2	510.1	500.9	494.8	493.3	490.3	497.9	508.6	513.2	516.2
47.5°	467.3	465.8	456.7	458.2	453.6	455.1	453.6	458.2	458.2	462.8	465.8
50°	432.2	427.6	423.1	420.0	415.4	415.4	413.9	415.4	421.5	427.6	426.1
52.5°	397.1	389.5	387.9	386.4	383.3	386.4	381.8	383.3	389.5	392.5	391.0
55°	355.9	354.3	351.3	348.2	346.7	345.2	345.2	345.2	351.3	355.9	357.4
57.5°	323.8	316.1	310.0	310.0	303.9	302.4	305.5	307.0	311.6	314.6	317.7
60°	279.5	276.4	267.3	262.7	253.5	252.0	252.0	258.1	265.7	276.4	279.5
62.5°	232.1	227.6	226.0	226.0	226.0	226.0	226.0	226.0	226.0	227.6	227.6
65°	206.2	207.7	206.2	204.7	206.2	206.2	204.7	204.7	204.7	206.2	207.7
67.5°	184.8	183.3	184.8	183.3	181.7	181.7	180.2	181.7	183.3	184.8	184.8
70°	160.4	160.4	158.8	160.4	158.8	157.3	155.8	155.8	158.8	160.4	160.4
72.5°	137.5	137.5	135.9	135.9	132.9	132.9	134.4	132.9	132.9	137.5	137.5
75°	114.5	113.0	111.5	111.5	110.0	110.0	110.0	108.4	111.5	111.5	113.0
77.5°	90.1	90.1	90.1	88.6	88.6	87.1	87.1	88.6	88.6	88.6	90.1
80°	68.7	68.7	68.7	67.2	65.7	65.7	65.7	65.7	65.7	67.2	65.7
82.5°	47.3	47.3	47.3	47.3	47.3	45.8	45.8	45.8	47.3	47.3	45.8
85°	29.0	27.5	29.0	29.0	27.5	29.0	27.5	27.5	26.0	26.0	27.5
87.5°	12.2	10.7	9.2	9.2	10.7	9.2	9.2	9.2	10.7	9.2	9.2
90°	17.4	17.6	17.9	18.2	18.5	18.8	18.5	18.2	17.9	17.6	17.4
92.5°	18.1	18.2	18.3	18.5	18.6	18.8	18.6	18.5	18.3	18.2	18.1
95°	30.6	30.5	30.4	30.2	30.1	29.9	30.1	30.2	30.4	30.5	30.6
97.5°	37.5	37.6	37.7	37.9	38.0	38.2	38.0	37.9	37.7	37.6	37.5
100°	45.2	45.3	45.6	45.9	46.2	46.5	46.2	45.9	45.6	45.3	45.2
102.5°	48.6	48.8	49.3	49.8	50.2	50.7	50.2	49.8	49.3	48.8	48.6
105°	50.0	50.3	50.9	51.6	52.2	52.8	52.2	51.6	50.9	50.3	50.0
107.5°	51.4	51.7	52.3	53.0	53.6	54.2	53.6	53.0	52.3	51.7	51.4
110°	52.1	52.4	53.0	53.7	54.3	54.9	54.3	53.7	53.0	52.4	52.1

TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	53.5	53.7	54.2	54.7	55.1	55.6	55.1	54.7	54.2	53.7	53.5
115°	107.0	101.4	90.3	79.2	68.1	57.0	68.1	79.2	90.3	101.4	107.0
117.5°	366.8	346.6	306.1	265.7	225.2	184.8	225.2	265.7	306.1	346.6	366.8
120°	517.5	507.1	486.2	465.4	444.5	423.7	444.5	465.4	486.2	507.1	517.5
122.5°	554.3	554.4	554.5	554.7	554.8	555.0	554.8	554.7	554.5	554.4	554.3
125°	591.8	592.0	592.5	593.0	593.4	593.9	593.4	593.0	592.5	592.0	591.8
127.5°	627.9	628.0	628.1	628.3	628.4	628.6	628.4	628.3	628.1	628.0	627.9
130°	661.3	661.2	661.1	660.9	660.8	660.6	660.8	660.9	661.1	661.2	661.3
132.5°	692.5	692.4	692.3	692.1	692.0	691.8	692.0	692.1	692.3	692.4	692.5
135°	723.1	722.9	722.6	722.3	722.0	721.7	722.0	722.3	722.6	722.9	723.1
137.5°	751.6	751.4	750.9	750.4	750.0	749.5	750.0	750.4	750.9	751.4	751.6
140°	778.7	778.3	777.5	776.8	776.0	775.2	776.0	776.8	777.5	778.3	778.7
142.5°	803.7	803.3	802.5	801.8	801.0	800.2	801.0	801.8	802.5	803.3	803.7
145°	826.6	826.2	825.4	824.7	823.9	823.1	823.9	824.7	825.4	826.2	826.6
147.5°	846.8	846.5	845.9	845.2	844.6	844.0	844.6	845.2	845.9	846.5	846.8
150°	866.2	865.8	865.0	864.3	863.5	862.7	863.5	864.3	865.0	865.8	866.2
152.5°	883.6	883.1	882.0	880.9	879.8	878.7	879.8	880.9	882.0	883.1	883.6
155°	898.8	898.2	897.0	895.7	894.5	893.3	894.5	895.7	897.0	898.2	898.8
157.5°	912.7	912.1	910.9	909.6	908.4	907.2	908.4	909.6	910.9	912.1	912.7
160°	923.9	923.4	922.3	921.2	920.1	919.0	920.1	921.2	922.3	923.4	923.9
162.5°	935.0	934.3	932.9	931.5	930.1	928.7	930.1	931.5	932.9	934.3	935.0
165°	943.3	942.8	941.7	940.6	939.5	938.4	939.5	940.6	941.7	942.8	943.3
167.5°	950.9	950.2	948.8	947.5	946.1	944.7	946.1	947.5	948.8	950.2	950.9
170°	956.5	955.8	954.4	953.1	951.7	950.3	951.7	953.1	954.4	955.8	956.5
172.5°	960.7	960.0	958.6	957.2	955.8	954.4	955.8	957.2	958.6	960.0	960.7
175°	963.4	962.6	961.1	959.6	958.0	956.5	958.0	959.6	961.1	962.6	963.4
177.5°	964.1	963.4	962.0	960.7	959.3	957.9	959.3	960.7	962.0	963.4	964.1
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2093.9	2101.5	2098.5	2081.7	2098.5	2103.1	2112.2	2121.4	2127.5	2136.7	2144.3
5°	1962.6	1977.8	1987.0	1977.8	2008.4	2013.0	2034.3	2046.6	2064.9	2080.2	2092.4
7.5°	1838.8	1851.1	1869.4	1872.4	1890.8	1912.2	1942.7	1973.2	2002.3	2017.5	2031.3
10°	1706.0	1727.4	1754.8	1748.7	1776.2	1809.8	1841.9	1890.8	1915.2	1942.7	1967.1
12.5°	1573.1	1586.8	1623.5	1635.7	1675.4	1701.4	1745.7	1776.2	1837.3	1869.4	1890.8
15°	1341.0	1397.5	1443.3	1498.3	1550.2	1599.1	1638.8	1693.8	1747.2	1771.6	1806.8
17.5°	1235.6	1261.5	1289.0	1316.5	1383.7	1470.8	1541.0	1600.6	1646.4	1678.5	1719.7
20°	1125.6	1151.6	1182.1	1208.1	1249.3	1311.9	1399.0	1501.3	1556.3	1589.9	1629.6
22.5°	1047.7	1072.2	1092.0	1114.9	1147.0	1192.8	1258.5	1385.2	1458.6	1499.8	1534.9
25°	963.7	994.3	1015.6	1032.4	1058.4	1108.8	1162.3	1234.0	1365.4	1397.5	1446.3
27.5°	905.7	914.8	939.3	965.2	991.2	1018.7	1073.7	1134.8	1223.4	1293.6	1353.2
30°	837.0	859.9	882.8	893.5	916.4	956.1	989.7	1055.4	1124.1	1179.1	1250.8
32.5°	785.0	798.8	814.0	840.0	861.4	888.9	922.5	977.5	1035.5	1070.6	1125.6
35°	727.0	736.1	768.2	778.9	800.3	827.8	861.4	904.2	966.8	994.3	1034.0
37.5°	672.0	693.4	702.5	727.0	746.8	774.3	798.8	847.6	888.9	921.0	957.6
40°	629.2	638.4	655.2	676.6	693.4	714.8	745.3	780.4	824.7	850.7	882.8
42.5°	577.3	584.9	606.3	618.5	646.0	665.9	684.2	727.0	766.7	786.6	818.6
45°	520.8	539.1	552.9	577.3	592.6	617.0	639.9	670.5	707.1	730.0	748.4
47.5°	471.9	490.3	504.0	526.9	551.3	562.0	586.5	618.5	652.1	670.5	696.4
50°	432.2	438.3	464.3	475.0	500.9	522.3	539.1	566.6	603.3	614.0	635.3
52.5°	394.0	398.6	415.4	429.2	452.1	470.4	491.8	517.7	548.3	565.1	581.9
55°	360.4	363.5	371.1	386.4	401.7	424.6	444.4	468.9	494.8	513.2	528.4
57.5°	322.3	328.4	334.5	343.6	358.9	380.3	401.7	424.6	446.0	458.2	478.0
60°	278.0	287.1	297.8	308.5	319.2	334.5	358.9	380.3	400.1	410.8	426.1
62.5°	230.6	248.9	258.1	270.3	279.5	293.2	311.6	336.0	349.7	363.5	375.7
65°	207.7	209.2	210.8	223.0	239.8	253.5	270.3	288.7	310.0	319.2	328.4
67.5°	184.8	186.3	189.4	190.9	197.0	212.3	230.6	250.5	267.3	273.4	282.5
70°	161.9	161.9	168.0	169.5	171.1	172.6	187.9	207.7	223.0	230.6	241.3
72.5°	137.5	139.0	142.0	143.6	146.6	149.7	154.3	164.9	183.3	190.9	203.1
75°	113.0	114.5	116.1	117.6	122.2	123.7	128.3	134.4	142.0	151.2	158.8
77.5°	90.1	90.1	91.6	94.7	97.7	99.3	103.9	106.9	110.0	114.5	120.7
80°	67.2	68.7	68.7	71.8	71.8	73.3	74.8	79.4	82.5	85.5	88.6
82.5°	45.8	48.9	48.9	48.9	50.4	51.9	53.5	53.5	56.5	58.0	62.6
85°	27.5	29.0	29.0	29.0	27.5	30.5	30.5	32.1	32.1	32.1	33.6
87.5°	10.7	9.2	10.7	10.7	10.7	12.2	10.7	10.7	12.2	13.7	13.7
90°	17.0	16.2	15.5	14.7	13.9	12.7	11.4	10.2	8.9	8.3	7.5
92.5°	17.9	17.6	17.3	17.0	16.7	16.2	15.8	15.3	14.8	14.6	14.9
95°	30.2	29.4	28.7	27.9	27.1	26.0	24.9	23.8	22.7	22.2	24.8
97.5°	37.3	36.8	36.3	35.9	35.4	32.9	30.5	28.0	25.5	24.3	30.6
100°	44.6	43.3	42.1	40.8	39.6	37.0	34.4	31.7	29.1	27.8	38.4
102.5°	47.8	46.1	44.4	42.7	41.0	69.1	97.2	125.3	153.4	167.4	167.6
105°	49.2	47.5	45.8	44.1	42.4	84.5	126.7	168.8	210.9	232.0	229.7
107.5°	50.6	48.9	47.2	45.5	43.8	95.8	147.8	199.9	251.9	277.9	276.0
110°	59.8	75.3	90.7	106.2	121.6	166.2	210.8	255.4	300.0	322.3	320.7

TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	86.8	153.3	219.8	286.4	352.9	355.5	358.1	360.8	363.4	364.7	363.3
115°	142.7	214.2	285.7	357.1	428.6	424.7	420.9	417.0	413.1	411.2	409.9
117.5°	377.8	399.9	422.0	444.0	466.1	463.5	460.9	458.2	455.6	454.3	452.8
120°	516.6	514.7	512.9	511.0	509.2	506.4	503.6	500.9	498.1	496.7	495.5
122.5°	553.8	552.9	552.0	551.0	550.1	547.0	544.0	540.9	537.8	536.3	535.1
125°	591.3	590.2	589.1	588.1	587.0	584.1	581.1	578.2	575.3	573.8	572.8
127.5°	627.1	625.6	624.1	622.5	621.0	618.7	616.4	614.1	611.8	610.6	609.5
130°	660.4	658.7	657.0	655.3	653.6	651.9	650.2	648.5	646.8	646.0	644.8
132.5°	691.8	690.4	689.1	687.7	686.3	684.6	682.9	681.2	679.5	678.7	677.7
135°	722.3	720.8	719.3	717.7	716.2	714.8	713.4	712.0	710.6	709.9	708.7
137.5°	750.8	749.3	747.7	746.2	744.6	743.1	741.5	740.0	738.5	737.7	736.8
140°	778.0	776.6	775.2	773.8	772.4	770.7	769.0	767.3	765.6	764.8	764.2
142.5°	803.1	801.8	800.6	799.3	798.1	796.1	794.1	792.1	790.1	789.1	788.6
145°	826.1	825.0	823.9	822.8	821.7	819.1	816.5	813.8	811.2	809.9	810.0
147.5°	846.4	845.6	844.9	844.1	843.3	840.7	838.1	835.4	832.8	831.5	831.7
150°	865.7	864.8	863.9	862.9	862.0	859.5	857.1	854.6	852.1	850.9	851.4
152.5°	883.1	882.2	881.3	880.3	879.4	877.1	874.8	872.5	870.2	869.0	869.6
155°	898.3	897.4	896.5	895.6	894.7	892.8	891.0	889.1	887.2	886.3	887.0
157.5°	912.2	911.1	910.0	909.0	907.9	906.5	905.1	903.7	902.3	901.6	902.2
160°	923.4	922.5	921.6	920.6	919.7	918.8	917.8	916.9	916.0	915.5	916.0
162.5°	934.5	933.4	932.3	931.2	930.1	929.3	928.5	927.8	927.0	926.6	927.1
165°	942.8	941.7	940.6	939.5	938.4	938.0	937.5	937.1	936.6	936.4	936.9
167.5°	950.4	949.3	948.2	947.2	946.1	945.6	945.2	944.7	944.2	944.0	944.5
170°	956.0	954.9	953.8	952.7	951.6	951.3	951.0	950.7	950.4	950.3	950.8
172.5°	960.2	959.1	958.0	956.9	955.8	955.5	955.2	954.9	954.6	954.4	954.9
175°	962.9	961.8	960.7	959.7	958.6	958.3	958.0	957.7	957.4	957.2	957.7
177.5°	963.6	962.5	961.4	960.4	959.3	959.1	959.0	958.8	958.7	958.6	959.1
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2197.8	2197.8	2197.8	2197.8
2.5°	2158.0	2153.5	2181.0	2211.5
5°	2113.8	2121.4	2156.5	2199.3
7.5°	2067.9	2084.7	2126.0	2182.5
10°	2003.8	2034.3	2097.0	2155.0
12.5°	1941.2	1982.4	2042.0	2110.7
15°	1870.9	1916.7	1990.0	2072.5
17.5°	1793.0	1845.0	1930.5	2020.6
20°	1710.6	1779.3	1869.4	1967.1
22.5°	1618.9	1701.4	1794.6	1903.0
25°	1530.3	1620.4	1713.6	1838.8
27.5°	1443.3	1531.9	1635.7	1762.5
30°	1356.2	1437.2	1548.7	1684.6
32.5°	1263.1	1347.1	1464.7	1603.6
35°	1177.5	1261.5	1371.5	1509.0
37.5°	1085.9	1176.0	1281.4	1423.4
40°	979.0	1084.4	1186.7	1322.6
42.5°	890.4	1001.9	1101.2	1229.5
45°	820.2	925.5	1008.0	1133.2
47.5°	754.5	840.0	924.0	1040.1
50°	691.9	757.5	844.6	948.4
52.5°	627.7	684.2	759.1	856.8
55°	569.7	623.1	690.3	765.2
57.5°	516.2	554.4	621.6	688.8
60°	456.7	496.4	548.3	604.8
62.5°	406.3	436.8	485.7	533.0
65°	352.8	381.8	418.5	462.8
67.5°	303.9	329.9	358.9	394.0
70°	259.6	279.5	300.9	331.4
72.5°	212.3	233.7	253.5	278.0
75°	174.1	183.3	200.1	216.9
77.5°	134.4	146.6	155.8	169.5
80°	96.2	106.9	110.0	120.7
82.5°	64.1	70.3	76.4	79.4
85°	36.7	39.7	45.8	47.3
87.5°	13.7	15.3	18.3	21.4
90°	5.8	4.1	2.4	0.7
92.5°	15.5	16.2	16.8	17.4
95°	29.9	35.0	40.1	45.2
97.5°	43.3	56.0	68.6	81.3
100°	59.5	80.6	101.8	122.9
102.5°	167.9	168.2	168.5	168.8
105°	225.1	220.4	215.8	211.2
107.5°	272.1	268.2	264.4	260.5
110°	317.4	314.2	310.9	307.7

TEST NUMBER: P1008327

CATALOG NUMBER: S122RDIP-B1005D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	360.5	357.8	355.0	352.2
115°	407.3	404.6	402.0	399.4
117.5°	449.7	446.6	443.5	440.4
120°	493.2	490.9	488.5	486.2
122.5°	532.6	530.1	527.6	525.1
125°	570.8	568.7	566.7	564.7
127.5°	607.4	605.2	603.1	600.9
130°	642.3	639.8	637.4	634.9
132.5°	675.7	673.6	671.6	669.6
135°	706.2	703.7	701.3	698.8
137.5°	734.9	733.1	731.2	729.4
140°	762.9	761.7	760.4	759.2
142.5°	787.5	786.4	785.3	784.2
145°	810.1	810.3	810.4	810.6
147.5°	832.2	832.7	833.1	833.6
150°	852.5	853.6	854.7	855.8
152.5°	870.8	872.1	873.3	874.5
155°	888.4	889.8	891.2	892.6
157.5°	903.5	904.7	906.0	907.2
160°	916.9	917.8	918.8	919.7
162.5°	928.0	928.9	929.9	930.8
165°	937.8	938.7	939.6	940.5
167.5°	945.4	946.3	947.3	948.2
170°	951.7	952.6	953.5	954.4
172.5°	955.8	956.7	957.7	958.6
175°	958.8	959.9	961.0	962.1
177.5°	960.2	961.3	962.3	963.4
180°	960.0	960.0	960.0	960.0

(END OF REPORT)