

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008410

Luminaire Tested: S122RDIP-B485D330UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008410
REPORT IS A COMBINATION OF REPORTS P988270 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D330UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3009.0 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008410

CATALOG NUMBER: S122RDIP-B485D330UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008410

CATALOG NUMBER: S122RDIP-B485D330UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30
6	65	53	46	40	61	50	43	38	44	38	34	38	34	31	33	30	27
7	61	49	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13007	13007	13007
5°	13028	12374	12283
10°	12900	11736	11349
15°	12723	10983	10285
20°	12488	10128	9173
25°	12247	9249	8154
30°	11924	8392	7042
35°	11610	7529	6086
40°	11287	6682	5104
45°	10913	5806	4245
50°	10527	4962	3456
55°	10126	4119	2743
60°	9659	3294	2076
65°	9122	2511	1688
70°	8471	1823	1343
75°	7653	1390	1024
80°	6475	941	687
85°	4520	430	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10913 cd/sqm

TEST NUMBER: P1008410

CATALOG NUMBER: S122RDIP-B485D330UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.0	2.6
10°-20°	211.4	7.0
20°-30°	296.8	9.9
30°-40°	323.6	10.8
40°-50°	297.4	9.9
50°-60°	233.5	7.8
60°-70°	152.0	5.1
70°-80°	78.3	2.6
80°-90°	20.8	0.7
90°-100°	14.8	0.5
100°-110°	55.3	1.8
110°-120°	146.6	4.9
120°-130°	243.1	8.1
130°-140°	258.3	8.6
140°-150°	240.0	8.0
150°-160°	193.0	6.4
160°-170°	124.3	4.1
170°-180°	42.8	1.4
0°-30°	585.3	19.5
0°-40°	908.8	30.2
0°-60°	1439.7	47.8
0°-90°	1690.8	56.2
90°-120°	216.7	7.2
90°-150°	958.1	31.8
90°-180°	1318.0	43.8
0°-180°	3009.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	822	822	822	822	822	
5°	822	818	808	815	813	78
15°	782	773	748	734	726	220
25°	709	686	637	606	595	326
35°	611	573	508	461	445	383
45°	500	450	372	319	301	386
55°	380	322	242	197	183	340
65°	257	196	129	104	102	254
75°	137	85	60	54	54	145
85°	32	16	14	14	14	37
90°	0	4	6	8	9	3
95°	21	10	13	14	14	25
105°	99	109	20	23	25	106
115°	187	193	201	50	27	184
125°	264	269	275	277	278	236
135°	327	332	335	339	338	253
145°	380	379	385	387	386	237
155°	418	415	419	421	418	193
165°	440	439	440	442	440	124
175°	451	448	449	451	448	43
180°	450	450	450	450	450	

TEST NUMBER: P1008410

CATALOG NUMBER: S122RDIP-B485D330UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	821.7	821.7	821.7	821.7	821.7
2.5°	825.5	821.7	813.6	821.0	819.5
5°	821.7	818.0	808.3	815.0	812.8
7.5°	815.0	810.6	800.2	803.1	799.4
10°	806.1	800.9	786.0	783.8	779.3
12.5°	795.0	788.3	768.2	763.7	755.5
15°	781.6	773.4	748.1	734.0	726.5
17.5°	766.0	754.1	722.8	706.5	694.6
20°	748.1	733.2	696.1	677.5	661.1
22.5°	728.8	711.7	668.5	643.3	632.1
25°	709.4	685.6	636.6	606.1	594.9
27.5°	686.4	661.1	606.8	571.9	554.8
30°	661.8	633.6	574.1	536.2	516.1
32.5°	638.1	603.8	542.9	498.2	479.7
35°	611.3	573.4	507.9	461.1	444.7
37.5°	585.3	544.4	475.2	423.9	405.3
40°	557.7	513.1	441.0	388.2	368.9
42.5°	529.5	481.9	406.8	351.7	333.2
45°	499.7	449.9	371.8	319.0	301.2
47.5°	471.5	418.7	338.4	285.6	269.2
50°	440.2	387.4	305.6	254.3	238.7
52.5°	409.8	354.0	274.4	225.3	211.2
55°	380.0	322.0	241.7	197.1	182.9
57.5°	349.5	290.0	212.7	171.0	159.1
60°	318.3	258.8	182.2	144.3	132.4
62.5°	287.8	228.3	156.2	120.5	114.5
65°	256.6	196.3	129.4	104.1	101.9
67.5°	226.8	166.6	104.1	91.5	89.2
70°	195.6	137.6	86.3	78.8	75.9
72.5°	165.8	110.8	72.1	66.2	64.7
75°	136.8	84.8	59.5	54.3	53.5
77.5°	107.8	60.2	46.8	43.9	42.4
80°	81.1	43.1	35.7	32.7	32.7
82.5°	56.5	29.0	24.5	23.1	23.1
85°	32.0	16.4	14.1	14.1	14.1
87.5°	11.9	5.9	5.9	5.2	5.2
90°	0.3	3.9	6.5	8.1	8.8
92.5°	8.1	6.8	7.8	8.5	8.8
95°	21.1	10.4	12.7	14.3	14.0
97.5°	38.1	11.4	16.6	17.6	17.9
100°	57.6	13.0	18.5	21.1	21.8
102.5°	79.1	78.4	19.2	22.8	23.8
105°	98.9	108.7	19.8	23.4	24.7
107.5°	122.0	130.1	20.5	24.1	25.4
110°	144.1	151.0	56.9	24.4	25.7



TEST NUMBER: P1008410

CATALOG NUMBER: S122RDIP-B485D330UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	165.0	170.8	165.3	25.1	26.0
115°	187.1	192.6	200.7	50.1	26.7
117.5°	206.3	212.8	218.3	171.8	86.5
120°	227.8	232.6	238.5	242.4	198.5
122.5°	246.0	251.2	257.7	259.6	260.0
125°	264.5	268.7	274.9	277.2	278.2
127.5°	281.4	286.0	290.9	294.1	294.5
130°	297.4	302.6	306.2	309.7	309.4
132.5°	313.6	317.9	321.5	324.4	324.1
135°	327.3	332.5	335.4	338.7	338.0
137.5°	341.6	345.5	348.8	352.0	351.1
140°	355.6	358.2	361.8	364.7	363.1
142.5°	367.3	369.6	373.8	376.4	374.8
145°	379.7	379.4	384.9	387.2	385.6
147.5°	390.4	389.5	395.0	396.6	395.3
150°	400.8	398.6	403.8	405.7	404.1
152.5°	409.6	407.0	411.9	413.9	411.6
155°	418.1	415.2	419.1	421.0	418.4
157.5°	424.9	422.3	425.2	427.5	424.9
160°	430.8	428.8	430.8	432.7	430.5
162.5°	436.0	434.0	435.7	437.9	435.0
165°	440.5	438.6	439.6	441.8	439.6
167.5°	444.1	442.2	443.1	445.4	442.5
170°	447.0	445.1	445.7	448.0	445.1
172.5°	449.0	447.0	447.7	450.0	447.0
175°	450.6	448.3	449.0	451.3	448.0
177.5°	451.3	449.0	449.3	451.6	448.7
180°	449.6	449.6	449.6	449.6	449.6

(END OF REPORT)