

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009019

Luminaire Tested: S122DIP-B485D1080UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009019
REPORT IS A COMBINATION OF REPORTS P984167 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D1080UB40-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5785.0 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009019

CATALOG NUMBER: S122DIP-B485D1080UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009019

CATALOG NUMBER: S122DIP-B485D1080UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	36	35
2	86	79	73	68	77	71	66	62	57	53	50	44	42	40	32	31	29
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	27	25
4	71	61	53	47	64	55	49	44	45	40	36	35	31	29	25	23	21
5	65	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19
6	60	49	41	35	54	44	37	32	36	31	27	28	24	22	21	18	16
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	19	16	15
8	52	40	32	27	46	36	29	25	29	24	21	23	20	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	14	12
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12176	12176	12176
5°	12196	11606	11524
10°	12097	11076	10857
15°	11919	10544	10156
20°	11680	9965	9493
25°	11441	9359	8829
30°	11141	8790	8133
35°	10857	8190	7451
40°	10508	7598	6805
45°	10160	7011	6172
50°	9781	6413	5514
55°	9382	5772	4892
60°	8933	5082	4245
65°	8439	4378	3564
70°	7817	3609	2878
75°	6953	2782	2222
80°	5908	1889	1430
85°	4280	878	609

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10160 cd/sqm

TEST NUMBER: P1009019

CATALOG NUMBER: S122DIP-B485D1080UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.4	1.3
10°-20°	203.7	3.5
20°-30°	299.3	5.2
30°-40°	347.7	6.0
40°-50°	347.2	6.0
50°-60°	302.8	5.2
60°-70°	223.8	3.9
70°-80°	126.6	2.2
80°-90°	37.3	0.6
90°-100°	84.6	1.5
100°-110°	269.0	4.6
110°-120°	460.3	8.0
120°-130°	605.3	10.5
130°-140°	679.5	11.7
140°-150°	666.3	11.5
150°-160°	558.9	9.7
160°-170°	370.7	6.4
170°-180°	129.6	2.2
0°-30°	575.4	9.9
0°-40°	923.1	16.0
0°-60°	1573.1	27.2
0°-90°	1960.9	33.9
90°-120°	813.9	14.1
90°-150°	2764.9	47.8
90°-180°	3824.0	66.1
0°-180°	5785.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	769	769	769	769	769	
5°	769	766	758	764	763	73
15°	732	728	718	721	717	206
25°	663	657	644	646	644	305
35°	572	564	552	548	544	357
45°	465	460	449	441	438	359
55°	352	348	339	330	326	315
65°	237	233	226	219	215	235
75°	124	123	119	115	116	133
85°	30	30	29	27	26	34
90°	1	15	40	38	39	6
95°	60	72	74	74	72	67
105°	248	252	254	256	256	262
115°	462	469	466	465	462	457
125°	672	682	679	675	674	600
135°	869	882	884	883	880	672
145°	1055	1063	1070	1071	1066	659
155°	1206	1210	1213	1219	1215	555
165°	1312	1311	1311	1319	1314	370
175°	1366	1362	1360	1368	1361	130
180°	1368	1368	1368	1368	1368	

TEST NUMBER: P1009019

CATALOG NUMBER: S122DIP-B485D1080UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	769.2	769.2	769.2	769.2	769.2
2.5°	773.7	770.0	761.8	769.2	767.7
5°	769.2	766.3	758.1	764.0	762.6
7.5°	764.0	759.6	751.5	757.4	755.9
10°	755.9	750.7	741.8	747.8	745.5
12.5°	744.8	740.4	731.5	735.2	733.7
15°	732.2	727.8	718.2	721.1	717.4
17.5°	716.7	712.3	702.6	706.3	702.6
20°	699.7	695.2	684.9	687.1	684.2
22.5°	682.7	676.0	666.4	666.4	664.9
25°	662.7	656.8	644.2	645.7	644.2
27.5°	640.5	635.3	625.7	623.5	619.8
30°	618.3	612.4	601.3	599.1	596.1
32.5°	594.7	590.2	578.4	574.0	571.0
35°	571.7	564.3	552.5	548.1	544.4
37.5°	545.8	539.2	527.4	522.2	518.5
40°	519.2	513.3	501.5	494.8	491.9
42.5°	493.3	487.4	475.6	468.2	463.7
45°	465.2	460.0	449.0	440.8	437.9
47.5°	437.9	432.7	420.8	412.7	408.3
50°	409.0	405.3	395.0	384.6	380.9
52.5°	380.9	375.7	366.1	358.0	352.8
55°	352.1	347.6	338.7	329.9	326.2
57.5°	323.2	319.5	309.9	301.0	298.1
60°	294.4	291.4	281.1	272.9	270.7
62.5°	266.3	261.1	253.7	246.3	243.3
65°	237.4	233.0	225.6	218.9	215.2
67.5°	207.8	204.1	197.5	192.3	189.3
70°	180.5	177.5	170.9	165.7	162.7
72.5°	152.4	149.4	145.7	140.5	138.3
75°	124.3	122.8	119.1	114.6	116.1
77.5°	99.1	96.2	94.7	92.5	90.2
80°	74.0	73.2	71.7	69.5	68.0
82.5°	50.3	50.3	49.6	46.6	46.6
85°	30.3	29.6	28.8	26.6	25.9
87.5°	13.3	11.8	10.4	8.1	7.4
90°	1.2	15.0	40.4	38.1	39.2
92.5°	25.4	34.6	35.8	36.9	36.9
95°	60.0	71.6	73.9	73.9	71.6
97.5°	100.4	110.8	115.4	115.4	115.4
100°	146.6	155.8	159.3	159.3	158.1
102.5°	195.1	202.0	206.6	207.8	206.6
105°	248.2	251.6	253.9	256.2	256.2
107.5°	301.3	305.9	305.9	307.0	301.3
110°	352.0	359.0	359.0	359.0	355.5

TEST NUMBER: P1009019

CATALOG NUMBER: S122DIP-B485D1080UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	407.5	414.4	413.2	409.8	407.5
115°	461.7	468.6	466.3	465.2	461.7
117.5°	516.0	525.2	519.4	516.0	512.5
120°	570.2	579.4	570.2	570.2	566.7
122.5°	619.8	631.4	625.6	622.1	619.8
125°	671.8	682.2	678.7	675.2	674.1
127.5°	722.6	735.3	730.6	726.0	722.6
130°	769.9	784.9	782.6	780.3	775.7
132.5°	823.0	834.5	835.7	829.9	826.5
135°	869.2	881.9	884.2	883.0	879.5
137.5°	919.9	930.3	932.6	931.5	926.9
140°	965.0	975.4	981.1	981.1	976.5
142.5°	1011.1	1021.5	1025.0	1026.1	1021.5
145°	1055.0	1063.1	1070.0	1071.2	1066.5
147.5°	1094.2	1104.6	1109.2	1111.6	1106.9
150°	1134.6	1141.6	1146.2	1149.6	1146.2
152.5°	1170.4	1177.3	1183.1	1187.7	1183.1
155°	1206.2	1209.7	1213.1	1218.9	1215.4
157.5°	1237.4	1239.7	1242.0	1250.1	1244.3
160°	1265.1	1267.4	1268.5	1275.5	1270.8
162.5°	1290.5	1290.5	1291.6	1299.7	1293.9
165°	1312.4	1311.2	1311.2	1319.3	1313.5
167.5°	1332.0	1328.6	1328.6	1336.6	1330.9
170°	1347.0	1343.6	1342.4	1350.5	1343.6
172.5°	1357.4	1353.9	1352.8	1360.9	1353.9
175°	1365.5	1362.0	1359.7	1367.8	1360.9
177.5°	1370.1	1366.6	1364.3	1371.3	1364.3
180°	1367.8	1367.8	1367.8	1367.8	1367.8

(END OF REPORT)