

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009029

Luminaire Tested: S122DIP-B485D1080UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009029
REPORT IS A COMBINATION OF REPORTS P984177 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D1080UB50-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5942.6 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009029

CATALOG NUMBER: S122DIP-B485D1080UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009029

CATALOG NUMBER: S122DIP-B485D1080UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40
1	94	90	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33
2	85	78	72	67	76	70	65	61	56	53	50	43	41	39	31	29	28
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	21
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	17	14	12
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11772	11772	11772
5°	11791	11220	11141
10°	11695	10709	10497
15°	11524	10194	9819
20°	11291	9633	9177
25°	11061	9048	8536
30°	10771	8498	7863
35°	10497	7919	7203
40°	10160	7345	6579
45°	9824	6777	5966
50°	9455	6199	5332
55°	9070	5582	4729
60°	8636	4912	4104
65°	8159	4233	3447
70°	7557	3489	2783
75°	6718	2689	2149
80°	5708	1829	1383
85°	4139	851	588

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9824 cd/sqm

TEST NUMBER: P1009029

CATALOG NUMBER: S122DIP-B485D1080UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.0	1.2
10°-20°	196.9	3.3
20°-30°	289.4	4.9
30°-40°	336.1	5.7
40°-50°	335.7	5.6
50°-60°	292.7	4.9
60°-70°	216.4	3.6
70°-80°	122.4	2.1
80°-90°	36.0	0.6
90°-100°	235.3	4.0
100°-110°	795.5	13.4
110°-120°	836.1	14.1
120°-130°	687.6	11.6
130°-140°	552.5	9.3
140°-150°	417.4	7.0
150°-160°	293.4	4.9
160°-170°	172.8	2.9
170°-180°	56.2	0.9
0°-30°	556.3	9.4
0°-40°	892.4	15.0
0°-60°	1520.9	25.6
0°-90°	1895.7	31.9
90°-120°	1866.9	31.4
90°-150°	3524.5	59.3
90°-180°	4047.0	68.1
0°-180°	5942.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	744	744	744	744	744	
5°	744	741	733	739	737	71
15°	708	704	694	697	694	199
25°	641	635	623	624	623	295
35°	553	546	534	530	526	345
45°	450	445	434	426	423	347
55°	340	336	328	319	315	304
65°	230	225	218	212	208	227
75°	120	119	115	111	112	128
85°	29	29	28	26	25	33
90°	1	15	38	36	37	4
95°	39	96	438	165	127	40
105°	136	205	827	1478	1258	145
115°	240	303	692	1428	1655	238
125°	335	396	665	1157	1343	298
135°	393	469	658	972	1113	304
145°	449	516	654	812	888	282
155°	510	551	635	718	747	235
165°	556	573	608	645	655	157
175°	579	580	585	592	590	55
180°	580	580	580	580	580	

TEST NUMBER: P1009029

CATALOG NUMBER: S122DIP-B485D1080UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	743.7	743.7	743.7	743.7	743.7
2.5°	748.0	744.4	736.5	743.7	742.2
5°	743.7	740.8	732.9	738.7	737.2
7.5°	738.7	734.4	726.5	732.2	730.8
10°	730.8	725.8	717.2	722.9	720.8
12.5°	720.1	715.8	707.2	710.8	709.3
15°	707.9	703.6	694.3	697.2	693.6
17.5°	692.9	688.6	679.3	682.9	679.3
20°	676.4	672.2	662.1	664.3	661.4
22.5°	660.0	653.6	644.3	644.3	642.8
25°	640.7	635.0	622.8	624.2	622.8
27.5°	619.2	614.2	604.9	602.8	599.2
30°	597.8	592.1	581.3	579.2	576.3
32.5°	574.9	570.6	559.2	554.9	552.0
35°	552.7	545.6	534.2	529.9	526.3
37.5°	527.7	521.3	509.8	504.8	501.3
40°	502.0	496.3	484.8	478.4	475.5
42.5°	476.9	471.2	459.8	452.6	448.3
45°	449.8	444.8	434.0	426.2	423.3
47.5°	423.3	418.3	406.9	399.0	394.7
50°	395.4	391.9	381.8	371.8	368.3
52.5°	368.3	363.3	354.0	346.1	341.1
55°	340.4	336.1	327.5	318.9	315.3
57.5°	312.5	308.9	299.6	291.0	288.2
60°	284.6	281.7	271.7	263.9	261.7
62.5°	257.4	252.4	245.3	238.1	235.3
65°	229.5	225.2	218.1	211.7	208.1
67.5°	200.9	197.4	190.9	185.9	183.1
70°	174.5	171.6	165.2	160.2	157.3
72.5°	147.3	144.4	140.9	135.9	133.7
75°	120.1	118.7	115.1	110.8	112.3
77.5°	95.8	93.0	91.5	89.4	87.2
80°	71.5	70.8	69.4	67.2	65.8
82.5°	48.6	48.6	47.9	45.0	45.0
85°	29.3	28.6	27.9	25.7	25.0
87.5°	12.9	11.4	10.0	7.9	7.2
90°	1.1	15.0	38.0	36.2	36.8
92.5°	16.7	53.0	171.9	79.2	68.1
95°	39.1	96.0	437.6	165.2	127.3
97.5°	58.0	126.7	713.3	331.5	213.2
100°	86.0	155.2	881.8	660.2	399.6
102.5°	111.6	180.8	887.4	1116.2	779.1
105°	136.2	205.4	827.1	1478.5	1258.0
107.5°	163.0	230.0	771.3	1609.6	1580.6
110°	189.8	255.0	733.4	1588.4	1712.3

TEST NUMBER: P1009029

CATALOG NUMBER: S122DIP-B485D1080UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	214.3	279.0	708.8	1516.4	1710.1
115°	240.0	303.0	692.1	1428.2	1655.4
117.5°	266.8	327.0	683.1	1344.0	1572.8
120°	291.3	350.5	675.3	1268.6	1493.5
122.5°	314.8	374.5	670.9	1210.1	1410.9
125°	334.9	396.2	665.3	1157.0	1342.8
127.5°	351.6	416.9	661.9	1111.8	1279.2
130°	366.1	435.4	659.7	1066.1	1226.8
132.5°	379.5	453.2	658.6	1018.6	1172.1
135°	392.9	468.8	657.5	972.2	1112.9
137.5°	405.2	482.2	657.5	925.4	1056.0
140°	419.7	494.5	656.4	884.0	996.8
142.5°	434.2	504.6	656.4	844.4	937.7
145°	448.7	515.7	654.1	812.1	888.5
147.5°	464.4	524.6	650.8	783.6	845.0
150°	480.0	533.6	647.4	759.0	807.0
152.5°	495.6	542.5	641.8	738.4	774.7
155°	510.1	550.8	635.1	718.3	746.8
157.5°	522.4	557.6	628.4	699.3	722.2
160°	534.7	564.2	621.8	680.3	698.8
162.5°	547.0	569.3	616.2	662.5	676.4
165°	555.9	572.6	608.4	645.2	655.2
167.5°	563.7	576.0	601.7	629.6	635.1
170°	571.5	577.6	596.1	615.0	617.3
172.5°	576.0	579.4	589.4	602.2	602.8
175°	579.3	579.9	584.9	592.2	590.5
177.5°	581.6	580.5	580.5	584.9	581.6
180°	580.5	580.5	580.5	580.5	580.5

(END OF REPORT)