

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009038

Luminaire Tested: S122DIP-B485D330UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009038
REPORT IS A COMBINATION OF REPORTS P984186 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D330UB27-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3229.5 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009038

CATALOG NUMBER: S122DIP-B485D330UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009038

CATALOG NUMBER: S122DIP-B485D330UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66
1	100	96	92	88	93	90	86	83	78	76	73	68	66	64	58	57	56
2	91	84	77	72	85	78	73	68	69	64	61	60	56	54	51	49	47
3	83	74	66	60	77	69	62	57	61	55	51	53	49	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	37	33	30
6	65	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26
7	60	47	39	33	56	45	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	30	52	41	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19
10	48	36	29	24	45	34	27	23	31	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12139	12139	12139
5°	12159	11571	11488
10°	12060	11044	10825
15°	11883	10512	10125
20°	11644	9934	9464
25°	11407	9330	8802
30°	11106	8764	8109
35°	10825	8165	7428
40°	10476	7574	6783
45°	10129	6989	6152
50°	9752	6394	5497
55°	9353	5755	4877
60°	8906	5066	4232
65°	8415	4365	3554
70°	7791	3597	2869
75°	6931	2773	2216
80°	5884	1884	1425
85°	4266	878	607

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10129 cd/sqm

TEST NUMBER: P1009038

CATALOG NUMBER: S122DIP-B485D330UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.2	2.2
10°-20°	203.1	6.3
20°-30°	298.4	9.2
30°-40°	346.6	10.7
40°-50°	346.2	10.7
50°-60°	301.9	9.3
60°-70°	223.1	6.9
70°-80°	126.3	3.9
80°-90°	34.5	1.1
90°-100°	74.3	2.3
100°-110°	251.1	7.8
110°-120°	263.9	8.2
120°-130°	217.0	6.7
130°-140°	174.4	5.4
140°-150°	131.7	4.1
150°-160°	92.6	2.9
160°-170°	54.5	1.7
170°-180°	17.7	0.5
0°-30°	573.7	17.8
0°-40°	920.3	28.5
0°-60°	1568.3	48.6
0°-90°	1952.2	60.4
90°-120°	589.2	18.2
90°-150°	1112.4	34.4
90°-180°	1277.0	39.5
0°-180°	3229.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	767	764	756	762	760	73
15°	730	726	716	719	715	206
25°	661	655	642	644	642	304
35°	570	563	551	546	543	356
45°	464	459	448	440	436	358
55°	351	347	338	329	325	314
65°	237	232	225	218	215	234
75°	124	122	119	114	116	132
85°	30	30	29	26	26	34
90°	0	5	12	11	12	3
95°	12	30	138	52	40	13
105°	43	65	261	467	397	46
115°	76	96	218	451	522	75
125°	106	125	210	365	424	94
135°	124	148	208	307	351	96
145°	142	163	206	256	280	89
155°	161	174	200	227	236	74
165°	176	181	192	204	207	49
175°	183	183	185	187	186	17
180°	183	183	183	183	183	

TEST NUMBER: P1009038

CATALOG NUMBER: S122DIP-B485D330UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	766.9	766.9	766.9	766.9	766.9
2.5°	771.3	767.6	759.5	766.9	765.4
5°	766.9	763.9	755.8	761.7	760.2
7.5°	761.7	757.3	749.2	755.1	753.6
10°	753.6	748.4	739.6	745.5	743.3
12.5°	742.5	738.1	729.2	732.9	731.5
15°	730.0	725.6	716.0	718.9	715.2
17.5°	714.5	710.1	700.5	704.2	700.5
20°	697.5	693.1	682.8	685.0	682.1
22.5°	680.6	673.9	664.4	664.4	662.9
25°	660.7	654.8	642.2	643.7	642.2
27.5°	638.6	633.4	623.8	621.6	617.9
30°	616.4	610.5	599.5	597.3	594.3
32.5°	592.8	588.4	576.6	572.2	569.2
35°	570.0	562.6	550.8	546.4	542.7
37.5°	544.2	537.5	525.7	520.6	516.9
40°	517.6	511.7	499.9	493.3	490.3
42.5°	491.8	485.9	474.1	466.7	462.3
45°	463.8	458.6	447.6	439.5	436.5
47.5°	436.5	431.4	419.6	411.4	407.0
50°	407.8	404.1	393.8	383.4	379.7
52.5°	379.7	374.6	365.0	356.9	351.7
55°	351.0	346.6	337.7	328.9	325.2
57.5°	322.2	318.5	309.0	300.1	297.2
60°	293.5	290.5	280.2	272.1	269.9
62.5°	265.4	260.3	252.9	245.5	242.6
65°	236.7	232.3	224.9	218.3	214.6
67.5°	207.2	203.5	196.9	191.7	188.8
70°	179.9	177.0	170.3	165.2	162.2
72.5°	151.9	148.9	145.3	140.1	137.9
75°	123.9	122.4	118.7	114.3	115.8
77.5°	98.8	95.9	94.4	92.2	90.0
80°	73.7	73.0	71.5	69.3	67.8
82.5°	50.1	50.1	49.4	46.5	46.5
85°	30.2	29.5	28.8	26.5	25.8
87.5°	13.3	11.8	10.3	8.1	7.4
90°	0.4	4.8	12.0	11.4	11.6
92.5°	5.3	16.8	54.3	25.0	21.5
95°	12.3	30.3	138.1	52.2	40.2
97.5°	18.3	40.0	225.1	104.6	67.3
100°	27.1	49.0	278.3	208.4	126.1
102.5°	35.2	57.0	280.1	352.3	245.9
105°	43.0	64.8	261.1	466.6	397.1
107.5°	51.4	72.6	243.4	508.0	498.9
110°	59.9	80.5	231.5	501.4	540.4

TEST NUMBER: P1009038

CATALOG NUMBER: S122DIP-B485D330UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	67.6	88.1	223.7	478.6	539.7
115°	75.7	95.6	218.4	450.8	522.5
117.5°	84.2	103.2	215.6	424.2	496.4
120°	92.0	110.6	213.1	400.4	471.4
122.5°	99.4	118.2	211.7	381.9	445.3
125°	105.7	125.0	210.0	365.2	423.8
127.5°	111.0	131.6	208.9	350.9	403.7
130°	115.6	137.4	208.2	336.5	387.2
132.5°	119.8	143.0	207.9	321.4	369.9
135°	124.0	148.0	207.5	306.8	351.3
137.5°	127.9	152.2	207.5	292.1	333.3
140°	132.5	156.1	207.2	279.0	314.6
142.5°	137.0	159.2	207.2	266.5	295.9
145°	141.6	162.8	206.5	256.3	280.4
147.5°	146.6	165.6	205.4	247.3	266.7
150°	151.5	168.4	204.3	239.6	254.7
152.5°	156.4	171.2	202.6	233.0	244.5
155°	161.0	173.8	200.5	226.8	235.7
157.5°	164.9	176.0	198.4	220.7	227.9
160°	168.8	178.1	196.2	214.8	220.5
162.5°	172.6	179.7	194.5	209.1	213.5
165°	175.5	180.8	192.0	203.6	206.8
167.5°	177.9	181.8	189.9	198.7	200.5
170°	180.4	182.3	188.1	194.2	194.8
172.5°	181.8	182.8	186.0	190.0	190.2
175°	182.8	183.0	184.6	186.9	186.4
177.5°	183.6	183.2	183.2	184.6	183.6
180°	183.2	183.2	183.2	183.2	183.2

(END OF REPORT)