

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008522

Luminaire Tested: S122RDIP-B865D530UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008522
REPORT IS A COMBINATION OF REPORTS P988713 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B865D530UB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5089.0 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008522

CATALOG NUMBER: S122RDIP-B865D530UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008522

CATALOG NUMBER: S122RDIP-B865D530UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	93	90	87	84	78	76	74	67	66	64	57	56	55
2	92	85	79	74	85	79	74	70	69	65	62	60	57	54	51	49	47
3	84	75	68	62	78	70	64	59	62	57	53	53	50	47	46	43	41
4	77	67	59	53	72	63	56	50	55	50	45	48	44	41	41	38	36
5	71	60	52	46	66	56	49	44	50	44	40	43	39	36	38	34	32
6	66	54	46	40	61	51	44	38	45	39	35	39	35	31	34	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	25	23
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	23	21
10	50	38	30	26	46	36	29	25	32	27	23	28	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22945	22945	22945
5°	22982	21828	21666
10°	22755	20703	20020
15°	22442	19374	18143
20°	22028	17863	16179
25°	21605	16312	14383
30°	21034	14804	12420
35°	20477	13280	10736
40°	19911	11786	9001
45°	19252	10242	7487
50°	18569	8753	6096
55°	17861	7265	4840
60°	17035	5811	3662
65°	16086	4429	2976
70°	14941	3214	2367
75°	13504	2450	1807
80°	11417	1660	1213
85°	7967	759	586

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19252 cd/sqm

TEST NUMBER: P1008522

CATALOG NUMBER: S122RDIP-B865D530UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.8	2.7
10°-20°	372.9	7.3
20°-30°	523.6	10.3
30°-40°	570.7	11.2
40°-50°	524.5	10.3
50°-60°	412.0	8.1
60°-70°	268.1	5.3
70°-80°	138.0	2.7
80°-90°	36.5	0.7
90°-100°	23.7	0.5
100°-110°	88.3	1.7
110°-120°	234.3	4.6
120°-130°	388.6	7.6
130°-140°	412.7	8.1
140°-150°	383.6	7.5
150°-160°	308.4	6.1
160°-170°	198.7	3.9
170°-180°	68.4	1.3
0°-30°	1032.3	20.3
0°-40°	1603.1	31.5
0°-60°	2539.6	49.9
0°-90°	2982.3	58.6
90°-120°	346.3	6.8
90°-150°	1531.2	30.1
90°-180°	2107.0	41.4
0°-180°	5089.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1450	1450	1450	1450	1450	
5°	1450	1443	1426	1438	1434	137
15°	1379	1364	1320	1295	1282	388
25°	1251	1209	1123	1069	1049	576
35°	1078	1011	896	813	784	675
45°	882	794	656	563	531	681
55°	670	568	426	348	323	599
65°	452	346	228	184	180	449
75°	241	150	105	96	94	255
85°	56	29	25	25	25	65
90°	0	6	10	13	14	5
95°	34	17	20	23	22	40
105°	158	174	32	37	40	169
115°	299	308	321	80	43	294
125°	423	430	439	443	445	377
135°	523	531	536	541	540	404
145°	607	606	615	619	616	380
155°	668	664	670	673	669	308
165°	704	701	702	706	702	199
175°	720	716	718	721	716	69
180°	719	719	719	719	719	

TEST NUMBER: P1008522

CATALOG NUMBER: S122RDIP-B865D530UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1449.5	1449.5	1449.5	1449.5	1449.5
2.5°	1456.0	1449.5	1435.0	1448.1	1445.5
5°	1449.5	1442.9	1425.8	1437.7	1433.7
7.5°	1437.7	1429.8	1411.4	1416.7	1410.1
10°	1421.9	1412.7	1386.5	1382.6	1374.7
12.5°	1402.2	1390.4	1355.0	1347.1	1332.7
15°	1378.6	1364.2	1319.6	1294.7	1281.6
17.5°	1351.1	1330.1	1275.0	1246.1	1225.2
20°	1319.6	1293.4	1227.8	1195.0	1166.1
22.5°	1285.5	1255.3	1179.2	1134.6	1115.0
25°	1251.4	1209.4	1122.8	1069.1	1049.4
27.5°	1210.7	1166.1	1070.4	1008.7	978.5
30°	1167.4	1117.6	1012.7	945.8	910.3
32.5°	1125.5	1065.1	957.6	878.9	846.1
35°	1078.2	1011.3	895.9	813.3	784.4
37.5°	1032.3	960.2	838.2	747.7	714.9
40°	983.8	905.1	777.9	684.7	650.6
42.5°	934.0	850.0	717.5	620.4	587.7
45°	881.5	793.6	655.9	562.7	531.2
47.5°	831.6	738.5	596.8	503.7	474.8
50°	776.5	683.4	539.1	448.6	421.1
52.5°	722.8	624.4	484.0	397.5	372.5
55°	670.3	568.0	426.3	347.6	322.7
57.5°	616.5	511.6	375.2	301.7	280.7
60°	561.4	456.5	321.4	254.5	233.5
62.5°	507.6	402.7	275.5	212.5	202.0
65°	452.5	346.3	228.2	183.6	179.7
67.5°	400.1	293.8	183.6	161.3	157.4
70°	345.0	242.7	152.2	139.0	133.8
72.5°	292.5	195.4	127.2	116.7	114.1
75°	241.4	149.5	104.9	95.8	94.4
77.5°	190.2	106.2	82.6	77.4	74.8
80°	143.0	76.1	63.0	57.7	57.7
82.5°	99.7	51.2	43.3	40.7	40.7
85°	56.4	28.9	24.9	24.9	24.9
87.5°	21.0	10.5	10.5	9.2	9.2
90°	0.5	6.2	10.4	13.0	14.0
92.5°	13.0	10.9	12.5	13.5	14.0
95°	33.8	16.6	20.3	22.9	22.4
97.5°	60.8	18.2	26.5	28.1	28.6
100°	92.0	20.8	29.6	33.8	34.8
102.5°	126.4	125.3	30.7	36.4	38.0
105°	158.1	173.7	31.7	37.4	39.5
107.5°	195.0	208.0	32.8	38.5	40.6
110°	230.4	241.3	91.0	39.0	41.1

TEST NUMBER: P1008522

CATALOG NUMBER: S122RDIP-B865D530UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	263.6	273.0	264.2	40.0	41.6
115°	299.0	307.8	320.8	80.1	42.6
117.5°	329.7	340.1	348.9	274.6	138.3
120°	364.0	371.8	381.1	387.4	317.2
122.5°	393.1	401.4	411.8	414.9	415.5
125°	422.7	429.5	439.4	443.0	444.6
127.5°	449.8	457.1	464.9	470.1	470.6
130°	475.3	483.6	489.3	495.0	494.5
132.5°	501.3	508.0	513.7	518.4	517.9
135°	523.1	531.4	536.1	541.3	540.3
137.5°	546.0	552.2	557.4	562.6	561.1
140°	568.3	572.5	578.2	582.9	580.3
142.5°	587.1	590.7	597.5	601.6	599.0
145°	606.8	606.3	615.1	618.8	616.2
147.5°	624.0	622.4	631.3	633.9	631.8
150°	640.6	637.0	645.3	648.4	645.8
152.5°	654.7	650.5	658.3	661.4	657.8
155°	668.2	663.5	669.7	672.9	668.7
157.5°	679.1	674.9	679.6	683.3	679.1
160°	688.5	685.3	688.5	691.6	687.9
162.5°	696.8	693.7	696.3	699.9	695.2
165°	704.1	700.9	702.5	706.1	702.5
167.5°	709.8	706.7	708.2	711.9	707.2
170°	714.5	711.3	712.4	716.0	711.3
172.5°	717.6	714.5	715.5	719.1	714.5
175°	720.2	716.5	717.6	721.2	716.0
177.5°	721.2	717.6	718.1	721.7	717.1
180°	718.6	718.6	718.6	718.6	718.6

(END OF REPORT)