

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008542

Luminaire Tested: S122RDIP-B865D925UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008542
REPORT IS A COMBINATION OF REPORTS P988793 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B865D925UB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6626.0 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008542

CATALOG NUMBER: S122RDIP-B865D925UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008542

CATALOG NUMBER: S122RDIP-B865D925UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38
3	81	72	65	60	74	67	60	56	56	51	48	46	43	40	37	35	33
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29
5	69	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	22
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	16
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22945	22945	22945
5°	22982	21828	21666
10°	22755	20703	20020
15°	22442	19374	18143
20°	22028	17863	16179
25°	21605	16312	14383
30°	21034	14804	12420
35°	20477	13280	10736
40°	19911	11786	9001
45°	19252	10242	7487
50°	18569	8753	6096
55°	17861	7265	4840
60°	17035	5811	3662
65°	16086	4429	2976
70°	14941	3214	2367
75°	13504	2450	1807
80°	11417	1660	1213
85°	7967	759	586

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19252 cd/sqm

TEST NUMBER: P1008542

CATALOG NUMBER: S122RDIP-B865D925UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.8	2.1
10°-20°	372.9	5.6
20°-30°	523.6	7.9
30°-40°	570.7	8.6
40°-50°	524.5	7.9
50°-60°	412.0	6.2
60°-70°	268.1	4.0
70°-80°	138.0	2.1
80°-90°	37.5	0.6
90°-100°	41.0	0.6
100°-110°	152.7	2.3
110°-120°	405.1	6.1
120°-130°	671.9	10.1
130°-140°	713.7	10.8
140°-150°	663.3	10.0
150°-160°	533.3	8.0
160°-170°	343.6	5.2
170°-180°	118.3	1.8
0°-30°	1032.3	15.6
0°-40°	1603.1	24.2
0°-60°	2539.6	38.3
0°-90°	2983.2	45.0
90°-120°	598.8	9.0
90°-150°	2647.7	40.0
90°-180°	3643.0	55.0
0°-180°	6626.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1450	1450	1450	1450	1450	
5°	1450	1443	1426	1438	1434	137
15°	1379	1364	1320	1295	1282	388
25°	1251	1209	1123	1069	1049	576
35°	1078	1011	896	813	784	675
45°	882	794	656	563	531	681
55°	670	568	426	348	323	599
65°	452	346	228	184	180	449
75°	241	150	105	96	94	255
85°	56	29	25	25	25	65
90°	1	11	18	22	24	6
95°	58	29	35	40	39	69
105°	273	300	55	65	68	292
115°	517	532	555	138	74	509
125°	731	743	760	766	769	652
135°	904	919	927	936	934	699
145°	1049	1048	1064	1070	1066	656
155°	1155	1147	1158	1164	1156	532
165°	1217	1212	1215	1221	1215	344
175°	1245	1239	1241	1247	1238	119
180°	1243	1243	1243	1243	1243	

TEST NUMBER: P1008542

CATALOG NUMBER: S122RDIP-B865D925UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1449.5	1449.5	1449.5	1449.5	1449.5
2.5°	1456.0	1449.5	1435.0	1448.1	1445.5
5°	1449.5	1442.9	1425.8	1437.7	1433.7
7.5°	1437.7	1429.8	1411.4	1416.7	1410.1
10°	1421.9	1412.7	1386.5	1382.6	1374.7
12.5°	1402.2	1390.4	1355.0	1347.1	1332.7
15°	1378.6	1364.2	1319.6	1294.7	1281.6
17.5°	1351.1	1330.1	1275.0	1246.1	1225.2
20°	1319.6	1293.4	1227.8	1195.0	1166.1
22.5°	1285.5	1255.3	1179.2	1134.6	1115.0
25°	1251.4	1209.4	1122.8	1069.1	1049.4
27.5°	1210.7	1166.1	1070.4	1008.7	978.5
30°	1167.4	1117.6	1012.7	945.8	910.3
32.5°	1125.5	1065.1	957.6	878.9	846.1
35°	1078.2	1011.3	895.9	813.3	784.4
37.5°	1032.3	960.2	838.2	747.7	714.9
40°	983.8	905.1	777.9	684.7	650.6
42.5°	934.0	850.0	717.5	620.4	587.7
45°	881.5	793.6	655.9	562.7	531.2
47.5°	831.6	738.5	596.8	503.7	474.8
50°	776.5	683.4	539.1	448.6	421.1
52.5°	722.8	624.4	484.0	397.5	372.5
55°	670.3	568.0	426.3	347.6	322.7
57.5°	616.5	511.6	375.2	301.7	280.7
60°	561.4	456.5	321.4	254.5	233.5
62.5°	507.6	402.7	275.5	212.5	202.0
65°	452.5	346.3	228.2	183.6	179.7
67.5°	400.1	293.8	183.6	161.3	157.4
70°	345.0	242.7	152.2	139.0	133.8
72.5°	292.5	195.4	127.2	116.7	114.1
75°	241.4	149.5	104.9	95.8	94.4
77.5°	190.2	106.2	82.6	77.4	74.8
80°	143.0	76.1	63.0	57.7	57.7
82.5°	99.7	51.2	43.3	40.7	40.7
85°	56.4	28.9	24.9	24.9	24.9
87.5°	21.0	10.5	10.5	9.2	9.2
90°	0.9	10.8	18.0	22.5	24.3
92.5°	22.5	18.9	21.6	23.4	24.3
95°	58.4	28.8	35.1	39.6	38.7
97.5°	105.2	31.5	45.9	48.6	49.5
100°	159.1	36.0	51.2	58.4	60.2
102.5°	218.5	216.7	53.0	62.9	65.6
105°	273.3	300.3	54.8	64.7	68.3
107.5°	337.2	359.6	56.6	66.5	70.1
110°	398.3	417.2	157.3	67.4	71.0

TEST NUMBER: P1008542

CATALOG NUMBER: S122RDIP-B865D925UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	455.9	472.0	456.8	69.2	71.9
115°	517.0	532.3	554.8	138.5	73.7
117.5°	570.0	588.0	603.3	474.7	239.2
120°	629.4	642.9	659.1	669.8	548.5
122.5°	679.7	694.1	712.1	717.5	718.4
125°	731.0	742.7	759.8	766.0	768.7
127.5°	777.7	790.3	803.8	812.8	813.7
130°	821.8	836.2	846.1	856.0	855.1
132.5°	866.8	878.4	888.3	896.4	895.5
135°	904.5	918.9	927.0	936.0	934.2
137.5°	944.1	954.9	963.9	972.8	970.1
140°	982.7	989.9	999.8	1007.9	1003.4
142.5°	1015.1	1021.4	1033.1	1040.3	1035.8
145°	1049.3	1048.4	1063.7	1070.0	1065.5
147.5°	1078.9	1076.2	1091.5	1096.0	1092.4
150°	1107.7	1101.4	1115.8	1121.2	1116.7
152.5°	1132.0	1124.8	1138.3	1143.7	1137.4
155°	1155.4	1147.3	1158.1	1163.5	1156.3
157.5°	1174.2	1167.1	1175.1	1181.4	1174.2
160°	1190.4	1185.0	1190.4	1195.8	1189.5
162.5°	1204.8	1199.4	1203.9	1210.2	1202.1
165°	1217.4	1212.0	1214.7	1221.0	1214.7
167.5°	1227.3	1221.9	1224.6	1230.9	1222.8
170°	1235.4	1230.0	1231.8	1238.1	1230.0
172.5°	1240.8	1235.4	1237.2	1243.5	1235.4
175°	1245.3	1239.0	1240.8	1247.1	1238.1
177.5°	1247.1	1240.8	1241.7	1248.0	1239.9
180°	1242.6	1242.6	1242.6	1242.6	1242.6

(END OF REPORT)