

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008560

Luminaire Tested: S122DIP-B1005D1080UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008560
REPORT IS A COMBINATION OF REPORTS P983549 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D1080UB30-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7914.0 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008560

CATALOG NUMBER: S122DIP-B1005D1080UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1008560

CATALOG NUMBER: S122DIP-B1005D1080UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	90	86	91	87	83	80	74	71	69	62	60	58	51	50	48
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	45	43	41
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	22	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25286	25286	25286
5°	25327	24101	23931
10°	25120	23004	22546
15°	24753	21896	21092
20°	24255	20693	19713
25°	23759	19436	18336
30°	23137	18254	16892
35°	22549	17008	15473
40°	21822	15778	14131
45°	21100	14558	12816
50°	20312	13317	11451
55°	19481	11990	10160
60°	18550	10553	8816
65°	17526	9093	7403
70°	16232	7493	5978
75°	14433	5777	4615
80°	12263	3926	2971
85°	8899	1826	1265

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21100 cd/sqm

TEST NUMBER: P1008560

CATALOG NUMBER: S122DIP-B1005D1080UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.3	1.9
10°-20°	423.0	5.3
20°-30°	621.6	7.9
30°-40°	722.0	9.1
40°-50°	721.1	9.1
50°-60°	628.8	7.9
60°-70°	464.8	5.9
70°-80°	263.0	3.3
80°-90°	73.3	0.9
90°-100°	85.1	1.1
100°-110°	270.5	3.4
110°-120°	462.9	5.8
120°-130°	608.8	7.7
130°-140°	683.4	8.6
140°-150°	670.1	8.5
150°-160°	562.1	7.1
160°-170°	372.8	4.7
170°-180°	130.3	1.6
0°-30°	1195.0	15.1
0°-40°	1917.0	24.2
0°-60°	3266.8	41.3
0°-90°	4067.9	51.4
90°-120°	818.5	10.3
90°-150°	2780.8	35.1
90°-180°	3846.0	48.6
0°-180°	7914.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1597	1597	1597	1597	1597	
5°	1597	1591	1574	1587	1584	152
15°	1521	1511	1491	1498	1490	428
25°	1376	1364	1338	1341	1338	633
35°	1187	1172	1147	1138	1130	741
45°	966	955	932	915	909	746
55°	731	722	704	685	677	654
65°	493	484	468	455	447	487
75°	258	255	247	238	241	275
85°	63	61	60	55	54	70
90°	1	15	41	38	40	8
95°	60	72	74	74	72	67
105°	250	253	255	258	258	264
115°	464	471	469	468	464	459
125°	676	686	683	679	678	604
135°	874	887	889	888	885	675
145°	1061	1069	1076	1077	1073	663
155°	1213	1217	1220	1226	1222	558
165°	1320	1319	1319	1327	1321	372
175°	1373	1370	1368	1376	1369	130
180°	1376	1376	1376	1376	1376	

TEST NUMBER: P1008560

CATALOG NUMBER: S122DIP-B1005D1080UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1597.4	1597.4	1597.4	1597.4	1597.4
2.5°	1606.6	1598.9	1582.0	1597.4	1594.3
5°	1597.4	1591.2	1574.3	1586.6	1583.6
7.5°	1586.6	1577.4	1560.5	1572.8	1569.7
10°	1569.7	1559.0	1540.6	1552.8	1548.2
12.5°	1546.7	1537.5	1519.1	1526.7	1523.7
15°	1520.6	1511.4	1491.4	1497.5	1489.9
17.5°	1488.3	1479.1	1459.1	1466.8	1459.1
20°	1453.0	1443.8	1422.3	1426.9	1420.8
22.5°	1417.7	1403.9	1383.9	1383.9	1380.8
25°	1376.2	1363.9	1337.8	1340.9	1337.8
27.5°	1330.1	1319.4	1299.4	1294.8	1287.1
30°	1284.1	1271.8	1248.7	1244.1	1238.0
32.5°	1234.9	1225.7	1201.1	1191.9	1185.8
35°	1187.3	1171.9	1147.4	1138.1	1130.5
37.5°	1133.5	1119.7	1095.1	1084.4	1076.7
40°	1078.2	1065.9	1041.4	1027.5	1021.4
42.5°	1024.5	1012.2	987.6	972.3	963.0
45°	966.1	955.4	932.3	915.4	909.3
47.5°	909.3	898.5	874.0	857.1	847.8
50°	849.4	841.7	820.2	798.7	791.0
52.5°	791.0	780.3	760.3	743.4	732.6
55°	731.1	721.9	703.5	685.0	677.4
57.5°	671.2	663.5	643.6	625.1	619.0
60°	611.3	605.2	583.7	566.8	562.2
62.5°	552.9	542.2	526.8	511.5	505.3
65°	493.0	483.8	468.5	454.6	447.0
67.5°	431.6	423.9	410.1	399.3	393.2
70°	374.8	368.6	354.8	344.1	337.9
72.5°	316.4	310.3	302.6	291.8	287.2
75°	258.0	255.0	247.3	238.1	241.1
77.5°	205.8	199.7	196.6	192.0	187.4
80°	153.6	152.1	149.0	144.4	141.3
82.5°	104.4	104.4	102.9	96.8	96.8
85°	63.0	61.4	59.9	55.3	53.8
87.5°	27.6	24.6	21.5	16.9	15.4
90°	1.2	15.1	40.6	38.3	39.5
92.5°	25.5	34.8	36.0	37.1	37.1
95°	60.4	72.0	74.3	74.3	72.0
97.5°	101.0	111.4	116.1	116.1	116.1
100°	147.4	156.7	160.2	160.2	159.0
102.5°	196.2	203.2	207.8	209.0	207.8
105°	249.6	253.1	255.4	257.7	257.7
107.5°	303.0	307.6	307.6	308.8	303.0
110°	354.1	361.0	361.0	361.0	357.6

TEST NUMBER: P1008560

CATALOG NUMBER: S122DIP-B1005D1080UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	409.8	416.8	415.6	412.1	409.8
115°	464.4	471.3	469.0	467.8	464.4
117.5°	518.9	528.2	522.4	518.9	515.4
120°	573.5	582.8	573.5	573.5	570.0
122.5°	623.4	635.0	629.2	625.7	623.4
125°	675.6	686.1	682.6	679.1	678.0
127.5°	726.7	739.5	734.8	730.2	726.7
130°	774.3	789.4	787.1	784.8	780.1
132.5°	827.7	839.3	840.5	834.7	831.2
135°	874.2	886.9	889.2	888.1	884.6
137.5°	925.2	935.7	938.0	936.8	932.2
140°	970.5	981.0	986.8	986.8	982.1
142.5°	1016.9	1027.4	1030.9	1032.0	1027.4
145°	1061.1	1069.2	1076.1	1077.3	1072.7
147.5°	1100.5	1111.0	1115.6	1117.9	1113.3
150°	1141.2	1148.1	1152.8	1156.3	1152.8
152.5°	1177.1	1184.1	1189.9	1194.6	1189.9
155°	1213.1	1216.6	1220.1	1225.9	1222.4
157.5°	1244.5	1246.8	1249.1	1257.2	1251.4
160°	1272.3	1274.7	1275.8	1282.8	1278.1
162.5°	1297.9	1297.9	1299.0	1307.2	1301.4
165°	1319.9	1318.8	1318.8	1326.9	1321.1
167.5°	1339.7	1336.2	1336.2	1344.3	1338.5
170°	1354.8	1351.3	1350.1	1358.2	1351.3
172.5°	1365.2	1361.7	1360.6	1368.7	1361.7
175°	1373.3	1369.9	1367.5	1375.7	1368.7
177.5°	1378.0	1374.5	1372.2	1379.1	1372.2
180°	1375.7	1375.7	1375.7	1375.7	1375.7

(END OF REPORT)