

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009101

Luminaire Tested: S122DIP-B485D530UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009101
REPORT IS A COMBINATION OF REPORTS P984279 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D530UB35-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4058.4 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009101

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009101

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49		
1	98	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46	41		
2	89	81	75	70	81	75	70	65	63	60	56	53	50	47	43	41	39	34		
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33	29		
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29	25		
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	27	25	22		
6	63	51	42	37	57	47	40	35	40	34	30	34	29	26	28	25	22	19		
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17		
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15		
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	21	18	16	14		
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12295	12295	12295
5°	12315	11719	11636
10°	12213	11184	10963
15°	12035	10647	10255
20°	11794	10061	9585
25°	11552	9451	8916
30°	11249	8876	8212
35°	10964	8270	7524
40°	10611	7671	6870
45°	10258	7078	6231
50°	9876	6475	5568
55°	9473	5829	4939
60°	9018	5131	4286
65°	8521	4421	3599
70°	7891	3643	2907
75°	7021	2808	2243
80°	5964	1908	1444
85°	4322	887	614

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10258 cd/sqm

TEST NUMBER: P1009101

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.1	1.8
10°-20°	205.7	5.1
20°-30°	302.3	7.4
30°-40°	351.0	8.6
40°-50°	350.6	8.6
50°-60°	305.7	7.5
60°-70°	226.0	5.6
70°-80°	127.9	3.2
80°-90°	35.6	0.9
90°-100°	121.0	3.0
100°-110°	409.0	10.1
110°-120°	429.9	10.6
120°-130°	353.5	8.7
130°-140°	284.1	7.0
140°-150°	214.6	5.3
150°-160°	150.9	3.7
160°-170°	88.8	2.2
170°-180°	28.9	0.7
0°-30°	581.0	14.3
0°-40°	932.1	23.0
0°-60°	1588.4	39.1
0°-90°	1977.9	48.7
90°-120°	959.8	23.6
90°-150°	1811.9	44.6
90°-180°	2080.0	51.3
0°-180°	4058.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	777	777	777	777	777	
5°	777	774	766	772	770	74
15°	739	735	725	728	724	208
25°	669	663	650	652	650	308
35°	577	570	558	553	550	360
45°	470	464	453	445	442	363
55°	356	351	342	333	329	318
65°	240	235	228	221	217	237
75°	126	124	120	116	117	134
85°	31	30	29	27	26	34
90°	1	8	20	19	19	3
95°	20	49	225	85	65	21
105°	70	106	425	760	647	74
115°	123	156	356	734	851	122
125°	172	204	342	595	690	153
135°	202	241	338	500	572	156
145°	231	265	336	418	457	145
155°	262	283	326	369	384	121
165°	286	294	313	332	337	81
175°	298	298	301	304	304	28
180°	298	298	298	298	298	

TEST NUMBER: P1009101

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	776.7	776.7	776.7	776.7	776.7
2.5°	781.2	777.4	769.2	776.7	775.2
5°	776.7	773.7	765.5	771.5	770.0
7.5°	771.5	767.0	758.8	764.7	763.2
10°	763.2	758.0	749.0	755.0	752.8
12.5°	752.0	747.6	738.6	742.3	740.8
15°	739.3	734.9	725.2	728.1	724.4
17.5°	723.7	719.2	709.5	713.2	709.5
20°	706.5	702.0	691.5	693.8	690.8
22.5°	689.3	682.6	672.9	672.9	671.4
25°	669.1	663.2	650.5	652.0	650.5
27.5°	646.7	641.5	631.8	629.6	625.8
30°	624.3	618.4	607.2	604.9	601.9
32.5°	600.4	596.0	584.0	579.5	576.5
35°	577.3	569.8	557.9	553.4	549.7
37.5°	551.1	544.4	532.5	527.2	523.5
40°	524.3	518.3	506.3	499.6	496.6
42.5°	498.1	492.1	480.2	472.7	468.2
45°	469.7	464.5	453.3	445.1	442.1
47.5°	442.1	436.9	424.9	416.7	412.2
50°	413.0	409.3	398.8	388.3	384.6
52.5°	384.6	379.4	369.7	361.5	356.2
55°	355.5	351.0	342.0	333.1	329.3
57.5°	326.4	322.6	312.9	304.0	301.0
60°	297.2	294.2	283.8	275.6	273.3
62.5°	268.9	263.6	256.2	248.7	245.7
65°	239.7	235.2	227.8	221.1	217.3
67.5°	209.9	206.1	199.4	194.2	191.2
70°	182.2	179.2	172.5	167.3	164.3
72.5°	153.8	150.9	147.1	141.9	139.7
75°	125.5	124.0	120.2	115.8	117.2
77.5°	100.1	97.1	95.6	93.4	91.1
80°	74.7	73.9	72.4	70.2	68.7
82.5°	50.8	50.8	50.0	47.0	47.0
85°	30.6	29.9	29.1	26.9	26.1
87.5°	13.4	11.9	10.5	8.2	7.5
90°	0.6	7.8	19.5	18.6	18.9
92.5°	8.6	27.2	88.4	40.7	35.0
95°	20.1	49.4	224.9	84.9	65.4
97.5°	29.8	65.2	366.7	170.4	109.6
100°	44.2	79.8	453.3	339.4	205.4
102.5°	57.4	93.0	456.2	573.9	400.5
105°	70.0	105.6	425.2	760.0	646.7
107.5°	83.8	118.2	396.5	827.5	812.6
110°	97.6	131.1	377.0	816.6	880.3

TEST NUMBER: P1009101

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	110.2	143.5	364.4	779.6	879.1
115°	123.4	155.8	355.8	734.2	851.0
117.5°	137.2	168.1	351.2	690.9	808.6
120°	149.8	180.2	347.2	652.2	767.8
122.5°	161.8	192.5	344.9	622.0	725.3
125°	172.2	203.8	342.0	594.8	690.3
127.5°	180.8	214.4	340.3	571.6	657.6
130°	188.2	223.8	339.1	548.0	630.7
132.5°	195.1	233.0	338.6	523.6	602.5
135°	202.0	241.0	338.0	499.8	572.1
137.5°	208.3	247.9	338.0	475.8	542.9
140°	215.8	254.2	337.4	454.5	512.4
142.5°	223.2	259.4	337.4	434.2	482.0
145°	230.7	265.1	336.3	417.5	456.8
147.5°	238.7	269.7	334.6	402.8	434.4
150°	246.8	274.3	332.8	390.2	414.9
152.5°	254.8	278.9	330.0	379.6	398.3
155°	262.2	283.2	326.5	369.2	383.9
157.5°	268.6	286.6	323.1	359.5	371.3
160°	274.9	290.0	319.6	349.8	359.2
162.5°	281.2	292.7	316.8	340.6	347.8
165°	285.8	294.4	312.7	331.6	336.9
167.5°	289.8	296.2	309.3	323.6	326.5
170°	293.8	297.0	306.4	316.2	317.3
172.5°	296.1	297.8	303.0	309.6	309.9
175°	297.8	298.1	300.7	304.4	303.6
177.5°	299.0	298.4	298.4	300.7	299.0
180°	298.4	298.4	298.4	298.4	298.4

(END OF REPORT)