

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008576

Luminaire Tested: S122DIP-B1005D1080UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008576
REPORT IS A COMBINATION OF REPORTS P983568 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D1080UB40-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8229.8 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008576

CATALOG NUMBER: S122DIP-B1005D1080UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1008576

CATALOG NUMBER: S122DIP-B1005D1080UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83		69	69	69		55
1	98	93	89	86	90	86	83	80	73	70	68		60	59	57		49
2	89	81	75	70	82	75	70	65	64	60	56		53	50	48		43
3	81	72	64	58	74	66	60	55	56	51	47		47	43	40		38
4	74	63	55	49	68	59	52	46	50	45	40		42	38	35		34
5	68	56	48	42	62	52	45	40	45	39	35		37	33	30		31
6	63	51	43	37	58	47	40	35	40	35	30		34	30	26		28
7	58	46	38	32	53	43	35	30	36	31	27		31	26	23		25
8	54	41	34	28	49	39	32	27	33	28	24		28	24	21		23
9	50	38	30	25	46	35	29	24	30	25	21		26	22	19		22
10	47	35	28	23	43	32	26	22	28	23	19		24	20	17		20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25142	25142	25142
5°	25183	23965	23795
10°	24979	22873	22420
15°	24613	21773	20971
20°	24118	20575	19601
25°	23625	19325	18232
30°	23005	18152	16796
35°	22421	16912	15385
40°	21698	15689	14051
45°	20979	14475	12743
50°	20197	13242	11386
55°	19372	11922	10101
60°	18443	10493	8766
65°	17426	9040	7360
70°	16136	7451	5944
75°	14354	5744	4590
80°	12191	3903	2954
85°	8843	1817	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20979 cd/sqm

TEST NUMBER: P1008576

CATALOG NUMBER: S122DIP-B1005D1080UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.5	1.8
10°-20°	420.6	5.1
20°-30°	618.1	7.5
30°-40°	717.9	8.7
40°-50°	717.0	8.7
50°-60°	625.2	7.6
60°-70°	462.2	5.6
70°-80°	261.5	3.2
80°-90°	72.8	0.9
90°-100°	243.3	3.0
100°-110°	822.6	10.0
110°-120°	864.7	10.5
120°-130°	711.0	8.6
130°-140°	571.4	6.9
140°-150°	431.6	5.2
150°-160°	303.4	3.7
160°-170°	178.7	2.2
170°-180°	58.1	0.7
0°-30°	1188.2	14.4
0°-40°	1906.1	23.2
0°-60°	3248.3	39.5
0°-90°	4044.8	49.1
90°-120°	1930.6	23.5
90°-150°	3644.7	44.3
90°-180°	4185.0	50.9
0°-180°	8229.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1588	1588	1588	1588	1588	
5°	1588	1582	1565	1578	1575	151
15°	1512	1503	1483	1489	1481	426
25°	1368	1356	1330	1333	1330	630
35°	1181	1165	1141	1132	1124	737
45°	961	950	927	910	904	741
55°	727	718	700	681	674	650
65°	490	481	466	452	444	485
75°	257	254	246	237	240	274
85°	63	61	60	55	54	70
90°	1	16	39	38	38	6
95°	40	99	452	171	132	42
105°	141	212	855	1529	1301	150
115°	248	313	716	1477	1712	246
125°	346	410	688	1196	1389	308
135°	406	485	680	1005	1151	314
145°	464	533	676	840	919	291
155°	528	570	657	743	772	243
165°	575	592	629	667	678	162
175°	599	600	605	612	611	57
180°	600	600	600	600	600	

TEST NUMBER: P1008576

CATALOG NUMBER: S122DIP-B1005D1080UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1588.3	1588.3	1588.3	1588.3	1588.3
2.5°	1597.5	1589.9	1573.1	1588.3	1585.3
5°	1588.3	1582.2	1565.4	1577.7	1574.6
7.5°	1577.7	1568.5	1551.7	1563.9	1560.9
10°	1560.9	1550.2	1531.8	1544.1	1539.5
12.5°	1537.9	1528.8	1510.5	1518.1	1515.0
15°	1512.0	1502.8	1483.0	1489.1	1481.4
17.5°	1479.9	1470.7	1450.9	1458.5	1450.9
20°	1444.8	1435.6	1414.2	1418.8	1412.7
22.5°	1409.7	1395.9	1376.1	1376.1	1373.0
25°	1368.4	1356.2	1330.2	1333.3	1330.2
27.5°	1322.6	1311.9	1292.1	1287.5	1279.8
30°	1276.8	1264.6	1241.7	1237.1	1231.0
32.5°	1227.9	1218.7	1194.3	1185.1	1179.0
35°	1180.6	1165.3	1140.9	1131.7	1124.1
37.5°	1127.1	1113.4	1088.9	1078.2	1070.6
40°	1072.1	1059.9	1035.5	1021.7	1015.6
42.5°	1018.7	1006.5	982.0	966.8	957.6
45°	960.6	950.0	927.0	910.2	904.1
47.5°	904.1	893.4	869.0	852.2	843.0
50°	844.6	836.9	815.6	794.2	786.5
52.5°	786.5	775.8	756.0	739.2	728.5
55°	727.0	717.8	699.5	681.2	673.5
57.5°	667.4	659.8	639.9	621.6	615.5
60°	607.8	601.7	580.4	563.6	559.0
62.5°	549.8	539.1	523.8	508.6	502.5
65°	490.2	481.1	465.8	452.1	444.4
67.5°	429.2	421.5	407.8	397.1	391.0
70°	372.6	366.5	352.8	342.1	336.0
72.5°	314.6	308.5	300.9	290.2	285.6
75°	256.6	253.5	245.9	236.7	239.8
77.5°	204.7	198.5	195.5	190.9	186.3
80°	152.7	151.2	148.1	143.6	140.5
82.5°	103.9	103.9	102.3	96.2	96.2
85°	62.6	61.1	59.6	55.0	53.5
87.5°	27.5	24.4	21.4	16.8	15.3
90°	1.2	15.6	39.2	37.5	38.1
92.5°	17.3	54.8	177.8	81.9	70.4
95°	40.4	99.2	452.5	170.8	131.6
97.5°	60.0	131.0	737.6	342.8	220.5
100°	88.9	160.4	911.9	682.8	413.2
102.5°	115.4	187.0	917.7	1154.4	805.7
105°	140.8	212.4	855.4	1528.9	1300.9
107.5°	168.5	237.8	797.6	1664.5	1634.5
110°	196.2	263.8	758.4	1642.6	1770.7

TEST NUMBER: P1008576

CATALOG NUMBER: S122DIP-B1005D1080UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	221.6	288.6	733.0	1568.2	1768.4
115°	248.2	313.4	715.7	1477.0	1711.9
117.5°	275.9	338.2	706.4	1389.8	1626.4
120°	301.3	362.5	698.4	1311.9	1544.5
122.5°	325.5	387.2	693.7	1251.3	1459.1
125°	346.3	409.8	688.0	1196.4	1388.7
127.5°	363.6	431.2	684.5	1149.7	1322.9
130°	378.6	450.2	682.2	1102.4	1268.6
132.5°	392.5	468.6	681.1	1053.3	1212.0
135°	406.3	484.8	679.9	1005.4	1150.9
137.5°	419.0	498.7	679.9	957.0	1092.0
140°	434.0	511.4	678.7	914.2	1030.8
142.5°	449.0	521.8	678.7	873.2	969.6
145°	464.0	533.3	676.4	839.8	918.8
147.5°	480.2	542.6	673.0	810.3	873.8
150°	496.4	551.8	669.5	785.0	834.6
152.5°	512.5	561.0	663.7	763.6	801.1
155°	527.5	569.6	656.8	742.8	772.2
157.5°	540.2	576.6	649.9	723.2	746.8
160°	552.9	583.6	643.0	703.6	722.6
162.5°	565.6	588.7	637.2	685.1	699.5
165°	574.9	592.2	629.1	667.2	677.6
167.5°	582.9	595.6	622.2	651.0	656.8
170°	591.0	597.4	616.4	636.0	638.3
172.5°	595.6	599.0	609.5	622.8	623.3
175°	599.1	599.7	604.9	612.3	610.6
177.5°	601.4	600.2	600.2	604.9	601.4
180°	600.2	600.2	600.2	600.2	600.2

(END OF REPORT)