

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008621

Luminaire Tested: S122DIP-B1005D330UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008621
REPORT IS A COMBINATION OF REPORTS P983628 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D330UB40-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5323.5 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008621

CATALOG NUMBER: S122DIP-B1005D330UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1008621

CATALOG NUMBER: S122DIP-B1005D330UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	98	98	98	88	88	88	80	80	80
1	104	99	95	91	98	95	91	88	86	83	81	78	76	74	71	69	68
2	94	87	80	75	90	83	77	72	75	71	67	69	65	62	62	59	57
3	86	76	69	62	82	73	66	60	67	61	56	61	56	52	55	52	49
4	79	68	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42
5	73	60	52	46	69	58	50	44	53	47	42	49	43	39	45	40	37
6	67	54	46	40	64	52	44	39	48	41	36	44	39	34	40	36	32
7	62	49	41	35	59	47	40	34	44	37	32	40	35	30	37	32	29
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26
9	54	41	33	28	51	40	32	27	37	30	26	34	29	25	31	27	23
10	50	38	30	25	48	37	29	25	34	28	24	32	26	22	29	25	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25142	25142	25142
5°	25183	23965	23795
10°	24979	22873	22420
15°	24613	21773	20971
20°	24118	20575	19601
25°	23625	19325	18232
30°	23005	18152	16796
35°	22421	16912	15385
40°	21698	15689	14051
45°	20979	14475	12743
50°	20197	13242	11386
55°	19372	11922	10101
60°	18443	10493	8766
65°	17426	9040	7360
70°	16136	7451	5944
75°	14354	5744	4590
80°	12191	3903	2954
85°	8843	1817	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20979 cd/sqm

TEST NUMBER: P1008621

CATALOG NUMBER: S122DIP-B1005D330UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.5	2.8
10°-20°	420.6	7.9
20°-30°	618.1	11.6
30°-40°	717.9	13.5
40°-50°	717.0	13.5
50°-60°	625.2	11.7
60°-70°	462.2	8.7
70°-80°	261.5	4.9
80°-90°	70.2	1.3
90°-100°	74.5	1.4
100°-110°	251.9	4.7
110°-120°	264.8	5.0
120°-130°	217.7	4.1
130°-140°	174.9	3.3
140°-150°	132.2	2.5
150°-160°	92.9	1.7
160°-170°	54.7	1.0
170°-180°	17.8	0.3
0°-30°	1188.2	22.3
0°-40°	1906.1	35.8
0°-60°	3248.3	61.0
0°-90°	4042.2	75.9
90°-120°	591.1	11.1
90°-150°	1115.9	21.0
90°-180°	1281.0	24.1
0°-180°	5323.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1588	1588	1588	1588	1588	
5°	1588	1582	1565	1578	1575	151
15°	1512	1503	1483	1489	1481	426
25°	1368	1356	1330	1333	1330	630
35°	1181	1165	1141	1132	1124	737
45°	961	950	927	910	904	741
55°	727	718	700	681	674	650
65°	490	481	466	452	444	485
75°	257	254	246	237	240	274
85°	63	61	60	55	54	70
90°	0	5	12	12	12	5
95°	12	30	138	52	40	13
105°	43	65	262	468	398	46
115°	76	96	219	452	524	75
125°	106	125	211	366	425	94
135°	124	148	208	308	352	96
145°	142	163	207	257	281	89
155°	162	174	201	227	236	74
165°	176	181	193	204	208	50
175°	183	184	185	188	187	17
180°	184	184	184	184	184	

TEST NUMBER: P1008621

CATALOG NUMBER: S122DIP-B1005D330UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1588.3	1588.3	1588.3	1588.3	1588.3
2.5°	1597.5	1589.9	1573.1	1588.3	1585.3
5°	1588.3	1582.2	1565.4	1577.7	1574.6
7.5°	1577.7	1568.5	1551.7	1563.9	1560.9
10°	1560.9	1550.2	1531.8	1544.1	1539.5
12.5°	1537.9	1528.8	1510.5	1518.1	1515.0
15°	1512.0	1502.8	1483.0	1489.1	1481.4
17.5°	1479.9	1470.7	1450.9	1458.5	1450.9
20°	1444.8	1435.6	1414.2	1418.8	1412.7
22.5°	1409.7	1395.9	1376.1	1376.1	1373.0
25°	1368.4	1356.2	1330.2	1333.3	1330.2
27.5°	1322.6	1311.9	1292.1	1287.5	1279.8
30°	1276.8	1264.6	1241.7	1237.1	1231.0
32.5°	1227.9	1218.7	1194.3	1185.1	1179.0
35°	1180.6	1165.3	1140.9	1131.7	1124.1
37.5°	1127.1	1113.4	1088.9	1078.2	1070.6
40°	1072.1	1059.9	1035.5	1021.7	1015.6
42.5°	1018.7	1006.5	982.0	966.8	957.6
45°	960.6	950.0	927.0	910.2	904.1
47.5°	904.1	893.4	869.0	852.2	843.0
50°	844.6	836.9	815.6	794.2	786.5
52.5°	786.5	775.8	756.0	739.2	728.5
55°	727.0	717.8	699.5	681.2	673.5
57.5°	667.4	659.8	639.9	621.6	615.5
60°	607.8	601.7	580.4	563.6	559.0
62.5°	549.8	539.1	523.8	508.6	502.5
65°	490.2	481.1	465.8	452.1	444.4
67.5°	429.2	421.5	407.8	397.1	391.0
70°	372.6	366.5	352.8	342.1	336.0
72.5°	314.6	308.5	300.9	290.2	285.6
75°	256.6	253.5	245.9	236.7	239.8
77.5°	204.7	198.5	195.5	190.9	186.3
80°	152.7	151.2	148.1	143.6	140.5
82.5°	103.9	103.9	102.3	96.2	96.2
85°	62.6	61.1	59.6	55.0	53.5
87.5°	27.5	24.4	21.4	16.8	15.3
90°	0.4	4.8	12.0	11.5	11.7
92.5°	5.3	16.8	54.4	25.1	21.6
95°	12.4	30.4	138.5	52.3	40.3
97.5°	18.4	40.1	225.8	105.0	67.5
100°	27.2	49.2	279.2	209.0	126.5
102.5°	35.3	57.2	281.0	353.4	246.7
105°	43.1	65.0	261.9	468.1	398.3
107.5°	51.6	72.8	244.2	509.6	500.4
110°	60.1	80.8	232.2	502.9	542.1



TEST NUMBER: P1008621

CATALOG NUMBER: S122DIP-B1005D330UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	67.9	88.4	224.4	480.2	541.4
115°	76.0	96.0	219.1	452.2	524.1
117.5°	84.5	103.6	216.3	425.5	498.0
120°	92.2	111.0	213.8	401.6	472.9
122.5°	99.7	118.6	212.4	383.1	446.7
125°	106.0	125.4	210.6	366.4	425.2
127.5°	111.3	132.0	209.6	352.0	405.0
130°	115.9	137.9	208.9	337.5	388.4
132.5°	120.2	143.4	208.5	322.5	371.1
135°	124.4	148.4	208.2	307.8	352.4
137.5°	128.3	152.7	208.2	293.0	334.3
140°	132.9	156.6	207.8	279.9	315.6
142.5°	137.5	159.8	207.8	267.4	296.9
145°	142.1	163.3	207.1	257.1	281.3
147.5°	147.0	166.1	206.0	248.1	267.5
150°	152.0	169.0	205.0	240.3	255.5
152.5°	156.9	171.8	203.2	233.8	245.3
155°	161.5	174.4	201.1	227.4	236.4
157.5°	165.4	176.5	199.0	221.4	228.7
160°	169.3	178.6	196.9	215.4	221.2
162.5°	173.2	180.2	195.1	209.8	214.2
165°	176.0	181.3	192.6	204.3	207.5
167.5°	178.5	182.4	190.5	199.3	201.1
170°	180.9	182.9	188.7	194.8	195.4
172.5°	182.4	183.4	186.6	190.6	190.8
175°	183.4	183.6	185.2	187.5	187.0
177.5°	184.1	183.8	183.8	185.2	184.1
180°	183.8	183.8	183.8	183.8	183.8

(END OF REPORT)