

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009128

Luminaire Tested: S122DIP-B485D725UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009128
REPORT IS A COMBINATION OF REPORTS P984306 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D725UB27-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4697.1 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009128

CATALOG NUMBER: S122DIP-B485D725UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009128

CATALOG NUMBER: S122DIP-B485D725UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41
2	87	80	74	69	79	73	68	64	60	57	53	49	46	44	38	36	34
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25
5	67	55	47	41	61	51	44	39	42	37	33	34	30	27	27	24	22
6	61	50	42	36	56	46	39	33	38	33	29	31	27	24	24	22	19
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12139	12139	12139
5°	12159	11571	11488
10°	12060	11044	10825
15°	11883	10512	10125
20°	11644	9934	9464
25°	11407	9330	8802
30°	11106	8764	8109
35°	10825	8165	7428
40°	10476	7574	6783
45°	10129	6989	6152
50°	9752	6394	5497
55°	9353	5755	4877
60°	8906	5066	4232
65°	8415	4365	3554
70°	7791	3597	2869
75°	6931	2773	2216
80°	5884	1884	1425
85°	4266	878	607

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10129 cd/sqm

TEST NUMBER: P1009128

CATALOG NUMBER: S122DIP-B485D725UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.2	1.5
10°-20°	203.1	4.3
20°-30°	298.4	6.4
30°-40°	346.6	7.4
40°-50°	346.2	7.4
50°-60°	301.9	6.4
60°-70°	223.1	4.8
70°-80°	126.3	2.7
80°-90°	35.8	0.8
90°-100°	159.5	3.4
100°-110°	539.3	11.5
110°-120°	566.9	12.1
120°-130°	466.2	9.9
130°-140°	374.6	8.0
140°-150°	283.0	6.0
150°-160°	198.9	4.2
160°-170°	117.1	2.5
170°-180°	38.1	0.8
0°-30°	573.7	12.2
0°-40°	920.3	19.6
0°-60°	1568.3	33.4
0°-90°	1953.5	41.6
90°-120°	1265.7	26.9
90°-150°	2389.4	50.9
90°-180°	2744.0	58.4
0°-180°	4697.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	767	764	756	762	760	73
15°	730	726	716	719	715	206
25°	661	655	642	644	642	304
35°	570	563	551	546	543	356
45°	464	459	448	440	436	358
55°	351	347	338	329	325	314
65°	237	232	225	218	215	234
75°	124	122	119	114	116	132
85°	30	30	29	26	26	34
90°	1	10	26	25	25	4
95°	26	65	297	112	86	27
105°	92	139	561	1002	853	98
115°	163	205	469	968	1122	161
125°	227	269	451	784	910	202
135°	266	318	446	659	754	206
145°	304	350	444	551	602	191
155°	346	374	431	487	506	159
165°	377	388	412	437	444	106
175°	393	393	396	402	400	37
180°	394	394	394	394	394	

TEST NUMBER: P1009128

CATALOG NUMBER: S122DIP-B485D725UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	766.9	766.9	766.9	766.9	766.9
2.5°	771.3	767.6	759.5	766.9	765.4
5°	766.9	763.9	755.8	761.7	760.2
7.5°	761.7	757.3	749.2	755.1	753.6
10°	753.6	748.4	739.6	745.5	743.3
12.5°	742.5	738.1	729.2	732.9	731.5
15°	730.0	725.6	716.0	718.9	715.2
17.5°	714.5	710.1	700.5	704.2	700.5
20°	697.5	693.1	682.8	685.0	682.1
22.5°	680.6	673.9	664.4	664.4	662.9
25°	660.7	654.8	642.2	643.7	642.2
27.5°	638.6	633.4	623.8	621.6	617.9
30°	616.4	610.5	599.5	597.3	594.3
32.5°	592.8	588.4	576.6	572.2	569.2
35°	570.0	562.6	550.8	546.4	542.7
37.5°	544.2	537.5	525.7	520.6	516.9
40°	517.6	511.7	499.9	493.3	490.3
42.5°	491.8	485.9	474.1	466.7	462.3
45°	463.8	458.6	447.6	439.5	436.5
47.5°	436.5	431.4	419.6	411.4	407.0
50°	407.8	404.1	393.8	383.4	379.7
52.5°	379.7	374.6	365.0	356.9	351.7
55°	351.0	346.6	337.7	328.9	325.2
57.5°	322.2	318.5	309.0	300.1	297.2
60°	293.5	290.5	280.2	272.1	269.9
62.5°	265.4	260.3	252.9	245.5	242.6
65°	236.7	232.3	224.9	218.3	214.6
67.5°	207.2	203.5	196.9	191.7	188.8
70°	179.9	177.0	170.3	165.2	162.2
72.5°	151.9	148.9	145.3	140.1	137.9
75°	123.9	122.4	118.7	114.3	115.8
77.5°	98.8	95.9	94.4	92.2	90.0
80°	73.7	73.0	71.5	69.3	67.8
82.5°	50.1	50.1	49.4	46.5	46.5
85°	30.2	29.5	28.8	26.5	25.8
87.5°	13.3	11.8	10.3	8.1	7.4
90°	0.8	10.2	25.7	24.6	25.0
92.5°	11.4	36.0	116.5	53.8	46.2
95°	26.5	65.1	296.7	112.0	86.3
97.5°	39.4	85.9	483.6	224.8	144.5
100°	58.3	105.2	597.8	447.6	270.9
102.5°	75.7	122.6	601.6	756.8	528.2
105°	92.3	139.2	560.8	1002.3	852.9
107.5°	110.5	155.9	522.9	1091.2	1071.6
110°	128.7	172.9	497.2	1076.9	1160.9

TEST NUMBER: P1009128

CATALOG NUMBER: S122DIP-B485D725UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	145.3	189.2	480.5	1028.1	1159.4
115°	162.7	205.4	469.2	968.3	1122.3
117.5°	180.9	221.7	463.1	911.2	1066.3
120°	197.5	237.6	457.8	860.0	1012.6
122.5°	213.4	253.9	454.8	820.4	956.6
125°	227.0	268.6	451.0	784.4	910.4
127.5°	238.4	282.6	448.8	753.8	867.3
130°	248.2	295.1	447.2	722.7	831.7
132.5°	257.3	307.2	446.5	690.6	794.6
135°	266.4	317.8	445.7	659.2	754.5
137.5°	274.7	327.0	445.7	627.3	715.9
140°	284.5	335.2	445.0	599.4	675.8
142.5°	294.4	342.0	445.0	572.4	635.7
145°	304.2	349.6	443.5	550.6	602.4
147.5°	314.8	355.6	441.2	531.2	572.9
150°	325.4	361.7	438.9	514.6	547.1
152.5°	336.0	367.8	435.1	500.6	525.2
155°	345.8	373.5	430.6	487.0	506.3
157.5°	354.2	378.0	426.1	474.1	489.6
160°	362.5	382.5	421.5	461.2	473.7
162.5°	370.8	386.0	417.7	449.1	458.6
165°	376.9	388.2	412.4	437.4	444.2
167.5°	382.2	390.5	407.9	426.8	430.6
170°	387.5	391.6	404.1	417.0	418.5
172.5°	390.5	392.8	399.6	408.3	408.7
175°	392.8	393.2	396.5	401.5	400.3
177.5°	394.3	393.5	393.5	396.5	394.3
180°	393.5	393.5	393.5	393.5	393.5

(END OF REPORT)