

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009136

Luminaire Tested: S122DIP-B485D725UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009136
REPORT IS A COMBINATION OF REPORTS P984329 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D725UB30-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4500.0 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009136

CATALOG NUMBER: S122DIP-B485D725UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009136

CATALOG NUMBER: S122DIP-B485D725UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	37	36
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	32	30
4	73	63	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12244	12244	12244
5°	12264	11672	11588
10°	12164	11139	10918
15°	11986	10603	10214
20°	11745	10020	9546
25°	11505	9411	8879
30°	11204	8840	8180
35°	10918	8236	7492
40°	10567	7641	6843
45°	10217	7050	6206
50°	9836	6449	5545
55°	9433	5807	4919
60°	8982	5109	4268
65°	8489	4404	3584
70°	7860	3628	2894
75°	6993	2796	2236
80°	5940	1900	1438
85°	4308	884	611

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10217 cd/sqm

TEST NUMBER: P1009136

CATALOG NUMBER: S122DIP-B485D725UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.8	1.6
10°-20°	204.8	4.6
20°-30°	301.0	6.7
30°-40°	349.6	7.8
40°-50°	349.2	7.8
50°-60°	304.5	6.8
60°-70°	225.1	5.0
70°-80°	127.3	2.8
80°-90°	36.2	0.8
90°-100°	56.0	1.2
100°-110°	177.9	4.0
110°-120°	304.4	6.8
120°-130°	400.4	8.9
130°-140°	449.4	10.0
140°-150°	440.7	9.8
150°-160°	369.7	8.2
160°-170°	245.2	5.4
170°-180°	85.7	1.9
0°-30°	578.7	12.9
0°-40°	928.3	20.6
0°-60°	1582.0	35.2
0°-90°	1970.6	43.8
90°-120°	538.3	12.0
90°-150°	1828.9	40.6
90°-180°	2529.0	56.2
0°-180°	4500.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	774	774	774	774	774	
5°	774	771	762	768	767	73
15°	736	732	722	725	722	207
25°	666	660	648	649	648	307
35°	575	568	556	551	547	359
45°	468	463	452	443	440	361
55°	354	350	341	332	328	317
65°	239	234	227	220	216	236
75°	125	124	120	115	117	133
85°	30	30	29	27	26	34
90°	1	10	27	25	26	4
95°	40	47	49	49	47	44
105°	164	166	168	170	170	173
115°	305	310	308	308	305	302
125°	444	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	703	708	708	706	436
155°	798	800	802	806	804	367
165°	868	867	867	873	869	245
175°	903	901	899	905	900	86
180°	905	905	905	905	905	

TEST NUMBER: P1009136

CATALOG NUMBER: S122DIP-B485D725UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	773.5	773.5	773.5	773.5	773.5
2.5°	778.0	774.3	766.1	773.5	772.0
5°	773.5	770.6	762.4	768.3	766.8
7.5°	768.3	763.9	755.7	761.6	760.1
10°	760.1	754.9	746.0	752.0	749.7
12.5°	749.0	744.5	735.6	739.3	737.8
15°	736.3	731.9	722.2	725.2	721.5
17.5°	720.7	716.3	706.6	710.3	706.6
20°	703.6	699.2	688.7	691.0	688.0
22.5°	686.5	679.8	670.2	670.2	668.7
25°	666.4	660.5	647.8	649.3	647.8
27.5°	644.1	638.9	629.2	627.0	623.3
30°	621.8	615.9	604.7	602.5	599.5
32.5°	598.0	593.5	581.6	577.2	574.2
35°	574.9	567.5	555.6	551.1	547.4
37.5°	548.9	542.2	530.3	525.1	521.4
40°	522.1	516.2	504.3	497.6	494.6
42.5°	496.1	490.2	478.3	470.8	466.4
45°	467.8	462.6	451.5	443.3	440.3
47.5°	440.3	435.1	423.2	415.0	410.6
50°	411.3	407.6	397.2	386.8	383.0
52.5°	383.0	377.8	368.2	360.0	354.8
55°	354.0	349.6	340.7	331.7	328.0
57.5°	325.0	321.3	311.6	302.7	299.7
60°	296.0	293.1	282.6	274.5	272.2
62.5°	267.8	262.6	255.1	247.7	244.7
65°	238.8	234.3	226.9	220.2	216.4
67.5°	209.0	205.3	198.6	193.4	190.4
70°	181.5	178.5	171.8	166.6	163.6
72.5°	153.2	150.2	146.5	141.3	139.1
75°	125.0	123.5	119.7	115.3	116.8
77.5°	99.7	96.7	95.2	93.0	90.7
80°	74.4	73.6	72.1	69.9	68.4
82.5°	50.6	50.6	49.8	46.9	46.9
85°	30.5	29.8	29.0	26.8	26.0
87.5°	13.4	11.9	10.4	8.2	7.4
90°	0.8	9.9	26.7	25.2	26.0
92.5°	16.8	22.9	23.7	24.4	24.4
95°	39.7	47.3	48.9	48.9	47.3
97.5°	66.4	73.3	76.3	76.3	76.3
100°	97.0	103.1	105.4	105.4	104.6
102.5°	129.0	133.6	136.7	137.4	136.7
105°	164.1	166.4	168.0	169.5	169.5
107.5°	199.3	202.3	202.3	203.1	199.3
110°	232.9	237.4	237.4	237.4	235.2

TEST NUMBER: P1009136

CATALOG NUMBER: S122DIP-B485D725UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.5	274.1	273.3	271.0	269.5
115°	305.4	310.0	308.4	307.7	305.4
117.5°	341.3	347.4	343.6	341.3	339.0
120°	377.2	383.3	377.2	377.2	374.9
122.5°	410.0	417.6	413.8	411.5	410.0
125°	444.3	451.2	448.9	446.6	445.9
127.5°	477.9	486.3	483.3	480.2	477.9
130°	509.2	519.2	517.6	516.1	513.1
132.5°	544.4	552.0	552.8	548.9	546.6
135°	574.9	583.3	584.8	584.1	581.8
137.5°	608.5	615.4	616.9	616.1	613.1
140°	638.3	645.1	649.0	649.0	645.9
142.5°	668.8	675.7	678.0	678.7	675.7
145°	697.8	703.2	707.7	708.5	705.5
147.5°	723.8	730.6	733.7	735.2	732.2
150°	750.5	755.1	758.1	760.4	758.1
152.5°	774.2	778.7	782.6	785.6	782.6
155°	797.8	800.1	802.4	806.2	803.9
157.5°	818.4	820.0	821.5	826.8	823.0
160°	836.8	838.3	839.1	843.6	840.6
162.5°	853.6	853.6	854.3	859.7	855.9
165°	868.1	867.3	867.3	872.7	868.8
167.5°	881.1	878.8	878.8	884.1	880.3
170°	891.0	888.7	887.9	893.3	888.7
172.5°	897.8	895.6	894.8	900.1	895.6
175°	903.2	900.9	899.4	904.7	900.1
177.5°	906.2	904.0	902.4	907.0	902.4
180°	904.7	904.7	904.7	904.7	904.7

(END OF REPORT)