

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009145

Luminaire Tested: S122DIP-B485D725UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009145
REPORT IS A COMBINATION OF REPORTS P984338 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D725UB35-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4519.0 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009145

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009145

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	37	36
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	32	30
4	73	63	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12295	12295	12295
5°	12315	11719	11636
10°	12213	11184	10963
15°	12035	10647	10255
20°	11794	10061	9585
25°	11552	9451	8916
30°	11249	8876	8212
35°	10964	8270	7524
40°	10611	7671	6870
45°	10258	7078	6231
50°	9876	6475	5568
55°	9473	5829	4939
60°	9018	5131	4286
65°	8521	4421	3599
70°	7891	3643	2907
75°	7021	2808	2243
80°	5964	1908	1444
85°	4322	887	614

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10258 cd/sqm

TEST NUMBER: P1009145

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.1	1.6
10°-20°	205.7	4.6
20°-30°	302.3	6.7
30°-40°	351.0	7.8
40°-50°	350.6	7.8
50°-60°	305.7	6.8
60°-70°	226.0	5.0
70°-80°	127.9	2.8
80°-90°	36.3	0.8
90°-100°	56.2	1.2
100°-110°	178.7	4.0
110°-120°	305.8	6.8
120°-130°	402.1	8.9
130°-140°	451.4	10.0
140°-150°	442.6	9.8
150°-160°	371.3	8.2
160°-170°	246.2	5.4
170°-180°	86.1	1.9
0°-30°	581.0	12.9
0°-40°	932.1	20.6
0°-60°	1588.4	35.1
0°-90°	1978.6	43.8
90°-120°	540.7	12.0
90°-150°	1836.8	40.6
90°-180°	2540.0	56.2
0°-180°	4519.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	777	777	777	777	777	
5°	777	774	766	772	770	74
15°	739	735	725	728	724	208
25°	669	663	650	652	650	308
35°	577	570	558	553	550	360
45°	470	464	453	445	442	363
55°	356	351	342	333	329	318
65°	240	235	228	221	217	237
75°	126	124	120	116	117	134
85°	31	30	29	27	26	34
90°	1	10	27	25	26	4
95°	40	48	49	49	48	45
105°	165	167	169	170	170	174
115°	307	311	310	309	307	303
125°	446	453	451	449	448	399
135°	577	586	587	587	584	446
145°	701	706	711	712	708	438
155°	801	804	806	810	807	369
165°	872	871	871	876	873	246
175°	907	905	903	909	904	86
180°	909	909	909	909	909	

TEST NUMBER: P1009145

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	776.7	776.7	776.7	776.7	776.7
2.5°	781.2	777.4	769.2	776.7	775.2
5°	776.7	773.7	765.5	771.5	770.0
7.5°	771.5	767.0	758.8	764.7	763.2
10°	763.2	758.0	749.0	755.0	752.8
12.5°	752.0	747.6	738.6	742.3	740.8
15°	739.3	734.9	725.2	728.1	724.4
17.5°	723.7	719.2	709.5	713.2	709.5
20°	706.5	702.0	691.5	693.8	690.8
22.5°	689.3	682.6	672.9	672.9	671.4
25°	669.1	663.2	650.5	652.0	650.5
27.5°	646.7	641.5	631.8	629.6	625.8
30°	624.3	618.4	607.2	604.9	601.9
32.5°	600.4	596.0	584.0	579.5	576.5
35°	577.3	569.8	557.9	553.4	549.7
37.5°	551.1	544.4	532.5	527.2	523.5
40°	524.3	518.3	506.3	499.6	496.6
42.5°	498.1	492.1	480.2	472.7	468.2
45°	469.7	464.5	453.3	445.1	442.1
47.5°	442.1	436.9	424.9	416.7	412.2
50°	413.0	409.3	398.8	388.3	384.6
52.5°	384.6	379.4	369.7	361.5	356.2
55°	355.5	351.0	342.0	333.1	329.3
57.5°	326.4	322.6	312.9	304.0	301.0
60°	297.2	294.2	283.8	275.6	273.3
62.5°	268.9	263.6	256.2	248.7	245.7
65°	239.7	235.2	227.8	221.1	217.3
67.5°	209.9	206.1	199.4	194.2	191.2
70°	182.2	179.2	172.5	167.3	164.3
72.5°	153.8	150.9	147.1	141.9	139.7
75°	125.5	124.0	120.2	115.8	117.2
77.5°	100.1	97.1	95.6	93.4	91.1
80°	74.7	73.9	72.4	70.2	68.7
82.5°	50.8	50.8	50.0	47.0	47.0
85°	30.6	29.9	29.1	26.9	26.1
87.5°	13.4	11.9	10.5	8.2	7.5
90°	0.8	10.0	26.8	25.3	26.1
92.5°	16.9	23.0	23.8	24.5	24.5
95°	39.9	47.5	49.1	49.1	47.5
97.5°	66.7	73.6	76.7	76.7	76.7
100°	97.4	103.5	105.8	105.8	105.1
102.5°	129.6	134.2	137.3	138.0	137.3
105°	164.9	167.2	168.7	170.2	170.2
107.5°	200.1	203.2	203.2	204.0	200.1
110°	233.9	238.5	238.5	238.5	236.2

TEST NUMBER: P1009145

CATALOG NUMBER: S122DIP-B485D725UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	270.7	275.3	274.5	272.2	270.7
115°	306.7	311.3	309.8	309.0	306.7
117.5°	342.8	348.9	345.1	342.8	340.5
120°	378.8	384.9	378.8	378.8	376.5
122.5°	411.8	419.4	415.6	413.3	411.8
125°	446.3	453.2	450.9	448.6	447.8
127.5°	480.0	488.4	485.4	482.3	480.0
130°	511.5	521.4	519.9	518.4	515.3
132.5°	546.7	554.4	555.2	551.3	549.0
135°	577.4	585.8	587.4	586.6	584.3
137.5°	611.1	618.0	619.6	618.8	615.7
140°	641.0	647.9	651.8	651.8	648.7
142.5°	671.7	678.6	680.9	681.7	678.6
145°	700.8	706.2	710.8	711.6	708.5
147.5°	726.9	733.8	736.9	738.4	735.4
150°	753.8	758.4	761.4	763.7	761.4
152.5°	777.5	782.1	786.0	789.0	786.0
155°	801.3	803.6	805.9	809.7	807.4
157.5°	822.0	823.5	825.1	830.4	826.6
160°	840.4	841.9	842.7	847.3	844.2
162.5°	857.3	857.3	858.0	863.4	859.6
165°	871.8	871.1	871.1	876.4	872.6
167.5°	884.9	882.6	882.6	887.9	884.1
170°	894.8	892.5	891.8	897.1	892.5
172.5°	901.7	899.4	898.7	904.0	899.4
175°	907.1	904.8	903.3	908.7	904.0
177.5°	910.2	907.9	906.3	911.0	906.3
180°	908.7	908.7	908.7	908.7	908.7

(END OF REPORT)