

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008629

Luminaire Tested: S122DIP-B1005D330UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008629
REPORT IS A COMBINATION OF REPORTS P983636 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D330UB50-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5041.0 lumens
Efficiency: N/A
Efficacy: 71.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008629

CATALOG NUMBER: S122DIP-B1005D330UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1008629

CATALOG NUMBER: S122DIP-B1005D330UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	108	108	108	108	99	99	99	90	90	90	81	81	81
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69
2	95	87	80	75	90	83	77	72	76	71	67	69	66	63	63	61	58
3	86	77	69	63	82	73	66	61	67	61	57	61	57	53	56	53	49
4	79	68	60	53	75	65	57	52	60	53	49	55	50	46	50	46	43
5	73	61	52	46	69	58	50	45	54	47	42	49	44	40	45	41	37
6	67	55	46	40	64	52	45	39	48	42	37	45	39	35	41	36	33
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	38	33	29
8	58	45	37	31	55	43	36	31	40	34	29	37	32	28	35	30	26
9	54	41	33	28	52	40	33	28	37	31	26	34	29	25	32	27	24
10	51	38	31	25	48	37	30	25	34	28	24	32	27	23	30	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24315	24315	24315
5°	24355	23176	23013
10°	24156	22120	21681
15°	23803	21057	20282
20°	23324	19899	18956
25°	22848	18690	17633
30°	22249	17554	16243
35°	21683	16355	14879
40°	20984	15172	13589
45°	20289	13999	12325
50°	19533	12805	11011
55°	18732	11530	9770
60°	17837	10148	8477
65°	16854	8743	7118
70°	15608	7206	5748
75°	13879	5555	4439
80°	11792	3776	2857
85°	8560	1756	1216

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20289 cd/sqm

TEST NUMBER: P1008629

CATALOG NUMBER: S122DIP-B1005D330UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.6	2.9
10°-20°	406.8	8.1
20°-30°	597.8	11.9
30°-40°	694.3	13.8
40°-50°	693.4	13.8
50°-60°	604.6	12.0
60°-70°	446.9	8.9
70°-80°	252.9	5.0
80°-90°	67.9	1.3
90°-100°	25.0	0.5
100°-110°	79.6	1.6
110°-120°	136.2	2.7
120°-130°	179.2	3.6
130°-140°	201.1	4.0
140°-150°	197.2	3.9
150°-160°	165.4	3.3
160°-170°	109.7	2.2
170°-180°	38.3	0.8
0°-30°	1149.1	22.8
0°-40°	1843.4	36.6
0°-60°	3141.4	62.3
0°-90°	3909.2	77.5
90°-120°	240.9	4.8
90°-150°	818.4	16.2
90°-180°	1132.0	22.5
0°-180°	5041.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1536	1536	1536	1536	1536	
5°	1536	1530	1514	1526	1523	146
15°	1462	1453	1434	1440	1433	412
25°	1323	1312	1286	1289	1286	609
35°	1142	1127	1103	1094	1087	713
45°	929	919	896	880	874	717
55°	703	694	676	659	651	629
65°	474	465	450	437	430	469
75°	248	245	238	229	232	265
85°	61	59	58	53	52	67
90°	0	4	12	11	12	5
95°	18	21	22	22	21	20
105°	74	74	75	76	76	78
115°	137	139	138	138	137	135
125°	199	202	201	200	200	178
135°	257	261	262	261	260	199
145°	312	315	317	317	316	195
155°	357	358	359	361	360	164
165°	388	388	388	390	389	110
175°	404	403	402	405	403	38
180°	405	405	405	405	405	

TEST NUMBER: P1008629

CATALOG NUMBER: S122DIP-B1005D330UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1536.1	1536.1	1536.1	1536.1	1536.1
2.5°	1544.9	1537.5	1521.3	1536.1	1533.1
5°	1536.1	1530.2	1513.9	1525.7	1522.8
7.5°	1525.7	1516.9	1500.6	1512.4	1509.5
10°	1509.5	1499.1	1481.4	1493.2	1488.8
12.5°	1487.3	1478.5	1460.7	1468.1	1465.2
15°	1462.2	1453.4	1434.2	1440.1	1432.7
17.5°	1431.2	1422.3	1403.1	1410.5	1403.1
20°	1397.2	1388.4	1367.7	1372.1	1366.2
22.5°	1363.3	1350.0	1330.8	1330.8	1327.8
25°	1323.4	1311.6	1286.5	1289.4	1286.5
27.5°	1279.1	1268.7	1249.5	1245.1	1237.7
30°	1234.8	1222.9	1200.8	1196.4	1190.5
32.5°	1187.5	1178.6	1155.0	1146.1	1140.2
35°	1141.7	1126.9	1103.3	1094.4	1087.1
37.5°	1090.0	1076.7	1053.1	1042.8	1035.4
40°	1036.8	1025.0	1001.4	988.1	982.2
42.5°	985.2	973.3	949.7	934.9	926.1
45°	929.0	918.7	896.5	880.3	874.4
47.5°	874.4	864.0	840.4	824.2	815.3
50°	816.8	809.4	788.7	768.0	760.6
52.5°	760.6	750.3	731.1	714.9	704.5
55°	703.0	694.2	676.5	658.7	651.4
57.5°	645.4	638.1	618.9	601.1	595.2
60°	587.8	581.9	561.3	545.0	540.6
62.5°	531.7	521.4	506.6	491.8	485.9
65°	474.1	465.3	450.5	437.2	429.8
67.5°	415.0	407.6	394.4	384.0	378.1
70°	360.4	354.5	341.2	330.8	324.9
72.5°	304.3	298.4	291.0	280.6	276.2
75°	248.1	245.2	237.8	228.9	231.9
77.5°	197.9	192.0	189.1	184.6	180.2
80°	147.7	146.2	143.3	138.8	135.9
82.5°	100.4	100.4	99.0	93.1	93.1
85°	60.6	59.1	57.6	53.2	51.7
87.5°	26.6	23.6	20.7	16.2	14.8
90°	0.3	4.4	12.0	11.3	11.6
92.5°	7.5	10.2	10.6	10.9	10.9
95°	17.8	21.2	21.9	21.9	21.2
97.5°	29.7	32.8	34.2	34.2	34.2
100°	43.4	46.1	47.1	47.1	46.8
102.5°	57.7	59.8	61.2	61.5	61.2
105°	73.5	74.5	75.2	75.8	75.8
107.5°	89.2	90.5	90.5	90.9	89.2
110°	104.2	106.2	106.2	106.2	105.2

TEST NUMBER: P1008629

CATALOG NUMBER: S122DIP-B1005D330UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	120.6	122.6	122.3	121.3	120.6
115°	136.7	138.7	138.0	137.7	136.7
117.5°	152.7	155.4	153.7	152.7	151.7
120°	168.8	171.5	168.8	168.8	167.7
122.5°	183.5	186.9	185.2	184.1	183.5
125°	198.8	201.9	200.9	199.9	199.5
127.5°	213.9	217.6	216.3	214.9	213.9
130°	227.9	232.3	231.6	230.9	229.6
132.5°	243.6	247.0	247.3	245.6	244.6
135°	257.3	261.0	261.7	261.4	260.3
137.5°	272.3	275.4	276.0	275.7	274.3
140°	285.6	288.7	290.4	290.4	289.0
142.5°	299.3	302.3	303.4	303.7	302.3
145°	312.3	314.6	316.7	317.0	315.7
147.5°	323.9	326.9	328.3	329.0	327.6
150°	335.8	337.9	339.2	340.3	339.2
152.5°	346.4	348.5	350.2	351.5	350.2
155°	357.0	358.0	359.1	360.8	359.7
157.5°	366.2	366.9	367.6	370.0	368.3
160°	374.4	375.1	375.5	377.5	376.1
162.5°	381.9	381.9	382.3	384.7	383.0
165°	388.4	388.1	388.1	390.5	388.8
167.5°	394.2	393.2	393.2	395.6	393.9
170°	398.7	397.7	397.3	399.7	397.7
172.5°	401.8	400.7	400.4	402.8	400.7
175°	404.2	403.1	402.4	404.8	402.8
177.5°	405.5	404.5	403.8	405.9	403.8
180°	404.8	404.8	404.8	404.8	404.8

(END OF REPORT)