

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009154

Luminaire Tested: S122DIP-B485D725UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009154
REPORT IS A COMBINATION OF REPORTS P984347 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D725UB40-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4474.0 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009154

CATALOG NUMBER: S122DIP-B485D725UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009154

CATALOG NUMBER: S122DIP-B485D725UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	37	36
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	32	31
4	73	63	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12176	12176	12176
5°	12196	11606	11524
10°	12097	11076	10857
15°	11919	10544	10156
20°	11680	9965	9493
25°	11441	9359	8829
30°	11141	8790	8133
35°	10857	8190	7451
40°	10508	7598	6805
45°	10160	7011	6172
50°	9781	6413	5514
55°	9382	5772	4892
60°	8933	5082	4245
65°	8439	4378	3564
70°	7817	3609	2878
75°	6953	2782	2222
80°	5908	1889	1430
85°	4280	878	609

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10160 cd/sqm

TEST NUMBER: P1009154

CATALOG NUMBER: S122DIP-B485D725UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.4	1.6
10°-20°	203.7	4.6
20°-30°	299.3	6.7
30°-40°	347.7	7.8
40°-50°	347.2	7.8
50°-60°	302.8	6.8
60°-70°	223.8	5.0
70°-80°	126.6	2.8
80°-90°	36.0	0.8
90°-100°	55.6	1.2
100°-110°	176.9	4.0
110°-120°	302.6	6.8
120°-130°	398.0	8.9
130°-140°	446.8	10.0
140°-150°	438.1	9.8
150°-160°	367.5	8.2
160°-170°	243.7	5.4
170°-180°	85.2	1.9
0°-30°	575.4	12.9
0°-40°	923.1	20.6
0°-60°	1573.1	35.2
0°-90°	1959.6	43.8
90°-120°	535.2	12.0
90°-150°	1818.0	40.6
90°-180°	2514.0	56.2
0°-180°	4474.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	769	769	769	769	769	
5°	769	766	758	764	763	73
15°	732	728	718	721	717	206
25°	663	657	644	646	644	305
35°	572	564	552	548	544	357
45°	465	460	449	441	438	359
55°	352	348	339	330	326	315
65°	237	233	226	219	215	235
75°	124	123	119	115	116	133
85°	30	30	29	27	26	34
90°	1	10	27	25	26	4
95°	40	47	49	49	47	44
105°	163	166	167	168	168	172
115°	304	308	307	306	304	300
125°	442	448	446	444	443	395
135°	572	580	581	581	578	442
145°	694	699	704	704	701	433
155°	793	795	798	802	799	365
165°	863	862	862	868	864	243
175°	898	896	894	899	895	85
180°	899	899	899	899	899	

TEST NUMBER: P1009154

CATALOG NUMBER: S122DIP-B485D725UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	769.2	769.2	769.2	769.2	769.2
2.5°	773.7	770.0	761.8	769.2	767.7
5°	769.2	766.3	758.1	764.0	762.6
7.5°	764.0	759.6	751.5	757.4	755.9
10°	755.9	750.7	741.8	747.8	745.5
12.5°	744.8	740.4	731.5	735.2	733.7
15°	732.2	727.8	718.2	721.1	717.4
17.5°	716.7	712.3	702.6	706.3	702.6
20°	699.7	695.2	684.9	687.1	684.2
22.5°	682.7	676.0	666.4	666.4	664.9
25°	662.7	656.8	644.2	645.7	644.2
27.5°	640.5	635.3	625.7	623.5	619.8
30°	618.3	612.4	601.3	599.1	596.1
32.5°	594.7	590.2	578.4	574.0	571.0
35°	571.7	564.3	552.5	548.1	544.4
37.5°	545.8	539.2	527.4	522.2	518.5
40°	519.2	513.3	501.5	494.8	491.9
42.5°	493.3	487.4	475.6	468.2	463.7
45°	465.2	460.0	449.0	440.8	437.9
47.5°	437.9	432.7	420.8	412.7	408.3
50°	409.0	405.3	395.0	384.6	380.9
52.5°	380.9	375.7	366.1	358.0	352.8
55°	352.1	347.6	338.7	329.9	326.2
57.5°	323.2	319.5	309.9	301.0	298.1
60°	294.4	291.4	281.1	272.9	270.7
62.5°	266.3	261.1	253.7	246.3	243.3
65°	237.4	233.0	225.6	218.9	215.2
67.5°	207.8	204.1	197.5	192.3	189.3
70°	180.5	177.5	170.9	165.7	162.7
72.5°	152.4	149.4	145.7	140.5	138.3
75°	124.3	122.8	119.1	114.6	116.1
77.5°	99.1	96.2	94.7	92.5	90.2
80°	74.0	73.2	71.7	69.5	68.0
82.5°	50.3	50.3	49.6	46.6	46.6
85°	30.3	29.6	28.8	26.6	25.9
87.5°	13.3	11.8	10.4	8.1	7.4
90°	0.8	9.9	26.6	25.0	25.8
92.5°	16.7	22.8	23.5	24.3	24.3
95°	39.5	47.1	48.6	48.6	47.1
97.5°	66.0	72.9	75.9	75.9	75.9
100°	96.4	102.5	104.7	104.7	104.0
102.5°	128.3	132.8	135.9	136.6	135.9
105°	163.2	165.5	167.0	168.5	168.5
107.5°	198.1	201.1	201.1	201.9	198.1
110°	231.5	236.0	236.0	236.0	233.8

TEST NUMBER: P1009154

CATALOG NUMBER: S122DIP-B485D725UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	267.9	272.5	271.7	269.4	267.9
115°	303.6	308.1	306.6	305.9	303.6
117.5°	339.3	345.3	341.5	339.3	337.0
120°	374.9	381.0	374.9	374.9	372.6
122.5°	407.6	415.1	411.4	409.1	407.6
125°	441.7	448.5	446.3	444.0	443.2
127.5°	475.1	483.5	480.4	477.4	475.1
130°	506.2	516.1	514.6	513.1	510.0
132.5°	541.1	548.7	549.5	545.7	543.4
135°	571.5	579.8	581.4	580.6	578.3
137.5°	604.9	611.7	613.2	612.5	609.4
140°	634.5	641.3	645.1	645.1	642.1
142.5°	664.8	671.7	674.0	674.7	671.7
145°	693.7	699.0	703.6	704.3	701.3
147.5°	719.5	726.3	729.4	730.9	727.8
150°	746.1	750.6	753.6	755.9	753.6
152.5°	769.6	774.1	777.9	781.0	777.9
155°	793.1	795.4	797.7	801.5	799.2
157.5°	813.6	815.1	816.6	821.9	818.2
160°	831.8	833.3	834.1	838.6	835.6
162.5°	848.5	848.5	849.3	854.6	850.8
165°	862.9	862.2	862.2	867.5	863.7
167.5°	875.8	873.6	873.6	878.9	875.1
170°	885.7	883.4	882.7	888.0	883.4
172.5°	892.5	890.3	889.5	894.8	890.3
175°	897.8	895.6	894.0	899.4	894.8
177.5°	900.9	898.6	897.1	901.6	897.1
180°	899.4	899.4	899.4	899.4	899.4

(END OF REPORT)