

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009163

Luminaire Tested: S122DIP-B485D725UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009163
REPORT IS A COMBINATION OF REPORTS P984356 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D725UB50-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4326.0 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009163

CATALOG NUMBER: S122DIP-B485D725UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009163

CATALOG NUMBER: S122DIP-B485D725UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	37	36
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	32	30
4	73	63	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11772	11772	11772
5°	11791	11220	11141
10°	11695	10709	10497
15°	11524	10194	9819
20°	11291	9633	9177
25°	11061	9048	8536
30°	10771	8498	7863
35°	10497	7919	7203
40°	10160	7345	6579
45°	9824	6777	5966
50°	9455	6199	5332
55°	9070	5582	4729
60°	8636	4912	4104
65°	8159	4233	3447
70°	7557	3489	2783
75°	6718	2689	2149
80°	5708	1829	1383
85°	4139	851	588

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9824 cd/sqm

TEST NUMBER: P1009163

CATALOG NUMBER: S122DIP-B485D725UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.0	1.6
10°-20°	196.9	4.6
20°-30°	289.4	6.7
30°-40°	336.1	7.8
40°-50°	335.7	7.8
50°-60°	292.7	6.8
60°-70°	216.4	5.0
70°-80°	122.4	2.8
80°-90°	34.8	0.8
90°-100°	53.8	1.2
100°-110°	171.0	4.0
110°-120°	292.7	6.8
120°-130°	384.9	8.9
130°-140°	432.0	10.0
140°-150°	423.7	9.8
150°-160°	355.4	8.2
160°-170°	235.7	5.4
170°-180°	82.4	1.9
0°-30°	556.3	12.9
0°-40°	892.4	20.6
0°-60°	1520.9	35.2
0°-90°	1894.5	43.8
90°-120°	517.5	12.0
90°-150°	1758.1	40.6
90°-180°	2432.0	56.2
0°-180°	4326.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	744	744	744	744	744	
5°	744	741	733	739	737	71
15°	708	704	694	697	694	199
25°	641	635	623	624	623	295
35°	553	546	534	530	526	345
45°	450	445	434	426	423	347
55°	340	336	328	319	315	304
65°	230	225	218	212	208	227
75°	120	119	115	111	112	128
85°	29	29	28	26	25	33
90°	1	10	26	24	25	4
95°	38	46	47	47	46	43
105°	158	160	162	163	163	167
115°	294	298	296	296	294	290
125°	427	434	432	429	429	382
135°	553	561	562	562	559	427
145°	671	676	680	681	678	419
155°	767	769	771	775	773	353
165°	834	834	834	839	835	235
175°	868	866	865	870	865	82
180°	870	870	870	870	870	

TEST NUMBER: P1009163

CATALOG NUMBER: S122DIP-B485D725UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	743.7	743.7	743.7	743.7	743.7
2.5°	748.0	744.4	736.5	743.7	742.2
5°	743.7	740.8	732.9	738.7	737.2
7.5°	738.7	734.4	726.5	732.2	730.8
10°	730.8	725.8	717.2	722.9	720.8
12.5°	720.1	715.8	707.2	710.8	709.3
15°	707.9	703.6	694.3	697.2	693.6
17.5°	692.9	688.6	679.3	682.9	679.3
20°	676.4	672.2	662.1	664.3	661.4
22.5°	660.0	653.6	644.3	644.3	642.8
25°	640.7	635.0	622.8	624.2	622.8
27.5°	619.2	614.2	604.9	602.8	599.2
30°	597.8	592.1	581.3	579.2	576.3
32.5°	574.9	570.6	559.2	554.9	552.0
35°	552.7	545.6	534.2	529.9	526.3
37.5°	527.7	521.3	509.8	504.8	501.3
40°	502.0	496.3	484.8	478.4	475.5
42.5°	476.9	471.2	459.8	452.6	448.3
45°	449.8	444.8	434.0	426.2	423.3
47.5°	423.3	418.3	406.9	399.0	394.7
50°	395.4	391.9	381.8	371.8	368.3
52.5°	368.3	363.3	354.0	346.1	341.1
55°	340.4	336.1	327.5	318.9	315.3
57.5°	312.5	308.9	299.6	291.0	288.2
60°	284.6	281.7	271.7	263.9	261.7
62.5°	257.4	252.4	245.3	238.1	235.3
65°	229.5	225.2	218.1	211.7	208.1
67.5°	200.9	197.4	190.9	185.9	183.1
70°	174.5	171.6	165.2	160.2	157.3
72.5°	147.3	144.4	140.9	135.9	133.7
75°	120.1	118.7	115.1	110.8	112.3
77.5°	95.8	93.0	91.5	89.4	87.2
80°	71.5	70.8	69.4	67.2	65.8
82.5°	48.6	48.6	47.9	45.0	45.0
85°	29.3	28.6	27.9	25.7	25.0
87.5°	12.9	11.4	10.0	7.9	7.2
90°	0.7	9.5	25.7	24.2	25.0
92.5°	16.1	22.0	22.8	23.5	23.5
95°	38.2	45.5	47.0	47.0	45.5
97.5°	63.9	70.5	73.4	73.4	73.4
100°	93.2	99.1	101.3	101.3	100.5
102.5°	124.0	128.4	131.4	132.1	131.4
105°	157.8	160.0	161.5	162.9	162.9
107.5°	191.6	194.5	194.5	195.2	191.6
110°	223.8	228.3	228.3	228.3	226.0

TEST NUMBER: P1009163

CATALOG NUMBER: S122DIP-B485D725UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	259.1	263.5	262.7	260.5	259.1
115°	293.6	298.0	296.5	295.8	293.6
117.5°	328.1	333.9	330.3	328.1	325.9
120°	362.6	368.4	362.6	362.6	360.4
122.5°	394.1	401.5	397.8	395.6	394.1
125°	427.1	433.8	431.5	429.3	428.6
127.5°	459.4	467.5	464.6	461.6	459.4
130°	489.5	499.1	497.6	496.1	493.2
132.5°	523.3	530.6	531.4	527.7	525.5
135°	552.6	560.7	562.2	561.5	559.3
137.5°	584.9	591.5	593.0	592.3	589.3
140°	613.6	620.2	623.8	623.8	620.9
142.5°	642.9	649.5	651.7	652.5	649.5
145°	670.8	675.9	680.4	681.1	678.1
147.5°	695.8	702.4	705.3	706.8	703.8
150°	721.4	725.9	728.8	731.0	728.8
152.5°	744.2	748.6	752.3	755.2	752.3
155°	767.0	769.2	771.4	775.0	772.8
157.5°	786.8	788.2	789.7	794.8	791.2
160°	804.4	805.9	806.6	811.0	808.1
162.5°	820.5	820.5	821.3	826.4	822.7
165°	834.5	833.7	833.7	838.9	835.2
167.5°	847.0	844.7	844.7	849.9	846.2
170°	856.5	854.3	853.6	858.7	854.3
172.5°	863.1	860.9	860.2	865.3	860.9
175°	868.2	866.0	864.6	869.7	865.3
177.5°	871.2	869.0	867.5	871.9	867.5
180°	869.7	869.7	869.7	869.7	869.7

(END OF REPORT)