

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008647

Luminaire Tested: S122DIP-B1005D530UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008647
REPORT IS A COMBINATION OF REPORTS P983669 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D530UB30-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5959.0 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008647

CATALOG NUMBER: S122DIP-B1005D530UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1008647

CATALOG NUMBER: S122DIP-B1005D530UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73
1	102	97	93	90	96	92	89	85	82	79	77	73	71	69	64	63	62
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	54	52
3	85	75	67	61	80	71	64	59	64	58	54	57	52	49	50	47	44
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	45	41	38
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	41	37	33
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29
7	61	48	40	34	57	46	38	33	42	35	31	37	32	28	34	29	26
8	57	44	36	30	53	42	35	29	38	32	27	34	29	25	31	27	23
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	24	21
10	49	37	30	25	47	35	28	24	32	26	22	29	24	21	27	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25286	25286	25286
5°	25327	24101	23931
10°	25120	23004	22546
15°	24753	21896	21092
20°	24255	20693	19713
25°	23759	19436	18336
30°	23137	18254	16892
35°	22549	17008	15473
40°	21822	15778	14131
45°	21100	14558	12816
50°	20312	13317	11451
55°	19481	11990	10160
60°	18550	10553	8816
65°	17526	9093	7403
70°	16232	7493	5978
75°	14433	5777	4615
80°	12263	3926	2971
85°	8899	1826	1265

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21100 cd/sqm

TEST NUMBER: P1008647

CATALOG NUMBER: S122DIP-B1005D530UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.3	2.5
10°-20°	423.0	7.1
20°-30°	621.6	10.4
30°-40°	722.0	12.1
40°-50°	721.1	12.1
50°-60°	628.8	10.6
60°-70°	464.8	7.8
70°-80°	263.0	4.4
80°-90°	71.3	1.2
90°-100°	41.9	0.7
100°-110°	133.2	2.2
110°-120°	227.8	3.8
120°-130°	299.7	5.0
130°-140°	336.4	5.6
140°-150°	329.9	5.5
150°-160°	276.7	4.6
160°-170°	183.5	3.1
170°-180°	64.1	1.1
0°-30°	1195.0	20.1
0°-40°	1917.0	32.2
0°-60°	3266.8	54.8
0°-90°	4065.9	68.2
90°-120°	402.9	6.8
90°-150°	1368.8	23.0
90°-180°	1893.0	31.8
0°-180°	5959.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1597	1597	1597	1597	1597	
5°	1597	1591	1574	1587	1584	152
15°	1521	1511	1491	1498	1490	428
25°	1376	1364	1338	1341	1338	633
35°	1187	1172	1147	1138	1130	741
45°	966	955	932	915	909	746
55°	731	722	704	685	677	654
65°	493	484	468	455	447	487
75°	258	255	247	238	241	275
85°	63	61	60	55	54	70
90°	1	7	20	19	19	6
95°	30	35	37	37	35	33
105°	123	125	126	127	127	130
115°	229	232	231	230	229	226
125°	333	338	336	334	334	297
135°	430	437	438	437	435	332
145°	522	526	530	530	528	326
155°	597	599	600	603	602	275
165°	650	649	649	653	650	183
175°	676	674	673	677	674	64
180°	677	677	677	677	677	

TEST NUMBER: P1008647

CATALOG NUMBER: S122DIP-B1005D530UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1597.4	1597.4	1597.4	1597.4	1597.4
2.5°	1606.6	1598.9	1582.0	1597.4	1594.3
5°	1597.4	1591.2	1574.3	1586.6	1583.6
7.5°	1586.6	1577.4	1560.5	1572.8	1569.7
10°	1569.7	1559.0	1540.6	1552.8	1548.2
12.5°	1546.7	1537.5	1519.1	1526.7	1523.7
15°	1520.6	1511.4	1491.4	1497.5	1489.9
17.5°	1488.3	1479.1	1459.1	1466.8	1459.1
20°	1453.0	1443.8	1422.3	1426.9	1420.8
22.5°	1417.7	1403.9	1383.9	1383.9	1380.8
25°	1376.2	1363.9	1337.8	1340.9	1337.8
27.5°	1330.1	1319.4	1299.4	1294.8	1287.1
30°	1284.1	1271.8	1248.7	1244.1	1238.0
32.5°	1234.9	1225.7	1201.1	1191.9	1185.8
35°	1187.3	1171.9	1147.4	1138.1	1130.5
37.5°	1133.5	1119.7	1095.1	1084.4	1076.7
40°	1078.2	1065.9	1041.4	1027.5	1021.4
42.5°	1024.5	1012.2	987.6	972.3	963.0
45°	966.1	955.4	932.3	915.4	909.3
47.5°	909.3	898.5	874.0	857.1	847.8
50°	849.4	841.7	820.2	798.7	791.0
52.5°	791.0	780.3	760.3	743.4	732.6
55°	731.1	721.9	703.5	685.0	677.4
57.5°	671.2	663.5	643.6	625.1	619.0
60°	611.3	605.2	583.7	566.8	562.2
62.5°	552.9	542.2	526.8	511.5	505.3
65°	493.0	483.8	468.5	454.6	447.0
67.5°	431.6	423.9	410.1	399.3	393.2
70°	374.8	368.6	354.8	344.1	337.9
72.5°	316.4	310.3	302.6	291.8	287.2
75°	258.0	255.0	247.3	238.1	241.1
77.5°	205.8	199.7	196.6	192.0	187.4
80°	153.6	152.1	149.0	144.4	141.3
82.5°	104.4	104.4	102.9	96.8	96.8
85°	63.0	61.4	59.9	55.3	53.8
87.5°	27.6	24.6	21.5	16.9	15.4
90°	0.6	7.4	20.0	18.9	19.4
92.5°	12.6	17.1	17.7	18.3	18.3
95°	29.7	35.4	36.6	36.6	35.4
97.5°	49.7	54.9	57.1	57.1	57.1
100°	72.6	77.1	78.9	78.9	78.3
102.5°	96.6	100.0	102.3	102.9	102.3
105°	122.9	124.6	125.7	126.9	126.9
107.5°	149.1	151.4	151.4	152.0	149.1
110°	174.3	177.7	177.7	177.7	176.0

TEST NUMBER: P1008647

CATALOG NUMBER: S122DIP-B1005D530UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	201.7	205.1	204.6	202.8	201.7
115°	228.6	232.0	230.8	230.3	228.6
117.5°	255.4	260.0	257.1	255.4	253.7
120°	282.3	286.8	282.3	282.3	280.6
122.5°	306.8	312.6	309.7	308.0	306.8
125°	332.6	337.7	336.0	334.3	333.7
127.5°	357.7	364.0	361.7	359.4	357.7
130°	381.1	388.6	387.4	386.3	384.0
132.5°	407.4	413.1	413.7	410.8	409.1
135°	430.3	436.6	437.7	437.1	435.4
137.5°	455.4	460.5	461.7	461.1	458.8
140°	477.7	482.8	485.7	485.7	483.4
142.5°	500.5	505.7	507.4	508.0	505.7
145°	522.3	526.3	529.7	530.3	528.0
147.5°	541.7	546.8	549.1	550.3	548.0
150°	561.7	565.1	567.4	569.1	567.4
152.5°	579.4	582.8	585.7	588.0	585.7
155°	597.1	598.8	600.5	603.4	601.7
157.5°	612.5	613.7	614.8	618.8	616.0
160°	626.3	627.4	628.0	631.4	629.1
162.5°	638.8	638.8	639.4	643.4	640.5
165°	649.7	649.1	649.1	653.1	650.3
167.5°	659.4	657.7	657.7	661.7	658.8
170°	666.8	665.1	664.5	668.5	665.1
172.5°	672.0	670.3	669.7	673.7	670.3
175°	676.0	674.3	673.1	677.1	673.7
177.5°	678.3	676.5	675.4	678.8	675.4
180°	677.1	677.1	677.1	677.1	677.1

(END OF REPORT)