

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008656

Luminaire Tested: S122DIP-B1005D530UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008656
REPORT IS A COMBINATION OF REPORTS P983678 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D530UB35-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5984.0 lumens
Efficiency: N/A
Efficacy: 78.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008656

CATALOG NUMBER: S122DIP-B1005D530UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1008656

CATALOG NUMBER: S122DIP-B1005D530UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73
1	102	97	93	90	96	92	89	85	82	79	77	73	71	69	64	63	62
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	54	52
3	85	75	67	61	80	71	64	59	64	58	54	57	52	49	50	47	44
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	45	41	38
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	41	37	33
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29
7	61	48	40	34	57	46	38	33	42	35	31	37	32	28	34	29	26
8	57	44	36	30	53	42	35	29	38	32	27	34	29	25	31	27	23
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	24	21
10	49	37	30	25	47	35	28	24	32	26	22	29	24	21	27	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25392	25392	25392
5°	25433	24202	24031
10°	25225	23099	22641
15°	24856	21987	21179
20°	24357	20779	19795
25°	23859	19517	18413
30°	23232	18330	16963
35°	22644	17079	15537
40°	21913	15843	14190
45°	21189	14619	12870
50°	20396	13372	11499
55°	19564	12039	10202
60°	18629	10597	8852
65°	17601	9129	7433
70°	16296	7525	6002
75°	14494	5800	4636
80°	12311	3942	2983
85°	8927	1836	1270

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21189 cd/sqm

TEST NUMBER: P1008656

CATALOG NUMBER: S122DIP-B1005D530UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.0	2.5
10°-20°	424.8	7.1
20°-30°	624.2	10.4
30°-40°	725.0	12.1
40°-50°	724.1	12.1
50°-60°	631.4	10.6
60°-70°	466.7	7.8
70°-80°	264.1	4.4
80°-90°	71.6	1.2
90°-100°	42.1	0.7
100°-110°	133.7	2.2
110°-120°	228.8	3.8
120°-130°	300.9	5.0
130°-140°	337.8	5.6
140°-150°	331.2	5.5
150°-160°	277.9	4.6
160°-170°	184.3	3.1
170°-180°	64.4	1.1
0°-30°	1200.0	20.1
0°-40°	1925.0	32.2
0°-60°	3280.5	54.8
0°-90°	4082.9	68.2
90°-120°	404.6	6.8
90°-150°	1374.5	23.0
90°-180°	1901.0	31.8
0°-180°	5984.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1604	1604	1604	1604	1604	
5°	1604	1598	1581	1593	1590	152
15°	1527	1518	1498	1504	1496	430
25°	1382	1370	1343	1346	1343	636
35°	1192	1177	1152	1143	1135	745
45°	970	959	936	919	913	749
55°	734	725	706	688	680	656
65°	495	486	470	456	449	490
75°	259	256	248	239	242	277
85°	63	62	60	56	54	70
90°	1	8	20	19	20	6
95°	30	36	37	37	36	33
105°	123	125	126	127	127	130
115°	230	233	232	231	230	227
125°	334	339	337	336	335	298
135°	432	438	440	439	437	334
145°	524	528	532	532	530	328
155°	600	601	603	606	604	276
165°	652	652	652	656	653	184
175°	679	677	676	680	676	64
180°	680	680	680	680	680	

TEST NUMBER: P1008656

CATALOG NUMBER: S122DIP-B1005D530UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1604.1	1604.1	1604.1	1604.1	1604.1
2.5°	1613.3	1605.6	1588.6	1604.1	1601.0
5°	1604.1	1597.9	1580.9	1593.3	1590.2
7.5°	1593.3	1584.0	1567.0	1579.4	1576.3
10°	1576.3	1565.5	1547.0	1559.3	1554.7
12.5°	1553.2	1543.9	1525.4	1533.1	1530.0
15°	1526.9	1517.7	1497.6	1503.8	1496.1
17.5°	1494.6	1485.3	1465.3	1473.0	1465.3
20°	1459.1	1449.8	1428.2	1432.9	1426.7
22.5°	1423.6	1409.7	1389.7	1389.7	1386.6
25°	1382.0	1369.6	1343.4	1346.5	1343.4
27.5°	1335.7	1324.9	1304.8	1300.2	1292.5
30°	1289.4	1277.1	1253.9	1249.3	1243.2
32.5°	1240.1	1230.8	1206.1	1196.9	1190.7
35°	1192.3	1176.8	1152.2	1142.9	1135.2
37.5°	1138.3	1124.4	1099.7	1088.9	1081.2
40°	1082.7	1070.4	1045.7	1031.8	1025.7
42.5°	1028.8	1016.4	991.7	976.3	967.1
45°	970.2	959.4	936.2	919.3	913.1
47.5°	913.1	902.3	877.6	860.6	851.4
50°	852.9	845.2	823.6	802.0	794.3
52.5°	794.3	783.5	763.5	746.5	735.7
55°	734.2	724.9	706.4	687.9	680.2
57.5°	674.0	666.3	646.3	627.7	621.6
60°	613.9	607.7	586.1	569.1	564.5
62.5°	555.3	544.5	529.0	513.6	507.4
65°	495.1	485.8	470.4	456.5	448.8
67.5°	433.4	425.7	411.8	401.0	394.8
70°	376.3	370.2	356.3	345.5	339.3
72.5°	317.7	311.6	303.8	293.1	288.4
75°	259.1	256.0	248.3	239.1	242.2
77.5°	206.7	200.5	197.4	192.8	188.2
80°	154.2	152.7	149.6	145.0	141.9
82.5°	104.9	104.9	103.3	97.2	97.2
85°	63.2	61.7	60.2	55.5	54.0
87.5°	27.8	24.7	21.6	17.0	15.4
90°	0.6	7.5	20.1	18.9	19.5
92.5°	12.6	17.2	17.8	18.4	18.4
95°	29.8	35.6	36.7	36.7	35.6
97.5°	49.9	55.1	57.4	57.4	57.4
100°	72.9	77.5	79.2	79.2	78.6
102.5°	97.0	100.4	102.7	103.3	102.7
105°	123.4	125.1	126.2	127.4	127.4
107.5°	149.8	152.1	152.1	152.6	149.8
110°	175.0	178.5	178.5	178.5	176.7

TEST NUMBER: P1008656

CATALOG NUMBER: S122DIP-B1005D530UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	202.6	206.0	205.4	203.7	202.6
115°	229.5	233.0	231.8	231.2	229.5
117.5°	256.5	261.1	258.2	256.5	254.8
120°	283.5	288.1	283.5	283.5	281.7
122.5°	308.1	313.9	311.0	309.3	308.1
125°	334.0	339.1	337.4	335.7	335.1
127.5°	359.2	365.5	363.2	360.9	359.2
130°	382.7	390.2	389.0	387.9	385.6
132.5°	409.1	414.9	415.4	412.6	410.9
135°	432.1	438.4	439.5	439.0	437.2
137.5°	457.3	462.5	463.6	463.1	460.8
140°	479.7	484.9	487.7	487.7	485.4
142.5°	502.7	507.8	509.5	510.1	507.8
145°	524.5	528.5	531.9	532.5	530.2
147.5°	544.0	549.1	551.4	552.6	550.3
150°	564.1	567.5	569.8	571.5	569.8
152.5°	581.8	585.3	588.2	590.5	588.2
155°	599.6	601.4	603.1	605.9	604.2
157.5°	615.1	616.3	617.4	621.4	618.6
160°	628.9	630.0	630.6	634.1	631.8
162.5°	641.5	641.5	642.1	646.1	643.2
165°	652.4	651.9	651.9	655.9	653.0
167.5°	662.2	660.5	660.5	664.5	661.6
170°	669.6	667.9	667.3	671.4	667.9
172.5°	674.8	673.1	672.5	676.5	673.1
175°	678.8	677.1	676.0	680.0	676.5
177.5°	681.1	679.4	678.2	681.7	678.2
180°	680.0	680.0	680.0	680.0	680.0

(END OF REPORT)