

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009182

Luminaire Tested: S122DIP-B485D925UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009182
REPORT IS A COMBINATION OF REPORTS P984390 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D925UB30-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5553.1 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009182

CATALOG NUMBER: S122DIP-B485D925UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009182

CATALOG NUMBER: S122DIP-B485D925UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43
1	95	90	86	83	85	82	79	76	66	64	62	51	50	48	38	37	36
2	86	79	73	68	78	71	66	62	58	54	51	45	43	40	33	32	30
3	78	69	62	56	71	63	57	52	51	46	43	40	37	34	29	28	26
4	72	61	53	48	65	56	49	44	45	40	36	35	32	29	26	24	22
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	21	19
6	61	49	41	35	55	44	38	32	36	31	27	29	25	22	21	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12244	12244	12244
5°	12264	11672	11588
10°	12164	11139	10918
15°	11986	10603	10214
20°	11745	10020	9546
25°	11505	9411	8879
30°	11204	8840	8180
35°	10918	8236	7492
40°	10567	7641	6843
45°	10217	7050	6206
50°	9836	6449	5545
55°	9433	5807	4919
60°	8982	5109	4268
65°	8489	4404	3584
70°	7860	3628	2894
75°	6993	2796	2236
80°	5940	1900	1438
85°	4308	884	611

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10217 cd/sqm

TEST NUMBER: P1009182

CATALOG NUMBER: S122DIP-B485D925UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.8	1.3
10°-20°	204.8	3.7
20°-30°	301.0	5.4
30°-40°	349.6	6.3
40°-50°	349.2	6.3
50°-60°	304.5	5.5
60°-70°	225.1	4.1
70°-80°	127.3	2.3
80°-90°	36.9	0.7
90°-100°	208.3	3.8
100°-110°	704.1	12.7
110°-120°	740.1	13.3
120°-130°	608.6	11.0
130°-140°	489.0	8.8
140°-150°	369.4	6.7
150°-160°	259.7	4.7
160°-170°	152.9	2.8
170°-180°	49.7	0.9
0°-30°	578.7	10.4
0°-40°	928.3	16.7
0°-60°	1582.0	28.5
0°-90°	1971.3	35.5
90°-120°	1652.4	29.8
90°-150°	3119.5	56.2
90°-180°	3582.0	64.5
0°-180°	5553.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	774	774	774	774	774	
5°	774	771	762	768	767	73
15°	736	732	722	725	722	207
25°	666	660	648	649	648	307
35°	575	568	556	551	547	359
45°	468	463	452	443	440	361
55°	354	350	341	332	328	317
65°	239	234	227	220	216	236
75°	125	124	120	115	117	133
85°	30	30	29	27	26	34
90°	1	13	34	32	33	4
95°	35	85	387	146	113	36
105°	120	182	732	1309	1113	128
115°	212	268	612	1264	1465	211
125°	296	351	589	1024	1188	263
135°	348	415	582	861	985	269
145°	397	456	579	719	786	249
155°	452	488	562	636	661	208
165°	492	507	538	571	580	139
175°	513	513	518	524	523	49
180°	514	514	514	514	514	

TEST NUMBER: P1009182

CATALOG NUMBER: S122DIP-B485D925UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	773.5	773.5	773.5	773.5	773.5
2.5°	778.0	774.3	766.1	773.5	772.0
5°	773.5	770.6	762.4	768.3	766.8
7.5°	768.3	763.9	755.7	761.6	760.1
10°	760.1	754.9	746.0	752.0	749.7
12.5°	749.0	744.5	735.6	739.3	737.8
15°	736.3	731.9	722.2	725.2	721.5
17.5°	720.7	716.3	706.6	710.3	706.6
20°	703.6	699.2	688.7	691.0	688.0
22.5°	686.5	679.8	670.2	670.2	668.7
25°	666.4	660.5	647.8	649.3	647.8
27.5°	644.1	638.9	629.2	627.0	623.3
30°	621.8	615.9	604.7	602.5	599.5
32.5°	598.0	593.5	581.6	577.2	574.2
35°	574.9	567.5	555.6	551.1	547.4
37.5°	548.9	542.2	530.3	525.1	521.4
40°	522.1	516.2	504.3	497.6	494.6
42.5°	496.1	490.2	478.3	470.8	466.4
45°	467.8	462.6	451.5	443.3	440.3
47.5°	440.3	435.1	423.2	415.0	410.6
50°	411.3	407.6	397.2	386.8	383.0
52.5°	383.0	377.8	368.2	360.0	354.8
55°	354.0	349.6	340.7	331.7	328.0
57.5°	325.0	321.3	311.6	302.7	299.7
60°	296.0	293.1	282.6	274.5	272.2
62.5°	267.8	262.6	255.1	247.7	244.7
65°	238.8	234.3	226.9	220.2	216.4
67.5°	209.0	205.3	198.6	193.4	190.4
70°	181.5	178.5	171.8	166.6	163.6
72.5°	153.2	150.2	146.5	141.3	139.1
75°	125.0	123.5	119.7	115.3	116.8
77.5°	99.7	96.7	95.2	93.0	90.7
80°	74.4	73.6	72.1	69.9	68.4
82.5°	50.6	50.6	49.8	46.9	46.9
85°	30.5	29.8	29.0	26.8	26.0
87.5°	13.4	11.9	10.4	8.2	7.4
90°	1.0	13.4	33.6	32.1	32.6
92.5°	14.8	47.0	152.1	70.2	60.3
95°	34.6	84.9	387.3	146.2	112.6
97.5°	51.4	112.2	631.3	293.5	188.7
100°	76.1	137.4	780.5	584.4	353.7
102.5°	98.8	160.0	785.4	988.0	689.6
105°	120.5	181.8	732.1	1308.6	1113.4
107.5°	144.2	203.6	682.7	1424.6	1399.0
110°	168.0	225.8	649.1	1405.9	1515.5

TEST NUMBER: P1009182

CATALOG NUMBER: S122DIP-B485D925UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	189.7	247.0	627.4	1342.2	1513.6
115°	212.4	268.2	612.5	1264.1	1465.1
117.5°	236.1	289.5	604.6	1189.5	1392.0
120°	257.9	310.2	597.7	1122.8	1321.9
122.5°	278.6	331.5	593.8	1071.0	1248.8
125°	296.4	350.8	588.8	1024.0	1188.5
127.5°	311.2	369.0	585.9	984.0	1132.2
130°	324.1	385.3	583.9	943.5	1085.8
132.5°	335.9	401.1	582.9	901.5	1037.4
135°	347.8	415.0	581.9	860.6	985.0
137.5°	358.6	426.8	581.9	819.0	934.6
140°	371.5	437.6	580.9	782.4	882.2
142.5°	384.3	446.6	580.9	747.4	829.9
145°	397.2	456.4	578.9	718.8	786.4
147.5°	411.0	464.4	576.0	693.6	747.9
150°	424.8	472.2	573.0	671.8	714.3
152.5°	438.7	480.2	568.1	653.5	685.6
155°	451.5	487.6	562.2	635.8	660.9
157.5°	462.4	493.5	556.2	619.0	639.2
160°	473.2	499.4	550.3	602.2	618.5
162.5°	484.1	503.8	545.4	586.3	598.7
165°	492.0	506.8	538.4	571.0	579.9
167.5°	498.9	509.8	532.5	557.2	562.2
170°	505.8	511.3	527.6	544.4	546.3
172.5°	509.8	512.8	521.6	533.0	533.5
175°	512.8	513.2	517.7	524.1	522.6
177.5°	514.7	513.7	513.7	517.7	514.7
180°	513.7	513.7	513.7	513.7	513.7

(END OF REPORT)