

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009227

Luminaire Tested: S122DIP-B675D1080UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009227
REPORT IS A COMBINATION OF REPORTS P984450 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D1080UB30-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6927.8 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009227

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009227

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	87	83	80	77	68	65	63	54	52	51	41	40	39
2	87	80	74	68	79	73	67	63	59	56	52	47	45	42	36	34	33
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28
4	72	62	54	48	66	56	50	45	46	41	38	37	34	31	28	26	24
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	18
7	56	44	37	31	51	41	34	29	34	29	25	27	23	21	21	18	16
8	52	40	33	27	47	37	30	26	31	26	22	25	21	18	19	17	15
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13
10	45	34	26	22	41	31	25	20	26	21	18	21	17	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16891	16891	16891
5°	16919	16102	15987
10°	16782	15368	15062
15°	16536	14627	14090
20°	16204	13824	13168
25°	15873	12984	12249
30°	15456	12195	11284
35°	15064	11362	10336
40°	14578	10541	9441
45°	14096	9725	8563
50°	13569	8896	7650
55°	13014	8010	6787
60°	12393	7049	5890
65°	11710	6075	4946
70°	10844	5005	3993
75°	9644	3859	3084
80°	8191	2622	1985
85°	5947	1220	844

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14096 cd/sqm

TEST NUMBER: P1009227

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.4	1.4
10°-20°	282.6	4.1
20°-30°	415.3	6.0
30°-40°	482.3	7.0
40°-50°	481.7	7.0
50°-60°	420.0	6.1
60°-70°	310.5	4.5
70°-80°	175.7	2.5
80°-90°	50.2	0.7
90°-100°	244.7	3.5
100°-110°	827.3	11.9
110°-120°	869.6	12.6
120°-130°	715.1	10.3
130°-140°	574.7	8.3
140°-150°	434.1	6.3
150°-160°	305.2	4.4
160°-170°	179.7	2.6
170°-180°	58.5	0.8
0°-30°	798.3	11.5
0°-40°	1280.6	18.5
0°-60°	2182.4	31.5
0°-90°	2718.8	39.2
90°-120°	1941.7	28.0
90°-150°	3665.6	52.9
90°-180°	4209.0	60.8
0°-180°	6927.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1067	1067	1067	1067	1067	
5°	1067	1063	1052	1060	1058	101
15°	1016	1010	996	1000	995	286
25°	919	911	894	896	894	423
35°	793	783	766	760	755	495
45°	645	638	623	612	608	498
55°	488	482	470	458	452	437
65°	329	323	313	304	299	326
75°	172	170	165	159	161	184
85°	42	41	40	37	36	47
90°	1	16	40	38	38	5
95°	41	100	455	172	132	42
105°	142	214	860	1538	1308	150
115°	250	315	720	1485	1722	248
125°	348	412	692	1203	1397	310
135°	409	488	684	1011	1158	316
145°	467	536	680	845	924	293
155°	531	573	661	747	777	244
165°	578	596	633	671	682	163
175°	602	603	608	616	614	57
180°	604	604	604	604	604	

TEST NUMBER: P1009227

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1067.1	1067.1	1067.1	1067.1	1067.1
2.5°	1073.3	1068.2	1056.9	1067.1	1065.1
5°	1067.1	1063.0	1051.8	1060.0	1057.9
7.5°	1060.0	1053.8	1042.5	1050.7	1048.7
10°	1048.7	1041.5	1029.2	1037.4	1034.3
12.5°	1033.3	1027.1	1014.8	1019.9	1017.9
15°	1015.8	1009.7	996.3	1000.5	995.3
17.5°	994.3	988.1	974.8	979.9	974.8
20°	970.7	964.5	950.2	953.3	949.1
22.5°	947.1	937.9	924.5	924.5	922.5
25°	919.4	911.2	893.7	895.8	893.7
27.5°	888.6	881.4	868.1	865.0	859.9
30°	857.8	849.6	834.2	831.1	827.0
32.5°	825.0	818.8	802.4	796.3	792.2
35°	793.2	782.9	766.5	760.3	755.2
37.5°	757.3	748.0	731.6	724.4	719.3
40°	720.3	712.1	695.7	686.5	682.4
42.5°	684.4	676.2	659.8	649.5	643.4
45°	645.4	638.2	622.8	611.6	607.5
47.5°	607.5	600.3	583.9	572.6	566.4
50°	567.4	562.3	547.9	533.6	528.4
52.5°	528.4	521.3	507.9	496.6	489.5
55°	488.4	482.3	470.0	457.6	452.5
57.5°	448.4	443.3	429.9	417.6	413.5
60°	408.4	404.3	389.9	378.6	375.6
62.5°	369.4	362.2	352.0	341.7	337.6
65°	329.4	323.2	313.0	303.7	298.6
67.5°	288.3	283.2	274.0	266.8	262.7
70°	250.4	246.3	237.0	229.8	225.7
72.5°	211.4	207.3	202.1	195.0	191.9
75°	172.4	170.3	165.2	159.0	161.1
77.5°	137.5	133.4	131.3	128.3	125.2
80°	102.6	101.6	99.5	96.5	94.4
82.5°	69.8	69.8	68.7	64.6	64.6
85°	42.1	41.0	40.0	36.9	35.9
87.5°	18.5	16.4	14.4	11.3	10.3
90°	1.2	15.6	39.5	37.8	38.3
92.5°	17.4	55.2	178.8	82.4	70.8
95°	40.6	99.8	455.1	171.8	132.3
97.5°	60.4	131.8	741.8	344.8	221.7
100°	89.4	161.4	917.1	686.7	415.6
102.5°	116.1	188.0	923.0	1161.0	810.3
105°	141.6	213.6	860.3	1537.6	1308.4
107.5°	169.5	239.2	802.2	1674.1	1643.9
110°	197.4	265.2	762.7	1652.0	1780.9

TEST NUMBER: P1009227

CATALOG NUMBER: S122DIP-B675D1080UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	222.9	290.2	737.2	1577.1	1778.6
115°	249.6	315.2	719.8	1485.4	1721.7
117.5°	277.5	340.2	710.5	1397.8	1635.8
120°	303.0	364.6	702.4	1319.4	1553.3
122.5°	327.4	389.5	697.7	1258.4	1467.4
125°	348.3	412.2	691.9	1203.4	1396.6
127.5°	365.7	433.6	688.4	1156.3	1330.4
130°	380.8	452.8	686.1	1108.7	1275.9
132.5°	394.7	471.4	685.0	1059.4	1219.0
135°	408.7	487.6	683.8	1011.2	1157.5
137.5°	421.4	501.5	683.8	962.4	1098.3
140°	436.5	514.3	682.6	919.4	1036.7
142.5°	451.6	524.8	682.6	878.2	975.2
145°	466.7	536.4	680.3	844.6	924.1
147.5°	483.0	545.6	676.8	815.0	878.8
150°	499.2	555.0	673.3	789.4	839.4
152.5°	515.5	564.2	667.5	768.0	805.7
155°	530.6	572.9	660.6	747.1	776.7
157.5°	543.3	579.8	653.6	727.4	751.1
160°	556.1	586.8	646.6	707.6	726.8
162.5°	568.9	592.0	640.8	689.0	703.5
165°	578.2	595.6	632.7	671.0	681.5
167.5°	586.3	599.0	625.7	654.8	660.6
170°	594.4	600.8	619.9	639.6	642.0
172.5°	599.0	602.6	613.0	626.3	626.9
175°	602.5	603.1	608.3	615.9	614.1
177.5°	604.9	603.7	603.7	608.3	604.9
180°	603.7	603.7	603.7	603.7	603.7

(END OF REPORT)